


Radiation Emissions: Q/DFXK 198-2018 PK/AV

EUT: M/N:XK6628
 Manufacturer: HBS
 Operating Condition: ON
 Test Site: 3M CHAMBER
 Operator: Tan
 Test Specification: DC 13.5V
 Comment: Polarisation:V
 Start of Test: 2019/5/6 / 0:03:49



MEASUREMENT RESULT: "HBS05050020_red"

2019/5/6 0:08

Frequency MHz	Level dB/m	Transd dB	Limit dB/m	Margin dB	Det.	Height cm	Azimuth deg	Polarization
1038.650000	47.60	-0.9	62.0	14.4	---	100.0	0.00	VERTICAL
1107.900000	46.70	-0.5	62.0	15.3	---	100.0	0.00	VERTICAL
1454.100000	32.80	1.4	40.0	7.2	---	100.0	0.00	VERTICAL
2387.950000	49.80	5.0	62.0	12.2	---	100.0	0.00	VERTICAL
2422.000000	54.80	4.9	56.0	1.2	---	100.0	0.00	VERTICAL
2449.300000	51.50	5.0	56.0	4.5	---	100.0	0.00	VERTICAL
2449.550000	51.30	5.0	56.0	4.7	---	100.0	0.00	VERTICAL
2449.950000	46.40	5.0	56.0	9.6	---	100.0	0.00	VERTICAL
2450.750000	44.30	5.0	56.0	11.7	---	100.0	0.00	VERTICAL

MEASUREMENT RESULT: "HBS05050020_red2"

2019/5/6 0:08

Frequency MHz	Level dB/m	Transd dB	Limit dB/m	Margin dB	Det.	Height cm	Azimuth deg	Polarization
1038.650000	44.50	-0.9	42.0	-2.5	---	100.0	0.00	VERTICAL
1107.900000	42.40	-0.5	42.0	-0.4	---	100.0	0.00	VERTICAL
1315.600000	33.80	0.9	42.0	8.2	---	100.0	0.00	VERTICAL
1454.100000	26.00	1.4	30.0	4.0	---	100.0	0.00	VERTICAL
1592.575000	11.80	1.9	10.0	-1.8	---	100.0	0.00	VERTICAL
1615.000000	13.40	1.9	10.0	-3.4	---	100.0	0.00	VERTICAL
1938.300000	30.70	2.2	36.0	5.3	---	100.0	0.00	VERTICAL
2423.000000	32.30	4.9	36.0	3.7	---	100.0	0.00	VERTICAL
2449.550000	30.30	5.0	36.0	5.7	---	100.0	0.00	VERTICAL