


Radiation Emissions: Q/DFXK 198-2018 PK/AV

EUT: M/N:XK6628
 Manufacturer: HBS
 Operating Condition: ON
 Test Site: 3M CHAMBER
 Operator: Tan
 Test Specification: DC 13.5V
 Comment: Polarisation:H
 Start of Test: 2019/5/5 / 23:57:14



MEASUREMENT RESULT: "HBS05050019_red"

2019/5/6 0:01

Frequency MHz	Level dB/m	Transd dB	Limit dB/m	Margin dB	Det.	Height cm	Azimuth deg	Polarization
1016.400000	55.70	-0.8	62.0	6.3	---	100.0	0.00	HORIZONTAL
1085.950000	57.90	-0.6	62.0	4.1	---	100.0	0.00	HORIZONTAL
1086.350000	55.70	-0.6	62.0	6.3	---	100.0	0.00	HORIZONTAL
1453.850000	33.20	1.4	40.0	6.8	---	100.0	0.00	HORIZONTAL
1564.980000	35.20	1.8	40.0	4.8	---	100.0	0.00	HORIZONTAL
1567.470000	32.40	1.8	40.0	7.6	---	100.0	0.00	HORIZONTAL
1947.650000	56.50	2.2	56.0	-0.5	---	100.0	0.00	HORIZONTAL
1948.050000	56.60	2.2	56.0	-0.6	---	100.0	0.00	HORIZONTAL
2332.250000	41.20	5.3	46.0	4.8	---	100.0	0.00	HORIZONTAL

MEASUREMENT RESULT: "HBS05050019_red2"

2019/5/6 0:01

Frequency MHz	Level dB/m	Transd dB	Limit dB/m	Margin dB	Det.	Height cm	Azimuth deg	Polarization
1038.650000	40.80	-0.9	42.0	1.2	---	100.0	0.00	HORIZONTAL
1107.900000	42.10	-0.5	42.0	-0.1	---	100.0	0.00	HORIZONTAL
1177.150000	38.50	-0.1	42.0	3.5	---	100.0	0.00	HORIZONTAL
1564.980000	17.90	1.8	10.0	-7.9	---	100.0	0.00	HORIZONTAL
1567.470000	12.00	1.8	10.0	-2.0	---	100.0	0.00	HORIZONTAL
1577.930000	11.30	1.9	10.0	-1.3	---	100.0	0.00	HORIZONTAL
1592.580000	12.10	1.9	10.0	-2.1	---	100.0	0.00	HORIZONTAL
1615.000000	13.60	1.9	10.0	-3.6	---	100.0	0.00	HORIZONTAL
1947.650000	34.00	2.2	36.0	2.0	---	100.0	0.00	HORIZONTAL