


Radiation Emissions: Q/DFXK 198-2018 PK/AV

EUT: M/N:XK6628
 Manufacturer: HBS
 Operating Condition: ON
 Test Site: 3M CHAMBER
 Operator: Tan
 Test Specification: DC 13.5V
 Comment: Polarisation:V
 Start of Test: 2019/5/5 / 23:23:29



MEASUREMENT RESULT: "HBS05050016_red"

2019/5/5 23:27

Frequency MHz	Level dB/m	Transd dB	Limit dB/m	Margin dB	Det.	Height cm	Azimuth deg	Polarization
1107.900000	47.90	-0.5	62.0	14.1	---	100.0	0.00	VERTICAL
1454.150000	33.90	1.4	40.0	6.1	---	100.0	0.00	VERTICAL
2380.000000	54.50	5.1	62.0	7.5	---	100.0	0.00	VERTICAL
2461.750000	49.80	5.0	56.0	6.2	---	100.0	0.00	VERTICAL
2471.500000	45.40	4.9	56.0	10.6	---	100.0	0.00	VERTICAL
2480.500000	47.10	4.8	56.0	8.9	---	100.0	0.00	VERTICAL
2480.850000	45.60	4.8	56.0	10.4	---	100.0	0.00	VERTICAL
2481.300000	63.20	4.8	56.0	-7.2	---	100.0	0.00	VERTICAL
2481.700000	59.80	4.8	56.0	-3.8	---	100.0	0.00	VERTICAL

MEASUREMENT RESULT: "HBS05050016_red2"

2019/5/5 23:27

Frequency MHz	Level dB/m	Transd dB	Limit dB/m	Margin dB	Det.	Height cm	Azimuth deg	Polarization
1038.650000	42.40	-0.9	42.0	-0.4	---	100.0	0.00	VERTICAL
1107.900000	44.10	-0.5	42.0	-2.1	---	100.0	0.00	VERTICAL
1384.850000	35.60	1.1	42.0	6.4	---	100.0	0.00	VERTICAL
1454.100000	28.20	1.4	30.0	1.8	---	100.0	0.00	VERTICAL
1615.000000	13.50	1.9	10.0	-3.5	---	100.0	0.00	VERTICAL
1939.300000	31.30	2.2	36.0	4.7	---	100.0	0.00	VERTICAL
2424.000000	30.20	4.9	36.0	5.8	---	100.0	0.00	VERTICAL
2481.300000	41.40	4.8	36.0	-5.4	---	100.0	0.00	VERTICAL
2481.700000	37.70	4.8	36.0	-1.7	---	100.0	0.00	VERTICAL