


Radiation Emissions: Q/DFXK 198-2018 PK/AV

EUT: M/N:XK6628  
 Manufacturer: HBS  
 Operating Condition: ON  
 Test Site: 3M CHAMBER  
 Operator: Tan  
 Test Specification: DC 13.5V  
 Comment: Polarisation:H  
 Start of Test: 2019/5/5 / 22:46:22



MEASUREMENT RESULT: "HBS05050010\_red"

2019/5/5 22:51

Frequency MHz	Level dBμV/m	Transd dB	Limit dBμV/m	Margin dB	Det.	Height cm	Azimuth deg	Polarization
0.165000	55.00	23.4	66.0	11.0	---	100.0	0.00	VERTICAL
0.175000	58.90	23.4	66.0	7.1	---	100.0	0.00	VERTICAL
0.185000	58.60	23.4	66.0	7.4	---	100.0	0.00	VERTICAL
0.195000	57.30	23.4	66.0	8.7	---	100.0	0.00	VERTICAL
0.205000	56.50	23.4	66.0	9.5	---	100.0	0.00	VERTICAL
0.215000	56.40	23.5	66.0	9.6	---	100.0	0.00	VERTICAL
0.225000	56.00	23.5	66.0	10.0	---	100.0	0.00	VERTICAL
0.235000	54.50	23.5	66.0	11.5	---	100.0	0.00	VERTICAL
0.540000	42.30	23.6	56.0	13.7	---	100.0	0.00	VERTICAL

MEASUREMENT RESULT: "HBS05050010\_red2"

2019/5/5 22:51

Frequency MHz	Level dBμV/m	Transd dB	Limit dBμV/m	Margin dB	Det.	Height cm	Azimuth deg	Polarization
0.180000	34.00	23.4	46.0	12.0	---	100.0	0.00	VERTICAL
1.655000	33.80	23.7	36.0	2.2	---	100.0	0.00	VERTICAL
3.310000	29.60	23.8	42.0	12.4	---	100.0	0.00	VERTICAL
16.515000	21.70	24.2	38.0	16.3	---	100.0	0.00	VERTICAL
23.105000	26.70	24.3	38.0	11.3	---	100.0	0.00	VERTICAL
24.750000	28.50	24.3	38.0	9.5	---	100.0	0.00	VERTICAL
26.400000	28.70	24.3	32.0	3.3	---	100.0	0.00	VERTICAL
28.050000	25.40	24.4	38.0	12.6	---	100.0	0.00	VERTICAL
29.700000	28.90	24.4	38.0	9.1	---	100.0	0.00	VERTICAL