



International size reference: C

ELECTRICAL CHARACTERISTICS

(typical values for cells stored for one year or less, at 25 °C)

Nominal capacity **8.5Ah**

(At 4.0 mA, +25 °C, 2.0V cut off. The capacity restored by the cell varies according to current drain, temperature and cut off voltage.)

Nominal voltage **3.6V**

Maximum recommended continuous current **150mA**

(To get 50% of the nominal capacity at +25 °C with 2.0V cut off. Higher currents possible, consult EVE.)

Pulse capability: Typically up to 300 mA (300mA/0.1 second pulses, drained every 2 min at 25 °C from undischarged cells with 10µA base current, yield voltage readings above 3.0 V. The readings may vary according to the pulse characteristics, the temperature, and the cell's previous history. Fitting cell with a capacitor may be recommended in severe conditions. consult EVE.)

Storage (recommended) **+30 °C max**
(for more severe condition consult EVE)

Operating temperature range **-60 °C / +85 °C**
(Operation at temperature different from ambient may lead to reduced capacity and lower voltage plateau readings.)

Typical weight **52g**

ER26500

**Lithium-thionyl Chloride
(Li-SOCl₂) Battery**

KEY FEATURES

- ✓ High and stable operating voltage
- ✓ High minimum voltage during pulsing
- ✓ Low self discharge rate (less than 1% after 1 year of storage at +25 °C)
- ✓ Stainless steel container
- ✓ Hermetic glass-to-metal sealing
- ✓ Non-flammable electrolyte
- ✓ **Restricted for transport (class9)**
- ✓ Compliant with IEC 60086-4 safety standard and EN60079-11 intrinsic safety standard

 Underwriters Laboratories (UL)
Component Recognition
(File Number MH28717)

MAIN APPLICATIONS

- ✓ Utility metering
- ✓ Alarms and security devices
- ✓ Memory back-up
- ✓ Tracking systems
- ✓ Automotive electronics
- ✓ Professional electronics
... etc.



WARNING:

Fire, explosion and severe burn hazard. Do not recharge, crush, disassemble, heat above 100 °C, incinerate, or expose contents to water.


Note: Any representations in this data sheet concerning performance are for informational purpose only and are not construed as warranties, either expressed or implied, of future performance.

ER26500

1. DISCHARGE CHARACTERISTICS@+25°C



2. VOLTAGE VS. TEMPERATURE




AVAILABLE TERMINATIONS


Suffix-/S Standard
 Suffix-/T Solder Tabs
 Suffix-/W Flying Leads

[View available terminations](#)

3. CAPACITY VS. CURRENT



4. STORAGE CHARACTERISTICS



EVE ENERGY CO., LTD.

Address: EVE Industrial Park, XiKeng Industrial zone, Huihuan Town, Huizhou, Guangdong, China

Operator: (86-752)260 6966 Fax: (86-752)260 6033

<http://www.evebattery.com> Email: sales@evebattery.com

Latest version can be downloaded from the EVE website

Feb 2014