

Differences Between the UCC3813 and UCC3800 PWM Families

Aung Thet Tu

Power Supply Control Products

ABSTRACT

This application report discusses the parametric differences between the UCC3813 and UCC3800 PWM families of integrated circuits available from Texas Instruments.

Contents

Comparing ICs

1.1 General Differences	1
1.2 Specific Differences	2

1 Comparing ICs

The UCC3813 family is a lower-cost version of the UCC3800 family of industry standard PWM controllers. Both families come from the identical base device with the UCC3813 family having relaxed limits on certain specifications. With wider limits, higher overall product yields are achievable making the UCC3813 family more attractive for high-volume, cost-sensitive applications.

The UCC3813 family corresponds to the UCC3800 family per the following table.

Table 1. Part Family Comparison

$T_A = T_J = 0^{\circ}\text{C to } 70^{\circ}\text{C}$			$T_A = T_J = -40^{\circ}\text{C to } 85^{\circ}\text{C}$		
UCC3800	=	UCC3813-0	UCC2800	=	UCC2813-0
UCC3801	=	UCC3813-1	UCC2801	=	UCC2813-1
UCC3802	=	UCC3813-2	UCC2802	=	UCC2813-2
UCC3803	=	UCC3813-3	UCC2803	=	UCC2813-3
UCC3804	=	UCC3813-4	UCC2804	=	UCC2813-4
UCC3805	=	UCC3813-5	UCC2805	=	UCC2813-5

1.1 General Differences

- The UCC3813 family is **NOT** available in the extended temperature range below -40°C and above 85°C .
- No special custom test or branding requirements (such as custom brand, additional tests and temperatures) are available with UCC3813 family.

1.2 Specific Differences

To help determine the design implications between the UCC3802 and UCC3813 families, Table 2 highlights the parametric specification differences.

Table 2. Electrical Characteristics

PARAMETER	TEST CONDITIONS	UCCx800 FAMILY			UCCx813 FAMILY			UNITS
		MIN	TYP	MAX	MIN	TYP	MAX	
Reference Section								
Load regulation (UCC38xx)			10	25		10	30	mV
Line regulation	T _J = 25°C			1.9			n/s	mV/V
	T _J = 0 to 70°C (UCC38xx)			2.1			n/s	mV/V
	T _J = -40 to 85°C (UCC28xx)			2.5			n/s	mV/V
Total variation	(-0,-1,-2,-4)	4.88	5.0	5.1	4.84	5.0	5.1	V
	(-3,-5)	3.90	4.0	4.08	3.84	4.0	4.08	V
Error Amplifier Section								
Input voltage	(-0,-1,-2,-4)	2.44	2.5	2.56	2.42	2.5	2.56	V
	(-3,-5)	1.95	2.0	2.05	1.92	2.0	2.05	V
Input bias current		-1		+1	-2		+2	uA
Current Sense Section								
Overcurrent threshold		1.42	1.55	1.68	1.32	1.55	1.70	V
Soft Start: COMP rise time			4	10		4	n/s	ms
Startup current			0.1	0.2		0.1	0.23	mA
Operating current			0.5	1.0		0.5	1.2	mA

NOTE: n/s = not specified

IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgment, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

Customers are responsible for their applications using TI components.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.