


VinMin = 2.8V  
 VinMax = 4.6V  
 Vout = 20.0V  
 Iout = 0.01A

Device = TPS61040DBVR  
 Topology = Boost  
 Created = 2021-10-13 23:22:54.263  
 BOM Cost = \$1.25  
 BOM Count = 8  
 Total Pd = 0.03W







# WEBENCH® Design Report







Design : 335 TPS61040DBVR  
 TPS61040DBVR 2.8V-4.6V to 20.00V @ 0.01A










## Electrical BOM

Name	Manufacturer	Part Number	Properties	Qty	Price	Footprint
Cff	Samsung Electro-Mechanics	CL10C100JB8NNNC Series= C0G/NP0	Cap= 10.0 pF VDC= 50.0 V IRMS= 0.0 A	1	\$0.01	0603 5 mm <sup>2</sup>
Cin	MuRata	GRM155R61A475MEAAD Series= X5R	Cap= 4.7 uF ESR= 1.0 mOhm VDC= 10.0 V IRMS= 0.0 A	1	\$0.03	0402_065 3 mm <sup>2</sup>
Cout	MuRata	GRM31CR72A105KA01L Series= X7R	Cap= 1.0 uF ESR= 5.334 mOhm VDC= 100.0 V IRMS= 1.55432 A	1	\$0.24	1206_190 11 mm <sup>2</sup>
D1	ON Semiconductor	MBR0530T1G	VF@Io= 430.0 mV VRRM= 30.0 V	1	\$0.05	SOD-123 13 mm <sup>2</sup>
L1	Bourns	SDR1307-120ML	L= 12.0 µH 30.0 mOhm	1	\$0.42	SDR1307 226 mm <sup>2</sup>
Rfbb	Vishay-Dale	CRCW0402147KFKED Series= CRCW..e3	Res= 147.0 kOhm Power= 63.0 mW Tolerance= 1.0%	1	\$0.01	0402 3 mm <sup>2</sup>
Rfht	Vishay-Dale	CRCW04022M21FKED Series= CRCW..e3	Res= 2.21 MOhm Power= 63.0 mW Tolerance= 1.0%	1	\$0.01	0402 3 mm <sup>2</sup>
U1	Texas Instruments	TPS61040DBVR	Switcher	1	\$0.48	DBV0005A 15 mm <sup>2</sup>









## Operating Values

#	Name	Value	Category	Description
1.	Cin IRMS	115.128 mA	Capacitor	Input capacitor RMS ripple current
2.	Cin Pd	13.255 $\mu$ W	Capacitor	Input capacitor power dissipation
3.	Cout IRMS	42.024 mA	Capacitor	Output capacitor RMS ripple current
4.	Cout Pd	9.42 $\mu$ W	Capacitor	Output capacitor power dissipation
5.	D1 Tj	30.606 degC	Diode	D1 junction temperature
6.	Diode Pd	2.941 mW	Diode	Diode power dissipation
7.	IC Ipk	0.0 A	IC	Peak switch current in IC
8.	IC Pd	30.243 mW	IC	IC power dissipation
9.	IC Tj	37.561 degC	IC	IC junction temperature
10.	IC Tolerance	25.0 mV	IC	IC Feedback Tolerance
11.	ICThetaJA	250.0 degC/W	IC	IC junction-to-ambient thermal resistance
12.	Iin Avg	83.559 mA	IC	Average input current
13.	L Ipp	368.97 mA	Inductor	Peak-to-peak inductor ripple current
14.	L Pd	588.31 $\mu$ W	Inductor	Inductor power dissipation
15.	M Irms	130.943 mA	Mosfet	MOSFET RMS ripple current
16.	M Vds Act	196.672 mV	Mosfet	Voltage drop across the MosFET
17.	Cin Pd	13.255 $\mu$ W	Power	Input capacitor power dissipation
18.	Cout Pd	9.42 $\mu$ W	Power	Output capacitor power dissipation
19.	Diode Pd	2.941 mW	Power	Diode power dissipation
20.	IC Pd	30.243 mW	Power	IC power dissipation
21.	L Pd	588.31 $\mu$ W	Power	Inductor power dissipation
22.	Total Pd	33.965 mW	Power	Total Power Dissipation
23.	BOM Count	8	System	Total Design BOM count
24.	Duty Cycle	37.784 %	System	Duty cycle
25.	Efficiency	85.483 %	System	Steady state efficiency
26.	FootPrint	279.0 mm <sup>2</sup>	System	Total Foot Print Area of BOM components
27.	Frequency	214.822 kHz	System	Switching frequency
28.	Iout	10.0 mA	System	Iout operating point
29.	Mode	DCM	System	Conduction Mode
30.	Mode	DCM	System	PWM/PFM Mode
31.	Pout	200.0 mW	System	Total output power
32.	Total BOM	\$1.254	System	Total BOM Cost
33.	Vin	2.8 V	System	Vin operating point
34.	Vout	20.0 V	System	Operational Output Voltage
35.	Vout Actual	19.77 V	System	Vout Actual calculated based on selected voltage divider resistors
36.	Vout Tolerance	3.96 %	System	Vout Tolerance based on IC Tolerance (no load) and voltage divider resistors if applicable
37.	Vout p-p	51.122 mV	System	Peak-to-peak output ripple voltage

## Design Inputs

Name	Value	Description
Iout	10.0 m	Maximum Output Current
VinMax	4.6	Maximum input voltage
VinMin	2.8	Minimum input voltage
Vout	20.0	Output Voltage
base_pn	TPS61040	Base Product Number
source	DC	Input Source Type
Ta	30.0	Ambient temperature

## WEBENCH® Assembly

### Component Testing

Some published data on components in datasheets such as Capacitor ESR and Inductor DC resistance is based on conservative values that will guarantee that the components always exceed the specification. For design purposes it is usually better to work with typical values. Since this data is not always available it is a good practice to measure the Capacitance and ESR values of  $C_{in}$  and  $C_{out}$ , and the inductance and DC resistance of L1 before assembly of the board. Any large discrepancies in values should be electrically simulated in WEBENCH to check for instabilities and thermally simulated in WebTHERM to make sure critical temperatures are not exceeded.

### Soldering Component to Board


If board assembly is done in house it is best to tack down one terminal of a component on the board then solder the other terminal. For surface mount parts with large tabs, such as the DPAK, the tab on the back of the package should be pre-tinned with solder, then tacked into place by one of the pins. To solder the tab down to the board place the iron down on the board while resting against the tab, heating both surfaces simultaneously. Apply light pressure to the top of the plastic case until the solder flows around the part and the part is flush with the PCB. If the solder is not flowing around the board you may need a higher wattage iron (generally 25W to 30W is enough).

### Initial Startup of Circuit

It is best to initially power up the board by setting the input supply voltage to the lowest operating input voltage 2.8V and set the input supply's current limit to zero. With the input supply off connect up the input supply to  $V_{in}$  and GND. Connect a digital volt meter and a load if needed to set the minimum load of the design from  $V_{out}$  and GND. Turn on the input supply and slowly turn up the current limit on the input supply. If the voltage starts to rise on the input supply continue increasing the input supply current limit while watching the output voltage. If the current increases on the input supply, but the voltage remains near zero, then there may be a short or a component misplaced on the board. Power down the board and visually inspect for solder bridges and recheck the diode and capacitor polarities. Once the power supply circuit is operational then more extensive testing may include full load testing, transient load and line tests to compare with simulation results.

### Load Testing

The setup is the same as the initial startup, except that an additional digital voltmeter is connected between  $V_{in}$  and GND, a load is connected between  $V_{out}$  and GND and a current meter is connected in series between  $V_{out}$  and the load. The load must be able to handle at least rated output power + 50% ( 7.5 watts for this design). Ideally the load is supplied in the form of a variable load test unit. It can also be done in the form of suitably large power resistors. When using an oscilloscope to measure waveforms on the prototype board, the ground leads of the oscilloscope probes should be as short as possible and the area of the loop formed by the ground lead should be kept to a minimum. This will help reduce ground lead inductance and eliminate EMI noise that is not actually present in the circuit.



### Design Assistance

1. Master key : D9CED8BEE5623EB1[v1]
2. **TPS61040** Product Folder : <http://www.ti.com/product/TPS61040> : contains the data sheet and other resources.

#### Important Notice and Disclaimer

TI provides technical and reliability data (including datasheets), design resources (including reference designs), application or other design advice, web tools, safety information, and other resources AS IS and with all faults, and disclaims all warranties. These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

Providing these resources does not expand or otherwise alter TI's applicable Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with TI products.