





SWFET_A
SWFET_B




waveform 1

Input : 200 V
Output : 0 V
0 A

	Scale	Bw
CH1	50 V/div	500MHz
CH2	50 V/div	500MHz
CH3	-	-
CH4	-	-
REF1	-	-
REF2	-	-
REF3	-	-
REF4	-	-
MATH	-	-

TIME	400 ms/div
MODE	Peakdetect

SWFET_A
SWFET_B




waveform 2

Input : 200 V
Output : 0 V
0 A

	Scale	Bw
CH1	50 V/div	500MHz
CH2	50 V/div	500MHz
CH3	-	-
CH4	-	-
REF1	-	-
REF2	-	-
REF3	-	-
REF4	-	-
MATH	-	-

TIME	20 ms/div
MODE	Peakdetect

SWFET_A
SWFET_B



waveform3

Input : 200 V
Output : 28 V
0 A

	Scale	Bw
CH1	50 V/div	500MHz
CH2	50 V/div	500MHz
CH3	-	-
CH4	-	-
REF1	-	-
REF2	-	-
REF3	-	-
REF4	-	-
MATH	-	-

TIME	20 us/div
MODE	Peakdetect