


# Flyback Transformer

For Linear Technology  
LT8584



- Developed for Linear Technology LT8584 Isolated Monolithic Active Cell Balancer
- Designed to operate at 140 kHz; Rated for 7–12 Watts
- 1500 Vrms, one minute isolation between primary and secondary
- AEC-Q200 Grade 1 qualified (–40°C to +125°C ambient)

**Core material** Ferrite

**Terminations** RoHS tin-silver over tin over nickel over phos bronze. Other terminations available at additional cost.

**Weight** 3.9 – 4.2 g

**Ambient temperature** –40°C to +125°C

**Maximum part temperature** +125°C (ambient + temp rise)

**Storage temperature** Component: –40°C to +125°C

Tape and reel packaging: –40°C to +80°C

**Resistance to soldering heat** Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

**Moisture Sensitivity Level (MSL)** 1 (unlimited floor life at <30°C / 85% relative humidity)

**Failures in Time (FIT) / Mean Time Between Failures (MTBF)**

38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

**Packaging** 200 per 13" reel Plastic tape: 32 mm wide, 0.5 mm thick, 24 mm pocket spacing, 11.2 mm pocket depth

**PCB washing** Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787 PCB Washing.pdf](#).

Part number <sup>1</sup>	Input voltage (V)	Inductance at 0 A <sup>2</sup> ±10% (µH)	Inductance at Ipk <sup>3</sup> min (µH)	DCR max (Ohms) <sup>4</sup>		Leakage inductance max (µH) <sup>5</sup>	Turns ratio <sup>6</sup> pri : sec	Ipk <sup>3</sup> (A)	Output voltage (V)
				pri	sec				
NA5743-AL_	2–8	4.0	3.6	0.012	0.500	0.116	1 : 4	7.0	30–80

1. When ordering, please specify **packaging** code:

**NA5743-ALD**

**Packaging:** D = 13" machine-ready reel. EIA-481 embossed plastic tape (200 parts per full reel).

B = Less than full reel. In tape, but not machine ready. To have a leader and trailer added (\$25 charge), use code letter D instead.

2. Inductance is for the primary, measured at 150 kHz, 0.1 Vrms, 0 Adc.

3. Ipk is peak primary current drawn at minimum input voltage.



4. DCR for the primary is measured with windings connected in parallel.

5. Leakage inductance is for the primary, measured with secondary pins shorted.


6. Turns ratio is with the primary windings connected in parallel.

7. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.



Dimensions are in  $\frac{\text{inches}}{\text{mm}}$



Primary windings to be connected in parallel on PC board



www.coilcraft.com

**US** +1-847-639-6400 sales@coilcraft.com

**UK** +44-1236-730595 sales@coilcraft-europe.com

**Taiwan** +886-2-2264 3646 sales@coilcraft.com.tw

**China** +86-21-6218 8074 sales@coilcraft.com.cn

**Singapore** +65-6484 8412 sales@coilcraft.com.sg

Document 1075 Revised 06/10/16

© Coilcraft Inc. 2016

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.