







MODE: Phase-Shift PWM Mode, I2C Address 0x3B
BST_SYNC: SpreadSpectrum Boost Frequency
BST_FSET: 400KHz
PWM_FSET: 4883Hz
LED_SET: 4 Chains of 6 LEDS
ISET: 60mA / Chain using the Klaran or Optan
 $I = (1.21V/Riset)*2580$

<Variant Name>		
CELERITY EMBEDDED DESIGN SERVICES 1 Jonathan Bourne Drive, Suite #8 Pocasset, MA 02559 508-403-0304		
Title UVC LED Driver		
Size B	Document Number	200-0512-00
	Thursday, September 09, 2021	Rev 00
Date: Sheet 8 of 10		

