



1. Solar input 3.5~9 volts
2. Battery LiIOn 3.7 volts 4400 mAh
3. Min VCC of the BQ24560 is 5 volts and the battery voltage is 3.7 volts we have to use a boost topology using TPS61041
4. Check other things and validate the entire circuit

Title		<Title>
Size	Document Number	Rev
B	<Doc>	<RevCode>
Date: Wednesday, February 22, 2017		Sheet 1 of 1