




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-2 @20°C	0.200 ohms ±10%
D.C. RESISTANCE	8-11 @20°C	0.030 ohms ±20%
INDUCTANCE	3-2 10kHz, 100mV, Ls	2.00mH ±10%
SATURATION CURRENT	3-2 20% rolloff from initial	1.5A
LEAKAGE INDUCTANCE	3-2 tie(8+11), 100kHz, 100mV, Ls	37µH typ., 70µH max.
DIELECTRIC	2-11 tie(3+5), 4000VAC, 1 second	3000VAC, 1 minute
URNS RATIO	(3-2):(8-11)	4:1, ±1%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

- Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 450Vpeak, Overvoltage Category II.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750315800
DATE	Method: Tray				
ENG	PKG-0825	www.we-online.com/midcom			
REV.	02				
DATE	4/21/2016				