


CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes




ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-6 @20°C	0.045 ohms max.
D.C. RESISTANCE	S1-F2 tie(F1+S2), @20°C	0.003 ohms max.
INDUCTANCE	1-6 10kHz, 100mV, Ls	2.27mH ±30%
LEAKAGE INDUCTANCE	1-6 tie(S1+F1+S2+F2),100kHz, 100mV, Ls	7µH max.
DIELECTRIC	1-F2 tie(F1+S2), 3750VAC, 1 second	3000VAC, 1 minute
URNS RATIO	(1-6):(S1-F1), tie(F1+S2)	9.5:1
URNS RATIO	(1-6):(S2-F2), tie(F1+S2)	9.5:1




Images only for reference,
to be updated upon release.
ALD 10/19/23



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety standard undefined



Customer to tie terminals F1 + S2 on PC board.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability. Marking method, font and color may vary on preproduction samples.

DFM	SP	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE TRANSFORMER	PART NO. 750371758
DATE	10/24/2023	Method: Tray		Angles: ±1° Decimals: ±.005 [.13]		
ENG	ALD	PKG-1318		Fractions: ±1/64 Footprint: ± .001 [.03]		
REV.	00					
DATE	11/22/2023	www.we-online.com/midcom		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		