



Technical Data Sheet

Customer :
Texas Instruments

Part designation :
SP- PQ50/50

Customer part number :



Core / material	PQ50/50 / K2010 or equiv.
Nominal inductance	Lo=2,27mH±30%
Ratio of transformation	19:2
Dielectric strength (50Hz/1s)	WI - WII = 3kV
Operating temperature	-25°C - +125°C
Storage temperature	-25°C - +85°C

a.) print

Measuring device of L: WK 3260A			Measuring conditions of L: 50mV/10kHz/25°C			
Measurement	Unit	No. 1	No. 2	No. 3	No. 4	No. 5

Kaschke Components GmbH Göttingen	Person responsible : Schwetje	Date: 14.03.2014	Design regulation no.: 145400-a
---	---	----------------------------	---

Please give us your written release and certified herewith the confirmation of the validation in the application !!!

Date	Signature
------	-----------