



CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes



**ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-6 @20°C	0.030 ohms ±20%
INDUCTANCE	1-6 10kHz, 100mV, 0A, Ls	500µH ±10%
INDUCTANCE	1-6 10kHz, 100mV, 6A, Ls	350µH min.
DIELECTRIC	1-Core 625VAC, 1 second	




RECOMMENDED P.C. PATTERN, COMPONENT SIDE

**GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

- Functional insulation only



**Tooling Required**  
**Preliminary**

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]	DRAWING TITLE <b>INDUCTOR</b>	PART NO. <b>750316373</b>
DATE	Method: Tray PKG-TBD		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		SPECIFICATION SHEET 1 OF 1
ENG	JLV				
REV.	00				
DATE	7/18/2016	www.we-online.com/midcom			