

WEBENCH[®] Transformer Report

Design : 14 UCC28740DR
UCC28740DR 90V-265V to 5.00V @ 1A

#	Name	Value
1.	Core Part Number	B66311G0000X127
2.	Core Manufacturer	TDK
3.	Coil Former Part Number	B66206C1012T001
4.	Coil Former Manufacturer	TDK

Transformer Electrical Diagram

Primary

Turns	120.0
AWG	35.0
Layers	4.0
Strands	2.0
Insulation Type	Heavy Insulated Magnet Wire

Secondary

Turns	7.0
AWG	25.0
Layers	1.0
Strands	2.0
Insulation Type	Triple Insulated

Auxiliary

Turns	23.0
AWG	28.0
Layers	1.0
Strands	1.0
Insulation Type	Heavy Insulated Magnet Wire

Transformer Construction Diagram

Winding Instruction

Winding	AWG	Turns	Winding Orientation
Primary First 2/4.0	35.0	60	Clockwise
Auxiliary	28.0	23.0	Counter Clockwise
Triple Insulated Secondary	25.0	7.0	Counter Clockwise
Primary Second 2/4.0	35.0	60	Clockwise

Transformer Parameters

#	Name	Value
1.	Lpri	0.00291H
2.	Inductance Factor(AI)	202.0nH
3.	Npri	120.0
4.	Nsec	7.0
5.	Naux	23.0

#	Name	Value
6.	Core Type	E20/10/6
7.	Core Material	N27
8.	Bmax	0.20T
9.	Switching Frequency	63.00kHz
10.	DMax	0.51
11.	Ipk(Primary)	0.26A
12.	Irms(Primary)	0.11A
13.	Ipk(Secondary)	4.51A
14.	Irms(Secondary)	1.7A

Design Assistance

1. Application Hints Rlc Rlc provides the function of feed-forward line compensation to eliminate change in IPP due to change in di/dt and the propagation delay of the internal comparator and MOSFET turn-off time. For best results the chosen value may need to be adjusted based on board, FET and transformer parasitics. Rtl Rtl is added to prevent excessive diode current and limit lopt to the maximum value necessary for regulation. The Rtl value may be adjusted for optimal limiting later during the prototype evaluation process. Rfbt & Rfbb The feedback resistors will set the output voltage of the circuit. The values chosen may need to be finely tuned based on the final Transformer turns ratios and the voltage across the output diode at close to zero current. Rfb3 & Cfb3 Rfb3 is necessary to limit the current into FB and to avoid excess draining of Cvdd during this type of transient situation. The value of Rfb3 is chosen to limit the excess Ifb and Rfb4 current to an acceptable level when the optocoupler is saturated. Cfb3 helps improve the transient response and is estimated initially by equating the time constant to 1ms. This can later be adjusted for optimal performance during prototype evaluation. Rfb4 Rfb4 speeds up the turnoff time of the optocoupler in the case of a heavy load-step transient condition. This value tends to fall within the range of 10k and 100k. A tradeoff must be made between a lower value for faster transient response and a higher value for lower standby power. Rfb4 also serves to set a minimum bias current for the optocoupler and to drain dark current. Part Description The UCC28740 isolated-flyback controller provides Constant-Voltage (CV) using an optical coupler to improve transient response. Constant-Current (CC) regulation is accomplished through Primary Side Regulation (PSR) techniques. Please see the datasheet for further design guidance. <http://www.ti.com/lit/ds/symlink/ucc28740.pdf>

2. **UCC28740 Product Folder** : <http://www.ti.com/product/UCC28740> : contains the data sheet and other resources.

Important Notice and Disclaimer

TI provides technical and reliability data (including datasheets), design resources (including reference designs), application or other design advice, web tools, safety information, and other resources AS IS and with all faults, and disclaims all warranties. These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

Providing these resources does not expand or otherwise alter TI's applicable Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with TI products.