


WEBENCH[®] Design Report

 Design : 8 UCC28632DR
 UCC28632DR 85V-265V to 19.00V @ 6.5A


1. Rbld is a starting point, but may need to be experimented with in order to get minimum current needed to hold Vout at no load. For more information please click the design assistance button.
2. Device operates in peak power region. So user needs to ensure the safe operation of 'D2' diode by using Heat sink if required.
3. Click on the transformer symbol and select 'Design Transformer' to design using specific transformer cores and bobbin

Design Alerts




Component Selection Information





Click on the transformer symbol in the schematic and select "Explore Transformer Core/Bobbin Selection" to design using specific transformer cores and bobbin. With the current design condition, suitable FET could not be found in the current database. Hence, this design is created using an ideal FET. Please note that the resulting FET parameters are ideal, so the efficiency/loss values have been disabled. Also, the schematic/PCB export and Thermal simulations will not work with the ideal FET.







Electrical BOM







Name	Manufacturer	Part Number	Properties	Qty	Price	Footprint
Cdd	TDK	C2012X5R1V156M125AC Series= X5R	Cap= 15.0 uF ESR= 1.669 mOhm VDC= 35.0 V IRMS= 5.0498 A	1	\$0.24	0805 7 mm ²
Cin	CUSTOM	CUSTOM Series= ?	Cap= 57.115 uF ESR= 398.08 mOhm VDC= 397.249 V IRMS= 1.0169 A	1	NA	CUSTOM 0 mm ²







Name	Manufacturer	Part Number	Properties	Qty	Price	Footprint
Cin2	Nichicon	LLS2G221MELZ Series= 2387	Cap= 220.0 uF ESR= 904.0 mOhm VDC= 400.0 V IRMS= 1.58 A	1	\$1.94	 Nichicon_2200x4500_Snap 576 mm ²
Cout	Kemet	A750MS477M1EAAE015 Series= 3273	Cap= 470.0 uF ESR= 15.0 mOhm VDC= 25.0 V IRMS= 4.9 A	4	\$0.33	 A750_MS 144 mm ²
D1	Microsemi	UFS180JE3/TR13	VF@Io= 1.2 V VRRM= 800.0 V	1	\$0.71	 DO-214BA 42 mm ²
D2	CUSTOM	CUSTOM	VF@Io= 300.0 mV VRRM= 90.622 V	1	NA	CUSTOM 0 mm ²
D3	SMC Diode Solutions	SK220ATR	VF@Io= 900.0 mV VRRM= 200.0 V	1	\$0.04	 SMA 37 mm ²
D6	Diodes Inc.	DFLS1100-7	VF@Io= 770.0 mV VRRM= 100.0 V	1	\$0.15	 PowerDI123 13 mm ²
Dac	Vishay-Semiconductor	GBU4K-E3/45	VF@Io= 1.0 V VRRM= 800.0 V	1	\$0.73	 GBU 131 mm ²
Dz1	Diodes Inc.	SMBJ150A-13-F	Zener	1	\$0.10	 SMB 44 mm ²
L1	Coilcraft	SER1390-473MLB	L= 47.0 uH DCR= 21.0 mOhm	1	\$0.95	 SER1390 240 mm ²
M1	NA	IdealFET	VdsMax= 630.0 V IdsMax= 9.0 Amps	1	NA	NA 0 mm ²
R1	Vishay-Dale	CMF5025K500FHEB Series= CMF50	Res= 25.5 kOhm Power= 250.0 mW Tolerance= 1.0%	1	\$0.20	 CMF50 46 mm ²
R2	Vishay-Dale	CMF5033K200FHEB Series= CMF50	Res= 33.2 kOhm Power= 250.0 mW Tolerance= 1.0%	1	\$0.20	 CMF50 46 mm ²
Rbld	Vishay-Dale	CRCW04024K53FKED Series= CRCW..e3	Res= 4.53 kOhm Power= 63.0 mW Tolerance= 1.0%	1	\$0.01	 0402 3 mm ²
Rcs	Bourns	PWR163S-25-R100F Series= ?	Res= 100.0 mOhm Power= 2.8 W Tolerance= 1.0%	1	\$1.26	 PWR163 145 mm ²
Rhv1	Vishay-Dale	CRCW2010100KJNEF Series= CRCW..e3	Res= 100.0 kOhm Power= 750.0 mW Tolerance= 5.0%	1	\$0.04	 2010 32 mm ²
Rp	Yageo	RC0603FR-073K9L Series= ?	Res= 3.9 kOhm Power= 100.0 mW Tolerance= 1.0%	1	\$0.01	 0603 5 mm ²



Name	Manufacturer	Part Number	Properties	Qty	Price	Footprint
Rprog	Vishay-Dale	CRCW080547K5FKEA Series= CRCW..e3	Res= 47.5 kOhm Power= 125.0 mW Tolerance= 1.0%	1	\$0.01	 0805 7 mm ²
T1	Core=TDK , CoilFormer=TDK	Core=B66229G0000X187 , CoilFormer=B66230A1114T001	Lp= 127.0 μH Turns Ratio(Nas)= 5:7 Turns Ratio(Nps)= 38:7 Npri= 38.0 Naux= 5.0 Nsec= 7.0	1	\$1.46	 1313 mm ²
U1	Texas Instruments	UCC28632DR	Switcher	1	\$0.68	 R-PDSO-G7 55 mm ²











Operating Values

#	Name	Value	Category	Description
1.	Cin IRMS	990.709 mA	Capacitor	Input capacitor RMS ripple current
2.	Cin Pd	391.0 mW	Capacitor	Input capacitor power dissipation
3.	Cin2 IRMS	2.21 A	Capacitor	Input Capacitor Cin2 RMS Ripple Current
4.	Cin2 Pd	4.415 W	Capacitor	Average Power Dissipation in the Input Capacitor Cin2
5.	Cout IRMS	11.607 A	Capacitor	Output capacitor RMS ripple current
6.	Cout Pd	505.24 mW	Capacitor	Output capacitor power dissipation
7.	Avg Bridge Diode Pd	2.2 W	Diode	Average Power Dissipation in the Bridge Diode over the AC Line Period
8.	Diode2 Pd	1.95 W	Diode	Diode2 power dissipation
9.	ICThetaJA	128.5 degC/W	IC	IC junction-to-ambient thermal resistance
10.	Avg Bridge Diode Pd	2.2 W	Power	Average Power Dissipation in the Bridge Diode over the AC Line Period
11.	Cin Pd	391.0 mW	Power	Input capacitor power dissipation
12.	Cin2 Pd	4.415 W	Power	Average Power Dissipation in the Input Capacitor Cin2
13.	Cout Pd	505.24 mW	Power	Output capacitor power dissipation
14.	Diode2 Pd	1.95 W	Power	Diode2 power dissipation
15.	Snubber Pd	2.703 W	Power	Snubber Power Dissipation
16.	T1 Copper Loss	6.284 W	Power	Transformer Copper Loss Power Dissipation
17.	T1 Core Loss	847.0 mW	Power	Transformer Core Loss Power Dissipation
18.	T1 Pd	7.131 W	Power	Estimated Losses in Transformer
19.	BOM Count	24	System	Total Design BOM count
20.	Duty Cycle	61.32 %	System	Duty cycle
21.	FootPrint	3.553 k mm ²	System	Total Foot Print Area of BOM components
22.	Frequency	60.0 kHz	System	Switching frequency
23.	Iin rms	1.691 A	System	RMS Input Current
24.	Iocc	14.469 A	System	Constant Current Limit
25.	Iout	6.5 A	System	Iout operating point
26.	Min Rectified Vin	78.135 V	System	Minimum voltage seen at rectified input
27.	Mode	DCM	System	Conduction Mode
28.	Peak Rectified Vin	120.207 V	System	Peak voltage seen at rectified input
29.	Pout	123.5 W	System	Total output power
30.	Total BOM	NA	System	Total BOM Cost
31.	Vin_RMS	85.0 V	System	Vin operating point
32.	Vout	19.0 V	System	Operational Output Voltage
33.	Vout p-p	117.772 mV	System	Peak-to-peak output ripple voltage
34.	T1 Copper Loss	6.284 W	Transformer	Transformer Copper Loss Power Dissipation
35.	T1 Core Loss	847.0 mW	Transformer	Transformer Core Loss Power Dissipation
36.	T1 Iprim RMS	2.688 A	Transformer	Transformer Primary RMS Current
37.	T1 Iprim pk	5.946 A	Transformer	Transformer Primary Peak Current

#	Name	Value	Category	Description
38.	T1 Is1 RMS	11.666 A	Transformer	Transformer Secondary1 RMS Current
39.	T1 Is1 pk	31.406 A	Transformer	Transformer Secondary1 Peak Current
40.	T1 Pd	7.131 W	Transformer	Estimated Losses in Transformer

Design Inputs

Name	Value	Description
Iout	6.5	Maximum Output Current
VinMax	265.0	Maximum input voltage
VinMin	85.0	Minimum input voltage
Vout	19.0	Output Voltage
acFrequency	50.0	AC Frequency
base_pn	UCC28632	Base Product Number
source	AC	Input Source Type
Ta	30.0	Ambient temperature

WEBENCH® Assembly

Component Testing

Some published data on components in datasheets such as Capacitor ESR and Inductor DC resistance is based on conservative values that will guarantee that the components always exceed the specification. For design purposes it is usually better to work with typical values. Since this data is not always available it is a good practice to measure the Capacitance and ESR values of C_{in} and C_{out} , and the inductance and DC resistance of L1 before assembly of the board. Any large discrepancies in values should be electrically simulated in WEBENCH to check for instabilities and thermally simulated in WebTHERM to make sure critical temperatures are not exceeded.

Soldering Component to Board


If board assembly is done in house it is best to tack down one terminal of a component on the board then solder the other terminal. For surface mount parts with large tabs, such as the DPAK, the tab on the back of the package should be pre-tinned with solder, then tacked into place by one of the pins. To solder the tab down to the board place the iron down on the board while resting against the tab, heating both surfaces simultaneously. Apply light pressure to the top of the plastic case until the solder flows around the part and the part is flush with the PCB. If the solder is not flowing around the board you may need a higher wattage iron (generally 25W to 30W is enough).

Initial Startup of Circuit

It is best to initially power up the board by setting the input supply voltage to the lowest operating input voltage 85.0V and set the input supply's current limit to zero. With the input supply off connect up the input supply to V_{in} and GND. Connect a digital volt meter and a load if needed to set the minimum load of the design from V_{out} and GND. Turn on the input supply and slowly turn up the current limit on the input supply. If the voltage starts to rise on the input supply continue increasing the input supply current limit while watching the output voltage. If the current increases on the input supply, but the voltage remains near zero, then there may be a short or a component misplaced on the board. Power down the board and visually inspect for solder bridges and recheck the diode and capacitor polarities. Once the power supply circuit is operational then more extensive testing may include full load testing, transient load and line tests to compare with simulation results.

Load Testing

The setup is the same as the initial startup, except that an additional digital voltmeter is connected between V_{in} and GND, a load is connected between V_{out} and GND and a current meter is connected in series between V_{out} and the load. The load must be able to handle at least rated output power + 50% (7.5 watts for this design). Ideally the load is supplied in the form of a variable load test unit. It can also be done in the form of suitably large power resistors. When using an oscilloscope to measure waveforms on the prototype board, the ground leads of the oscilloscope probes should be as short as possible and the area of the loop formed by the ground lead should be kept to a minimum. This will help reduce ground lead inductance and eliminate EMI noise that is not actually present in the circuit.



WEBENCH® Transformer Report

#	Name	Value
1.	Core Part Number	B66229G0000X187
2.	Core Manufacturer	TDK
3.	Coil Former Part Number	B66230A1114T001
4.	Coil Former Manufacturer	TDK

Transformer Electrical Diagram

Primary


Turns	38.0
AWG	30.0
Layers	2.0
Strands	3.0
Insulation Type	Heavy Insulated Magnet Wire

Auxiliary


Turns	5.0
AWG	28.0
Layers	1.0
Strands	4.0
Insulation Type	Heavy Insulated Magnet Wire

Secondary

Turns	7.0
AWG	24.0
Layers	1.0
Strands	3.0
Insulation Type	Triple Insulated



Transformer Construction Diagram



Winding Instruction

Winding	AWG	Turns	Winding Orientation
Primary First 1/2.0	30.0	19	Clockwise

Winding	AWG	Turns	Winding Orientation
Triple Insulated Secondary	24.0	7.0	Counter Clockwise
Auxiliary	28.0	5.0	Counter Clockwise
Primary Second 1/2.0	30.0	19	Clockwise

Transformer Parameters

#	Name	Value
1.	Lpri	1.27E-10H
2.	Inductance Factor(AI)	89.0nH
3.	Npri	38.0
4.	Nsec	7.0
5.	Naux	5.0
6.	Core Type	E32/16/9
7.	Core Material	N87
8.	Bmax	0.26T
9.	Switching Frequency	0.06kHz
10.	DMax	0.58
11.	Ipk(Primary)	6.4A
12.	Irms(Primary)	2.8A
13.	Ipk(Secondary)	34.7A
14.	Irms(Secondary)	13.1A

Design Assistance

1. Application Hints High Power Operation The UCC28630 allows a peak power delivery up to 200% the nominal rating with only a modest increase in peak current. The combination of up to 2x frequency increase and 1.25x peak current increase in CCM allows up to 2x peak power delivery capability for a given transformer size. Rbld Rbld is used to set a minimum load for the circuit, so that in standby the output voltage does not float up. The value chosen by WEBENCH should be a good starting point but may need to be adjusted to achieve minimum power dissipation at standby as well. Active X-Cap Discharge The X-capacitor discharge function discharges the X-capacitor to the SELV 60V level in 1 sec. When adjusting the components for the design, ensure that the bulk capacitance value is not too large for the power level desired, which ensures that the bulk capacitor discharge rate is fast enough to discharge the X-capacitor to meet the 1-second discharge target. The VSENSE terminal In order to protect the VSENSE terminal from excessive negative current, an additional series limiting resistor and clamping diode can be added on the VSENSE terminal. The DRV pull up diode can be combined with the clamping diode in a single package common-cathode diode to reduce the component count of the circuit (see Figure 24 in the datasheet for illustration). Magnetic Sense Resistor Network When adjusting components for the design, check that the equivalent Thevenin resistance (Rth) of the R1/R2 falls within the required range of 10kOhm and 20kOhm. If the Rth is outside of this range, it triggers the VSENSE terminal open or short terminal check at start-up. Peak Current Mode Control and the CS Terminal Depending on the PCB layout, an additional RC filter may be required on the CS terminal, as show in Figure 30 of the datasheet. The capacitor, Ccs, should be positioned as close as possible to terminals 3 and 4 and tracked directly to the terminals. Rcs2 should also be located close to terminal 3 to minimize noise, and should not exceed 20kOhms since larger values could be detected as a possible open circuit on the CS terminal during the start-up terminal checks. The time constant for this RC filter should no be excessive so that the filter does not reduce the measured peak current. Typical time values would fall between 100ns and 200ns. Primary-Side Overload Timer An internal overload timer tracks the power stage thermal stress and protects the power stage against output overload. The overload timer trip level and time constant are both selectable from a defined list of combinations (See Table 1 in datasheet for combinations), and is set using a pull-down resistance, Rprog, on the DRV terminal. The values of the Rprog resistor that corresponds to specific trip levels and time constants can also be seen in Table 1 in the datasheet. Please see the datasheet for further design guidance and recommendations. <http://www.ti.com/lit/ds/symlink/ucc28630.pdf>

2. Master key : 5E76CE7B44FBB6CA[v1]

3. **UCC28632** Product Folder : <http://www.ti.com/product/UCC28632> : contains the data sheet and other resources.

Important Notice and Disclaimer

TI provides technical and reliability data (including datasheets), design resources (including reference designs), application or other design advice, web tools, safety information, and other resources AS IS and with all faults, and disclaims all warranties. These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

Providing these resources does not expand or otherwise alter TI's applicable Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with TI products.