



FF-M20VA

Features:

- NdFeB Magnet
- Precious Metal Brush
- Stainless Steel Shaft
- Oil-impregnated Bearing

Typical Applications:


- Blood Pressure Pump
- Camcorder
- Electric Shaver
- Toy

OUTLINE



Customization:

- 1.Length A, B
- 2.Technical Data
- 3.Varistor for Option



WEIGHT:4g(APPROX)

Technical Data:

MODEL	VOLTAGE		NO LOAD		AT MAXIMUM EFFICIENCY					STALL			
	OPERATING	NOMINAL	SPEED	CURRENT	SPEED	CURRENT	TORQUE		OUTPUT	TORQUE		CURRENT	
	RANGE	V	r/min	A	r/min	A	mNm	g.cm	W	mNm	g.cm	A	
FF-M20VA	8130	2.0-3.0	3	15200	0.045	11800	0.16	0.16	1.6	0.19	0.69	7	0.55
	7170	1.5-3.0	2	8000	0.025	6000	0.075	0.09	0.9	0.06	0.35	3.6	0.23
	10100	1.5-4.0	2.8	18000	0.05	14800	0.19	0.2	2	0.3	1.1	11	0.88

Unit Conversion: 1g.cm \approx 0.098mN.m \approx 0.014oz.in 1mm=0.039in 1g=0.035oz