


Radiated Emission Measurement

File :1126 Data :#1 Date: 2025/11/26 Time: 9:03:25



Site: Polarization: **Horizontal** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-振动
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree degree	Comment
1	X	51.5078	27.11	14.48	41.59	40.00	1.59	peak	100	116	
2	*	52.9546	38.86	14.32	53.18	40.00	13.18	peak	100	116	
3	!	92.9011	27.76	12.13	39.89	40.00	-0.11	peak	199	354	
4	X	553.2712	26.62	21.94	48.56	47.00	1.56	peak	100	56	
5	X	575.5332	26.55	22.40	48.95	47.00	1.95	peak	199	241	
6	X	616.6960	24.38	23.21	47.59	47.00	0.59	peak	100	56	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#2 Date: 2025/11/26 Time: 9:08:59



Site Polarization: **Horizontal** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-振动
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree	Comment
1	X	459.0339	28.33	20.24	48.57	47.00	1.57	peak	100	220	
2	X	542.7982	30.80	21.63	52.43	47.00	5.43	peak	199	353	
3	*	590.3524	30.87	22.73	53.60	47.00	6.60	peak	100	202	
4	X	625.5166	27.65	23.30	50.95	47.00	3.95	peak	100	211	
5	X	709.4310	25.29	24.10	49.39	47.00	2.39	peak	100	133	
6	X	919.6090	25.07	27.14	52.21	47.00	5.21	peak	100	82	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#3 Date: 2025/11/26 Time: 9:15:14



Site: Polarization: **Horizontal** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN1
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree degree	Comment
1	*	67.7820	34.22	11.58	45.80	40.00	5.80	peak	100	264	
2	!	84.0215	26.54	10.45	36.99	40.00	-3.01	peak	200	57	
3	!	208.3974	26.09	12.86	38.95	40.00	-1.05	peak	100	135	
4	!	459.0339	23.89	20.24	44.13	47.00	-2.87	peak	100	169	
5		602.5875	16.77	23.01	39.78	47.00	-7.22	peak	200	354	
6	!	860.3368	17.84	26.04	43.88	47.00	-3.12	peak	200	162	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#4 Date: 2025/11/26 Time: 9:18:00



Site Polarization: **Vertical** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN1
 Mode:
 Note:


No.	Mk.	Freq.	Reading Level	Correct Factor	Measurement	Limit	Margin	Antenna Height	Table Degree	
		MHz	dBuV	dB/m	dBuV/m	dBuV/m	dB	cm	degree	Comment
1	!	30.1318	26.61	12.47	39.08	40.00	-0.92	peak	100	354
2	*	30.3279	32.04	12.49	44.53	40.00	4.53	peak	100	354
3	!	46.3727	21.57	14.13	35.70	40.00	-4.30	QP	100	49
4	!	61.6698	23.42	13.09	36.51	40.00	-3.49	peak	100	327
5	X	312.7821	31.73	16.75	48.48	47.00	1.48	peak	200	177
6	X	783.5808	23.14	24.60	47.74	47.00	0.74	peak	100	14

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#5 Date: 2025/11/26 Time: 11:38:36



Site Polarization: **Horizontal** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN2
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree	Comment
1		48.8343	14.39	14.48	28.87	40.00	-11.13	peak	200	312	
2		58.5612	12.54	13.66	26.20	40.00	-13.80	peak	200	346	
3	*	88.9637	48.78	11.35	60.13	40.00	20.13	peak	200	242	
4		104.0971	13.68	13.71	27.39	40.00	-12.61	peak	200	119	
5		836.8309	12.30	25.65	37.95	47.00	-9.05	peak	100	294	
6		872.4891	7.32	26.30	33.62	47.00	-13.38	peak	100	302	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#6 Date: 2025/11/26 Time: 11:41:20



Site Polarization: **Vertical** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN2
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree degree	Comment
1	!	48.8087	24.32	14.48	38.80	40.00	-1.20	peak	100	171	
2	*	87.1270	32.20	11.01	43.21	40.00	3.21	peak	200	260	
3	X	93.0805	28.42	12.17	40.59	40.00	0.59	peak	100	75	
4	!	118.0827	26.70	12.02	38.72	40.00	-1.28	peak	100	32	
5		562.4651	16.65	22.17	38.82	47.00	-8.18	peak	100	171	
6	X	901.5689	20.97	26.97	47.94	47.00	0.94	peak	200	138	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#7 Date: 2025/11/26 Time: 11:43:58



Site Polarization: **Horizontal** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN3
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree	Comment
1		88.6213	17.13	11.29	28.42	40.00	-11.58	peak	100	146	
2		204.8114	17.21	12.75	29.96	40.00	-10.04	peak	100	146	
3		636.6919	12.26	23.40	35.66	47.00	-11.34	peak	100	120	
4		675.0896	15.32	23.70	39.02	47.00	-7.98	peak	100	138	
5		705.9568	16.31	24.06	40.37	47.00	-6.63	peak	100	164	
6	*	909.8261	24.32	27.05	51.37	47.00	4.37	peak	100	103	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#8 Date: 2025/11/26 Time: 11:45:18



Site Polarization: **Vertical** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN3
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree	Comment
1	!	49.1521	23.57	14.53	38.10	40.00	-1.90	peak	100	143	
2	!	52.3821	21.90	14.37	36.27	40.00	-3.73	peak	100	352	
3	!	88.5592	25.45	11.27	36.72	40.00	-3.28	peak	100	126	
4	!	92.1711	27.35	11.99	39.34	40.00	-0.66	peak	100	5	
5	!	93.2275	27.48	12.20	39.68	40.00	-0.32	peak	100	31	
6	*	108.0770	34.83	13.99	48.82	40.00	8.82	peak	100	118	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#9 Date: 2025/11/26 Time: 11:47:40



Site Polarization: **Horizontal** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN4
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree	Comment
1		48.3572	12.40	14.42	26.82	40.00	-13.18	peak	100	242	
2	!	58.3051	21.28	13.69	34.97	40.00	-5.03	peak	100	95	
3		114.4142	14.18	12.97	27.15	40.00	-12.85	peak	100	329	
4	*	115.7053	29.35	12.64	41.99	40.00	1.99	peak	100	329	
5		474.3333	20.61	20.27	40.88	47.00	-6.12	peak	100	208	
6		682.2288	12.81	23.77	36.58	47.00	-10.42	peak	100	95	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#10 Date: 2025/11/26 Time: 11:49:00



Site Polarization: **Vertical** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN4
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree	Comment
1	!	48.8772	24.48	14.48	38.96	40.00	-1.04	peak	100	248	
2		60.6618	15.62	13.34	28.96	40.00	-11.04	peak	100	14	
3		67.5684	17.78	11.63	29.41	40.00	-10.59	peak	100	14	
4	*	93.4239	28.12	12.24	40.36	40.00	0.36	peak	100	74	
5		107.6232	16.65	13.96	30.61	40.00	-9.39	peak	100	352	
6	!	899.0433	16.95	26.94	43.89	47.00	-3.11	peak	100	135	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#11 Date: 2025/11/26 Time: 11:53:13



Site: Polarization: **Horizontal** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN5
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree	Comment
1	*	54.7483	35.52	14.11	49.63	40.00	9.63	peak	100	150	
2		78.5234	14.76	9.94	24.70	40.00	-15.30	peak	100	29	
3		93.2765	11.62	12.20	23.82	40.00	-16.18	peak	100	150	
4		722.8656	6.49	24.21	30.70	47.00	-16.30	peak	100	159	
5		868.6731	4.80	26.21	31.01	47.00	-15.99	peak	100	227	
6		929.0081	3.21	27.18	30.39	47.00	-16.61	peak	100	227	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#12 Date: 2025/11/26 Time: 11:54:33



Site Polarization: **Vertical** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN5
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree	Comment
1	!	44.7670	22.92	13.89	36.81	40.00	-3.19	peak	100	99	
2	*	50.0303	24.77	14.65	39.42	40.00	-0.58	peak	100	160	
3		61.2496	18.60	13.19	31.79	40.00	-8.21	peak	100	318	
4		67.4974	18.57	11.64	30.21	40.00	-9.79	peak	100	300	
5	!	92.9012	26.91	12.13	39.04	40.00	-0.96	peak	100	23	
6		372.7226	20.62	18.64	39.26	47.00	-7.74	peak	100	186	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#13 Date: 2025/11/26 Time: 12:01:28



Site Polarization: **Horizontal** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN6
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree degree	Comment
1	X	171.9643	32.31	11.04	43.35	40.00	3.35	peak	100	294	
2	*	367.4023	32.16	18.47	50.63	47.00	3.63	peak	100	61	
3	X	634.0184	24.14	23.38	47.52	47.00	0.52	peak	100	130	
4	X	787.4369	22.45	24.62	47.07	47.00	0.07	peak	100	217	
5	!	843.4595	20.90	25.78	46.68	47.00	-0.32	peak	100	199	
6	X	956.4437	20.91	27.25	48.16	47.00	1.16	peak	100	328	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#14 Date: 2025/11/26 Time: 12:02:48



Site: Polarization: **Vertical** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN6
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree degree	Comment
1	!	49.8290	24.25	14.63	38.88	40.00	-1.12	peak	100	161	
2		66.6507	20.80	11.85	32.65	40.00	-7.35	peak	100	5	
3	X	93.0316	29.12	12.15	41.27	40.00	1.27	peak	100	40	
4	*	592.4261	32.44	22.78	55.22	47.00	8.22	peak	100	49	
5	!	654.0025	21.26	23.56	44.82	47.00	-2.18	peak	100	204	
6		989.5355	11.72	27.45	39.17	47.00	-7.83	peak	100	291	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#15 Date: 2025/11/26 Time: 12:28:25



Site Polarization: **Horizontal** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN7
 Mode:
 Note:


No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree degree	Comment
1	X	65.0688	30.05	12.24	42.29	40.00	2.29	peak	100	62	
2	X	358.4939	33.54	18.20	51.74	47.00	4.74	peak	100	227	
3	X	432.6215	28.02	19.76	47.78	47.00	0.78	peak	100	28	
4	X	625.5165	24.43	23.30	47.73	47.00	0.73	peak	100	227	
5	!	771.9897	21.83	24.51	46.34	47.00	-0.66	peak	100	210	
6	*	900.1474	31.02	26.96	57.98	47.00	10.98	peak	100	175	

*:Maximum data x:Over limit !:over margin

<Reference Only

Radiated Emission Measurement

File :1126 Data :#16 Date: 2025/11/26 Time: 12:29:45



Site Polarization: **Vertical** Temperature: (C)
 Limit: GB 4343.1 Radiation Power: AC 220V/50Hz Humidity: %
 EUT: Distance:
 M/N: 29V-143-CN7
 Mode:
 Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB/m	Measure- ment dBuV/m	Limit dBuV/m	Margin dB	Detector	Antenna Height cm	Table Degree degree	Comment
1	*	65.5497	47.93	12.13	60.06	40.00	20.06	peak	100	273	
2	X	67.2375	47.70	11.71	59.41	40.00	19.41	peak	100	273	
3	X	80.6018	48.09	9.85	57.94	40.00	17.94	peak	100	273	
4	X	82.2578	48.26	10.14	58.40	40.00	18.40	peak	100	273	
5	X	83.9479	46.15	10.44	56.59	40.00	16.59	peak	100	273	
6	X	87.2340	45.68	11.03	56.71	40.00	16.71	peak	100	273	

*:Maximum data x:Over limit !:over margin

<Reference Only