

Reference Pro

Revision History	
Revision	Notes

DIMENSIONS:

- Rectangular shape with height minimized (SMA spacing + board stand offs)
- Final PCB thickness 62 mil +/- 10% ****

STACKUP:


- Layer 1: Device layer, Power/GPIO Jumper/Switches, RF microstrip from DUT to SMA, USB connector, Silkscreens + Labeling
- ==== FR4: 8 mil
- Layer 2: Ground Plane
- ==== FR4: 38 mil
- Layer 3: Split Power planes for USB circuitry and DUT circuitry
- ==== FR4: 8 mil
- Layer 4: USB circuitry

Controlled Impedance Traces


- TOP: 13 mil traces to be 50 ohm Zo +/- 5% reference to L2

HARDWARE AND MARKINGS


LAYOUT NOTE:
Place 4 standoffs at corners of board.




H1
TCBS-6-01




H2
TCBS-6-01




H3
TCBS-6-01



H4
TCBS-6-01



FID1



FID2

PCB LOGO
Pb-Free Symbol

PCB LOGO
FCC disclaimer

PCB LOGO
Texas Instruments

Label Table	
Variant	Label Text
001	LMX Tester

PCB Number: SV601349
 PCB Rev: A

ASSEMBLY NOTES

ZZ1
Label Assembly Note
 This Assembly Note is for PCB labels only

ZZ2
Assembly Note
 These assemblies are ESD sensitive. ESD precautions shall be observed.

ZZ3
Assembly Note
 These assemblies must be clean and free from flux and all contaminants. Use of no clean flux is not acceptable.

ZZ4
Assembly Note
 These assemblies must comply with workmanship standards IPC-A-610 Class 2, unless otherwise specified.

ZZ5
Assembly Note
 Default Shunt settings: SH1_2-3 means short Pins 2-3 of SUP2REG jumper.

ZZ6
Assembly Note
 Default Shunt settings: SH2_2-3 means short Pins 2-3 of SUP2LMK jumper.

ZZ7
Assembly Note
 Default Shunt settings: SH3_2-3 means short Pins 2-3 of OE jumper.



ZZ8
Assembly Note
 Default Shunt settings: SH4_2-1 means short Pins 1-2 of OS jumper.




ZZ9
Assembly Note
 Default Shunt settings: SH5_2-1 means short Pins 1-2 of FS0 jumper.

ZZ10
Assembly Note
 Default Shunt settings: SH6_2-1 means short Pins 1-2 of FS1 jumper.

ZZ11
Assembly Note
 Default Shunt settings: SH7_2-3 means short Pins 2-3 of J7 jumper.

ZZ12
Assembly Note
 Default Shunt settings: SH7_2-3 means short Pins 2-3 of J8 jumper.





Default:
LMK61E2 with I2C.

FOR LMK61E2 Board
1) Shared ports for GPIO0, GPIO1 & I2C (SDA AND SCL)
-Populate J7 & J8, R10b, R11b. DNP: R10, R10a, R11, R11a
2) Different ports for SDA and SCL
- J7 & J8 DNP. Populate R10, R11, R10a, R11a, R10b, R11b

FOR LMK61PD0A2 Board
1) Populate R10 & R11
-DNP J7 & J8, R10b, R11b

