




STEP	A	B	C	D
1	+	+	-	-
2	-	+	+	-
3	-	-	+	+
4	+	-	-	+

从安装面看为顺时针方向
Clockwise view from mouting side.

1. 相数 Number of Phase	2
2. 步距角 Step Angle	1.8°
3. 额定电压 Rated Voltage	6.3 V DC
4. 额定电流 Rated Current	1.0 Amp
5. 保持力矩 Holding Torque	0.82 Nm Typ. (Two phase on/ rated current)
6. 相电阻 Phase Resistance	6.3 ohm(20℃)
7. 相电感 Phase Inductance	15.9 mH±20%(1kHz 1V rms)
8. 转子惯量 Rotor Inertia	105 g.cm ²
9. 电机重量 Motor Weight	0.4Kg
10. 绝缘等级 Insulation Class	B(130℃)



MOONS' STEPPING MOTOR
Insulation: Class B, 60VDC Max
3000RPM Max.

 US

MOONS' Electric CO., LTD

TYPE ML23HS0P4100
1.0 Amps Holding: 0.82N.m
XXXXXXXX YY/MM/DD

Work Order Date Format

密 保

			Unit: mm 第一角画法 FIRST ANGLE METHOD 	批准 Approve	张明	3.9	MOONS'		Hybrid Stepping Motor	
			未注线性与角度尺寸公差 Tolerances for linear and angular dimensions without Individual tolerance indications GB/T 1804-m eqv ISO 2768-1: m	标准化 Standard	王磊	5.9	Shanghai MOONS' Electric Co., Ltd.			
			未注形状与位置尺寸公差 Geometrical tolerance for features without Individual tolerance indications GB/T 1184-K eqv ISO 2768-2: K	工艺 Technology	李强	5.9	This document is released for information only. Its reproduction in whole or in part or its dissemination to third parties is prohibited. All trademarks and registered trademarks appearing on this document are the property of their respective owners.			
B	无UL铭牌 Update nameplate 	2017.4.01		审核 Check	张明	5.9				
A	原始版本 Original revision	2013.02.28		设计 Design	甘建军	2017.4.01				
REV.	版本记录 REVISION RECORD	DATE	UNLESS OTHERWISE SPECIFIED	NAMES	SIGNATURE	DATE	Type: ML23HS0P4100	Rev. B	SCALE 1:1	Sheet 1 of 1