



Measure	P1:freq(C3)	P2:freq(C2)	P3:freq(C2)	P4:freq(C1)	P5:dper@lv(C1)	P6:---	P7:---	P8:---
value	---	12.2265 MHz	12.2265 MHz	24.7412 MHz	-296 ps			
mean	---	12.28386 MHz	12.28245 MHz	24.57007 MHz	-5.9 ps			
min	---	12.2265 MHz	12.2265 MHz	24.2817 MHz	-458 ps			
max	---	12.3253 MHz	12.3253 MHz	24.8553 MHz	531 ps			
sdev	---	20.65 kHz	20.66 kHz	88.01 kHz	180.5 ps			
num	0	171	155	392	49			
status								

C1	DC1M	C2	DC1M	C3	DC1M	C4	DC1M
2.00 V/div	2.00 V/div	2.00 V/div	2.00 V/div	2.00 V/div	2.00 V/div	2.00 V/div	2.00 V/div
4.150 V	-100 mV	-1.350 V	-6.000 V	1.29 V	5.94 V	7.72 V	1.78 V
-4.21 V	40 mV	1.29 V	5.94 V	3.07 V	7.72 V	1.78 V	1.78 V
-2.43 V	1.82 V	3.07 V	7.72 V	1.78 V	1.78 V	1.78 V	1.78 V
Δy	Δy	Δy	Δy	Δy	Δy	Δy	Δy

Tbase	-8.84 μs	Trigger	CS DB	
	2.00 μs/div	Stop	1.62 V	
	200 kS	10 GS/s	Edge	Neg
X1=	3.7512 μs	ΔX=	7.9800 μs	
X2=	11.7312 μs	1/ΔX=	125.313 kHz	