

Conducted Emission Measurement


File : 惠威_tmp

Data : #39

Date: 2018/10/22

Time: 16:01:41

80.0 dBuV



Site LAB

Phase: **N**

Temperature: 25.1

Limit: GB 4343.1 (QP)

Power: AC220V/50Hz

Humidity: 55.0 %

EUT: 音响

M/N:

Mode: ON

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1	*	0.4515	44.01	11.01	55.02	56.85	-1.83	peak	

*:Maximum data x:Over limit !:over margin

〈Reference Only

Conducted Emission Measurement


File : 惠威_tmp

Data : #40

Date: 2018/10/22

Time: 16:09:35

80.0 dBuV



Site LAB

Phase: **L1**

Temperature: 25.1

Limit: GB 4343.1 (QP)

Power: AC220V/50Hz

Humidity: 55.0 %

EUT: 音响

M/N:

Mode:

Note:

No.	Mk.	Freq.	Reading Level	Correct Factor	Measurement	Limit	Over	
		MHz	dBuV	dB	dBuV	dBuV	dB	Detector Comment

*:Maximum data x:Over limit !:over margin

〈Reference Only


Conducted Emission Measurement

File : 惠威_tmp

Data : #41

Date: 2018/10/22

Time: 16:09:35



Site LAB

Phase: **N**

Temperature: 25.1

Limit: GB 4343.1 (QP)

Power: AC220V/50Hz

Humidity: 55.0 %

EUT: 音响

M/N:

Mode:

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.4515	41.93	11.01	52.94	56.85	-3.91	peak	
2	*	0.4515	40.18	11.01	51.19	47.10	4.09	AVG	
3		1.3605	35.27	11.05	46.32	56.00	-9.68	peak	
4		1.3605	33.73	11.05	44.78	46.00	-1.22	AVG	

*:Maximum data x:Over limit !:over margin

〈Reference Only


Conducted Emission Measurement

File : 惠威_tmp

Data : #42

Date: 2018/10/22

Time: 16:11:34



Site LAB

Phase: **L1**

Temperature: 25.1

Limit: GB 4343.1 (QP)

Power: AC220V/50Hz

Humidity: 55.0 %

EUT: 音响

M/N:

Mode: ON

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.4515	42.19	11.01	53.20	56.85	-3.65	peak	
2	*	0.4515	40.81	11.01	51.82	47.10	4.72	AVG	
3		1.3605	35.37	11.05	46.42	56.00	-9.58	peak	
4		1.3605	34.20	11.05	45.25	46.00	-0.75	AVG	

*:Maximum data x:Over limit !:over margin

〈Reference Only

Disturbance Power Measurement


File : 惠威_tmp

Data : #43

Date: 2018/10/22

Time: 16:19:18

65.0 dBpW



Site LAB

Temperature: 25.1

Limit: GB 4343.1-P (QP)

Humidity: 55.0 %

EUT: 音响

Power: AC220V/50Hz

M/N:

Mode: ON

Note:

No.	Mk.	Freq. MHz	Reading Level dBpW	Correct Factor dB	Measure- ment dBpW	Limit dBpW	Over dB	Detector	Position cm	Comment
1	*	216.0300	-1.23	21.13	19.90	41.89	-21.99	AVG		
2		217.1100	5.92	21.17	27.09	51.93	-24.84	peak		

*:Maximum data x:Over limit !:over margin

〈Reference Only

Final Factor=probe factor+Cable loss.

File : 惠威_tmp\Data :#43

Page: 1

Engineer Signature:

Disturbance Power Measurement


File : 惠威_tmp

Data : #44

Date: 2018/10/22

Time: 16:19:57

65.0 dBpW



Site LAB

Temperature: 25.1

Limit: GB 4343.1-P (QP)

Humidity: 55.0 %

EUT: 音响

Power: AC220V/50Hz

M/N:

Mode: ON

Note: 喇叭输出R

No.	Mk.	Freq. MHz	Reading Level dBpW	Correct Factor dB	Measure- ment dBpW	Limit dBpW	Over dB	Detector	Position cm	Comment
1		217.1100	6.03	21.17	27.20	51.93	-24.73	peak		
2	*	217.1100	-1.06	21.17	20.11	41.93	-21.82	AVG		

*:Maximum data x:Over limit !:over margin

〈Reference Only

Final Factor=probe factor+Cable loss.

File : 惠威_tmp\Data :#44

Page: 1

Engineer Signature:

Disturbance Power Measurement


File : 惠威_tmp

Data : #45

Date: 2018/10/22

Time: 16:23:24

65.0 dBpW



Site LAB

Temperature: 25.1

Limit: GB 4343.1-P (QP)

Humidity: 55.0 %

EUT: 音响

Power: AC220V/50Hz

M/N:

Mode: ON

Note: 喇叭输出L

No.	Mk.	Freq. MHz	Reading Level dBpW	Correct Factor dB	Measure- ment dBpW	Limit dBpW	Over dB	Detector	Position cm	Comment
1		215.2200	12.72	21.10	33.82	51.86	-18.04	peak		
2	*	215.2200	4.87	21.10	25.97	41.86	-15.89	AVG		

*:Maximum data x:Over limit !:over margin

〈Reference Only

Final Factor=probe factor+Cable loss.

File : 惠威_tmp\Data :#45

Page: 1

Engineer Signature:

Disturbance Power Measurement


File : 惠威_tmp

Data : #46

Date: 2018/10/22

Time: 16:27:48

65.0 dBpW



Site LAB

Temperature: 25.1

Limit: GB 4343.1-P (QP)

Humidity: 55.0 %

EUT: 音响

Power: AC220V/50Hz

M/N:

Mode: ON

Note: 音频输入

No.	Mk.	Freq. MHz	Reading Level dBpW	Correct Factor dB	Measure- ment dBpW	Limit dBpW	Over dB	Detector	Position cm	Comment
1	*	32.1600	2.96	24.42	27.38	45.08	-17.70	peak		
2		32.1600	-7.64	24.42	16.78	35.08	-18.30	AVG		
3		210.3600	-3.55	20.80	17.25	41.68	-24.43	AVG		
4		212.2500	4.06	20.92	24.98	51.75	-26.77	peak		

*:Maximum data x:Over limit !:over margin

〈Reference Only

Final Factor=probe factor+Cable loss.

File : 惠威_tmp\Data : #46

Page: 1

Engineer Signature:

Disturbance Power Measurement


File : 惠威_tmp

Data : #47

Date: 2018/10/22

Time: 16:30:19

65.0 dBpW



Site LAB

Temperature: 25.1

Limit: GB 4343.1-P (QP)

Humidity: 55.0 %

EUT: 音响

Power: AC220V/50Hz

M/N:

Mode: ON

Note: 电源输入

No.	Mk.	Freq. MHz	Reading Level dBpW	Correct Factor dB	Measure- ment dBpW	Limit dBpW	Over dB	Detector	Position cm	Comment
1	*	36.2100	-0.67	23.95	23.28	35.23	-11.95	AVG		
2		37.0200	8.79	24.32	33.11	45.26	-12.15	peak		
3		209.2800	8.63	20.77	29.40	51.64	-22.24	peak		
4		209.2800	0.72	20.77	21.49	41.64	-20.15	AVG		


*:Maximum data x:Over limit !:over margin

〈Reference Only

Final Factor=probe factor+Cable loss.

Conducted Emission Measurement

File : 惠威_tmp Data : #48 Date: 2018/10/22 Time: 16:47:53



Site LAB

Phase: **L1**

Temperature: 25.1

Limit: GB 4343.1 (QP)

Power: AC220V/50Hz

Humidity: 55.0 %

EUT: 音响

M/N:

Mode: ON

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.4515	43.26	11.01	54.27	56.85	-2.58	peak	
2	*	0.4515	42.58	11.01	53.59	47.10	6.49	AVG	


Conducted Emission Measurement

File : 惠威_tmp

Data : #49

Date: 2018/10/22

Time: 16:52:43



Site LAB

Phase: **L1**

Temperature: 25.1

Limit: GB 4343.1 (QP)

Power: AC220V/50Hz

Humidity: 55.0 %

EUT: 音响

M/N:

Mode: ON

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.4515	43.87	11.01	54.88	56.85	-1.97	peak	
2	*	0.4515	43.34	11.01	54.35	47.10	7.25	AVG	


Conducted Emission Measurement

File : 惠威_tmp

Data : #50

Date: 2018/10/22

Time: 17:08:39



Site LAB

Phase: **L1**

Temperature: 25.1

Limit: GB 4343.1 (QP)

Power: AC220V/50Hz

Humidity: 55.0 %

EUT: 音响

M/N:

Mode: ON

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.4515	45.15	11.01	56.16	56.85	-0.69	peak	
2	*	0.4515	43.67	11.01	54.68	47.10	7.58	AVG	
3		1.3605	37.71	11.05	48.76	56.00	-7.24	peak	
4	X	1.3605	35.80	11.05	46.85	46.00	0.85	AVG	

*:Maximum data x:Over limit !:over margin

〈Reference Only


Conducted Emission Measurement

File : 惠威_tmp

Data : #51

Date: 2018/10/22

Time: 17:25:51



Site LAB

Phase: **L1**

Temperature: 25.1

Limit: GB 4343.1 (QP)

Power: AC220V/50Hz

Humidity: 55.0 %

EUT: 音响

M/N:

Mode: ON

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.4515	44.89	11.01	55.90	56.85	-0.95	peak	
2	*	0.4515	44.39	11.01	55.40	47.10	8.30	AVG	
3		1.3560	37.45	11.04	48.49	56.00	-7.51	peak	
4	X	1.3560	36.24	11.04	47.28	46.00	1.28	AVG	

*:Maximum data x:Over limit !:over margin

〈Reference Only


Conducted Emission Measurement

File : 惠威_tmp

Data : #52

Date: 2018/10/22

Time: 17:40:18



Site LAB

Phase: **L1**

Temperature: 25.1

Limit: GB 4343.1 (QP)

Power: AC220V/50Hz

Humidity: 55.0 %

EUT: 音响

M/N:

Mode: ON

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.4515	44.59	11.01	55.60	56.85	-1.25	peak	
2	*	0.4515	43.79	11.01	54.80	47.10	7.70	AVG	
3		1.3560	37.03	11.04	48.07	56.00	-7.93	peak	
4	X	1.3560	35.83	11.04	46.87	46.00	0.87	AVG	

*:Maximum data x:Over limit !:over margin

〈Reference Only


Conducted Emission Measurement

File : 惠威_tmp

Data : #53

Date: 2018/10/22

Time: 17:42:38



Site LAB

Phase: **L1**

Temperature: 25.1

Limit: GB 4343.1 (QP)

Power: AC220V/50Hz

Humidity: 55.0 %

EUT: 音响

M/N:

Mode: ON

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV	Limit dBuV	Over dB	Detector	Comment
1		0.4515	44.14	11.01	55.15	56.85	-1.70	peak	
2	*	0.4515	43.56	11.01	54.57	47.10	7.47	AVG	
3		1.3560	36.75	11.04	47.79	56.00	-8.21	peak	
4	X	1.3560	35.60	11.04	46.64	46.00	0.64	AVG	

*:Maximum data x:Over limit !:over margin

〈Reference Only