

Sequence Report




Summary

Signal Path1

Signal Path Setup  PASSED

Sequence Result:

Sequence Result:  PASSED

Signal Path1 : Signal Path Setup

Output Connector:	Digital Optical
Output Sample Rate:	48.0000 kHz
Output Bit Depth:	24
Dither:	Enabled
Output Mode:	Consumer
Status Bits:	Auto (Consumer)
Output EQ:	None
Input Connector:	Analog Balanced
Channels:	1
Channel:	Ch1
Termination:	200 kohm
Input Bandwidth:	AC (<10 Hz) - AES17 (20 kHz)
Device Delay:	0.000 s
Input EQ:	None

• References

dBr G:	-20.000 dBFS
Shared Frequency Reference:	1.00000 kHz
dBrA:	1.000 Vrms
dBrB:	1.000 Vrms
dBrA Offset:	0.000 dB
dBrB Offset:	0.000 dB
dB SPL1:	10.00 mVrms
dB SPL2:	10.00 mVrms
dB SPL1 Calibrator Level:	94.000 dB SPL
dB SPL2 Calibrator Level:	94.000 dB SPL
dBm (Input Power):	600.0 ohm
W(watts) (Input Power):	8.000 ohm

• DCX

DCX is not detected.

Sequence Report



Signal Path1 : Verify Connections

Waveform: Sine

Generator Level: -17.000 dBFS

DC Offset: 0.000 D

Frequency: 1.00000 kHz

RMS Level (12/10/2015 11:55:37.899 AM)

Ch1 40.32 W

THD+N Ratio (12/10/2015 11:55:37.899 AM)

Ch1 4.379125 %

Frequency (12/10/2015 11:55:37.899 AM)

Ch1 1.00000 kHz