


Standard: (RE)EN 55032 Class B  
 Test item: Radiation Test  
 Temp.( C)/Hum.(%) 15.2 / 50 %  
 EUT:  
 Mode:  
 Model: HT700-整改

Polarization: Vertical  
 Power Source: AC 230V/50Hz  
 Engineer Signature:  
 Distance:

Note: 4喇叭




| No. | Freq. (MHz) | Reading (dBuV) | Factor (dB/m) | Result (dBuV/m) | Limit (dBuV/m) | Over Limit (dB) | Detector | Height (cm) | degree (deg) | Remark |
|-----|-------------|----------------|---------------|-----------------|----------------|-----------------|----------|-------------|--------------|--------|
| 1   | 37.3509     | 56.11          | -15.25        | 40.86           | 40.00          | 0.86            | peak     |             |              |        |
| 2   | 47.7422     | 66.82          | -14.35        | 52.47           | 40.00          | 12.47           | peak     |             |              |        |
| 3   | 106.0126    | 60.86          | -14.67        | 46.19           | 40.00          | 6.19            | peak     |             |              |        |
| 4   | 130.8369    | 61.32          | -16.69        | 44.63           | 40.00          | 4.63            | peak     |             |              |        |
| 5   | 187.4241    | 68.43          | -14.28        | 54.15           | 40.00          | 14.15           | peak     |             |              |        |
| 6   | 202.8104    | 51.94          | -12.93        | 39.01           | 40.00          | -0.99           | peak     |             |              |        |

Standard: (RE)EN 55032 Class B  
 Test item: Radiation Test  
 Temp.( C)/Hum.(%) 15.2 / 50 %  
 EUT:  
 Mode:  
 Model: HT700-整改

Polarization: Horizontal  
 Power Source: AC 230V/50Hz

Engineer Signature:  
 Distance:


Note: 4喇叭



| No. | Freq. (MHz) | Reading (dBuV) | Factor (dB/m) | Result (dBuV/m) | Limit (dBuV/m) | Over Limit (dB) | Detector | Height (cm) | degree (deg) | Remark |
|-----|-------------|----------------|---------------|-----------------|----------------|-----------------|----------|-------------|--------------|--------|
| 1   | 48.5867     | 62.67          | -14.35        | 48.32           | 40.00          | 8.32            | peak     |             |              |        |
| 2   | 106.0126    | 64.09          | -14.67        | 49.42           | 40.00          | 9.42            | peak     |             |              |        |
| 3   | 139.1172    | 59.92          | -16.76        | 43.16           | 40.00          | 3.16            | peak     |             |              |        |
| 4   | 155.9101    | 59.46          | -15.80        | 43.66           | 40.00          | 3.66            | peak     |             |              |        |
| 5   | 168.7093    | 58.42          | -15.29        | 43.13           | 40.00          | 3.13            | peak     |             |              |        |
| 6   | 208.2148    | 54.86          | -12.77        | 42.09           | 40.00          | 2.09            | peak     |             |              |        |

Standard: (RE)EN 55032 Class B  
 Test item: Radiation Test  
 Temp.( C)/Hum.(%) 15.2 / 50 %  
 EUT:  
 Mode:  
 Model: HT700-整改  
 Note: 4喇叭 短线

Polarization: Horizontal  
 Power Source: AC 230V/50Hz  
 Engineer Signature:  
 Distance:



| No. | Freq. (MHz) | Reading (dBuV) | Factor (dB/m) | Result (dBuV/m) | Limit (dBuV/m) | Over Limit (dB) | Detector | Height (cm) | degree (deg) | Remark |
|-----|-------------|----------------|---------------|-----------------|----------------|-----------------|----------|-------------|--------------|--------|
| 1   | 95.4270     | 69.32          | -14.78        | 54.54           | 40.00          | 14.54           | peak     |             |              |        |
| 2   | 106.0126    | 57.85          | -14.67        | 43.18           | 40.00          | 3.18            | peak     |             |              |        |
| 3   | 136.6992    | 61.21          | -16.74        | 44.47           | 40.00          | 4.47            | peak     |             |              |        |
| 4   | 155.9100    | 57.78          | -15.80        | 41.98           | 40.00          | 1.98            | peak     |             |              |        |
| 5   | 168.7093    | 57.78          | -15.29        | 42.49           | 40.00          | 2.49            | peak     |             |              |        |
| 6   | 208.2148    | 52.90          | -12.77        | 40.13           | 40.00          | 0.13            | peak     |             |              |        |

Standard: (RE)EN 55032 Class B  
 Test item: Radiation Test  
 Temp.( C)/Hum.(%) 15.2 / 50 %  
 EUT:  
 Mode:  
 Model: HT700-整改  
 Note: 4喇叭 短线

Polarization: Vertical  
 Power Source: AC 230V/50Hz  
 Engineer Signature:  
 Distance:




| No. | Freq. (MHz) | Reading (dBuV) | Factor (dB/m) | Result (dBuV/m) | Limit (dBuV/m) | Over Limit (dB) | Detector | Height (cm) | degree (deg) | Remark |
|-----|-------------|----------------|---------------|-----------------|----------------|-----------------|----------|-------------|--------------|--------|
| 1   | 30.2641     | 49.51          | -16.13        | 33.38           | 40.00          | -6.62           | peak     |             |              |        |
| 2   | 37.3509     | 49.05          | -15.25        | 33.80           | 40.00          | -6.20           | peak     |             |              |        |
| 3   | 47.7422     | 52.44          | -14.35        | 38.09           | 40.00          | -1.91           | peak     |             |              |        |
| 4   | 95.4270     | 59.33          | -14.78        | 44.55           | 40.00          | 4.55            | peak     |             |              |        |
| 5   | 130.8369    | 55.76          | -16.69        | 39.07           | 40.00          | -0.93           | peak     |             |              |        |
| 6   | 311.6326    | 50.12          | -10.32        | 39.80           | 47.00          | -7.20           | peak     |             |              |        |

Standard: (RE)EN 55032 Class B  
 Test item: Radiation Test  
 Temp.( C)/Hum.(%) 15.2 / 50 %  
 EUT:  
 Mode:  
 Model: HT700-整改

Polarization: Horizontal  
 Power Source: AC 230V/50Hz

Engineer Signature:  
 Distance:

Note: 2喇叭 短线




| No. | Freq. (MHz) | Reading (dBuV) | Factor (dB/m) | Result (dBuV/m) | Limit (dBuV/m) | Over Limit (dB) | Detector | Height (cm) | degree (deg) | Remark |
|-----|-------------|----------------|---------------|-----------------|----------------|-----------------|----------|-------------|--------------|--------|
| 1   | 106.9461    | 60.99          | -14.73        | 46.26           | 40.00          | 6.26            | peak     |             |              |        |
| 2   | 134.3235    | 66.73          | -16.73        | 50.00           | 40.00          | 10.00           | peak     |             |              |        |
| 3   | 155.9101    | 59.69          | -15.80        | 43.89           | 40.00          | 3.89            | peak     |             |              |        |
| 4   | 167.2368    | 55.60          | -15.33        | 40.27           | 40.00          | 0.27            | peak     |             |              |        |
| 5   | 179.3863    | 53.52          | -14.76        | 38.76           | 40.00          | -1.24           | peak     |             |              |        |
| 6   | 311.6326    | 56.31          | -10.32        | 45.99           | 47.00          | -1.01           | peak     |             |              |        |

Standard: (RE)EN 55032 Class B  
 Test item: Radiation Test  
 Temp.( C)/Hum.(%) 15.2 / 50 %  
 EUT:  
 Mode:  
 Model: HT700-整改

Polarization: Horizontal  
 Power Source: AC 230V/50Hz

Engineer Signature:  
 Distance:


Note: 1喇叭 短线



| No. | Freq. (MHz) | Reading (dBuV) | Factor (dB/m) | Result (dBuV/m) | Limit (dBuV/m) | Over Limit (dB) | Detector | Height (cm) | degree (deg) | Remark |
|-----|-------------|----------------|---------------|-----------------|----------------|-----------------|----------|-------------|--------------|--------|
| 1   | 107.8877    | 54.74          | -14.78        | 39.96           | 40.00          | -0.04           | peak     |             |              |        |
| 2   | 131.9889    | 58.12          | -16.70        | 41.42           | 40.00          | 1.42            | peak     |             |              |        |
| 3   | 155.9101    | 58.49          | -15.80        | 42.69           | 40.00          | 2.69            | peak     |             |              |        |
| 4   | 167.2368    | 52.47          | -15.33        | 37.14           | 40.00          | -2.86           | peak     |             |              |        |
| 5   | 311.6326    | 54.05          | -10.32        | 43.73           | 47.00          | -3.27           | peak     |             |              |        |
| 6   | 416.1791    | 47.88          | -7.49         | 40.39           | 47.00          | -6.61           | peak     |             |              |        |

Standard: (RE)EN 55032 Class B  
 Test item: Radiation Test  
 Temp.( C)/Hum.(%) 15.2 / 50 %  
 EUT:  
 Mode:  
 Model: HT360-整改  
 Note: 2喇叭

Polarization: Horizontal  
 Power Source: AC 230V/50Hz  
 Engineer Signature:  
 Distance:




| No. | Freq. (MHz) | Reading (dBuV) | Factor (dB/m) | Result (dBuV/m) | Limit (dBuV/m) | Over Limit (dB) | Detector | Height (cm) | degree (deg) | Remark |
|-----|-------------|----------------|---------------|-----------------|----------------|-----------------|----------|-------------|--------------|--------|
| 1   | 106.9461    | 54.32          | -14.73        | 39.59           | 40.00          | -0.41           | peak     |             |              |        |
| 2   | 127.4409    | 57.36          | -16.59        | 40.77           | 40.00          | 0.77            | peak     |             |              |        |
| 3   | 151.8632    | 58.16          | -16.05        | 42.11           | 40.00          | 2.11            | peak     |             |              |        |
| 4   | 162.8959    | 49.28          | -15.47        | 33.81           | 40.00          | -6.19           | peak     |             |              |        |
| 5   | 229.2931    | 44.75          | -12.07        | 32.68           | 40.00          | -7.32           | peak     |             |              |        |
| 6   | 311.6326    | 53.64          | -10.32        | 43.32           | 47.00          | -3.68           | peak     |             |              |        |

Standard: (RE)EN 55032 Class B  
 Test item: Radiation Test  
 Temp.( C)/Hum.(%) 15.2 / 50 %  
 EUT:  
 Mode:  
 Model: HT360-整改

Polarization: Vertical  
 Power Source: AC 230V/50Hz  
 Engineer Signature:  
 Distance:

Note: 2喇叭




| No. | Freq. (MHz) | Reading (dBuV) | Factor (dB/m) | Result (dBuV/m) | Limit (dBuV/m) | Over Limit (dB) | Detector | Height (cm) | degree (deg) | Remark |
|-----|-------------|----------------|---------------|-----------------|----------------|-----------------|----------|-------------|--------------|--------|
| 1   | 30.2641     | 56.18          | -16.13        | 40.05           | 40.00          | 0.05            | peak     |             |              |        |
| 2   | 38.0115     | 51.45          | -15.32        | 36.13           | 40.00          | -3.87           | peak     |             |              |        |
| 3   | 48.5867     | 53.14          | -14.35        | 38.79           | 40.00          | -1.21           | peak     |             |              |        |
| 4   | 123.0495    | 63.69          | -16.42        | 47.27           | 40.00          | 7.27            | peak     |             |              |        |
| 5   | 149.2239    | 56.66          | -16.22        | 40.44           | 40.00          | 0.44            | peak     |             |              |        |
| 6   | 916.0687    | 38.74          | 4.55          | 43.29           | 47.00          | -3.71           | peak     |             |              |        |



Standard: (RE)EN 55032 Class B  
 Test item: Radiation Test  
 Temp.( C)/Hum.(%) 15.2 / 50 %  
 EUT:  
 Mode:  
 Model: HT360-整改  
 Note: 1喇叭

Polarization: Vertical  
 Power Source: AC 230V/50Hz  
 Engineer Signature:  
 Distance:



| No. | Freq. (MHz) | Reading (dBuV) | Factor (dB/m) | Result (dBuV/m) | Limit (dBuV/m) | Over Limit (dB) | Detector | Height (cm) | degree (deg) | Remark |
|-----|-------------|----------------|---------------|-----------------|----------------|-----------------|----------|-------------|--------------|--------|
| 1   | 30.2641     | 55.34          | -16.13        | 39.21           | 40.00          | -0.79           | peak     |             |              |        |
| 2   | 48.5867     | 50.70          | -14.35        | 36.35           | 40.00          | -3.65           | peak     |             |              |        |
| 3   | 51.2106     | 48.92          | -14.57        | 34.35           | 40.00          | -5.65           | peak     |             |              |        |
| 4   | 118.8095    | 60.85          | -16.13        | 44.72           | 40.00          | 4.72            | peak     |             |              |        |
| 5   | 129.6950    | 53.61          | -16.67        | 36.94           | 40.00          | -3.06           | peak     |             |              |        |
| 6   | 149.2239    | 54.58          | -16.22        | 38.36           | 40.00          | -1.64           | peak     |             |              |        |

Standard: (RE)EN 55032 Class B

Test item: Radiation Test

Temp.( C)/Hum.(%) 15.2 / 50 %

EUT:

Mode:

Model: HT360-整改


Polarization: Vertical

Power Source: AC 230V/50Hz

Engineer Signature:

Distance:


Note: 1喇叭



| No. | Freq. (MHz) | Reading (dBuV) | Factor (dB/m) | Result (dBuV/m) | Limit (dBuV/m) | Over Limit (dB) | Detector | Height (cm) | degree (deg) | Remark |
|-----|-------------|----------------|---------------|-----------------|----------------|-----------------|----------|-------------|--------------|--------|
| 1   | 30.2641     | 55.34          | -16.13        | 39.21           | 40.00          | -0.79           | peak     |             |              |        |
| 2   | 48.5867     | 50.70          | -14.35        | 36.35           | 40.00          | -3.65           | peak     |             |              |        |
| 3   | 51.2106     | 48.92          | -14.57        | 34.35           | 40.00          | -5.65           | peak     |             |              |        |
| 4   | 118.8095    | 60.85          | -16.13        | 44.72           | 40.00          | 4.72            | peak     |             |              |        |
| 5   | 129.6950    | 53.61          | -16.67        | 36.94           | 40.00          | -3.06           | peak     |             |              |        |
| 6   | 149.2239    | 54.58          | -16.22        | 38.36           | 40.00          | -1.64           | peak     |             |              |        |

Standard: (RE)EN 55032 Class B  
 Test item: Radiation Test  
 Temp.( C)/Hum.(%) 15.2 / 50 %  
 EUT:  
 Mode:  
 Model: HT360-整改  
 Note: 2喇叭 加磁环

Polarization: Horizontal  
 Power Source: AC 230V/50Hz  
 Engineer Signature:  
 Distance:



| No. | Freq. (MHz) | Reading (dBuV) | Factor (dB/m) | Result (dBuV/m) | Limit (dBuV/m) | Over Limit (dB) | Detector | Height (cm) | degree (deg) | Remark |
|-----|-------------|----------------|---------------|-----------------|----------------|-----------------|----------|-------------|--------------|--------|
| 1   | 145.3506    | 50.12          | -16.44        | 33.68           | 40.00          | -6.32           | peak     |             |              |        |
| 2   | 298.2681    | 46.99          | -10.90        | 36.09           | 47.00          | -10.91          | peak     |             |              |        |
| 3   | 311.6326    | 51.18          | -10.32        | 40.86           | 47.00          | -6.14           | peak     |             |              |        |
| 4   | 337.2155    | 49.26          | -9.56         | 39.70           | 47.00          | -7.30           | peak     |             |              |        |
| 5   | 364.8987    | 48.94          | -9.00         | 39.94           | 47.00          | -7.06           | peak     |             |              |        |
| 6   | 387.9920    | 44.63          | -8.69         | 35.94           | 47.00          | -11.06          | peak     |             |              |        |