


【Ref1】 the output waveform of SN65LVDS alone



※ 出力信号は特に問題無し


VOD出力規定

MIN	TYP	MAX	UNIT
250	310	450	mV


VOCM出力規定

MIN	TYP	MAX	UNIT
1.125	1.17	1.375	V


①Deferential waveform



②Single waveform




【Ref2】 the SYSREF output waveform of SN65LVDS with ADS52J65



②Single waveform

SYNCとSYSREFで信号DCレベル相違 (SYSREFのDCレベルが低く Common-mode voltageがNGとな



[Ref3] the SYNC output waveform of SN65LVDS with ADS52J65

