



ADS5560_62

Capture
Test Selection
Single Tone

	Value	Unit
SNR	6.653	dBFS
SFDR	4.907	dBFS
THD	4.036	dBFS
SINAD	2.141	dBFS
ENOB	0.063	Bits
Fund.	-3.365	dBFS
Phase	2.787	Rad
Next Spur	-13.92	dBFS
HD2	-12.017	dBFS
HD3	-4.907	dBFS
HD4	-21.549	dBFS
HD5	-28.704	dBFS
NSD/Hz	-82.657	dBFS/Hz
		dBFS Hz
M1	-51.791	0.00E+00
M2	-51.791	1.61E+00

Test Parameters
 Auto Calculation of Coherent Frequencies
 Analysis Window (samples)
 65536
 ADC Output Data Rate
 80M
 ADC Input Target Frequency
 0.000000000

