


Modified Power off sequence



Channel Status

	C1	C2	C3	C4
V / Div	2.00 V	500 mV	1.00 V	1.00 V
Offset	-6.050 V	-1.920 V	-520 mV	-1.075 V
Coupling	DC1MΩ	DC1MΩ	DC1MΩ	DC1MΩ
BW-Limit	1GHZ	1GHZ	1GHZ	1GHZ
Probe	10	10	10	10
Sweeps	1 #	1 #	1 #	1 #

Acquisition Status

Time / Div	500 μs	Sampling Rate	500.000000 MS/s
Time / Pt	2.000000 ns	Sampling Mode	RealTime
Pts / Div	250.0000 kS	Trigger Delay	-910 μs
Mode	Stop	Slope	Negative
Type	Edge	Level	1.27 V
Source	C4	Coupling	DC