











NOTES:


Schematic default is DAC38RF83.

For DAC38RF80:


Install R238, R241
DNI C179, C400, L9, L10, T5, T7, C330, C331, C332,
C401, C403, C404, C328, C327, C399, R273,
C398, C397, J6

Title		
DAC OUTPUT		
Size	Document Number	Rev
B	DAC38RF8xEVM	E
Date:	Thursday, March 03, 2016 Sheet 4 of 10	





Title		
LMK		
Size	Document Number	Rev
B	DAC38RF8xEVM	E
Date: Tuesday, March 01, 2016 Sheet 6 of 10		



**TEXAS INSTRUMENTS**

Title

USB INTERFACE

Size
B


Document Number
DAC38RF8xEVM


Rev
E

Date:

Thursday, March 03, 2016

Sheet 7 of 10
















NOTES:

To bypass LDO U37: Install R298, R121, R122
DNI R221, R296, R284

To use LDO U34 (U35 output = 2.5V): DNI R330
Install R227



Title			POWER SUPPLIES +.9V, +1.8V		
Size			Document Number		
B			DAC38RF8xEVM		
Date: Tuesday, March 01, 2016			Sheet 9 of 10		
			Rev E		



Title		
POWER SUPPLIES		
Size	Document Number	Rev
B	DAC38RF8xEVM	E
Date: Tuesday, March 01, 2016		
Sheet 10 of 10		