

SN54ALS374, SN54AS374, SN74ALS374, SN74AS374

OCTAL D-TYPE EDGE-TRIGGERED FLIP-FLOPS WITH 3-STATE OUTPUTS

D2661, APRIL 1982 REVISED MAY 1986

- **D-Type Flip-Flops In a Single Package**
- **3-State Bus-Driving True Outputs**
- **Full Parallel Access for Loading**
- **Buffered Control Inputs**
- **Package Options Include Plastic "Small Outline" Packages, Ceramic Chip Carriers, and Standard Plastic and Ceramic 300-mil DIPs**
- **Dependable Texas Instruments Quality and Reliability**

description

These 8-bit flip-flops feature three-state outputs designed specifically for driving highly capacitive or relatively low-impedance loads. They are particularly suitable for implementing buffer registers, I/O ports, bidirectional bus drivers, and working registers.

The eight flip-flops of the 'ALS374 and 'AS374 are edge-triggered D-type flip-flops. On the positive transition of the clock the Q outputs will be set to the logic levels that were set up at the D inputs.


A buffered output-control input can be used to place the eight outputs in either a normal logic state (high or low logic levels) or a high-impedance state. In the high-impedance state the outputs neither load nor drive the bus lines significantly. The high-impedance third state and increased drive provide the capability to drive the bus lines in a bus-organized system without need for interface or pull-up components.

The output control (\overline{OC}) does not affect the internal operation of the flip-flops. Old data can be retained or new data can be entered while the outputs are in the high-impedance state.

The SN54ALS374 and SN54AS374 are characterized for operation over the full military temperature range of -55°C to 125°C . The SN74ALS374 and SN74AS374 are characterized for operation from 0°C to 70°C .


**SN54ALS374, SN54AS374 . . . J PACKAGE
SN74ALS374, SN74AS374 . . . DW OR N PACKAGE**

(TOP VIEW)



SN54ALS374, SN54AS374 . . . FK PACKAGE

(TOP VIEW)



FUNCTION TABLE (EACH FLIP-FLOP)

INPUTS			OUTPUT
\overline{OC}	CLK	D	Q
L	↑	H	H
L	↑	L	L
L	L	X	Q_0
H	X	X	Z

PRODUCTION DATA documents contain information current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Copyright © 1982, Texas Instruments Incorporated

**TEXAS
INSTRUMENTS**


POST OFFICE BOX 655012 • DALLAS, TEXAS 75265

SN54ALS374, SN54AS374, SN74ALS374, SN74AS374 OCTAL D-TYPE EDGE-TRIGGERED FLIP-FLOPS WITH 3-STATE OUTPUTS


logic symbol[†]

2

ALS and AS Circuits



logic diagram (positive logic)



[†]This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.
Pin numbers shown are for DW, J, and N packages.

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

Supply voltage, V _{CC}	7 V
Input voltage	7 V
Voltage applied to a disabled 3-state output	5.5 V
Operating free-air temperature range: SN54ALS374, SN54AS374 SN74ALS374, SN74AS374	-55 °C to 125 °C 0 °C to 70 °C
Storage temperature range	-65 °C to 150 °C

recommended operating conditions

		SN54ALS374			SN74ALS374			UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	
V _{CC}	Supply voltage	4.5	5	5.5	4.5	5	5.5	V
V _{IH}	High-level input voltage		2			2		V
V _{IL}	Low-level input voltage			0.8			0.8	V
I _{OH}	high-level output current			-1			-2.6	mA
I _{OL}	Low-level output current			12			24	mA
f _{clock}	Clock frequency	0		30	0		35	MHz
t _w	Pulse duration	CLK high	16.5		14			ns
		CLK low	16.5		14			
t _{su}	Setup time, data before CLK1		10		10			ns
t _h	Hold time, data after CLK1		4		0			ns
T _A	Operating free-air temperature	-55		125	0		70	°C

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	SN54ALS374			SN74ALS374			UNIT
		MIN	TYP [†]	MAX	MIN	TYP [†]	MAX	
V _{IK}	V _{CC} = 4.5 V, I _I = -18 mA			-1.5			-1.5	V
V _{OH}	V _{CC} = 4.5 V to 5.5 V, I _{OH} = -0.4 mA	V _{CC} - 2			V _{CC} - 2			V
	V _{CC} = 4.5 V, I _{OH} = -1 mA	2.4	3.3					
	V _{CC} = 4.5 V, I _{OH} = -2.6 mA			2.4	3.2			
V _{OL}	V _{CC} = 4.5 V, I _{OL} = 12 mA		0.25	0.4	0.25	0.4		V
	V _{CC} = 4.5 V, I _{OL} = 24 mA				0.35	0.5		
I _{OZH}	V _{CC} = 5.5 V, V _O = 2.7 V			20			20	μA
I _{OZL}	V _{CC} = 5.5 V, V _O = 0.4 V			-20			-20	μA
I _I	V _{CC} = 5.5 V, V _I = 7 V			0.1			0.1	mA
I _{IIH}	V _{CC} = 5.5 V, V _I = 2.7 V			20			20	μA
I _{IL}	V _{CC} = 5.5 V, V _I = 0.4 V			-0.2			-0.2	mA
I _{O[‡]}	V _{CC} = 5.5 V, V _O = 2.25 V	-30	-112		-30	-112		mA
I _{CC}	V _{CC} = 5.5 V	Outputs high	11	19	11	19		mA
		Outputs low	19	28	19	28		
		Outputs disabled	20	31	20	31		

[†]All typical values are at V_{CC} = 5 V, T_A = 25°C.[‡]The output conditions have been chosen to produce a current that closely approximates one half of the true short-circuit output current, I_{OS}.

SN54ALS374, SN74ALS374
OCTAL D-TYPE EDGE-TRIGGERED FLIP-FLOPS WITH 3-STATE OUTPUTS

switching characteristics (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V _{CC} = 4.5 V to 5.5 V, C _L = 50 pF, R ₁ = 500 Ω, R ₂ = 500 Ω, T _A = MIN to MAX				UNIT	
			SN54ALS374		SN74ALS374			
			MIN	MAX	MIN	MAX		
f _{max}			30		35		MHz	
t _{PLH}	CLK	Q	3	21	3	12	ns	
t _{PHL}			5	19	5	16		
t _{PZH}	\overline{OC}	Q	5	27	5	17	ns	
t _{PZL}			6	23	7	18		
t _{PHZ}	\overline{OC}	Q	2	12	2	10	ns	
t _{PLZ}			3	33	3	18		


NOTE 1: Load circuit and voltage waveforms are shown in Section 1.

2

ALS and AS Circuits

TYPICAL APPLICATION DATA

EXPANDABLE 4-WORD BY 8-BIT GENERAL REGISTER FILE



recommended operating conditions

		SN54AS374			SN74AS374			UNIT
		MIN	NOM	MAX	MIN	NOM	MAX	
V _{CC}	Supply voltage	4.5	5	5.5	4.5	5	5.5	V
V _{IH}	High-level input voltage	2			2			V
V _{IL}	Low-level input voltage			0.7			0.8	V
I _{OH}	High-level output current			-12			-15	mA
I _{OL}	Low-level output current			32			48	mA
f _{clock}	Clock frequency	0	100		0	125		MHz
t _w	Pulse duration	CLK high	5.5		4			ns
		CLK low	5		3			
t _{su}	Setup time data before CLK1		3		2			ns
t _h	Hold time, data after CLK1		3		2			ns
T _A	Operating free-air temperature	-55		125	0		70	°C

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	SN54AS374			SN74AS374			UNIT
		MIN	TYP [†]	MAX	MIN	TYP [†]	MAX	
V _{IK}	V _{CC} = 4.5 V, I _I = -18 mA			-1.2			-1.2	V
	V _{CC} = 4.5 V to 5.5 V, I _{OH} = -2 mA	V _{CC} - 2			V _{CC} - 2			
V _{OH}	V _{CC} = 4.5 V, I _{OH} = -12 mA	2.4	3.2					V
	V _{CC} = 4.5 V, I _{OH} = -15 mA			2.4	3.3			
V _{OL}	V _{CC} = 4.5 V, I _{OL} = 32 mA	0.29	0.5					V
	V _{CC} = 4.5 V, I _{OL} = 48 mA			0.34	0.5			
I _{OZH}	V _{CC} = 5.5 V, V _O = 2.7 V	50			50			μA
I _{OZL}	V _{CC} = 5.5 V, V _O = 0.4 V		-50		-50			μA
I _I	V _{CC} = 5.5 V, V _I = 7 V	0.1			0.1			mA
I _{IIH}	V _{CC} = 5.5 V, V _I = 2.7 V	20			20			μA
I _{IL}	OC, CLK		-0.5		-0.5			
	Data	V _{CC} = 5.5 V, V _I = 0.4 V		-3		-2		mA
I _{O[‡]}	V _{CC} = 5.5 V, V _O = 2.25 V	-30	-112		-30	-112		mA
		Outputs high	77	120	77	120		
ICC	V _{CC} = 5.5 V	Outputs low	84	128	84	128		mA
		Outputs disabled	84	128	84	128		

[†]All typical values are at V_{CC} = 5 V, T_A = 25 °C.[‡]The output conditions have been chosen to produce a current that closely approximates one half of the true short-circuit output current, I_{OS}.

SN54AS374, SN74AS374
OCTAL D-TYPE EDGE-TRIGGERED FLIP-FLOPS WITH 3-STATE OUTPUTS

switching characteristics (see Note 1)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$, $C_L = 50 \text{ pF}$, $R1 = 500 \Omega$, $R2 = 500 \Omega$				UNIT	
			SN54AS374		SN74AS374			
			MIN	MAX	MIN	MAX		
t_{max}			100		125		MHz	
t_{PLH}	CLK	Q	3	11	3	8	ns	
t_{PHL}			4	11.5	4	9		
t_{PZH}	\overline{OC}	Q	2	7	2	6	ns	
t_{PZL}			3	11	3	10		
t_{PHZ}	\overline{OC}	Q	2	7	2	6	ns	
t_{PLZ}			2	7	2	6		

NOTE 1: Load circuit and voltage waveforms are shown in Section 1.

2

ALS and AS Circuits

TYPICAL APPLICATION DATA

