



Features:

- ◆ Capacity : 50kg, 75kg
- ◆ Material: alloy steel
- ◆ Type: micro load cell
- ◆ Defend grade: IP65
- ◆ Application : body scales, hand scales, kitchen scales, postal scales, fishing scales, baby body scales and other micro electronic weighing systems..

Electrical connection and Dimensions:(dimension unit: mm)



Specifications:

capacity	kg	50, 75
safe overload	%FS	120
ultimate overload	%FS	150
rated output	mV/V	1.0 ± 0.15
excitation voltage	Vdc	3 ~ 10
combined error	%FS	± 0.2
zero balance	%FS	± 0.2
non-linearity	%FS	± 0.20
hysteresis	%FS	± 0.20
repeatability	%FS	± 0.20
creep	%FS/3min	± 0.10
input resistance	Ω	1000 ± 10
output resistance	Ω	1000 ± 10
insulation resistance	M Ω	≥ 2000
operating temperature range	°C	-10 ~ +55
compensated temperature range	°C	-10 ~ +40
temperature coefficient of SPAN	%FS/10°C	± 0.20
temperature coefficient of ZERO	%FS/10°C	± 0.20
Electrical connection	cable	3 color wire , Ø0.8×420 mm Red, black, white

※Ordering code: model-capacity- rated output-accuracy-defend grade- the length of cable