


TPS60500
Load transient response (50mA - 250mA) 100uF



Vin = 3.5V
Iload = 50mA to 250mA
no modechange
Temp. = 25°C

Measurement 1 MEAN , 784.41E-3,"V" , CH2

Measurement 2 PK2 , 8.8E-3,"V" , CH2

Measurement 3 MINI , 53.0E-3,"A" , CH4

Measurement 4 MAX , 237.0E-3,"A" , CH4

WFM

Y0

V / DIV.

Time / DIV.

CH2 680.000E-3 20.00mVolts/ 50.00us/div

CH4 0.000E+0 100.0mAmps/ 0.00us/div,