


**TPS60500**  
**Load transient response (50mA - 250mA) 22uF**



Vin = 3.5V  
Iload = 50mA to 250mA  
no modechange  
Temp. = 25°C

Measurement 1 MEAN , 784.99E-3,"V" , CH2

Measurement 2 PK2 , 25.5E-3,"V" , CH2

Measurement 3 MINI , 53.0E-3,"A" , CH4

Measurement 4 MAX , 236.0E-3,"A" , CH4

WFM

Y0

V / DIV.

Time / DIV.

CH2 680.000E-3 20.00mVolts/ 50.00us/div

CH4 0.000E+0 100.0mAmps/ 0.00us/div,