# **NEC** NEC LCD Technologies, Ltd.

# TFT COLOR LCD MODULE

NL10276BC20-04

26.3cm (10.4 Type) XGA



This DATA SHEET is updated document from DOD-M-1255(5).

All information is subject to change without notice. Please confirm the sales representative before starting to design your system.

#### INTRODUCTION

No part of this document shall be copied in any form or by any means without the prior written consent of NEC LCD Technologies, Ltd. (hereinafter called "NEC").

NEC does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a product described herein or any other liability arising from use of such application. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC or of others.

While NEC has been making continuous effort to enhance the reliability of its products, the possibility of failures cannot be eliminated entirely. To minimize risks of damage to property or injury to person arising from a failure in an NEC product, customers must incorporate sufficient safety measures in their design, such as redundancy, fire-containment and anti-failure features.

NEC products are classified into the following three quality grades:

```
"Standard", "Special", "Specific"
```

The "Specific" quality grade applies only to applications developed based on a customer designated "quality assurance program" for a specific application. The recommended applications of a product depend on its quality grade, as indicated below. Customers must check the quality grade of each application before using it in a particular application.

- *Standard:* Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots
- *Special:* Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)
- *Specific:* Military systems, aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems (medical equipment, etc.) and any other equipment

The quality grade of this product is "Standard" unless otherwise specified in this document. If customers intend to use this product for applications other than those specified for "Standard" quality grade, they should contact NEC sales representative in advance.

# **CONTENTS**

INTRODUCTION	2
1. OUTLINE	5
1.1 STRUCTURE AND PRINCIPLE	5
1.2 APPLICATIONS	5
1.3 FEATURES	5
2. GENERAL SPECIFICATIONS	6
3. BLOCK DIAGRAM	7
4. DETAILED SPECIFICATIONS	
4.1 MECHANICAL SPECIFICATIONS	8
4.2 ABSOLUTE MAXIMUM RATINGS	8
4.3 ELECTRICAL CHARACTERISTICS	9
4.3.1 Driving for LCD panel signal processing board	9
4.3.2 Working for backlight lamp	9
4.3.3 Power supply voltage ripple	10
4.3.4 Fuses	10
4.4 POWER SUPPLY VOLTAGE SEQUENCE	11
4.4.1 Sequence for LCD panel signal processing board	11
4.4.2 Sequence for backlight inverter (Option)	11
4.5 CONNECTIONS AND FUNCTIONS FOR INTERFACE PINS	12
4.5.1 LCD panel signal processing board	
4.5.2 Backlight lamp	13
4.5.3 Positions of a plug and a socket	13
4.5.4 Connection between receiver and transmitter for LVDS	14
4.6 DISPLAY COLORS AND INPUT DATA SIGNALS	15
4.7 DISPLAY POSITIONS	16
4.8 SCANNING DIRECTIONS	
4.9 INPUT SIGNAL TIMINGS FOR LCD PANEL SIGNAL PROCESSING BOARD	17
4.9.1 Outline of input signal timings	17
4.9.2 Input signal timing chart	17
4.9.3 Timing characteristics	18
4.10 OPTICS	19
4.10.1 Optical characteristics	
4.10.2 Definition of contrast ratio	
4.10.3 Definition of luminance uniformity	
4.10.4 Definition of response times	
4.10.5 Definition of viewing angles	20

# **CONTENTS**

5. RELIABILITY TESTS	21
6. PRECAUTIONS	22
6.1 MEANING OF CAUTION SIGNS	22
6.2 CAUTIONS	22
6.3 ATTENTIONS	22
6.3.1 Handling of the product	22
6.3.2 Environment	
6.3.3 Characteristics	23
6.3.4 Other	23
7. OUTLINE DRAWINGS	24
7.1 FRONT VIEW	24
7.2 REAR VIEW	25

#### 1. OUTLINE

#### 1.1 STRUCTURE AND PRINCIPLE

NL10276BC20-04 module is composed of the amorphous silicon thin film transistor liquid crystal display (a-Si TFT LCD) panel structure with driver LSIs for driving the TFT (Thin Film Transistor) array and a backlight unit.

The a-Si TFT LCD panel structure is injected liquid crystal material into a narrow gap between the TFT array glass substrate and a color-filter glass substrate.

Color (Red, Green, Blue) data signals from a host system (e.g. PC, signal generator, etc.) are modulated into best form for active matrix system by a signal processing board, and sent to the driver LSIs which drive the individual TFT arrays.

The TFT array as an electro-optical switch regulates the amount of transmitted light from the backlight assembly, when it is controlled by data signals. Color images are created by regulating the amount of transmitted light through the TFT array of red, green and blue dots.

#### 1.2 APPLICATIONS

- Display terminal for control system
- Industrial PC

#### 1.3 FEATURES

- High luminance
- Wide viewing angle
- Extensive temperature
- 6-bit digital RGB signals
- Single link LVDS interface
- Reversible-scan direction
- Edge light type
- Replaceable lamp for backlight unit (Inverter less)
- Acquisition product for UL1950 3rd edition/CSA C22.2 No.950-95 (File number: E170632)

#### 2. GENERAL SPECIFICATIONS

**Display area**  $210.4 \text{ (W)} \times 157.8 \text{ (H) mm (typ.)}$ 

Diagonal size of display 26.3 cm (10.4 inches)

Drive system a-Si TFT active matrix

*Display color* 262,144 colors

*Pixel*  $1,024 \text{ (H)} \times 768 \text{ (V)} \text{ pixels}$ 

Pixel arrangement RGB (Red dot, Green dot, Blue dot) vertical stripe

 Dot pitch
  $0.0685 (W) \times 0.2055 (H) mm$  

 Pixel pitch
  $0.2055 (W) \times 0.2055 (H) mm$ 

**Module size**  $243.0 \text{ (W)} \times 185.1 \text{ (H)} \times 11.0 \text{ (D)} \text{ mm (typ.)}$ 

Weight 530 g (typ.)
Contrast ratio 300:1 (typ.)

Viewing angle At the contrast ratio 10:1

Horizontal: Left side 60° (typ.), Right side 60° (typ.)
Vertical: Up side 45° (typ.), Down side 60° (typ.)

**Designed viewing direction** At DPSR: normal scan

Viewing direction without image reversal: up side (12 o'clock)
Viewing direction with contrast peak: down side 5° to 10° (6 o'clock)

• Viewing angle with optimum grayscale ( $\gamma$ =2.2): normal axis

**Polarizer surface** Non matt treatment

**Polarizer pencil-hardness** 3H (min.) [by JIS K5400]

Color gamut At LCD panel center

40 % (typ.) [against NTSC color space]

**Response time** Ton (White  $90\% \rightarrow Black 10\%$ )

15 ms (typ.)

Luminance At 5.0mArms / lamp

 $300 \text{ cd/m}^2 \text{ (typ.)}$ 

Signal system Single link LVDS (Receiver: THC63LVDF64A, THine Electronics Inc.)

[6-bit digital signals for data of RGB colors, Dot clock (CLK), Data enable (DE)]

Power supply voltage LCD panel signal processing board: 3.3V

Backlight Edge light type: 2 cold cathode fluorescent lamps

Replaceable parts


• Lamps for backlight unit: Type No. 104LHS35

Recommended inverter (Option)
• Inverter: Type No. 104PW191

**Power consumption** At maximum luminance and checkered flag pattern

6.2W (typ., Power dissipation of the inverter does not include.)

#### 3. BLOCK DIAGRAM



Note1: Connections between GND (Signal ground), FG (Frame ground) and VBLC (Lamp low voltage terminal) in the LCD module

GND - FG	Not connected
GND - VBLC	Not connected
FG - VBLC	Not connected

Note2: GND, FG and GNDB must be connected to customer equipment's ground, and it is recommended that these grounds are connected together in customer equipment.

Note3: Pull-down resistance of DPSR pin

		$(k\Omega)$
min.	typ.	max.
20	50	132

# 4. DETAILED SPECIFICATIONS

#### 4.1 MECHANICAL SPECIFICATIONS

Parameter	Specification		Unit
Module size	$243.0 \pm 0.5 \text{ (W)} \times 185.1 \pm 0.5 \text{ (H)} \times 11.0 \pm 0.5 \text{ (D)}$	Note1	mm
Display area	$210.4 \pm 0.5 \text{ (W)} \times 157.8 \pm 0.5 \text{ (H)}$	Note1	mm
Weight	530 (typ.), 550 (max.)		g

Note1: See "11. OUTLINE DRAWINGS".

#### 4.2 ABSOLUTE MAXIMUM RATINGS

Parameter			Symbol	Rating	Unit	Remarks		
Power supply	LCD p	anel signal board	VCC	-0.3 to +4.0	V			
voltage			VBLH	1,500	Vrms	Ta = 25°C		
Input voltage	Di	splay signals Note2	VD	-0.3 to VCC+0.3	V	1a – 25 C		
for signals	Fu	nction signals Note3	VF	-0.3 to VCC+0.3	V			
Storage temperature  Front surface  Operating temperature  Rear surface		Tst	-20 to +70	°C				
				0 to +60	°C	-		
		Rear surface	TopR	0 to +60	°C			
	Relative humidity Note4					≤ 95	%	Ta ≤ 40°C
				RH	≤ 85	%	40 < Ta ≤ 50°C	
				Note4		KH	≤ 70	%
				≤ 60	%	55 < Ta ≤ 60°C		
Absolute humidity Note4			АН	≤ 78 Note5	g/m³	Ta > 60°C		

Note1: "VBLH" is the voltage value between low voltage terminal (Cold) and high voltage terminal (Hot).

Note2: Display signals are D0+/-, D1+/-, D2+/- and CK+/-. Also controller with LVDS receiver are worked by +3.3V from DC/DC converter.

Note3: Function signal is DPSR.

Note4: No condensation Note5: Ta = 60°C, RH = 60%

#### 4.3 ELECTRICAL CHARACTERISTICS

## 4.3.1 Driving for LCD panel signal processing board

 $(Ta = 25^{\circ}C)$ 

Parameter		Symbol	Min.	Тур.	Max.	Unit	Remarks
Power supply voltage		VCC	3.0	3.3	3.6	V	-
Power supply current		ICC	-	300 Note1	500 Note2	mA	VCC = 3.3V
Input voltage for LVDS	Low	VDRL	0	-	0.8	V	
receiver	High	VDRH	2.0	-	2.4	V	-
Differential input threshold	Low	VTL	-100	-	-	mV	VOC=1.2V
voltage for LVDS receiver	High	VTH	-	-	+100	mV	Note3
Input voltage for DPSR	Low	VFDL	0	-	0.8	V	
signal	High	VFDH	2.0	-	VCC	V	-

Note1: Checkered flag pattern (by EIAJ ED-2522)

Note2: Pattern for maximum current

Note3: Common mode voltage for LVDS receiver

#### 4.3.2 Working for backlight lamp

Parameter	Symbol	Ta	Min.	Тур.	Max.	Unit	Remarks
Lamp starting voltage	VS	0°C	1,100	-	-	Vrms	Note1
Lamp starting voltage	VS	25°C	850	1	1	Vrms	Note1
Lamp voltage	VBLH	25°C	-	520	-	Vrms	Note1,Note2
Lamp current	IBL	25°C	2.0	5.0	5.5	mArms	Note2, Note3
Lamp oscillation frequency	FO	25°C	60	65	70	kHz	Note4

Note1: The power supply voltage cycle between lamps should be kept on a same phase. "VS" and "VBLH" are the voltage value between low voltage side (Cold) and high voltage side (Hot).

Note2: The asymmetric ratio of working waveform for lamps (Power supply voltage peak ratio, power supply current peak ratio and waveform space ratio) should be less than 5 % (See the following figure.). If the waveform is asymmetric, DC (Direct current) element apply into the lamp. In this case, a lamp lifetime may be shortened, because a distribution of a lamp enclosure substance inclines toward one side between low voltage terminal (Cold terminal) and high voltage terminal (Hot terminal).

$$\frac{|Pa - Pb|}{Pb} \times 100 \le 5 \%$$

$$\frac{|Sa - Sb|}{Sb} \times 100 \le 5 \%$$

Pa: Supply voltage/current peak for positive, Pb: Supply voltage/current peak for negative Sa: Waveform space for positive part, Sb: Waveform space for negative part

Note3: The lamp holder of this product contains two backlight lamps. The low voltage terminal of both lamps is connected to one contact point. Also above power supply current specification is one lamp duty. Therefore, this lamp holder becomes twice as many power supply current as above value on low voltage (Cold) line. The measurement for the power supply current value of one lamp should measure on high voltage (Hot) line to each lamp.

Note4: In case "FO" is not the recommended value, beat noise may display on the screen, because of interference between "FO" and "1/th". Recommended value of "FO" is as following.

FO = 
$$\frac{1}{4} \times \frac{1}{\text{th}} \times (2\text{n-1})$$

th: Horizontal synchronous cycle (See "4.9.3 Timing characteristics".)

n: Natural number (1, 2, 3 .....)

# 4.3.3 Power supply voltage ripple

This product works, even if the ripple voltage levels are beyond the permissible values as following the table, but there might be noise on the display image.

Parameter	Power supply voltage	Ripple voltage Note1 (Measure at input terminal of power supply)	Unit
VCC	3.3 V	≤ 100	mVp-p

Note1: The permissible ripple voltage includes spike noise.


#### 4.3.4 Fuses

Eusing line	Fu	ise	Dating	Fusing current
Fusing line	Туре	Supplier	Rating	Note1
VCC	TF16N2.00	VOA Corneration	2.0 A	4.0 A
VCC	1F10N2.00	KOA Corporation	47 V	4.0 A

Note1: The power supply capacity should be more than the fusing current. If the power supply capacity is less than the fusing current, the fuse may not blow for a short time, and then nasty smell, smoking and so on may occur.

#### 4.4 POWER SUPPLY VOLTAGE SEQUENCE

# 4.4.1 Sequence for LCD panel signal processing board




Note1: In terms of voltage variation (voltage drop) while VCC rising edge is below 3.0V, a protection circuit may work, and then this product may not work.

Note2: Display (D0+/-, D1+/-, D2+/- and CK+/-) with  $100\Omega$  (Characteristic impedance) and function (DPSR) signals must be Low or High-impedance, exclude the VALID period (See above sequence diagram), in order to avoid that internal circuits is damaged.

If some of display and function signals of this product are cut while this product is working, even if the signal input to it once again, it might not work normally. If customer stops the display and function signals, they should be cut VCC.

## 4.4.2 Sequence for backlight inverter (Option)



Note1: These are display and function signals for LCD panel signal processing board.

Note2: The backlight inverter voltage (VDDB) should be inputted within the valid period of display and function signals, in order to avoid unstable data display.

#### 4.5 CONNECTIONS AND FUNCTIONS FOR INTERFACE PINS

# 4.5.1 LCD panel signal processing board


CN1 socket (Module side): FI-SE20P-HF (Japan Aviation Electronics Industry Limited) Adaptable plug: FI-S20S (Japan Aviation Electronics Industry Limited)

Pin No.	Symbol	Function	Remarks		
1	GND	Commit			
2	GND	Ground	-		
3	DPSR	Select of scan direction	High: Reverse scan Low or Open: Normal scan Note1		
4	NC	Non connection			
5	GND	Ground	-		
6	CK+	Pired de de	NI-4-2		
7	CK-	Pixel clock	Note2		
8	GND	Ground	-		
9	D2+	D' 11.	N 2		
10	D2-	Pixel data	Note2		
11	GND	Ground	-		
12	D1+	Direct data	NI-4-2		
13	D1-	Pixel data	Note2		
14	GND	Ground	-		
15	D0+	D' 11.	N 2		
16	D0-	Pixel data	Note2		
17	GND	Const			
18	GND	Ground			
19	VCC	D	-		
20	VCC	Power supply			

Note1: See "4.8 SCANNING DIRECTIONS".

Note2: Twist pair wires with  $100\Omega$  (Characteristic impedance) should be connected between LCD panel signal processing board and LVDS transmitter.

CN1: Figure of socket




# 4.5.2 Backlight lamp


CN2 plug: BHR-03VS-1 (J.S.T Mfg. Co., Ltd.)

Adaptable socket: SM03 (4.0) B-BHS-TB (J.S.T Mfg. Co., Ltd.)


Pin No.	Symbol	Signal	Remarks
1	VBLC	Low voltage (Cold)	
2	VBLH	High voltage (Hot)	-
3	VBLH	High voltage (Hot)	



# 4.5.3 Positions of a plug and a socket



#### 4.5.4 Connection between receiver and transmitter for LVDS



Note1: Recommended transmitter

See the data sheet for THC63LVDM63A (THine Electronics Inc.).

Note2: TC4 should be fixed to "High".

#### 4.6 DISPLAY COLORS AND INPUT DATA SIGNALS

This product can display in equivalent to 262,144 colors in 64 scale. Also the relation between display colors and input data signals is as the following table.

Display colors		Data signal (0: Low level, 1: High level)																	
Displa	Display colors		R 4	R 3	R 2	R 1	R 0	G 5	G4	G 3	G 2	G 1	G 0	B 5	B 4	В3	B 2	B 1	В0
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	Blue	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1
	Red	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0
Basic colors	Magenta	1	1	1	1	1	1	0	0	0	0	0	0	1	1	1	1	1	1
Basic colors	Green	0	0	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0
	Cyan	0	0	0	0	0	0	1	1	1	1	1	1	1	1	1	1	1	1
	Yellow	1	1	1	1	1	1	1	1	1	1	1	1	0	0	0	0	0	0
	White	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		0	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0
	dark	0	0	0	0	1	0	0	0	0	0	0	0	0	0	0	0	0	0
Red scale	1			:	:						:						:		
Red searc	$\downarrow$			:	:						:						:		
	bright	1	1	1	1	0	1	0	0	0	0	0	0	0	0	0	0	0	0
		1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0	0
	Red	1	1	1	1	1	1	0	0	0	0	0	0	0	0	0	0	0	0
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		0	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0
	dark	0	0	0	0	0	0	0	0	0	0	1	0	0	0	0	0	0	0
Green scale	Î	:								:			:						
	<b>↓</b>				:						:		_				:		
	bright	0	0	0	0	0	0	1	1	1	1	0	1	0	0	0	0	0	0
	G	0	0	0	0	0	0	1	1	1	1	1	0	0	0	0	0	0	0
	Green	0	0	0	0	0	0	1	1	1	1	1	1	0	0	0	0	0	0
	Black	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
	41.	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	1
	dark ↑	0	U	0	0	U	0	0	U	U		U	0	0	U	U		1	U
Blue scale	<u> </u>			:				:				<u> </u>							
	↓ bright	0	0	0	: 0	0	0	0	0	0	: 0	0	0	1	1	1	: 1	0	1
	origin	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	0
	Blue	0	0	0	0	0	0	0	0	0	0	0	0	1	1	1	1	1	1

#### 4.7 DISPLAY POSITIONS

The following table is the coordinates	per pixel (See figure	e of "4.8 SCANNING DIRECTIONS".).

C( 0, 0)	C( 1, 0)	•••	C( X, 0)	•••	C(1022, 0)	C(1023, 0)
C( 0, 1)	C( 1, 1)	•••	C( X, 1)	•••	C(1022, 1)	C(1023, 1)
•	•	•	•	•	•	•
•	•	• • •	•	• • •	•	• • •
•	•	•	•	•	•	•
C( 0, Y)	C( 1, Y)	•••	C( X, Y)	• • •	C(1022, Y)	C(1023, Y)
•	•	•	•	•	•	•
•	•	• • •	•	• • •	•	•
•	•	•	•	•	•	•
C(0, 766)	C( 1, 766)	•••	C( X, 766)	•••	C(1022, 766)	C(1023, 766)
C( 0, 767)	C( 1, 767)	•••	C( X, 767)	•••	C(1022, 767)	C(1023, 767)

#### 4.8 SCANNING DIRECTIONS

The following figures are seen from a front view. Also the arrow shows the direction of scan.




Figure 1. Normal scan (DPSR: Low or Open)




Figure 2. Reverse scan (DPSR: High)


Note1: Meaning of C(X, Y) and D(X, Y)

C (X, Y): The coordinates of the display position (See "4.7 DISPLAY POSITIONS".)


D (X, Y): The data number of input signal for LCD panel signal processing board

#### 4.9 INPUT SIGNAL TIMINGS FOR LCD PANEL SIGNAL PROCESSING BOARD

# 4.9.1 Outline of input signal timings



Note1: This diagram indicates virtual signal for set up to timing.



Note1: This diagram indicates virtual signal for set up to timing.


Note2: See "4.9.2 Input signal timing chart" for numeration of pulse.

# 4.9.2 Input signal timing chart

# Outline chart VDRH CLK 0.5VCC VDRL DATA VDRH (R0 to R5) (G0 to G5) (B0 to B5) VDRL VDRH DE 0.5VCC VDRL 1 2 768

Note1: X is data number from 1 to 1022. See "4.8 SCANNING DIRECTIONS".

# • Detail of A part



Note1: X is data number from 1 to 1022. See "4.8 SCANNING DIRECTIONS".

# 4.9.3 Timing characteristics

	Parame	eter Note1	Symbol	Min.	Тур.	Max.	Unit	Remarks	
	Frequency (L	tcf	60.0	65.0	68.0	MHz	15.4 ns (typ.) Note1		
CLK	D	tcd	-	-	-	-	Note1, Note2		
	Rise time	terf	-	-	ı	ı			
	CLK-DATA	Setup time	tds	-	-	-	-	Note2	
DATA	CLK-DAIA	Hold time	tdh	-	-	-	-	Note2	
	Rise time	, Fall time	tdrf	-	-	-	-		
		Cycle	th	19.67	20.676	22.4	μs	48.363kHz (Typ.)	
	Horizontal	Cycle		-	1,344	-	CLK	Note1, Note3	
		Display period	thd	1,024			CLK		
	37 (* 1	Cycle	tv	13.3	16.666	18.5	ms	60.0Hz (Typ.)	
DE	Vertical (One frame)	Cycle		780	806	-	Н	Note1	
	(one frame)	Display period	tvd		768		Н		
	CLK-DE	Setup time	tdes	-	-	ı	ı		
	CLK-DE	Hold time	tdeh	-	-	ı	ı	Note2	
	Rise time	, Fall time	tderf	-	-	-	-		

Note1: Definition of parameters is as follows.

tcf = 1/tc,  $tcd = tch/tc = tch \times tcf$ , tc = 1CLK, th = 1H

Note2: See the data sheet of LVDS transmitter.

Note3: "th" must keep the fluctuation within ±1 CLK, because of avoidance of image sticking.

#### 4.10 OPTICS

#### 4.10.1 Optical characteristics

(Note1, Note2)


Parameter		Condition	Symbol	Min.	Тур.	Max.	Unit	Remarks	
Contrast ratio		White/Black at center $\theta R = 0^{\circ}$ , $\theta L = 0^{\circ}$ , $\theta U = 0^{\circ}$ , $\theta D = 0^{\circ}$	CR	150	300	ı	1	Note3	
Luminance		White at center $\theta R = 0^{\circ}$ , $\theta L = 0^{\circ}$ , $\theta U = 0^{\circ}$ , $\theta D = 0^{\circ}$	L	240	300	1	cd/m <sup>2</sup>	-	
Luminance unit	formity	-	LU	-	1.24	1.40	-	Note4	
	XX/I-:4-	<b>x</b> coordinate	Wx	-	0.315	-	-		
	White	y coordinate	Wy	-	0.340	-	-		
	Red	x coordinate	Rx	-	0.575	-	-		
Chamatiaity	Red	y coordinate	Ry	-	0.335	-	-		
Chromaticity	Green	x coordinate	Gx	-	0.332	-	-	Note5	
		y coordinate	Gy	-	0.536	-	-		
	Blue	x coordinate Bx -		-	0.153	-	-		
		y coordinate	Ву	•	0.150	•	•		
Color gam	ut	$\theta R = 0^{\circ}, \ \theta L = 0^{\circ}, \ \theta U = 0^{\circ}, \ \theta D = 0^{\circ}$ at center, against NTSC color space		35	40	ı	%		
D		White to black	Ton	-	15	30	ms	Note6	
Response ti	me	Black to white	Toff	1	40	60	ms	Note7	
	Right	$\theta$ U = 0°, $\theta$ D = 0°, CR = 10	θR	ı	60	ı	0		
Viewing angle	Left	$\theta U = 0^{\circ},  \theta D = 0^{\circ},  CR = 10$	θL	-	60	-	0	Note8	
	Up	$\theta R = 0^{\circ},  \theta L = 0^{\circ},  CR = 10$	θU	-	45	-	0	Notes	
	Down	$\theta R = 0^{\circ},  \theta L = 0^{\circ},  CR = 10$	θD	-	60	-	0		

Note1: These are initial characteristics.

Note2: Measurement conditions are as follows.

Ta = 25°C, VCC = 3.3V, IBL = 5.0mArms/lamp, Display mode: XGA, Horizontal cycle = 48.363kHz, Vertical cycle = 60.0Hz, DPSR = Low or Open: Normal scan

Optical characteristics are measured at luminance saturation after 20minutes from working the product, in the dark room. Also measurement method for luminance is as follows.



Note3: See "4.10.2 Definition of contrast ratio".

Note4: See "4.10.3 Definition of luminance uniformity".

Note5: These coordinates are found on CIE 1931 chromaticity diagram.

Note6: Product surface temperature:  $TopF = 25^{\circ}C$ 

Note7: See "4.10.4 Definition of response times".

Note8: See "4.10.5 Definition of viewing angles".

#### 4.10.2 Definition of contrast ratio


The contrast ratio is calculated by using the following formula.

# 4.10.3 Definition of luminance uniformity

The luminance uniformity is calculated by using following formula.


Luminance uniformity (LU) = 
$$\frac{\text{Maximum luminance from } \textcircled{1} \text{ to } \textcircled{5}}{\text{Minimum luminance from } \textcircled{1} \text{ to } \textcircled{5}}$$

The luminance is measured at near the 5 points shown below.




#### 4.10.4 Definition of response times

Response time is measured, the luminance changes from "white" to "black", or "black" to "white" on the same screen point, by photo-detector. Ton is the time it takes the luminance change from 90% down to 10%. Also Toff is the time it takes the luminance change from 10% up to 90% (See the following diagram.).



## 4.10.5 Definition of viewing angles




# 5. RELIABILITY TESTS

Test item	Condition	Judgement
High temperature and humidity (Operation)	① 55 ± 2°C, RH = 85%, 240hours ② Display data is black.	
High temperature (Operation)	① 60 ± 2°C, 240hours ② Display data is black.	
Heat cycle (Operation)	① 0 ± 3°C1hour 60 ± 3°C1hour ② 50cycles, 4hours/cycle ③ Display data is black.	
Thermal shock (Non operation)	① -20 ± 3°C30minutes 70 ± 3°C30minutes ② 100cycles, 1hour/cycle ③ Temperature transition time is within 5 minutes.	No display malfunctions Note1
ESD (Operation)	<ul> <li>① 150pF, 150Ω, ±10kV</li> <li>② 9 places on a panel surface Note2</li> <li>③ 10 times each places at 1 sec interval</li> </ul>	
Dust (Operation)	① Sample dust: No. 15 (by JIS-Z8901) ② 15 seconds stir ③ 8 times repeat at 1 hour interval	
Vibration (Non operation)	No display malfunctions No physical damages	
Mechanical shock (Non operation)	① 539m/ s², 11ms ② ±X, ±Y, ±Z direction ③ 5 times each directions	Note1

Note1: Display and appearance are checked under environmental conditions equivalent to the inspection conditions of defect criteria.

Note2: See the following figure for discharge points.



6. PRECAUTIONS

#### 6.1 MEANING OF CAUTION SIGNS

The following caution signs have very important meaning. Be sure to read "6.2 CAUTIONS" and "6.3 ATTENTIONS", after understanding this contents!



This sign has the meaning that customer will be injured by himself or the product will sustain a damage, if customer has wrong operations.



This sign has the meaning that customer will get an electrical shock, if customer has wrong operations.



This sign has the meaning that customer will be injured by himself, if customer has wrong operations.

#### **6.2 CAUTIONS**



\* Do not touch the working backlight. Customer will be in danger of an electric shock.



- \* Do not touch the working backlight. Customer will be in danger of burn injury.
- \* Do not shock and press the LCD panel and the backlight! There is a danger of breaking, because they are made of glass. (Shock: To be not greater 539m/s² and to be not greater 11ms, Pressure: To be not greater 19.6 N)

# 6.3 ATTENTIONS



#### 6.3.1 Handling of the product

- ① Take hold of both ends without touch the circuit board cover when customer pulls out products (LCD modules) from inner packing box. If customer touches it, products may be broken down or out of adjustment, because of stress to mounting parts.
- ② Do not hook cables nor pull connection cables such as lamp cable and so on, for fear of damage.
- 3 If customer puts down the product temporarily, the product puts on flat subsoil as a display side turns down.
- ① Take the measures of electrostatic discharge such as earth band, ionic shower and so on, when customer deals with the product, because products may be damaged by electrostatic.
- ⑤ The torque for mounting screws must never exceed 0.294N·m. Higher torque values might result in distortion of the bezel.
- ⑥ The product must be installed using mounting holes without undue stress such as bends or twist (See outline drawings). And do not add undue stress to any portion (such as bezel flat area) except mounting hole portion.
  - Bends or twist described above and undue stress to any portion except mounting hole portion may cause display un-uniformity.

- ② Do not press or rub on the sensitive display surface. If customer clean on the panel surface, NEC recommends using the cloth with ethanolic liquid such as screen cleaner for LCD.
- ® Do not push-pull the interface connectors while the product is working, because wrong power sequence may break down the product.
- Do not bend or unbend the lamp cable at the near part of the lamp holding rubber, to avoid the
   damage for high voltage side of the lamp. This damage may cause a lamp breaking and abnormal
   operation of high voltage circuit.

#### 6.3.2 Environment

- ① Do not operate or store in high temperature, high humidity, dewdrop atmosphere or corrosive gases. Keep the product in antistatic pouch in room temperature, because of avoidance for dusts and sunlight, if customer stores the product.
- ② In order to prevent dew condensation occurring by temperature difference, the product packing box must be opened after leave under the environment of an unpacking room temperature enough. Because a situation of dew condensation occurring is changed by the environmental temperature and humidity, evaluate the leaving time sufficiently. (Recommendation leaving time: 6 hour or more with packing state)
- 3 Do not operate in high magnetic field. Circuit boards may be broken down by it.
- ④ This product is not designed as radiation hardened.
- ⑤ Use an original protection sheet on the product surface (polarizer). Adhesive type protection sheet should be avoided, because it may change color or properties of the polarizer.

#### 6.3.3 Characteristics

# The following items are neither defects nor failures.


- ① Response time, luminance and color may be changed by ambient temperature.
- ② The LCD may be seemed luminance non-uniformity, flicker, vertical seam or small spot by display patterns.
- ③ Optical characteristics (e.g. luminance, display uniformity, etc.) gradually is going to change depending on operating time, and especially low temperature, because the LCD has cold cathode fluorescent lamps.
- ① Do not display the fixed pattern for a long time because it may cause image sticking. Use a screen saver, if the fixed pattern is displayed on the screen.
- (5) The display color may be changed by viewing angle because of the use of condenser sheet in the backlight.
- 6 Optical characteristics may be changed by input signal timings.
- The interference noise of input signal frequency for this product's signal processing board and luminance control frequency of customer's backlight inverter may appear on a display. Set up luminance control frequency of backlight inverter so that the interference noise does not appear.

# 6.3.4 Other

- ① All GND and VCC terminals should be used without a non-connected line.
- ② Do not disassemble a product or adjust volume without permission of NEC.
- 3 See "REPLACEMENT MANUAL FOR LAMP HOLDER SET", if customer would like to replace backlight lamps.
- Pay attention not to insert waste materials inside of products, if customer uses screwnails.
- ⑤ Pack the product with original shipping package, because of avoidance of some damages during transportation, when customer returns it to NEC for repair and so on.

# 7. OUTLINE DRAWINGS

# 7.1 FRONT VIEW




Note1: The values in parentheses are for reference.

Note2: Distance between center of CN1 and surface of front shield.

Unit: mm

# 7.2 REAR VIEW



Note1: The values in parentheses are for reference.

Unit: mm