



# CE Radio Test Report

**APPLICANT** : Texas Instruments Incorporated  
**EQUIPMENT** : WiFi and Bluetooth Module  
**BRAND NAME** : Texas Instruments  
**MODEL NAME** : WL18MODGB  
**MARKETING NAME** : WL18xxMOD WiLink™ 8 Single-Band Combo Module –  
Wi-Fi®, Bluetooth®, and Bluetooth Low Energy (LE)  
**STANDARD** : ETSI EN 300 328 V2.1.1 (2016-11)  
**TEST DATE(S)** : Jun. 12, 2017

The measurement shown in this variant report is tested in accordance with the test procedures given in ETSI EN 300 328 V2.1.1 (2016-11).

The test results in this report apply exclusively to the tested model / sample. Without written approval of SPORTON INTERNATIONAL INC., the test report shall not be reproduced except in full.

Reviewed by: Joseph Lin / Supervisor

Approved by: Jones Tsai / Manager



## SPORTON INTERNATIONAL INC.

No. 52, Hwa Ya 1st Rd., Hwa Ya Technology Park, Kwei-Shan District, Tao Yuan City, Taiwan R.O.C.



## TABLE OF CONTENTS

**REVISION HISTORY.....3**

**SUMMARY OF TEST RESULT .....4**

**1 GENERAL DESCRIPTION .....5**

    1.1 Applicant .....5

    1.2 Manufacturer.....5

    1.3 Product Feature of Equipment Under Test.....5

    1.4 Modification of EUT .....5

    1.5 Testing Facility.....6

    1.6 Applied Standards .....6

**2 RECEIVER PARAMETERS.....7**

    2.1 Receiver Blocking Test.....7

**3 LIST OF MEASURING EQUIPMENT .....13**

**4 UNCERTAINTY EVALUATION .....14**

**APPENDIX A. ORIGINAL REPORT**



## REVISION HISTORY

REPORT NO.	VERSION	DESCRIPTION	ISSUED DATE
ER741320	Rev. 01	Initial issue of report	Jun. 15, 2017



### SUMMARY OF TEST RESULT

CLAUSE (EN 300 328)	TEST PARAMETER	PASS/FAIL	REMARK
<b>Transmitter Parameters</b>			
4.3.1.2 4.3.2.2	Maximum Transmit Power	Not Required	-
4.3.2.3	Maximum Equivalent Isotropically Radiated Power (E.I.R.P.) Spectral Density	Not Required	Only applicable for modulations other than FHSS
4.3.1.8 4.3.2.7	Occupied Channel Bandwidth	Not Required	-
4.3.1.4 4.3.1.5	Frequency Hopping Requirements	Not Required	Only applicable for FHSS
4.3.1.9 4.3.2.8	Transmitter spurious emissions in OOB	Not Required	-
4.3.1.10 4.3.2.9	Transmitter spurious emissions	Not Required	-
<b>Receiver Parameters</b>			
4.3.1.11 4.3.2.10	Receiver spurious emissions	Not Required	-
<b>Adaptive Test Item</b>			
4.3.1.7 4.3.2.6	Adaptivity	Not Required	Only applicable for adaptive equipment Output Power >10dBm
4.3.1.12 4.3.2.11	Receiver Blocking	PASS	
<b>Non-Adaptive Test Item</b>			
4.3.1.3 4.3.2.4	Duty cycle, Tx-Sequence, Tx-gap	Not Required	Only applicable for non-adaptive equipment Output Power >10dBm
4.3.1.6 4.3.2.5	Medium Utilisation (MU) factor	Not Required	
<b>Note:</b> Not required means after assessing, test items are not necessary to carry out.			



# 1 General Description

## 1.1 Applicant

Texas Instruments Incorporated  
12500 TI BLVD., Dallas Texas, 75243

## 1.2 Manufacturer

Texas Instruments Incorporated  
12500 TI BLVD., Dallas Texas, 75243

## 1.3 Product Feature of Equipment Under Test

Bluetooth and Wi-Fi 2.4GHz 802.11b/g/n.

Antenna information				
	Brand	Antenna Type	Model	2.4GHz ~2.5GHz Gain
1	Ethertronics	PCB	100423	-0.6dBi
2	LSR	Rubber Whip / Dipole	001-0012	2dBi
3			080-0013	2dBi
4			080-0014	2dBi
5		PIFA	001-0016	2.5dBi
6			001-0021	2.5dBi
7		Laird	PCB	CAF94504
8	CAF94505			2dBi
9	Pulse	Chip	W3006	3.2dBi
10	TDK	CHIP	ANT016008	2.5dBi

**Remark:**

1. This is a variant report by updating test standards to RED. All the test cases were performed on the Sporton variant report, ER4O2349, which was performed on the original Sporton report, ER3N2752-01 as shown in Appendix A.
2. The EUT used a dual band CHIP antenna (Brand: TDK)

## 1.4 Modification of EUT

No modifications are made to the EUT during all test items.



### 1.5 Testing Facility

<b>Test Site</b>	SPORTON INTERNATIONAL INC.
<b>Test Site Location</b>	No. 52, Hwa Ya 1st Rd.,Hwa Ya Technology Park, Kwei-Shan District, Tao Yuan City, Taiwan R.O.C. TEL: +886-3-327-3456 FAX: +886-3-328-4978
<b>Test Site No.</b>	<b>Sporton Site No. :</b> DFS02-HY

### 1.6 Applied Standards

According to the specifications of the manufacturer, the EUT must comply with the requirements of **ETSI EN 300 328 V2.1.1 (2016-11)**.

**Note:** All test items were verified and recorded according to the standards and without any deviation during the test.

## 2 Receiver Parameters

### 2.1 Receiver Blocking Test

#### 2.1.1 Limit of Receiver Blocking Test

##### Receiver category 1

1. Adaptive equipment with maximum RF output power > 10dBm e.i.r.p. (EX: WiFi)

Wanted signal mean power from companion device (dBm)	Blocking signal frequency (MHz)	Blocking signal power (dBm) (see note 2)	Type of blocking signal
$P_{min} + 6$ dB	2 380 2 503,5	-53	CW
$P_{min} + 6$ dB	2 300 2 330 2 360	-47	CW
$P_{min} + 6$ dB	2 523,5 2 553,5 2 583,5 2 613,5 2 643,5 2 673,5	-47	CW
NOTE 1: $P_{min}$ is the minimum level of wanted signal (in dBm) required to meet the minimum performance criteria as defined in clause 4.3.1.12.3 in the absence of any blocking signal.			
NOTE 2: The levels specified are levels in front of the UUT antenna. In case of conducted measurements, the levels have to be corrected by the actual antenna assembly gain.			

##### Receiver category 2

1. Non-adaptive equipment with MU 1% ~ 10%
2. Adaptive equipment with Maximum RF output power < 10dBm e.i.r.p. (EX: Bluetooth)

Wanted signal mean power from companion device (dBm)	Blocking signal frequency (MHz)	Blocking signal power (dBm) (see note 2)	Type of blocking signal
$P_{min} + 6$ dB	2 380 2 503,5	-57	CW
$P_{min} + 6$ dB	2 300 2 583,5	-47	CW
NOTE 1: $P_{min}$ is the minimum level of the wanted signal (in dBm) required to meet the minimum performance criteria as defined in clause 4.3.1.12.3 in the absence of any blocking signal.			
NOTE 2: The levels specified are levels in front of the UUT antenna. In case of conducted measurements, the levels have to be corrected by the actual antenna assembly gain.			

**Receiver category 3**

1. Non-adaptive equipment with  $MU < 1\%$
2. Adaptive equipment with Maximum RF output power  $< 0\text{dBm e.i.r.p.}$

Wanted signal mean power from companion device (dBm)	Blocking signal frequency (MHz)	Blocking signal power (dBm) (see note 2)	Type of blocking signal
$P_{\min} + 12\text{ dB}$	2 380 2 503,5	-57	CW
$P_{\min} + 12\text{ dB}$	2 300 2 583,5	-47	CW

NOTE 1:  $P_{\min}$  is the minimum level of the wanted signal (in dBm) required to meet the minimum performance criteria as defined in clause 4.3.1.12.3 in the absence of any blocking signal.

NOTE 2: The levels specified are levels in front of the UUT antenna. In case of conducted measurements, the levels have to be corrected by the actual antenna assembly gain.


**2.1.2 Measuring Instruments**

The measuring equipment is listed in the section 3 of this test report.

**2.1.3 Test Procedures**

1. The measurement procedure follows the clause 5.4.11.2.1 of the ETSI EN 300 328 V2.1.1 (2016-11).
2. For systems using multiple receive chains only one chain (antenna port) need to be tested. All other receiver inputs shall be terminated.

**2.1.4 Test Setup**



**Test Set-up for receiver blocking**





### 2.1.5 Test Results of Receiver Blocking

Pmin = CMW500 burst power - path cable loss - attenuator.

Bluetooth 1Mbps hopping mode			
Wanted signal From companion	Blocking signal Frequency(MHz)	Blocking signal Power(dBm)	PER (%)
Pmin + 6dB	2380	-53	0.2
Pmin + 6dB	2503.5	-53	0
Pmin + 6dB	2300	-47	0
Pmin + 6dB	2330	-47	0.1
Pmin + 6dB	2360	-47	0.2
Pmin + 6dB	2523.5	-47	0
Pmin + 6dB	2553.5	-47	0.2
Pmin + 6dB	2583.5	-47	0
Pmin + 6dB	2613.5	-47	0
Pmin + 6dB	2643.5	-47	0
Pmin + 6dB	2673.5	-47	0
PER = 5.97 % when Pmin= -94 dBm before blocker is injected.			

Note:

1. Antenna gain is 3.2 dBi.
2. Blocking signal power level has been offset antenna gain.

Bluetooth BLE Channel 00			
Wanted signal From companion	Blocking signal Frequency(MHz)	Blocking signal Power(dBm)	PER (%)
Pmin + 6dB	2380	-53	0
Pmin + 6dB	2503.5	-53	0
Pmin + 6dB	2300	-47	0
Pmin + 6dB	2330	-47	0
Pmin + 6dB	2360	-47	0
Pmin + 6dB	2523.5	-47	0
Pmin + 6dB	2553.5	-47	0
Pmin + 6dB	2583.5	-47	0
Pmin + 6dB	2613.5	-47	0
Pmin + 6dB	2643.5	-47	0
Pmin + 6dB	2673.5	-47	0
PER = 3.26 % when Pmin= -94 dBm before blocker is injected.			

Note:

1. Antenna gain is 3.2 dBi.
2. Blocking signal power level has been offset antenna gain.



Bluetooth BLE Channel 39			
Wanted signal From companion	Blocking signal Frequency(MHz)	Blocking signal Power(dBm)	PER (%)
Pmin + 6dB	2380	-53	0
Pmin + 6dB	2503.5	-53	0
Pmin + 6dB	2300	-47	0
Pmin + 6dB	2330	-47	0
Pmin + 6dB	2360	-47	0
Pmin + 6dB	2523.5	-47	0
Pmin + 6dB	2553.5	-47	0
Pmin + 6dB	2583.5	-47	0
Pmin + 6dB	2613.5	-47	0
Pmin + 6dB	2643.5	-47	0
Pmin + 6dB	2673.5	-47	0
PER = 8 % when Pmin= -95 dBm before blocker is injected.			

Note:

1. Antenna gain is 3.2 dBi.
2. Blocking signal power level has been offset antenna gain.

WiFi 802.11b 1Mbps Channel 01			
Wanted signal From companion	Blocking signal Frequency(MHz)	Blocking signal Power(dBm)	PER (%)
Pmin + 6dB	2380	-53	0.2
Pmin + 6dB	2503.5	-53	0.2
Pmin + 6dB	2300	-47	0.1
Pmin + 6dB	2330	-47	0.1
Pmin + 6dB	2360	-47	0.2
Pmin + 6dB	2523.5	-47	0.1
Pmin + 6dB	2553.5	-47	0
Pmin + 6dB	2583.5	-47	0.1
Pmin + 6dB	2613.5	-47	0
Pmin + 6dB	2643.5	-47	0
Pmin + 6dB	2673.5	-47	0
PER = 1.6 % when Pmin= -96 dBm before blocker is injected.			

Note:

1. Antenna gain is 3.2 dBi.
2. Blocking signal power level has been offset antenna gain.



WiFi 802.11b 1Mbps Channel 13			
Wanted signal From companion	Blocking signal Frequency(MHz)	Blocking signal Power(dBm)	PER (%)
Pmin + 6dB	2380	-53	0.1
Pmin + 6dB	2503.5	-53	0.1
Pmin + 6dB	2300	-47	0
Pmin + 6dB	2330	-47	0.1
Pmin + 6dB	2360	-47	0.2
Pmin + 6dB	2523.5	-47	0.2
Pmin + 6dB	2553.5	-47	0
Pmin + 6dB	2583.5	-47	0
Pmin + 6dB	2613.5	-47	0
Pmin + 6dB	2643.5	-47	0
Pmin + 6dB	2673.5	-47	0
PER = 6.5 % when Pmin= -95 dBm before blocker is injected.			

Note:

1. Antenna gain is 3.2 dBi.
2. Blocking signal power level has been offset antenna gain.

WiFi 802.11g 6Mbps Channel 01			
Wanted signal From companion	Blocking signal Frequency(MHz)	Blocking signal Power(dBm)	PER (%)
Pmin + 6dB	2380	-53	0.5
Pmin + 6dB	2503.5	-53	0.9
Pmin + 6dB	2300	-47	0.7
Pmin + 6dB	2330	-47	0.6
Pmin + 6dB	2360	-47	0.6
Pmin + 6dB	2523.5	-47	0.3
Pmin + 6dB	2553.5	-47	0.7
Pmin + 6dB	2583.5	-47	1
Pmin + 6dB	2613.5	-47	0.5
Pmin + 6dB	2643.5	-47	0.7
Pmin + 6dB	2673.5	-47	0.9
PER = 5.9 % when Pmin= -90 dBm before blocker is injected.			

Note:

1. Antenna gain is 3.2 dBi.
2. Blocking signal power level has been offset antenna gain.



WiFi 802.11g 6Mbps Channel 13			
Wanted signal From companion	Blocking signal Frequency(MHz)	Blocking signal Power(dBm)	PER (%)
Pmin + 6dB	2380	-53	0.8
Pmin + 6dB	2503.5	-53	1.1
Pmin + 6dB	2300	-47	0.8
Pmin + 6dB	2330	-47	1.4
Pmin + 6dB	2360	-47	0.5
Pmin + 6dB	2523.5	-47	0.7
Pmin + 6dB	2553.5	-47	1.1
Pmin + 6dB	2583.5	-47	0.6
Pmin + 6dB	2613.5	-47	0
Pmin + 6dB	2643.5	-47	1.1
Pmin + 6dB	2673.5	-47	0.3
PER = 4.4 % when Pmin= -88 dBm before blocker is injected.			

**Note:**

- 1. Antenna gain is 3.2 dBi.
- 2. Blocking signal power level has been offset antenna gain.



### 3 List of Measuring Equipment

Instrument	Manufacturer	Model No.	Serial No.	Characteristics	Calibration Date	Test Date	Due Date	Remark
Spectrum Analyzer	Agilent	E4445A	MY41000161	3Hz~13.2GHz	Nov. 28, 2016	Jun. 12, 2017	Nov. 27, 2017	DFS (DFS02-HY)
Base Station	Rohde & Schwarz	CMW500	132247	GSM/GPRS/WC DMA/FD-LTE/TD -LTE/MIMO	Dec. 14, 2016	Jun. 12, 2017	Dec. 13, 2017	DFS (DFS02-HY)
Signal Generator	Rohde & Schwarz	SMF100A	101107	100kHz~40GHz	May 22, 2017	Jun. 12, 2017	May 21, 2018	DFS (DFS02-HY)

**Note:** Test equipment calibration is traceable to the procedure of ISO17025.



## 4 Uncertainty Evaluation

Test Item	Uncertainty
Temperature	$\pm 0.8$ °C
Humidity	$\pm 3$ %



## **Appendix A. Original Report**

Please refer to Sporton report number ER4O2349 and ER3N2752-01 as below.



# Variant CE Radio Test Report

**APPLICANT** : Texas Instruments Incorporated  
**EQUIPMENT** : WiFi and Bluetooth Module  
**BRAND NAME** : Texas Instruments  
**MODEL NAME** : WL18MODGB  
**STANDARD** : ETSI EN 300 328 V1.9.1 (2015-02)  
**TEST DATE(S)** : Aug. 08, 2015 ~ Sep. 23, 2015

This is a variant report which is only valid together with the original test report. The measurement shown in this test report is tested in accordance with the test procedures given in EN 300 328 V1.9.1 (2015-02).

The test results in this report apply exclusively to the tested model / sample. Without written approval of SPORTON INTERNATIONAL INC., the test report shall not be reproduced except in full.

Reviewed by: Joseph Lin / Supervisor

Approved by: Jones Tsai / Manager



## SPORTON INTERNATIONAL INC.

No. 52, Hwa Ya 1st Rd., Hwa Ya Technology Park, Kwei-Shan District, Tao Yuan City, Taiwan R.O.C.

SPORTON INTERNATIONAL INC.  
TEL : 886-3-327-3456  
FAX : 886-3-328-4978

Page Number : 1 of 79  
Report Issued Date : Oct. 15, 2015  
Report Version : Rev. 01

Report Template No.: BU5-ER328191 Version 1.0





## TABLE OF CONTENTS

<b>REVISION HISTORY</b> .....	<b>3</b>
<b>SUMMARY OF TEST RESULT</b> .....	<b>4</b>
<b>1 GENERAL DESCRIPTION</b> .....	<b>5</b>
1.1 Applicant .....	5
1.2 Manufacturer.....	5
1.3 Product Feature of Equipment Under Test.....	5
1.4 Product Specification subjective to this standard .....	6
1.5 Modification of EUT .....	7
1.6 Testing Facility.....	7
1.7 Applied Standards .....	8
1.8 Test Condition.....	8
<b>2 TEST CONFIGURATION OF EQUIPMENT UNDER TEST</b> .....	<b>9</b>
2.1 Descriptions of Test Mode.....	9
2.2 Connection Diagram of EUT Test Configurations .....	12
2.3 Supported Unit used in test configuration and system .....	12
2.4 EUT Operation Test Setup .....	12
<b>3 TRANSMITTER PARAMETERS</b> .....	<b>13</b>
3.1 Maximum Transmit Power.....	13
3.2 Maximum Equivalent Isotropically Radiated Power (E.I.R.P.) Spectral Density .....	14
3.3 Occupied Channel Bandwidth .....	16
3.4 Frequency Hopping Requirements.....	18
3.5 Transmitter unwanted emissions in the out-of-band domain .....	25
3.6 Transmitter spurious emissions.....	27
<b>4 RECEIVER PARAMETERS</b> .....	<b>51</b>
4.1 Receiver spurious emissions.....	51
<b>5 ADAPTIVITY TEST</b> .....	<b>59</b>
5.1 Adaptivity and Receiver Blocking .....	59
<b>6 GEO-LOCATION CAPABILITY</b> .....	<b>76</b>
<b>7 PHOTOGRAPHS OF RADIATED EMISSION TEST CONFIGURATION</b> .....	<b>77</b>
<b>8 LIST OF MEASURING EQUIPMENT</b> .....	<b>78</b>
<b>9 UNCERTAINTY EVALUATION</b> .....	<b>79</b>
<b>APPENDIX A. TEST RESULT OF CONDUCTED TEST ITEMS</b>	



### REVISION HISTORY

REPORT NO.	VERSION	DESCRIPTION	ISSUED DATE
ER4O2349	Rev. 01	This is a variant report by adding 6 new antennas. All the test cases were performed on original report which can be referred to Sporton Report Number ER3N2752-01. Based on the original report, all tests were verified.	Oct. 15, 2015



## SUMMARY OF TEST RESULT

CLAUSE (EN 300 328)	TEST PARAMETER	PASS/FAIL	REMARK
<b>Transmitter Parameters</b>			
4.3.1.2 4.3.2.2	Maximum Transmit Power	PASS	-
4.3.2.3	Maximum Equivalent Isotropically Radiated Power (E.I.R.P.) Spectral Density	PASS	Only applicable for modulations other than FHSS
4.3.1.8 4.3.2.7	Occupied Channel Bandwidth	PASS	-
4.3.1.4 4.3.1.5	Frequency Hopping Requirements	PASS	Only applicable for FHSS
4.3.1.9 4.3.2.8	Transmitter spurious emissions in OOB	PASS	-
4.3.1.10 4.3.2.9	Transmitter spurious emissions	PASS	Under limit 13.87 dB at 11906.250 MHz
<b>Receiver Parameters</b>			
4.3.1.11 4.3.2.10	Receiver spurious emissions	PASS	Under limit 7.39 dB at 11621.250 MHz
<b>Adaptive Test Item</b>			
4.3.1.7 4.3.2.6	Adaptivity	PASS	Only applicable for adaptive equipment Output Power >10dBm
4.3.1.12 4.3.2.11	Receiver Blocking	PASS	
<b>Non-Adaptive Test Item</b>			
4.3.1.3 4.3.2.4	Duty cycle, Tx-Sequence, Tx-gap	Not Required	Only applicable for non-adaptive equipment Output Power >10dBm
4.3.1.6 4.3.2.5	Medium Utilisation (MU) factor	Not Required	
<b>Note:</b>			
1. Bluetooth belongs to adaptive equipment and EIRP > 10dBm.			
2. WiFi belongs to adaptive equipment and EIRP > 10dBm.			



# 1 General Description

## 1.1 Applicant

**Texas Instruments Incorporated**  
12500 TI Boulevard, M/S 8751, Dallas, TX 75243, USA

## 1.2 Manufacturer

**Jorjin Technologies Inc**  
17F, No. 239, Sec. 1, Datong Rd., Xizhi Dist., New Taipei City 221, Taiwan

## 1.3 Product Feature of Equipment Under Test

Product Feature	
Equipment	WiFi and Bluetooth Module
Brand Name	Texas Instruments
Model Name	WL18MODGB
EUT supports Radios application	WLAN 11b/g/n HT20/HT40 Bluetooth v4.0 EDR/LE
EUT Stage	Identical Prototype

**Remark:** The above EUT's information was declared by manufacturer. Please refer to the specifications or user's manual for more detailed description.

## 1.4 Product Specification subjective to this standard

Product Specification subjective to this standard																							
<b>Transmitter / Receiver Frequency Range</b>	2400 MHz ~ 2483.5 MHz																						
<b>Number of Channels</b>	WLAN : 13 Bluetooth : 79 Bluetooth 4.0 – LE: 40																						
<b>Channel Spacing</b>	WLAN : 5 MHz Bluetooth : 1 MHz Bluetooth 4.0 – LE: 2 MHz																						
<b>Geo-location capability</b>	Not Supported																						
<b>Maximum EIRP Average Power</b>	<b>&lt;Ant. 1&gt;</b> 802.11b : 19.10 dBm 802.11g : 19.60 dBm 802.11n HT40 : 17.20 dBm Bluetooth BR (1Mbps) : 15.60 dBm Bluetooth 4.0 - LE (1Mbps) : 10.90 dBm <b>SISO &lt;Ant. 1&gt;</b> 802.11n HT20 : 18.80 dBm <b>MIMO &lt;Ant. 1+2&gt;</b> 802.11n HT20 : 19.80 dBm																						
<b>Type of Modulation</b>	Bluetooth (1Mbps) : GFSK Bluetooth (2Mbps) : $\pi/4$ -DQPSK Bluetooth (3Mbps) : 8-DPSK Bluetooth LE : GFSK 802.11b : DSSS (DBPSK / DQPSK / CCK) 802.11g/n: OFDM (BPSK / QPSK / 16QAM / 64QAM)																						
<b>Antenna Function for Transmitter</b>	<table border="1"> <thead> <tr> <th></th> <th>Ant. 1</th> <th>Ant. 2</th> </tr> </thead> <tbody> <tr> <td>Bluetooth</td> <td>V</td> <td>-</td> </tr> <tr> <td>802.11 b</td> <td>V</td> <td>-</td> </tr> <tr> <td>802.11 g</td> <td>V</td> <td>-</td> </tr> <tr> <td>802.11n HT20 SISO</td> <td>V</td> <td>-</td> </tr> <tr> <td>802.11n HT20 MIMO</td> <td>V</td> <td>V</td> </tr> <tr> <td>802.11n HT40</td> <td>V</td> <td>-</td> </tr> </tbody> </table>			Ant. 1	Ant. 2	Bluetooth	V	-	802.11 b	V	-	802.11 g	V	-	802.11n HT20 SISO	V	-	802.11n HT20 MIMO	V	V	802.11n HT40	V	-
	Ant. 1	Ant. 2																					
Bluetooth	V	-																					
802.11 b	V	-																					
802.11 g	V	-																					
802.11n HT20 SISO	V	-																					
802.11n HT20 MIMO	V	V																					
802.11n HT40	V	-																					
<b>Power Supply</b>	from DC power supply																						

**Note:** For other wireless features of this EUT, test report will be issued separately.

Antenna Information		
Antenna Type	Brand	2.4GHz~2.5GHz
PCB	Ethertronics	-0.6
Dipole	LSR	2
PCB	Laird	2
Chip	Pulse	3.2
PIFA	LSR	2
Chip	TDK	2.4

## 1.5 Modification of EUT

No modifications are made to the EUT during all test items.

## 1.6 Testing Facility

<b>Test Site</b>	SPORTON INTERNATIONAL INC.
<b>Test Site Location</b>	No. 52, Hwa Ya 1st Rd., Hwa Ya Technology Park, Kwei-Shan District, Tao Yuan City, Taiwan R.O.C. TEL: +886-3-327-3456 FAX: +886-3-328-4978
<b>Test Site No.</b>	<b>Sporton Site No. :</b> TH05-HY; DFS02-HY

<b>Test Site</b>	SPORTON INTERNATIONAL INC.
<b>Test Site Location</b>	No.58, Aly. 75, Ln. 564, Wenhua 3rd Rd. Guishan Dist, Taoyuan City, Taiwan (R.O.C.) TEL: +886-3-327-0868 FAX: +886-3-327-0855
<b>Test Site No.</b>	<b>Sporton Site No. :</b> 05CH05-HY



## 1.7 Applied Standards

According to the specifications of the manufacturer, the EUT must comply with the requirements of **ETSI EN 300 328 V1.9.1 (2015-02)**.

**Note:** All test items were verified and recorded according to the standards and without any deviation during the test.

## 1.8 Test Condition

<b>Normal Voltage</b>	DC 5V
<b>Normal Temperature</b>	20°C
<b>Extreme Temperature</b>	-20°C and 70°C

**Note:** The test temperature was between -20°C ~ 70°C by manufacturer requested.

## 2 Test Configuration of Equipment under Test

### 2.1 Descriptions of Test Mode

- a. Preliminary tests were performed in different data rate and recorded the RF power output in the following tables:

<Ant. 1>

Average Bluetooth RF Output Power (dBm)			
Data rate	1Mbps	2Mbps	3Mbps
Avg. Power	11.70	7.40	7.40

Note: Data rate Bluetooth 1Mbps was chosen to be tested due to the highest RF output power.

<Ant. 1>

Average Bluetooth 4.0 - LE RF Output Power (dBm)			
Data Rate	CH 00	CH 19	CH 39
Frequency	2402 MHz	2440 MHz	2480 MHz
Avg. Power	6.70	6.40	5.80

2.4GHz 802.11b RF Output Power (dBm)			
Channel	CH 01	CH 07	CH 13
Frequency	2412 MHz	2442 MHz	2472 MHz
Avg. Power	15.90	15.80	15.70

2.4GHz 802.11g RF Output Power (dBm)			
Channel	CH 01	CH 07	CH 13
Frequency	2412 MHz	2442 MHz	2472 MHz
Avg. Power	11.90	16.40	16.20

2.4GHz 802.11n HT40 RF Output Power (dBm)			
Channel	CH 03	CH 07	CH 11
Frequency	2422 MHz	2442 MHz	2462 MHz
Avg. Power	9.60	14.00	13.80





SISO <Ant. 1>

2.4GHz 802.11n HT20 RF Output Power (dBm)			
Channel	CH 01	CH 07	CH 13
Frequency	2412 MHz	2442 MHz	2472 MHz
Avg. Power	12.00	15.60	15.30

MIMO <Ant. 1+2>

2.4GHz 802.11n HT20 RF Output Power (dBm)			
Channel	CH 01	CH 07	CH 13
Frequency	2412 MHz	2442 MHz	2472 MHz
Avg. Power	15.60	16.50	16.40

**Note:** The data rates of WLAN 802.11b/g/n were set in 1Mbps for 802.11b, 6Mbps for 802.11g, and MCS0 for HT40 for <Ant. 1>; MCS0 for 802.11n HT20 for SISO <Ant. 1>; MCS12 for 802.11n HT20 for MIMO < Ant. 1+2> due to the highest RF output power.

- b. During radiated spurious emissions testing, the interface cables and equipment positions were varied according to European Standard EN 300 328 V1.9.1 (2015-02), and the frequency range of radiation was investigated from 25 MHz to 12750 MHz.



The following tables for radiated measurement, pre-scanned in three orthogonal panels, X, Y, Z. The worst cases were recorded in this report.


Test Modes		
RF	802.11b DSSS	802.11g OFDM
Tx	802.11b CH01 (2412MHz) for Ant. 1 <b>802.11b CH13 (2472MHz) for Ant. 1</b>	<b>802.11g CH01 (2412MHz) for Ant. 1</b> 802.11g CH13 (2472MHz) for Ant. 1
Rx	802.11b CH13 (2472MHz) for Ant. 1	802.11g CH01 (2412MHz) for Ant. 1

Test Modes		
RF	802.11n HT20 OFDM	802.11n HT40 OFDM
Tx	802.11n HT20 CH13 (2472MHz) for SISO Ant. 1 802.11n HT20 CH01 (2412MHz) for MIMO Ant. 1+2 <b>802.11n HT20 CH13 (2472MHz) for MIMO Ant. 1+2</b>	802.11n HT40 CH03 (2422MHz) for Ant. 1 <b>802.11n HT40 CH11 (2462MHz) for Ant. 1</b>

Test Modes		
RF	Bluetooth (1Mbps) GFSK	Bluetooth 4.0 - LE GFSK
Tx	Bluetooth (1Mbps) CH00 (2402MHz) for Ant. 1 <b>Bluetooth (1Mbps) CH78 (2480MHz) for Ant. 1</b>	Bluetooth 4.0 - LE CH00 (2402MHz) for Ant. 1 <b>Bluetooth 4.0 - LE CH39 (2480MHz) for Ant. 1</b>
Rx	<b>Bluetooth (1Mbps) CH78 (2480MHz) for Ant. 1</b>	Bluetooth 4.0 - LE CH39 (2480MHz) for Ant. 1

**Remark:** All test modes of the Transmitter Radiated Spurious Emission (RSE) and Receiver Radiated Spurious Emission (RSE) were tested; only the test worse data in bold of these modes were reported.

## 2.2 Connection Diagram of EUT Test Configurations



## 2.3 Supported Unit used in test configuration and system

Item	Equipment	Trade Name	Model Name	FCC ID	Data Cable	Power Cord
1.	Notebook	Lenovo	TP00034A	FCC DoC/ Contains FCC ID:QDS-BRCM1058	N/A	AC I/P: Unshielded, 1.2 m DC O/P: Shielded, 1.8 m
2.	Fixture	N/A	N/A	N/A	N/A	N/A
3.	Evaluation board	N/A	WG1300BE00	N/A	N/A	N/A

## 2.4 EUT Operation Test Setup

For Bluetooth and Bluetooth 4.0 – LE function, programmed RF utility, “HCIttest” installed in the notebook make the EUT provide functions like channel selection and power level for continuous transmitting and receiving signals.

For WLAN function, programmed RF utility, “RTTT” installed in the notebook make the EUT provide functions like channel selection and power level for continuous transmitting and receiving signals.

### 3 Transmitter Parameters

#### 3.1 Maximum Transmit Power

##### 3.1.1 Limit of Effective Isotropic Radiated Power

SUBCLAUSE 4.3.1.2.3 and 4.3.2.2.3	
TEST CONDITION	LIMIT
Normal and Extreme Temperature Conditions	20dBm (e.i.r.p)


##### 3.1.2 Measuring Instruments

The measuring equipment is listed in the section 8 of this test report.

##### 3.1.3 Test Procedure

1. The measurement procedure follows the clause 5.3.2.2.1 of the ETSI EN 300 328 V1.9.1 (2015-02).
2. Placing the EUT in thermal chamber.
3. The EUT is connected to external power supply.
4. Setting thermal chamber temperature and power supply voltage at suitable values.
5. The EIRP = A+G+Y, where A is the power measured, G is the assembly gain of the individual antenna of the EUT in dBi and Y is the additional beamforming gain of the EUT in dB if applicable, here, Y=0.
6. The measurement duration is at least 1 second to ensure a minimum number of bursts (at least 10) are captured.

##### 3.1.4 Test Setup



##### 3.1.5 Test Results

Refer to Appendix A of this test report.

## 3.2 Maximum Equivalent Isotropically Radiated Power (E.I.R.P.) Spectral Density

### 3.2.1 Limit of Maximum Power Spectral Density

SUBCLAUSE 4.3.2.3.3	
TEST CONDITION	LIMIT
Normal and Extreme Temperature Conditions	10dBm / MHz

**Remark:** Maximum spectral power density is not applicable to FHSS system device.

### 3.2.2 Measuring Instruments

The measuring equipment is listed in the section 8 of this test report.

### 3.2.3 Test Procedure

1. The measurement procedure follows the clause 5.3.3.2.1 of the ETSI EN 300 328 V1.9.1 (2015-02).
2. These measurements shall only be performed at normal test conditions.
3. The measurement shall be repeated for the equipment being configured to operate at the lowest, the middle, and the highest frequency of the stated frequency range.
4. The test procedure shall be as follows:

**Step 1:**

Connect the EUT to the spectrum analyzer and use the following settings:

Start Frequency	2400MHz
Stop Frequency	2483.5MHz
Resolution BW	10kHz
Video BW	30kHz
Sweep Points	8350
Detector	RMS
Trace Mode	Max Hold
Sweep time	10 sec

**Step 2:**

Add up the values for amplitude (power) for all the samples in the file.

**Step 3:**

Normalize the individual values for amplitude so that the sum is equal to the RF Output Power (e.i.r.p.) measured.

**Step 4:**

Starting from the first sample in the file (lowest frequency), add up the power of the following samples representing a 1 MHz segment and record the results for power and position (i.e. sample #1 to #100). This is the Power Spectral Density (e.i.r.p.) for the first 1 MHz segment which shall be recorded.

**Step 5:**


Shift the start point of the samples added up in step 4 by 1 sample and repeat the procedure in step 4 (i.e. sample #2 to #101).

**Step 6:**

Repeat step 5 until the end of the data set and record the radiated Power Spectral Density values for each of the 1 MHz segments.

From all the recorded results, the highest value is the maximum Power Spectral Density for the EUT. This value shall be recorded in the test report.

### 3.2.4 Test Setup



### 3.2.5 Test Results

Refer to Appendix A of this test report.

### 3.3 Occupied Channel Bandwidth

#### 3.3.1 Limit of Occupied Channel Bandwidth

Occupied Channel Bandwidth fall completely within 2.4 GHz – 2.4835 GHz

#### 3.3.2 Measuring Instruments

The measuring equipment is listed in the section 8 of this test report.

#### 3.3.3 Test Procedure

1. The measurement procedure follows the clause 5.3.8.2.1 of the ETSI EN 300 328 V1.9.1 (2015-02).
2. The measurement shall be performed only on the lowest and the highest frequency within the stated frequency range.
3. The test procedure shall be as follows:

**Step 1:**

Connect the EUT to the spectrum analyzer and use the following settings:

Center Frequency	Channel under test
Resolution BW	1 % of the span
Video BW	3 × RBW
Frequency Span	Frequency hopping equipment: Lowest frequency separation that is used within the hopping sequence. Other equipment: 2 × Occupied Channel Bandwidth (e.g. 40 MHz for a 20 MHz channel)
Detector	RMS
Trace Mode	Max Hold
Sweep Time	1 s

**Step 2:**

Wait until the trace is completed.

Find the peak value of the trace and place the analyzer marker on this peak.

**Step 3:**

Use the 99 % bandwidth function of the spectrum analyzer to measure the Occupied Channel Bandwidth of the EUT.

### 3.3.4 Test Setup



### 3.3.5 Test Results

Refer to Appendix A of this test report.



### 3.4 Frequency Hopping Requirements

#### 3.4.1 Dwell Time and Minimum Frequency Occupation Time

##### 3.4.1.1 Limit of Dwell Time

SUBCLAUSE 4.3.1.4.3	
TEST CONDITION	LIMIT
Non-Adaptive Frequency Hopping Systems	15 ms within 15ms * hopping frequencies (N)
Adaptive Frequency Hopping Systems	0.4s within 0.4s * hopping frequencies (N)

##### Limit of Minimum Frequency Occupation Time

SUBCLAUSE 4.3.1.4.3	
TEST CONDITION	LIMIT
Normal Condition	Option1: The Minimum Frequency Occupation Time shall be equal to one dwell time within a period not exceeding four times the product of the dwell time per hop and the number of hopping frequencies in use.

**Remark:** This test item is not applicable to DSSS/OFDM device.

##### 3.4.1.2 Measuring Instruments

The measuring equipment is listed in the section 8 of this test report.


**3.4.1.3 Test Procedures**

1. The measurement shall be performed on a minimum of 2 hopping frequencies chosen arbitrary from the actual hopping sequence. The results as well as the frequencies on which the test was performed shall be recorded in the test report.
2. The measurement procedure follows the clause 5.3.4.2.1 of the ETSI EN 300 328 V1.9.1 (2015-02).
3. The analyzer shall be set as follows:

Center Frequency	Channel under test
Frequency Span	0 Hz
Resolution BW	300kHz
Video BW	300kHz
Detector	RMS
Sweep time	Equal to the Dwell Time × Minimum number of hopping frequencies (N)
Number of sweep points	30000
Trace Mode	Clear / Write
Trigger	Free Run

4. For accuracy measurement, the sweep time would be zoomed in and verify the dwell time which is from the dwell time per hop across the total number of hopping channel. Then record test result.
5. Make the following changes on the analyzer to get Minimum Frequency Occupation Time  
Sweep time: Equal to 4 × Dwell Time × Actual number of hopping frequencies in use

**3.4.1.4 Test Setup**




**3.4.1.5 Test Results**

Refer to Appendix A of this test report.




3.4.1.6 Test Plots






Dwell Time - Channel 78 DH1




Date: 12.AUG.2015 05:15:10

Frequency Occupation Time - Channel 78 DH1




Date: 12.AUG.2015 05:15:16

Dwell Time - Channel 78 DH3




Date: 12.AUG.2015 05:17:32

Frequency Occupation Time - Channel 78 DH3




Date: 12.AUG.2015 05:17:39

Dwell Time - Channel 78 DH5



Date: 12.AUG.2015 05:25:20

Frequency Occupation Time - Channel 78 DH5



Date: 12.AUG.2015 05:25:27

### 3.4.2 Hopping Sequence

#### 3.4.2.1 Limit of Hopping Sequence

SUBCLAUSE 4.3.1.4.3	
TEST CONDITION	LIMIT
Non-Adaptive Frequency Hopping Systems	N
Adaptive Frequency Hopping Systems	N Ch 70% of band

N= 15 or 15 divided by the minimum Hopping Frequency Separation in MHz, whichever is the greater.

**Remark:** Hopping Sequence is not applicable to DSSS/OFDM device.


#### 3.4.2.2 Measuring Instruments

The measuring equipment is listed in the section 8 of this test report.

#### 3.4.2.3 Test Procedures

The measurement procedure follows the clause 5.3.4.2.1 of the ETSI EN 300 328 V1.9.1 (2015-02).

#### 3.4.2.4 Test Setup




#### 3.4.2.5 Test Results

Refer to Appendix A of this test report.




3.4.2.6 Test Plots

Total Number of Hopping Channel Plot on Channel 00 - 78



Date: 12.AUG.2015 03:52:04



Date: 12.AUG.2015 04:58:53

### 3.4.3 Hopping Frequency Separation

#### 3.4.3.1 Limit of Hopping Frequency Separation

SUBCLAUSE 4.3.1.5.3.	
TEST CONDITION	LIMIT
Non-Adaptive Frequency Hopping Systems	MAX [ OBW, 100kHz ]
Adaptive Frequency Hopping Systems	100kHz

**Remark:** Hopping Frequency Separation is not applicable to DSSS/OFDM device.


#### 3.4.3.2 Measuring Instruments

The measuring equipment is listed in the section 8 of this test report.

#### 3.4.3.3 Test Procedures

1. These measurements shall only be performed at normal test conditions.
2. The measurement shall be performed on 2 adjacent hopping frequencies.
3. The frequencies on which the test was performed shall be recorded.
4. The measurement procedure follows the clause 5.3.5.2.1.2 Option 2 of the ETSI EN 300 328 V1.9.1 (2015-02).

#### 3.4.3.4 Test Setup




#### 3.4.3.5 Test Results

Refer to Appendix A of this test report.

### 3.5 Transmitter unwanted emissions in the out-of-band domain

#### 3.5.1 Transmitter unwanted emissions in the out-of-band domain limit




#### 3.5.2 Measuring Instruments

The measuring equipment is listed in the section 8 of this test report.

#### 3.5.3 Test Procedures

1. The measurement procedure follows the clause 5.3.9.2.1 of the ETSI EN 300 328 V1.9.1 (2015-02).
2. These measurements shall only be performed at normal test conditions.
3. For conducted measurements on devices with multiple transmit chains using the results for each of the transmit chains for the corresponding 1 MHz segments shall be added and compared with the transmit mask limit.



#### 3.5.4 Test Setup



#### 3.5.5 Test Results

Refer to Appendix A of this test report.





## 3.6 Transmitter spurious emissions

### 3.6.1 Limit of Transmitter spurious emissions

Spurious emission limits for transmitter:

SUBCLAUSE 4.3.1.10.3 and 4.3.2.9.3		
FREQUENCY RANGE	MAXIMUM POWER E.R.P.	BANDWIDTH
30 MHz to 47 MHz	-36 dBm	100 kHz
47 MHz to 74 MHz	-54 dBm	100 kHz
74 MHz to 87,5 MHz	-36 dBm	100 kHz
87,5 MHz to 118 MHz	-54 dBm	100 kHz
118 MHz to 174 MHz	-36 dBm	100 kHz
174 MHz to 230 MHz	-54 dBm	100 kHz
230 MHz to 470 MHz	-36 dBm	100 kHz
470 MHz to 862 MHz	-54 dBm	100 kHz
862 MHz to 1 GHz	-36 dBm	100 kHz
1 GHz to 12,75 GHz	-30 dBm	1 MHz

### 3.6.2 Measuring Instruments

The measuring equipment is listed in the section 8 of this test report.

### 3.6.3 Test Procedures

1. The measurement procedure follows the clause 5.3.10.2.2 of the ETSI EN 300 328 V1.9.1 (2015-02).
2. The EUT was placed on a turntable with 1.5m height.
3. The test distance between the receiving antenna and the EUT is 3meter below 1GHz frequency range, and 3 meter which is in far field test condition for measured frequency above 1GHz, while the receiving (test) antenna is kept at 1.5 meter height.
4. Set EUT in continuous transmitting with maximum output power.
5. The table was rotated from 0 to 360 degree to search the highest radiated emission.
6. Repeating step 3 and 4 for each polarization and channel to find the worst emission level.
7. The results obtained are compared to the limits in order to prove compliance with the requirement.


### 3.6.4 Test Setup

Conducted Setup:




Radiated Test Setup:

<Below 1GHz>



<Above 1GHz>






### 3.6.5 Test Results for Conducted Setup

Number of TX = 1, Ant. 1 (Measured)

Test Mode :	802.11b CH01 (2412MHz) for Ant. 1	Temperature :	22~24°C
Test Engineer :	Kenny Chen	Relative Humidity :	52~54%




Site : TH05-HY  
Condition : 300328-TX

	Freq	Level	Over Limit	Limit Line	Read Level	Cable Loss	Aux Factor	Aux2 Factor
	MHz	dBm	dB	dBm	dBm	dB	dB	dB
1	7240.08	-52.93	-22.93	-30.00	-54.98	2.05	0.00	0.00



Test Mode :	802.11g CH13 (2472MHz) for Ant. 1	Temperature :	22~24°C
Test Engineer :	Kenny Chen	Relative Humidity :	52~54%




Site : TH05-HY  
 Condition : 300328-TX

	Freq	Level	Over Limit	Limit Line	Read Level	Cable Loss	Aux Factor	Aux2 Factor
	MHz	dBm	dB	dBm	dBm	dB	dB	dB
1	7418.23	-57.56	-27.56	-30.00	-59.46	1.90	0.00	0.00



<b>Test Mode :</b>	802.11n HT20 CH13 (2472MHz) for SISO <Ant. 1>	<b>Temperature :</b>	22~24°C
<b>Test Engineer :</b>	Kenny Chen	<b>Relative Humidity :</b>	52~54%




Site : TH05-HY  
 Condition : 300328-TX

	Freq	Level	Over Limit	Limit Line	Read Level	Cable Loss	Aux Factor	Aux2 Factor
	MHz	dBm	dB	dBm	dBm	dB	dB	dB
1	7430.95	-60.08	-30.08	-30.00	-61.96	1.88	0.00	0.00



<b>Test Mode :</b>	802.11n HT40 CH11 (2462MHz) for Ant. 1	<b>Temperature :</b>	22~24°C
<b>Test Engineer :</b>	Kenny Chen	<b>Relative Humidity :</b>	52~54%




Site : TH05-HY  
 Condition : 300328-TX

	Freq	Level	Over Limit	Limit Line	Read Level	Cable Loss	Aux Factor	Aux2 Factor
	MHz	dBm	dB	dBm	dBm	dB	dB	dB
1	7405.50	-64.41	-34.41	-30.00	-66.31	1.90	0.00	0.00



<b>Test Mode :</b>	Bluetooth (1Mbps) CH00 (2402MHz) for Ant. 1	<b>Temperature :</b>	22~24°C
<b>Test Engineer :</b>	Kenny Chen	<b>Relative Humidity :</b>	52~54%




Site : TH05-HY  
 Condition : 300328-TX ANT GAIN+3.2 2.46 HORIZONTAL

	Freq	Level	Over Limit	Limit Line	Read Level	Cable Loss	Aux Factor	Aux2 Factor
	MHz	dBm	dB	dBm	dBm	dB	dB	dB
1	4809.60	-35.76	-5.76	-30.00	-40.63	1.67	0.00	0.00





<b>Test Mode :</b>	Bluetooth 4.0 - LE CH00 (2402MHz) for Ant. 1	<b>Temperature :</b>	22~24°C
<b>Test Engineer :</b>	Kenny Chen	<b>Relative Humidity :</b>	52~54%




Site : TH05-HY  
 Condition : 300328-TX

	Freq	Level	Over Limit	Limit Line	Read Level	Cable Loss	Aux Factor	Aux2 Factor
	MHz	dBm	dB	dBm	dBm	dB	dB	dB
1	4796.88	-52.02	-22.02	-30.00	-53.69	1.67	0.00	0.00



Number of TX = 2, Ant. 1 (Measured)

Test Mode :	802.11n HT20 CH01 (2412MHz) for MIMO <Ant. 1+2(1)>	Temperature :	22~24°C
Test Engineer :	Kenny Chen	Relative Humidity :	52~54%




Site : TH05-HY  
 Condition : 300328-TX ANT GAIN+3.2 2.4G HORIZONTAL

	Freq	Level	Over Limit	Limit Line	Read Level	Cable Loss	Aux Factor	Aux2 Factor
	MHz	dBm	dB	dBm	dBm	dB	dB	dB
1	7621.83	-55.66	-25.66	-30.00	-57.54	1.88	0.00	0.00



<b>Test Mode :</b>	802.11n HT20 CH13 (2472MHz) for MIMO <Ant. 1+2(1)>	<b>Temperature :</b>	22~24°C
<b>Test Engineer :</b>	Kenny Chen	<b>Relative Humidity :</b>	52~54%




Site : TH05-HY  
 Condition : 300328-TX ANT GAIN+3.2 2.4G HORIZONTAL

	Freq	Level	Over Limit	Limit Line	Read Level	Cable Loss	Aux Factor	Aux2 Factor
	MHz	dBm	dB	dBm	dBm	dB	dB	dB
1	7430.95	-55.42	-25.42	-30.00	-57.30	1.88	0.00	0.00



Number of TX = 2, Ant. 2 (Measured)

Test Mode :	802.11n HT20 CH01 (2412MHz) for MIMO <Ant. 1+2(2)>	Temperature :	22~24°C
Test Engineer :	Kenny Chen	Relative Humidity :	52~54%




Site : TH05-HY  
 Condition : 300328-TX ANT GAIN+3.2 2.4G HORIZONTAL

	Freq	Level	Over Limit	Limit Line	Read Level	Cable Loss	Aux Factor	Aux2 Factor
	MHz	dBm	dB	dBm	dBm	dB	dB	dB
1	7169.10	-53.94	-23.94	-30.00	-56.04	2.10	0.00	0.00



<b>Test Mode :</b>	802.11n HT20 CH13 (2472MHz) for MIMO <Ant. 1+2(2)>	<b>Temperature :</b>	22~24°C
<b>Test Engineer :</b>	Kenny Chen	<b>Relative Humidity :</b>	52~54%




Site : TH05-HY  
 Condition : 300328-TX ANT GAIN+3.2 2.4G HORIZONTAL

	Freq	Level	Over Limit	Limit Line	Read Level	Cable Loss	Aux Factor	Aux2 Factor
	MHz	dBm	dB	dBm	dBm	dB	dB	dB
1	4911.40	-56.33	-26.33	-30.00	-58.03	1.70	0.00	0.00




3.6.6 Test Results for Radiated Setup (Cabinet Radiation)





Test Mode :	802.11b CH13 (2472MHz) for Ant. 1	Temperature :	23~24°C
Test Engineer :	Elvis Chen	Relative Humidity :	43~44%
		Polarization :	Vertical




Site : 05CH05-HY  
 Condition : 300328-TX VERTICAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over Limit	Limit Line	Read Level	Factor	Pol/Phase
	MHz	dBm	dB	dBm	dBm	dB	
1	221.35	-84.10	-30.10	-54.00	-59.09	-25.01	VERTICAL
2	722.10	-68.95	-14.95	-54.00	-59.28	-9.67	VERTICAL
3	2206.00	-59.55	-29.55	-30.00	-64.96	5.41	VERTICAL
4	2914.00	-56.72	-26.72	-30.00	-64.67	7.95	VERTICAL
5	4944.00	-49.59	-19.59	-30.00	-62.14	12.55	VERTICAL
6	8745.00	-49.14	-19.14	-30.00	-70.95	21.81	VERTICAL
7 @	11418.75	-44.58	-14.58	-30.00	-71.10	26.52	VERTICAL



<b>Test Mode :</b>	802.11g CH01 (2412MHz) for Ant. 1	<b>Temperature :</b>	23~24°C
<b>Test Engineer :</b>	Elvis Chen	<b>Relative Humidity :</b>	43~44%
		<b>Polarization :</b>	Horizontal




Site : 05CH05-HY  
 Condition : 300328-TX HORIZONTAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over	Limit	Read		
	MHz	dBm	Limit	Line	Level	Factor	Pol/Phase
			dB	dBm	dBm	dB	
1	144.35	-66.62	-30.62	-36.00	-44.05	-22.57	HORIZONTAL
2	769.70	-75.23	-21.23	-54.00	-66.98	-8.25	HORIZONTAL
3	2266.00	-58.88	-28.88	-30.00	-64.50	5.62	HORIZONTAL
4	2664.00	-56.22	-26.22	-30.00	-63.67	7.45	HORIZONTAL
5	5880.00	-55.93	-25.93	-30.00	-71.42	15.49	HORIZONTAL
6	8739.00	-47.92	-17.92	-30.00	-69.80	21.88	HORIZONTAL
7 @	12131.25	-43.92	-13.92	-30.00	-71.18	27.26	HORIZONTAL





Test Mode :	802.11g CH01 (2412MHz) for Ant. 1	Temperature :	23~24°C
Test Engineer :	Elvis Chen	Relative Humidity :	43~44%
		Polarization :	Vertical




Site : 05CH05-HY  
 Condition : 300328-TX VERTICAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over Limit	Limit Line	Read Level	Factor	Pol/Phase
	MHz	dBm	dB	dBm	dBm	dB	
1	221.35	-83.45	-29.45	-54.00	-58.44	-25.01	VERTICAL
2	831.30	-75.42	-21.42	-54.00	-68.32	-7.10	VERTICAL
3	2206.00	-59.78	-29.78	-30.00	-65.19	5.41	VERTICAL
4	2658.00	-50.50	-20.50	-30.00	-57.69	7.19	VERTICAL
5	3996.00	-55.66	-25.66	-30.00	-66.71	11.05	VERTICAL
6	8958.00	-47.82	-17.82	-30.00	-70.29	22.47	VERTICAL
7 @	11463.75	-45.17	-15.17	-30.00	-71.78	26.61	VERTICAL



Test Mode :	802.11n HT20 CH13 (2472MHz) for MIMO Ant. 1+2	Temperature :	23~24°C
Test Engineer :	Elvis Chen	Relative Humidity :	43~44%
		Polarization :	Horizontal




Site : 05CH05-HY  
 Condition : 300328-TX HORIZONTAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over	Limit	Read		
	MHz	dBm	Limit	Line	Level	Factor	Pol/Phase
			dB	dBm	dBm	dB	
1	221.35	-68.74	-14.74	-54.00	-43.59	-25.15	HORIZONTAL
2	769.70	-73.93	-19.93	-54.00	-65.68	-8.25	HORIZONTAL
3	2332.00	-59.40	-29.40	-30.00	-65.27	5.87	HORIZONTAL
4	2662.00	-56.01	-26.01	-30.00	-63.46	7.45	HORIZONTAL
5	5517.00	-56.66	-26.66	-30.00	-71.34	14.68	HORIZONTAL
6	8931.00	-48.65	-18.65	-30.00	-71.20	22.55	HORIZONTAL
7 @	12060.00	-44.27	-14.27	-30.00	-71.67	27.40	HORIZONTAL



<b>Test Mode :</b>	802.11n HT20 CH13 (2472MHz) for MIMO Ant. 1+2	<b>Temperature :</b>	23~24°C
<b>Test Engineer :</b>	Elvis Chen	<b>Relative Humidity :</b>	43~44%
		<b>Polarization :</b>	Vertical




Site : 05CH05-HY  
 Condition : 300328-TX VERTICAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over Limit	Limit Line	Read Level	Factor	Pol/Phase
	MHz	dBm	dB	dBm	dBm	dB	
1	221.35	-84.28	-30.28	-54.00	-59.27	-25.01	VERTICAL
2	832.00	-77.91	-23.91	-54.00	-70.86	-7.05	VERTICAL
3	2238.00	-59.30	-29.30	-30.00	-64.85	5.55	VERTICAL
4	2632.00	-58.95	-28.95	-30.00	-65.93	6.98	VERTICAL
5	4998.00	-55.09	-25.09	-30.00	-67.74	12.65	VERTICAL
6	8433.00	-49.20	-19.20	-30.00	-70.02	20.82	VERTICAL
7 @	12097.50	-44.32	-14.32	-30.00	-71.38	27.06	VERTICAL



<b>Test Mode :</b>	802.11n HT40 CH11 (2462MHz) for Ant. 1	<b>Temperature :</b>	23~24°C
<b>Test Engineer :</b>	Elvis Chen	<b>Relative Humidity :</b>	43~44%
		<b>Polarization :</b>	Horizontal




Site : 05CH05-HY  
 Condition : 300328-TX HORIZONTAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over Limit	Limit Line	Read Level	Factor	Pol/Phase
	MHz	dBm	dB	dBm	dBm	dB	
1 @	221.35	-68.16	-14.16	-54.00	-43.01	-25.15	HORIZONTAL
2	866.30	-76.12	-40.12	-36.00	-69.33	-6.79	HORIZONTAL
3	2316.00	-58.91	-28.91	-30.00	-64.73	5.82	HORIZONTAL
4	2658.00	-55.38	-25.38	-30.00	-62.83	7.45	HORIZONTAL
5	5868.00	-55.89	-25.89	-30.00	-71.40	15.51	HORIZONTAL
6	8532.00	-49.45	-19.45	-30.00	-70.65	21.20	HORIZONTAL
7	12018.75	-44.26	-14.26	-30.00	-71.76	27.50	HORIZONTAL



<b>Test Mode :</b>	802.11n HT40 CH11 (2462MHz) for Ant. 1	<b>Temperature :</b>	23~24°C
<b>Test Engineer :</b>	Elvis Chen	<b>Relative Humidity :</b>	43~44%
		<b>Polarization :</b>	Vertical




Site : 05CH05-HY  
 Condition : 300328-TX VERTICAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over Limit	Limit Line	Read Level	Factor	Pol/Phase
	MHz	dBm	dB	dBm	dBm	dB	
1	221.35	-83.47	-29.47	-54.00	-58.46	-25.01	VERTICAL
2	828.50	-78.45	-24.45	-54.00	-71.22	-7.23	VERTICAL
3	2286.00	-60.99	-30.99	-30.00	-66.74	5.75	VERTICAL
4	2646.00	-57.32	-27.32	-30.00	-64.41	7.09	VERTICAL
5	3990.00	-53.12	-23.12	-30.00	-64.17	11.05	VERTICAL
6	8727.00	-49.57	-19.57	-30.00	-71.32	21.75	VERTICAL
7 @	11940.00	-44.50	-14.50	-30.00	-71.69	27.19	VERTICAL



Test Mode :	Bluetooth (1Mbps) CH78 (2480MHz) for Ant. 1	Temperature :	23~24°C
Test Engineer :	Elvis Chen	Relative Humidity :	43~44%
		Polarization :	Horizontal




Site : 05CH05-HY  
 Condition : 300328-TX HORIZONTAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over Limit	Limit	Read	Factor	Pol/Phase
	MHz	dBm	dB	dBm	dBm	dB	
1	224.93	-74.77	-20.77	-54.00	-49.77	-25.00	HORIZONTAL
2	828.50	-85.79	-31.79	-54.00	-78.52	-7.27	HORIZONTAL
3	1998.00	-56.60	-26.60	-30.00	-61.25	4.65	HORIZONTAL
4	2666.00	-56.75	-26.75	-30.00	-64.20	7.45	HORIZONTAL
5	4959.00	-52.02	-22.02	-30.00	-64.40	12.38	HORIZONTAL
6	8736.00	-49.40	-19.40	-30.00	-71.27	21.87	HORIZONTAL
7 @	11906.25	-43.87	-13.87	-30.00	-71.33	27.46	HORIZONTAL



Test Mode :	Bluetooth (1Mbps) CH78 (2480MHz) for Ant. 1	Temperature :	23~24°C
Test Engineer :	Elvis Chen	Relative Humidity :	43~44%
		Polarization :	Vertical




Site : 05CH05-HY  
 Condition : 300328-TX VERTICAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over Limit	Limit Line	Read Level	Factor	Pol/Phase
	MHz	dBm	dB	dBm	dBm	dB	
1	224.93	-90.55	-36.55	-54.00	-65.66	-24.89	VERTICAL
2	823.60	-84.48	-30.48	-54.00	-77.02	-7.46	VERTICAL
3	1996.00	-51.32	-21.32	-30.00	-55.91	4.59	VERTICAL
4	2662.00	-50.89	-20.89	-30.00	-58.08	7.19	VERTICAL
5	4959.00	-49.99	-19.99	-30.00	-62.58	12.59	VERTICAL
6	7440.00	-48.52	-18.52	-30.00	-68.72	20.20	VERTICAL
7 @	12105.00	-44.35	-14.35	-30.00	-71.41	27.06	VERTICAL



Test Mode :	Bluetooth 4.0 - LE CH39 (2480MHz) for Ant. 1	Temperature :	23~24°C
Test Engineer :	Elvis Chen	Relative Humidity :	43~44%
		Polarization :	Horizontal




Site : 05CH05-HY  
 Condition : 300328-TX HORIZONTAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over Limit	Limit Line	Read Level	Factor	Pol/Phase
	MHz	dBm	dB	dBm	dBm	dB	
1	152.60	-75.28	-39.28	-36.00	-51.87	-23.41	HORIZONTAL
2	704.60	-81.99	-27.99	-54.00	-71.28	-10.71	HORIZONTAL
3	2286.00	-60.79	-30.79	-30.00	-66.52	5.73	HORIZONTAL
4	2868.00	-57.66	-27.66	-30.00	-65.76	8.10	HORIZONTAL
5	5166.00	-57.10	-27.10	-30.00	-70.69	13.59	HORIZONTAL
6	8607.00	-49.84	-19.84	-30.00	-71.26	21.42	HORIZONTAL
7 @	11587.50	-43.94	-13.94	-30.00	-71.11	27.17	HORIZONTAL





<b>Test Mode :</b>	Bluetooth 4.0 - LE CH39 (2480MHz) for Ant. 1	<b>Temperature :</b>	23~24°C
<b>Test Engineer :</b>	Elvis Chen	<b>Relative Humidity :</b>	43~44%
		<b>Polarization :</b>	Vertical



Site : 05CH05-HY  
 Condition : 300328-TX VERTICAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over Limit	Limit Line	Read Level	Factor	Pol/Phase
	MHz	dBm	dB	dBm	dBm	dB	
1	125.65	-96.62	-60.62	-36.00	-72.88	-23.74	VERTICAL
2	496.70	-81.07	-27.07	-54.00	-66.37	-14.70	VERTICAL
3	2298.00	-58.67	-28.67	-30.00	-64.43	5.76	VERTICAL
4	2568.00	-58.22	-28.22	-30.00	-64.78	6.56	VERTICAL
5	3993.00	-55.04	-25.04	-30.00	-66.09	11.05	VERTICAL
6	8778.00	-49.84	-19.84	-30.00	-71.77	21.93	VERTICAL
7 @	12150.00	-44.19	-14.19	-30.00	-71.14	26.95	VERTICAL

## 4 Receiver Parameters

### 4.1 Receiver spurious emissions

#### 4.1.1 Limit of Receiver spurious emissions

FHSS spurious emission limits for receivers:

SUBCLAUSE 4.3.1.11.3		
FREQUENCY RANGE	MAXIMUM POWER, E.R.P.	MEASUREMENT BANDWIDTH
30 MHz to 1 GHz	-57 dBm	100kHz
1 GHz to 12,75 GHz	-47 dBm	1MHz

WLAN spurious emission limits for receivers

SUBCLAUSE 4.3.2.10.3		
FREQUENCY RANGE	MAXIMUM POWER, E.R.P.	MEASUREMENT BANDWIDTH
30 MHz to 1 GHz	-57 dBm	100kHz
1 GHz to 12,75 GHz	-47 dBm	1MHz

#### 4.1.2 Measuring Instruments

The measuring equipment is listed in the section 8 of this test report.

#### 4.1.3 Test Procedures

1. The measurement procedure follows the clause 5.3.11.2.2 of the ETSI EN 300 328 V1.9.1 (2015-02).
2. The EUT was placed on a turntable with 1.5m height.
3. The test distance between the receiving antenna and the EUT is 3meter below 1GHz frequency range, and 3 meter which is in far field test condition for measured frequency above 1GHz, while the receiving (test) antenna is kept at 1.5 meter height.
4. Set EUT in receiving mode.
5. The table was rotated from 0 to 360 degree to search the highest radiated emission.
6. Repeating step 3 and 4 for each polarization and channel to find the worst emission level.
7. The results obtained are compared to the limits in order to prove compliance with the requirement.


### 4.1.4 Test Setup

Conducted Setup:




Radiated Test Setup:

<Below 1GHz>



<Above 1GHz>






### 4.1.5 Test Results for Conducted Setup

Number of TX = 1, Ant. 1 (Measured)


Test Mode :	802.11b CH01 (2472MHz) for Ant. 1	Temperature :	22~24°C
Test Engineer :	Kenny Chen	Relative Humidity :	52~54%
		Polarization :	Horizontal



Site : TH05-HY  
Condition : 300328-RX




Test Mode :	802.11g CH13 (2472MHz) for Ant. 1	Temperature :	22~24°C
Test Engineer :	Kenny Chen	Relative Humidity :	52~54%
		Polarization :	Vertical



Site : TH05-HY  
Condition : 300328-RX




Test Mode :	Bluetooth (1Mbps) CH00 (2402MHz) for Ant. 1	Temperature :	22~24°C
Test Engineer :	Kenny Chen	Relative Humidity :	52~54%



Site : TH05-HY  
Condition : 300328-RX



Test Mode :	Bluetooth (1Mbps) CH00 (2402MHz) for Ant. 1	Temperature :	22~24°C
Test Engineer :	Kenny Chen	Relative Humidity :	52~54%




Site : TH05-HY  
Condition : 300328-RX

No significant emission found.



4.1.6 Test Results for Radiated Setup (Cabinet Radiation)

Test Mode :	Bluetooth (1Mbps) CH78 (2480MHz) for Ant. 1	Temperature :	23~24°C
Test Engineer :	Elvis Chen	Relative Humidity :	43~44%
		Polarization :	Horizontal




Site : 05CH05-HY  
 Condition : 300328-RX HORIZONTAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over Limit	Limit Line	Read Level	Factor	Pol/Phase
	MHz	dBm	dB	dBm	dBm	dB	
1	144.35	-65.91	-8.91	-57.00	-43.34	-22.57	HORIZONTAL
2	721.40	-69.80	-12.80	-57.00	-60.06	-9.74	HORIZONTAL
3	2534.00	-65.63	-18.63	-47.00	-53.52	-12.11	HORIZONTAL
4	5622.00	-62.58	-15.58	-47.00	-54.99	-7.59	HORIZONTAL
5	8865.00	-56.73	-9.73	-47.00	-58.10	1.37	HORIZONTAL
6 @	11621.25	-54.39	-7.39	-47.00	-61.63	7.24	HORIZONTAL





<b>Test Mode :</b>	Bluetooth (1Mbps) CH78 (2480MHz) for Ant. 1	<b>Temperature :</b>	23~24°C
<b>Test Engineer :</b>	Elvis Chen	<b>Relative Humidity :</b>	43~44%
		<b>Polarization :</b>	Vertical



Site : 05CH05-HY  
 Condition : 300328-RX VERTICAL  
 Power : From system  
 Project : ER 402349

	Freq	Level	Over Limit	Limit Line	Read Level	Factor	Pol/Phase
	MHz	dBm	dB	dBm	dBm	dB	
1	221.35	-84.47	-27.47	-57.00	-59.46	-25.01	VERTICAL
2	781.60	-81.14	-24.14	-57.00	-72.71	-8.43	VERTICAL
3	2550.00	-65.20	-18.20	-47.00	-53.00	-12.20	VERTICAL
4	5325.00	-63.61	-16.61	-47.00	-55.95	-7.66	VERTICAL
5	8433.00	-58.37	-11.37	-47.00	-58.16	-0.21	VERTICAL
6 @	11613.75	-55.12	-8.12	-47.00	-61.92	6.80	VERTICAL

## 5 Adaptivity Test

### 5.1 Adaptivity and Receiver Blocking

#### 5.1.1 Limit of Adaptivity and Receiver Blocking

Only for adaptive systems and RF Output Power > 10 dBm

LBT based Detect and Avoid (Load Based Equipment with spectrum sharing mechanism IEEE Std.):

LBT based spectrum sharing mechanism may implement in IEEE Std. 802.11-2012 clauses 9, clause 10, clause 16, clause 17, clause 19 and clause 20, or in IEEE Std. IEEE 802.15.4-2011, clause 4, clause 5 and clause 8.

Short Control Signaling Transmissions shall have a maximum TxOn / (TxOn + TxOff) ratio of 10 % within an observation period of 50 ms.


#### 5.1.2 Measurement Instruments

The measuring equipment is listed in the section 8 of this test report.

#### 5.1.3 Test Procedures

1. The measurement procedure follows the clause 5.3.7.2.1 of the ETSI EN 300 328 V1.9.1 (2015-02).
2. For conducted measurements on devices with multiple transmit chains and receive chains. The power splitter/combiner shall be used to combine all the transmit/receive chains (antenna outputs) into a single test point. The insertion loss of the power splitter/combiner shall be taken into account.

#### 5.1.4 Test Setup





**5.1.5 Support Unit used in test configuration and system**

Item	Instrument	Manufacturer	Model No.	Characteristics
1.	WLAN AP	D-LINK	DIR-855	Dual Band AP
2.	Notebook	Lenovo	E335	FTP / LAN

**5.1.6 Test Results of Adaptivity and Receiver Blocking**



Equipment Information:	
<input type="checkbox"/>	Non-Adaptive Equipment
	The maximum RF output power (E.I.R.P.) dBm:
	The maximum (Corresponding) Duty Cycle : %
<input checked="" type="checkbox"/>	Adaptive Equipment without the possibility to switch to a non-adaptive mode:
<input checked="" type="checkbox"/>	The equipment has implemented an LBT based DAA mechanism:
	<input type="checkbox"/> The equipment is Frame Based equipment
	<input checked="" type="checkbox"/> The equipment is Load Based equipment
	<input type="checkbox"/> The equipment can switch dynamically between Frame Based and Load Based equipment
<input type="checkbox"/>	The equipment has implemented a non-LBT based DAA mechanism
<input type="checkbox"/>	The equipment can operate in more than one adaptive mode
<input checked="" type="checkbox"/>	Adaptive Frequency Hopping using other forms of DAA (non-LBT based)
<input type="checkbox"/>	Adaptive Equipment which can also operate in non-adaptive mode

	Modulation	Data Rate (single)	Nominal Bandwidth	Channel	Test Frequency	Test Result
WIFI 2.4GHz	802.11b	11Mbit/s	20MHz	01	2412 MHz	PASS
				13	2472 MHz	PASS
	802.11g	54Mbit/s	20MHz	01	2412 MHz	PASS
				13	2472 MHz	PASS
	802.11n HT20	65Mbit/s	20MHz	01	2412 MHz	PASS
				13	2472 MHz	PASS
802.11n HT40	135 Mbit/s	40MHz	03	2422 MHz	PASS	
			11	2462 MHz	PASS	
BT Nom	GFSK	1Mbit/s	1MHz	00	2402 MHz	PASS
				78	2480 MHz	PASS

**Note:** The CCA time is declared by the manufacturer.



5.1.7 Test Plots of Adaptivity Test







802.11b 2412MHz



Detection Level = -66.60dBm/MHz  
Interference dwell time = 60 seconds

Transmission abort within Maximum Channel  
Occupancy Time after interference added and the  
short control signaling is less than 10% duty cycle

AWGN (Interference)



AWGN (Interference) + CW (Blocking Signal)



Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.




802.11b 2472MHz


Detection Level = -66.60 dBm/MHz  
Interference dwell time = 60 seconds

Transmission abort within Maximum Channel  
Occupancy Time after interference added and the  
short control signaling is less than 10% duty cycle



AWGN (Interference)



AWGN (Interference) + CW (Blocking Signal)



Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.







802.11g 2412MHz



Detection Level = -66.60dBm/MHz  
Interference dwell time = 60 seconds

Transmission abort within Maximum Channel  
Occupancy Time after interference added and the  
short control signaling is less than 10% duty cycle

AWGN (Interference)



AWGN (Interference) + CW (Blocking Signal)



Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.







**802.11g 2472MHz**

Detection Level = -66.60dBm/MHz Interference dwell time = 60 seconds	Transmission abort within Maximum Channel Occupancy Time after interference added and the short control signaling is less than 10% duty cycle
---	---

**AWGN (Interference)**



**AWGN (Interference) + CW (Blocking Signal)**





**Note:** Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.



802.11n HT20 2412MHz

Maximum Channel Occupancy Time = 5.285ms


Minimum Idle Period = 154.5 μs



802.11n HT20 2472MHz

Maximum Channel Occupancy Time = 2.690ms

Minimum Idle Period = 226.8 μs






802.11n HT20 2412MHz



Detection Level = -66.60dBm/MHz  
Interference dwell time = 60 seconds

Transmission abort within Maximum Channel  
Occupancy Time after interference added and the  
short control signaling is less than 10% duty cycle

AWGN (Interference)



AWGN (Interference) + CW (Blocking Signal)



Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.




802.11n HT20 2472MHz


Detection Level = -66.60dBm/MHz  
Interference dwell time = 60 seconds

Transmission abort within Maximum Channel  
Occupancy Time after interference added and the  
short control signaling is less than 10% duty cycle



AWGN (Interference)



AWGN (Interference) + CW (Blocking Signal)



Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.







802.11n HT40 2422MHz



Detection Level = -66.60dBm/MHz  
Interference dwell time = 60 seconds

Transmission abort within Maximum Channel  
Occupancy Time after interference added and the  
short control signaling is less than 10% duty cycle

AWGN (Interference)



AWGN (Interference) + CW (Blocking Signal)



Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.





802.11n HT40 2462MHz



Detection Level = -66.60dBm/MHz  
Interference dwell time = 60 seconds

Transmission abort within Maximum Channel  
Occupancy Time after interference added and the  
short control signaling is less than 10% duty cycle



AWGN (Interference)



AWGN (Interference) + CW (Blocking Signal)



Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.











**BT Nom 2402MHz**

Detection Level = -62.40dBm/MHz Interference dwell time = 60 seconds	Transmission abort within Maximum Channel Occupancy Time after interference added and the short control signaling is less than 10% duty cycle
---	---

**AWGN (Interference)**



**AWGN (Interference) + CW (Blocking Signal)**



**Note:** Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.





BT Nom 2480MHz



Detection Level = -62.40dBm/MHz  
Interference dwell time = 60 seconds

Transmission abort within Maximum Channel  
Occupancy Time after interference added and the  
short control signaling is less than 10% duty cycle

AWGN (Interference)



AWGN (Interference) + CW (Blocking Signal)



Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.



## **6 Geo-location Capability**

### **6.1.1 Definition and Requirement**

Geo-location capability is a feature of the equipment to determine its geographical location with the purpose to configure itself according to the regulatory requirements applicable at the geographical location where it operates.

The geo-location capability may be present in the equipment or in an external device (temporary) associated with the equipment operating at the same geographical location during the initial power up of the equipment. The geographical location may also be available in equipment already installed and operating at the same geographical location.

The geographical location determined by the equipment shall not be accessible to the user.

### **6.1.2 Description**


This device does not support this capability declared by the manufacturer.

## 7 Photographs of Radiated Emission Test Configuration

LF



HF





## 8 List of Measuring Equipment

Instrument	Manufacturer	Model No.	Serial No.	Characteristics	Calibration Date	Test Date	Due Date	Remark
Power Sensor	DARE	RadiPower	15I00041SN O09	10MHz~6GHz	Apr. 30, 2015	Aug. 08, 2015 ~ Aug. 31, 2015	Apr. 29, 2016	Conducted (TH05-HY)
Power Sensor	DARE	RadiPower	15I00041SN O10	10MHz~6GHz	Apr. 30, 2015	Aug. 08, 2015 ~ Aug. 31, 2015	Apr. 29, 2016	Conducted (TH05-HY)
Spectrum Analyzer	Rohde & Schwarz	FSP40	100055	9kHz-40GHz	Jun. 18, 2015	Aug. 08, 2015 ~ Aug. 31, 2015	Jun. 17, 2016	Conducted (TH05-HY)
Temperature Chamber	ESPEC	SU-241	92003713	-30°C~95°C	Jun. 15, 2015	Aug. 08, 2015 ~ Aug. 31, 2015	Jun. 14, 2016	Conducted (TH05-HY)
Spectrum Analyzer	Agilent	N9030A	MY52350276	3Hz~44GHz	Mar. 18, 2015	Aug. 27, 2015 ~ Sep. 23, 2015	Mar. 17, 2016	Conducted (DFS02-HY)
Signal Generator (Interferer)	Rohde & Schwarz	SMJ100A	101375	9kHz~6GHz	Feb. 12, 2015	Aug. 27, 2015 ~ Sep. 23, 2015	Feb. 11, 2016	Conducted (DFS02-HY)
Signal Generator	Agilent	E4438C	MY49070755	250KHz ~ 6GHz	Oct. 08, 2014	Aug. 27, 2015 ~ Sep. 23, 2015	Oct. 07, 2015	Conducted (DFS02-HY)
Bilog Antenna	TESEQ	6111D	35419	30MHz to 1GHz	Mar. 30, 2015	Aug. 14, 2015	Mar. 29, 2016	Radiation (05CH05-HY)
Horn Antenna	SCHWARZBE CK	BBHA 9120 D	BBHA 9120 D 1212	1GHz ~ 18GHz	Mar. 11, 2015	Aug. 14, 2015	Mar. 10, 2016	Radiation (05CH05-HY)
Spectrum Analyzer	Agilent	N9010A	MY53470118	10Hz~44GHz	Mar. 03, 2015	Aug. 14, 2015	Mar. 02, 2016	Radiation (05CH05-HY)
Preamplifier	Agilent	8449B	3008A02665	1GHz~26.5GHz	Jan. 21, 2015	Aug. 14, 2015	Jan. 20, 2016	Radiation (05CH05-HY)
Amplifier	EMCI	EMC001830	980191	10MHz~8GHz	Jan. 20, 2015	Aug. 14, 2015	Jan. 19, 2016	Radiation (05CH05-HY)
Antenna Mast	ChainTek	MD-200	1308055	1m~4m	N/A	Aug. 14, 2015	N/A	Radiation (05CH05-HY)
Turn Table	EMEC	TT 2000	N/A	0-360 degree	N/A	Aug. 14, 2015	N/A	Radiation (05CH05-HY)



## 9 Uncertainty Evaluation

Test Item	Uncertainty
Occupied Channel Bandwidth	± 0.49 %
RF output power, conducted	±0.61 dB
Power density, conducted	±0.60 dB
Radiated emissions	±2.96 dB
Temperature	±0.8 °C
Humidity	±3 %
Time	±0.33 %



## **Appendix A. Test Result of Conducted Test Items**

Test Engineer:	Bill Kuo	Temperature:	24-26	°C
Test Date:	2015/08/08 ~ 2015/08/12	Relative Humidity:	46-49	%



**TEST RESULTS DATA**  
**EIRP Power**

Conducted Power (dBm)												
Mod.	Data Rate	NTx	CH.	Freq. (MHz)	Temperature Nomal		Extreme Temperature Low		Extreme Temperature High		Gain (dBi)	
					20 °C		-20 °C		70 °C			
					Ant 1	Ant 2	Ant 1	Ant 2	Ant 1	Ant 2		
BTNom	1Mbps	1	0	2402	11.60		12.40		11.60		3.20	
BTNom	1Mbps	1	39	2441	11.60		12.00		11.30		3.20	
BTNom	1Mbps	1	78	2480	11.70		11.90		11.20		3.20	
BLE	1Mbps	1	0	2402	6.70		7.70		6.00		3.20	
BLE	1Mbps	1	19	2440	6.40		7.10		5.40		3.20	
BLE	1Mbps	1	39	2480	5.80		6.50		4.80		3.20	
11b	1Mbps	1	1	2412	15.90		15.90		15.50		3.20	
11b	1Mbps	1	7	2442	15.80		15.60		14.90		3.20	
11b	1Mbps	1	13	2472	15.70		15.10		14.60		3.20	
11g	6Mbps	1	1	2412	11.90		11.90		10.80		3.20	
11g	6Mbps	1	7	2442	16.40		16.00		15.20		3.20	
11g	6Mbps	1	13	2472	16.20		15.40		15.00		3.20	
HT20	MCS0	1	1	2412	12.00		12.00		10.90		3.20	
HT20	MCS0	1	7	2442	15.60		15.20		14.40		3.20	
HT20	MCS0	1	13	2472	15.30		14.70		14.20		3.20	
HT40	MCS0	1	3	2422	9.60		9.80		8.60		3.20	
HT40	MCS0	1	7	2442	14.00		13.50		12.90		3.20	
HT40	MCS0	1	11	2462	13.80		13.20		12.70		3.20	
HT20	MCS12	2	1	2412	15.60		16.30		14.00		3.20	
HT20	MCS12	2	7	2442	16.50		15.40		15.80		3.20	
HT20	MCS12	2	13	2472	16.40		16.60		15.70		3.20	

EIRP Power (dBm)												
Mod.	Data Rate	NTX	CH.	Freq. (MHz)	Temperature Nomal		Temperature Low		Temperature High		Limit (dBm)	Pass/Fail
					Ant 1	Ant 2	Ant 1	Ant 2	Ant 1	Ant 2		
BTNom	1Mbps	1	0	2402	14.80		15.60		14.80		20	Pass
BTNom	1Mbps	1	39	2441	14.80		15.20		14.50		20	Pass
BTNom	1Mbps	1	78	2480	14.90		15.10		14.40		20	Pass
BLE	1Mbps	1	0	2402	9.90		10.90		9.20		20	Pass
BLE	1Mbps	1	19	2440	9.60		10.30		8.60		20	Pass
BLE	1Mbps	1	39	2480	9.00		9.70		8.00		20	Pass
11b	1Mbps	1	1	2412	19.10		19.10		18.70		20	Pass
11b	1Mbps	1	7	2442	19.00		18.80		18.10		20	Pass
11b	1Mbps	1	13	2472	18.90		18.30		17.80		20	Pass
11g	6Mbps	1	1	2412	15.10		15.10		14.00		20	Pass
11g	6Mbps	1	7	2442	19.60		19.20		18.40		20	Pass
11g	6Mbps	1	13	2472	19.40		18.60		18.20		20	Pass
HT20	MCS0	1	1	2412	15.20		15.20		14.10		20	Pass
HT20	MCS0	1	7	2442	18.80		18.40		17.60		20	Pass
HT20	MCS0	1	13	2472	18.50		17.90		17.40		20	Pass
HT40	MCS0	1	3	2422	12.80		13.00		11.80		20	Pass
HT40	MCS0	1	7	2442	17.20		16.70		16.10		20	Pass
HT40	MCS0	1	11	2462	17.00		16.40		15.90		20	Pass
HT20	MCS12	2	1	2412	18.80		19.50		17.20		20	Pass
HT20	MCS12	2	7	2442	19.70		18.60		19.00		20	Pass
HT20	MCS12	2	13	2472	19.60		19.80		18.90		20	Pass

**TEST RESULTS DATA**  
**EIRP Power Density**

Power Density								
Mod.	Data Rate	NTX	CH.	Freq. (MHz)	EIRP Power Density (dBm/MHz)		Limit (dBm /MHz)	Pass/Fail
					Ant 1	Ant 2		
BLE	1Mbps	1	0	2402	9.95		10	Pass
BLE	1Mbps	1	19	2440	9.55		10	Pass
BLE	1Mbps	1	39	2480	8.94		10	Pass
11b	1Mbps	1	1	2412	9.90		10	Pass
11b	1Mbps	1	7	2442	9.83		10	Pass
11b	1Mbps	1	13	2472	9.80		10	Pass
11g	6Mbps	1	1	2412	4.82		10	Pass
11g	6Mbps	1	7	2442	8.98		10	Pass
11g	6Mbps	1	13	2472	8.92		10	Pass
HT20	MCS0	1	1	2412	4.71		10	Pass
HT20	MCS0	1	7	2442	8.37		10	Pass
HT20	MCS0	1	13	2472	7.78		10	Pass
HT40	MCS0	1	3	2422	-0.72		10	Pass
HT40	MCS0	1	7	2442	3.62		10	Pass
HT40	MCS0	1	11	2462	3.39		10	Pass
HT20	MCS12	2	1	2412		8.25	10	Pass
HT20	MCS12	2	7	2442		8.94	10	Pass
HT20	MCS12	2	13	2472		8.81	10	Pass

**TEST RESULTS DATA**  
**99% Occupied Bandwidth**

Occupied Bandwidth												
Mod.	Data Rate	NTX	CH.	Freq. (MHz)	99% Occupied BW (MHz)		Freq. Low (MHz)		Freq. High (MHz)		Limit (Within operating Band)	Pass/Fail
					Ant 1	Ant 2	Ant 1	Ant 2	Ant 1	Ant 2		
BTNom	1Mbps	1	0	2402	0.83		2401.58		2402.41			Pass
BTNom	1Mbps	1	78	2480	0.83		2479.58		2480.41			Pass
BTNom	2Mbps	1	0	2402	1.17		2401.40		2402.56			Pass
BTNom	2Mbps	1	78	2480	1.16		2479.40		2480.56			Pass
BTNom	3Mbps	1	0	2402	1.16		2401.42		2402.58			Pass
BTNom	3Mbps	1	78	2480	1.16		2479.42		2480.58			Pass
BLE	1Mbps	1	0	2402	1.02		2401.49		2402.51			Pass
BLE	1Mbps	1	39	2480	1.02		2479.48		2480.51			Pass
11b	1Mbps	1	1	2412	14.84		2404.60		2419.44			Pass
11b	1Mbps	1	13	2472	14.84		2464.56		2479.40			Pass
11g	6Mbps	1	1	2412	16.80		2403.60		2420.40			Pass
11g	6Mbps	1	13	2472	17.60		2463.16		2480.76			Pass
HT20	MCS0	1	1	2412	17.80		2403.08		2420.88			Pass
HT20	MCS0	1	13	2472	18.28		2462.84		2481.12			Pass
HT40	MCS0	1	3	2422	35.92		2404.00		2439.92			Pass
HT40	MCS0	1	11	2462	36.08		2443.92		2480.00			Pass
HT20	MCS12	2	1	2412	17.80		2403.08		2420.88			Pass
HT20	MCS12	2	13	2472	18.04		2462.96		2481.00			Pass

**TEST RESULTS DATA**  
**OOB Emission Level**

Mod.	Data Rate	NTX	CH.	Freq. (MHz)	OOB Emission Worst Level (dBm/MHz)		Limit (dBm /MHz)	Pass/Fail
					Ant 1	Ant 2		
BTNom	1Mbps	1	hopping		-26.71		-10,-20	Pass
BTNom	2Mbps	1	hopping		-27.95		-10,-20	Pass
BTNom	3Mbps	1	hopping		-28.80		-10,-20	Pass
BLE	1Mbps	1	0	2402	-20.19		-10,-20	Pass
BLE	1Mbps	1	39	2480	-34.64		-10,-20	Pass
11b	1Mbps	1	1	2412	-30.57		-10,-20	Pass
11b	1Mbps	1	13	2472	-31.46		-10,-20	Pass
11g	6Mbps	1	1	2412	-25.91		-10,-20	Pass
11g	6Mbps	1	13	2472	-10.34		-10,-20	Pass
HT20	MCS0	1	1	2412	-24.66		-10,-20	Pass
HT20	MCS0	1	13	2472	-10.78		-10,-20	Pass
HT40	MCS0	1	3	2422	-32.28		-10,-20	Pass
HT40	MCS0	1	11	2462	-17.01		-10,-20	Pass
HT20	MCS12	2	1	2412		-22.36	-10,-20	Pass
HT20	MCS12	2	13	2472		-13.68	-10,-20	Pass

**TEST RESULTS DATA**  
**Bluetooth Test Items**

**Dwell Time of each Frequency Measurement**

BT (Hopping Mode)	Dwell Time per hop(ms)	Dwell Time(ms)	Dwell Time Max. Limit (ms)	Frequency Occupation		Frequency Occupation Time min. Limit (ms)	Pass /Fail	
				Hop#	Time (ms)			
DH1	2402 MHz	0.40	128.88	400	2	0.81	0.40	Pass
	2480 MHz	0.40	128.47	400	1	0.40	0.40	Pass
DH3	2402 MHz	1.67	277.03	400	4	6.68	1.67	Pass
	2480 MHz	1.67	281.24	400	3	5.01	1.67	Pass
DH5	2402 MHz	2.92	278.08	400	3	8.76	2.92	Pass
	2480 MHz	2.92	304.41	400	2	5.84	2.92	Pass

**Hopping Sequence Measurement**

Total Number of Hopping Frequency	Limit of operating minimum channel (at least 70% of band)	Minimum Number of Adaptive Frequency Hopping	Limit of hopping frequencies at all times
79	59	20	15

**Hopping Channel Separation Measurement**

BT	Separation(MHz)	Limit(MHz)	Pass /Fail
CH 00	1.002	>0.1	Pass
CH 39	0.987	>0.1	Pass
CH 78	1.008	>0.1	Pass



# CE Radio Test Report

APPLICANT : Texas Instruments Incorporated  
EQUIPMENT : WiFi and Bluetooth Module  
BRAND NAME : Texas Instruments  
MODEL NAME : WL18MODGB  
STANDARD : ETSI EN 300 328 V1.8.1 (2012-06)  
TEST DATE(S) : Dec. 04, 2013 ~ Jan. 06, 2014

The measurements shown in this test report were made in accordance with the procedures given in EUROPEAN COUNCIL DIRECTIVE 1999/5/EC and found to be in compliance with ETSI Standard EN 300 328 V1.8.1 (2012-06).

The test results in this report apply exclusively to the tested model / sample. Without written approval of SPORTON INTERNATIONAL INC., the test report shall not be reproduced except in full.

Reviewed by: Joseph Lin / Supervisor

Approved by: Jones Tsai / Manager



## SPORTON INTERNATIONAL INC.

No. 52, Hwa Ya 1<sup>st</sup> Rd., Hwa Ya Technology Park, Kwei-Shan Hsiang, Tao Yuan Hsien, Taiwan, R.O.C.



## TABLE OF CONTENTS

<b>REVISION HISTORY</b> .....	<b>3</b>
<b>SUMMARY OF TEST RESULT</b> .....	<b>4</b>
<b>1 GENERAL DESCRIPTION</b> .....	<b>5</b>
1.1 Applicant .....	5
1.2 Manufacturer.....	5
1.3 Feature of Equipment Under Test .....	5
1.4 Details of Tested Sample (EUT) Information.....	6
1.5 Modification of EUT .....	6
1.6 Testing Facility.....	7
1.7 Applied Standards .....	7
1.8 Test Condition.....	7
<b>2 TEST CONFIGURATION OF EQUIPMENT UNDER TEST</b> .....	<b>8</b>
2.1 Descriptions of Test Mode.....	8
2.2 Connection Diagram of EUT Test Configurations .....	11
2.3 Supported Unit used in test configuration and system .....	12
2.4 EUT Operation Test Setup .....	12
<b>3 TRANSMITTER PARAMETERS</b> .....	<b>13</b>
3.1 Maximum Transmit Power.....	13
3.2 Maximum Equivalent Isotropically Radiated Power (E.I.R.P.) Spectral Density .....	17
3.3 Occupied Channel Bandwidth .....	20
3.4 Frequency Hopping Requirements.....	23
3.5 Transmitter unwanted emissions in the out-of-band domain .....	31
3.6 Transmitter spurious emissions.....	35
<b>4 RECEIVER PARAMETERS</b> .....	<b>49</b>
4.1 Receiver spurious emissions.....	49
<b>5 ADAPTIVITY TEST</b> .....	<b>53</b>
5.1 Adaptivity and Receiver Blocking .....	53
<b>6 PHOTOGRAPHS OF RADIATED EMISSION TEST CONFIGURATION</b> .....	<b>65</b>
<b>7 LIST OF MEASURING EQUIPMENT</b> .....	<b>67</b>
<b>8 UNCERTAINTY EVALUATION</b> .....	<b>69</b>





### REVISION HISTORY

REPORT NO.	VERSION	DESCRIPTION	ISSUED DATE
ER3N2752-01	Rev. 01	Initial issue of report	Jan. 27, 2014



## SUMMARY OF TEST RESULT

CLAUSE (EN 300 328)	TEST PARAMETER	PASS/FAIL	REMARK
<b>Transmitter Parameters</b>			
4.3.1.1 4.3.2.1	Maximum Transmit Power	PASS	-
4.3.2.2	Maximum Equivalent Isotropically Radiated Power (E.I.R.P.) Spectral Density	PASS	Only applicable for modulations other than FHSS
4.3.1.7 4.3.2.6	Occupied Channel Bandwidth	PASS	-
4.3.1.3 4.3.1.4	Frequency Hopping Requirements	PASS	Only applicable for FHSS
4.3.1.8 4.3.2.7	Transmitter spurious emissions in OOB	PASS	-
4.3.1.9 4.3.2.8	Transmitter spurious emissions	PASS	Under limit 0.97 dB at 4944.000 MHz
<b>Receiver Parameters</b>			
4.3.1.10 4.3.2.9	Receiver spurious emissions	PASS	Under limit 6.19 dB at 1970.000 MHz
<b>Adaptive Test Item</b>			
4.3.1.6 4.3.2.5	Adaptivity	PASS	Only applicable for adaptive equipment Output Power >10dBm
4.3.1.11 4.3.2.10	Receiver Blocking	PASS	
<b>Non-Adaptive Test Item</b>			
4.3.1.2 4.3.2.3	Duty cycle, Tx-Sequence, Tx-gap	Not Required	Only applicable for non-adaptive equipment Output Power >10dBm
4.3.1.5 4.3.2.4	Medium Utilisation (MU) factor	Not Required	
<b>Note:</b>			
1. Bluetooth belongs to adaptive equipment and EIRP > 10dBm.			
2. WiFi belongs to adaptive equipment and EIRP > 10dBm.			



# 1 General Description

## 1.1 Applicant

**Texas Instruments Incorporated**  
12500 TI Boulevard, M/S 8751, Dallas, TX 75243, USA

## 1.2 Manufacturer

**Jorjin Technologies Inc.**  
17F, No. 239, Sec. 1, Datong Rd, Xizhi Dist. New Taipei City 221, Taiwan. R.O.C.

## 1.3 Feature of Equipment Under Test

The Equipment Under Test (hereafter called: EUT) is WiFi and Bluetooth Module supporting, Wi-Fi 2.4GHz 802.11b/g/n and Bluetooth features, and below is details of information.

General Information of Equipment Under Test	
Equipment	WiFi and Bluetooth Module
Brand Name	Texas Instruments
Model Name	WL18MODGB
Wi-Fi Specification	802.11b/g/n (HT20/HT40)
Bluetooth Version	v3.0 + EDR / v4.0 - LE
Power Supply	From test jig

**Remark:** The above EUT's information was declared by manufacturer. Please refer to the specifications or user's manual for more detailed description.

### 1.4 Details of Tested Sample (EUT) Information

Product Specification subjective to this Test Standard																									
<b>Transmitter / Receiver Frequency Range</b>	2400 MHz ~ 2483.5 MHz																								
<b>Number of Channels</b>	WLAN : 13 Bluetooth : 79 Bluetooth 4.0 – LE: 40																								
<b>Channel Spacing</b>	WLAN : 5 MHz Bluetooth : 1 MHz Bluetooth 4.0 – LE: 2 MHz																								
<b>Maximum EIRP Average Power</b>	<b>&lt;Ant. 1&gt;</b> 802.11b : 17.74 dBm 802.11g : 17.34 dBm 802.11n HT40 : 15.24 dBm Bluetooth BR (1Mbps) : 11.84 dBm Bluetooth 4.0 - LE (1Mbps) : 10.44 dBm <b>SISO &lt;Ant. 1&gt;</b> 802.11n HT20 : 16.64 dBm <b>MIMO &lt;Ant. 1+2&gt;</b> 802.11n HT20 : 18.14 dBm																								
<b>Antenna Type / Gain</b>	WLAN:           Antenna 1: Chip Antenna / -0.36 dBi Antenna 2: Chip Antenna / 1.22 dBi Bluetooth :    Antenna 1: Chip Antenna / -0.36 dBi																								
<b>Type of Modulation</b>	Bluetooth 3.0 BR (1Mbps) : GFSK Bluetooth 3.0 EDR (2Mbps) : $\pi/4$ -DQPSK Bluetooth 3.0 EDR (3Mbps) : 8-DPSK Bluetooth 4.0 - LE : GFSK 802.11b : DSSS (DBPSK / DQPSK / CCK) 802.11g/n: OFDM (BPSK / QPSK / 16QAM / 64QAM)																								
<b>Antenna Function for Transmitter</b>	<table border="1"> <thead> <tr> <th></th> <th>Ant. 1</th> <th>Ant. 2</th> </tr> </thead> <tbody> <tr> <td>Bluetooth v3.0</td> <td>V</td> <td>-</td> </tr> <tr> <td>Bluetooth v4.0</td> <td>V</td> <td>-</td> </tr> <tr> <td>802.11 b</td> <td>V</td> <td>-</td> </tr> <tr> <td>802.11 g</td> <td>V</td> <td>-</td> </tr> <tr> <td>802.11 n HT20 SISO</td> <td>V</td> <td>-</td> </tr> <tr> <td>802.11 n HT20 MIMO</td> <td>V</td> <td>V</td> </tr> <tr> <td>802.11 n HT40</td> <td>V</td> <td>-</td> </tr> </tbody> </table>		Ant. 1	Ant. 2	Bluetooth v3.0	V	-	Bluetooth v4.0	V	-	802.11 b	V	-	802.11 g	V	-	802.11 n HT20 SISO	V	-	802.11 n HT20 MIMO	V	V	802.11 n HT40	V	-
	Ant. 1	Ant. 2																							
Bluetooth v3.0	V	-																							
Bluetooth v4.0	V	-																							
802.11 b	V	-																							
802.11 g	V	-																							
802.11 n HT20 SISO	V	-																							
802.11 n HT20 MIMO	V	V																							
802.11 n HT40	V	-																							
<b>EUT Stage</b>	Production Unit																								

**Note:** For other wireless features of this EUT, test report will be issued separately.

### 1.5 Modification of EUT

No modifications are made to the EUT during all test items.

## 1.6 Testing Facility

<b>Test Site</b>	SPORTON INTERNATIONAL INC.
<b>Test Site Location</b>	No. 52, Hwa Ya 1 <sup>st</sup> Rd., Hwa Ya Technology Park, Kwei-Shan Hsiang, Tao Yuan Hsien, Taiwan, R.O.C. TEL: +886-3-327-3456 FAX: +886-3-328-4978
<b>Test Site No.</b>	<b>Sporton Site No. :</b> 05CH02-HY ; 05CH01-HY ; TH02-HY

## 1.7 Applied Standards

According to the specifications of the manufacturer, the EUT must comply with the requirements of **ETSI EN 300 328 V1.8.1 (2012-06)**.

**Note:** All test items were verified and recorded according to the standards and without any deviation during the test.

## 1.8 Test Condition

<b>Normal Voltage</b>	DC 3.7V
<b>Normal Temperature</b>	25°C
<b>Extreme Temperature</b>	-30°C and 70°C

**Note:** The test temperature was between -30°C ~ 70°C by manufacturer requested.

## 2 Test Configuration of Equipment under Test

### 2.1 Descriptions of Test Mode

- a. Preliminary tests were performed in different data rate and recorded the RF power output in the following tables:

<Ant. 1>

Average Bluetooth RF Output Power (dBm)			
Data rate	1Mbps	2Mbps	3Mbps
Avg. Power	12.10	7.60	7.60

Note:

Data rate Bluetooth 1Mbps was chosen to be tested due to the highest RF output power.

Average Bluetooth 4.0 - LE RF Output Power (dBm)			
Data Rate	CH 00	CH 19	CH 39
Avg. Power	10.30	10.30	9.90

2.4GHz 802.11b RF Output Power (dBm)				
Data rate	1Mbps	2Mbps	5.5Mbps	11Mbps
Avg. Power	16.20	16.10	16.10	16.10

2.4GHz 802.11g RF Output Power (dBm)								
Data rate	6Mbps	9Mbps	12Mbps	18Mbps	24Mbps	36Mbps	48Mbps	54Mbps
Avg. Power	16.30	16.20	16.20	16.20	15.30	14.50	13.90	13.20

2.4GHz 802.11n HT40 RF Output Power (dBm)								
Data rate	MCS0	MCS1	MCS2	MCS3	MCS4	MCS5	MCS6	MCS7
Avg. Power	13.90	13.80	13.80	13.80	13.80	13.80	12.80	11.50

SISO <Ant. 1>

2.4GHz 802.11n HT20 RF Output Power (dBm)								
Data rate	MCS0	MCS1	MCS2	MCS3	MCS4	MCS5	MCS6	MCS7
Avg. Power	15.30	15.20	15.20	15.20	14.60	14.00	13.40	12.30



**MIMO <Ant. 1+2>**

2.4GHz 802.11n HT20 RF Output Power (dBm)								
Data rate	MCS8	MCS9	MCS10	MCS11	MCS12	MCS13	MCS14	MCS15
<b>Avg. Power</b>	<b>18.00</b>	17.90	17.90	17.90	17.60	17.10	13.40	12.60

**Note:**

The data rates of WLAN 802.11b/g/n were set in 1Mbps for 802.11b (Ant. 1), 6Mbps for 802.11g (Ant. 1), MCS0 for 802.11n HT20 (Ant. 1), MCS8 for 802.11n HT20 (Ant. 1+2), MCS0 for 802.11n HT40 (Ant. 1) with both antennas transmit due to the highest RF output power for rest of test items.

- b. During radiated spurious emissions testing, the interface cables and equipment positions were varied according to European Standard EN 300 328 V1.8.1 (2012-06), and the frequency range of radiation was investigated from 25 MHz to 12750 MHz.



Pre-scanned tests were conducted to determine the final configuration from all possible combinations. The following tables are showing the test modes as the worst cases and recorded in this report.

Test Modes		
RF	802.11b DSSS	802.11g OFDM
Tx	802.11b CH01 (2412MHz) for Ant. 1 <b>802.11b CH13 (2472MHz) for Ant. 1</b>	<b>802.11g CH01 (2412MHz) for Ant. 1</b> 802.11g CH13 (2472MHz) for Ant. 1
Rx	802.11b CH13 (2472MHz) for Ant. 1	-

Test Modes		
RF	802.11n HT20 OFDM	802.11n HT40 OFDM
Tx	802.11n HT20 CH01 (2412MHz) for MIMO <Ant. 1+2> 802.11n HT20 CH13 (2472MHz) for MIMO <Ant. 1+2> <b>802.11n HT20 CH01 (2412MHz) for SISO &lt;Ant. 1&gt;</b>	<b>802.11n HT40 CH03 (2422MHz) for Ant. 1</b> 802.11n HT40 CH11 (2462MHz) for Ant. 1
Rx	<b>802.11n HT20 CH01 (2412MHz) for SISO &lt;Ant. 1&gt;</b>	-


Test Modes		
RF	Bluetooth (1Mbps) GFSK	Bluetooth 4.0 - LE GFSK
Tx	<b>Bluetooth (1Mbps) CH00 (2402MHz) for Ant. 1</b> Bluetooth (1Mbps) CH78 (2480MHz) for Ant. 1	<b>Bluetooth 4.0 - LE CH00 (2402MHz) for Ant. 1</b> Bluetooth 4.0 - LE CH39 (2480MHz) for Ant. 1
Rx	Bluetooth (1Mbps) CH00 (2402MHz) for Ant. 1	Bluetooth 4.0 - LE CH00 (2402MHz) for Ant. 1

**Remark:** All test modes of the Transmitter Radiated Spurious Emission (RSE) and Receiver Radiated Spurious Emission (RSE) were tested; only the test worse data in bold of these modes were reported.




## 2.2 Connection Diagram of EUT Test Configurations

<Bluetooth Tx/Rx Mode>



<WLAN Tx/Rx Mode>



### 2.3 Supported Unit used in test configuration and system

Item	Equipment	Trade Name	Model Name	FCC ID	Data Cable	Power Cord
1.	Notebook	DELL	P20G	FCC DoC	N/A	AC I/P: Unshielded, 1.2 m DC O/P: Shielded, 1.8 m
2.	Notebook	Lenovo	G480	N/A	N/A	AC I/P: Unshielded, 1.2 m DC O/P: Shielded, 1.8 m
3.	Bluetooth Base Station	R&S	CBT32	N/A	N/A	Unshielded, 1.8 m
4.	Fixture	N/A	WG7XXXT01	N/A	N/A	N/A
5.	Adapter	Aviv Energy	HK-IP15-A05	N/A	N/A	Unshielded, 1.8 m

### 2.4 EUT Operation Test Setup

For Bluetooth test items, a programmed RF utility, “HCT Tester” was installed in notebook which was programmed in order to make the EUT get into the engineering modes to contact with Bluetooth base station for continuous transmitting and receiving signals.

For WLAN and Bluetooth 4.0 – LE test items, programmed RF utility, “HCT Tester” installed in the notebook make the EUT provides functions like channel selection and power level for continuous transmitting and receiving signals.

### 3 Transmitter Parameters

#### 3.1 Maximum Transmit Power

##### 3.1.1 Limit of Effective Isotropic Radiated Power

SUBCLAUSE 4.3.1.1.2 and 4.3.2.1.2	
TEST CONDITION	LIMIT
Normal and Extreme Temperature Conditions	20dBm (e.i.r.p)


##### 3.1.2 Measuring Instruments

The measuring equipment is listed in the section 7 of this test report.

##### 3.1.3 Test Procedure

1. The measurement procedure follows the clause 5.3.2.2.1 of the ETSI EN 300 328 V1.8.1 (2012-06).
2. Placing the EUT in thermal chamber.
3. The EUT is connected to external power supply.
4. Setting thermal chamber temperature and power supply voltage at suitable values.
5. The EIRP = A+G+Y, where A is the power measured, G is the assembly gain of the individual antenna of the EUT in dBi and Y is the additional beamforming gain of the EUT in dB if applicable, here, Y=0.

##### 3.1.4 Test Setup





**3.1.5 Test Results**

<b>Test Item :</b>	EIRP Power	<b>Temperature :</b>	24~26°C
<b>Test Engineer :</b>	Alex Lee	<b>Relative Humidity :</b>	51~54%

Mod.	Data Rate	N <sub>TX</sub>	Channel	Freq. (MHz)	Conducted Power (dBm)			Gain (dBi)	Pass/Fail
					T nom	T min	T max		
					25 °C	-30 °C	70 °C		
11b	1Mbps	1	1	2412	15.80	18.10	16.50	-0.36	Pass
11b	1Mbps	1	7	2442	16.20	17.60	16.80	-0.36	Pass
11b	1Mbps	1	13	2472	15.90	17.90	17.00	-0.36	Pass
11g	6Mbps	1	1	2412	13.60	14.90	13.90	-0.36	Pass
11g	6Mbps	1	7	2442	16.30	17.70	16.80	-0.36	Pass
11g	6Mbps	1	13	2472	13.10	15.10	14.10	-0.36	Pass
HT20	MCS0	1	1	2412	13.60	15.00	14.10	-0.36	Pass
HT20	MCS0	1	7	2442	15.30	17.00	16.00	-0.36	Pass
HT20	MCS0	1	13	2472	13.30	15.10	14.10	-0.36	Pass
HT40	MCS0	1	3	2422	11.50	13.00	12.00	-0.36	Pass
HT40	MCS0	1	7	2442	13.70	15.50	14.50	-0.36	Pass
HT40	MCS0	1	11	2462	13.90	15.60	14.50	-0.36	Pass
BT2.0	1Mbps	1	0	2402	12.10	12.20	11.70	-0.36	Pass
BT2.0	1Mbps	1	39	2441	12.00	11.90	11.50	-0.36	Pass
BT2.0	1Mbps	1	78	2480	12.10	11.80	11.30	-0.36	Pass
BT4.0	1Mbps	1	0	2402	10.30	10.80	10.20	-0.36	Pass
BT4.0	1Mbps	1	19	2440	10.30	10.70	10.20	-0.36	Pass
BT4.0	1Mbps	1	39	2480	9.90	10.30	9.90	-0.36	Pass



Mod.	Data Rate	N <sub>TX</sub>	Channel	Freq. (MHz)	EIRP Power (dBm)			Power Limit (dBm)	Pass/Fail
					T nom	T min	T max		
					25 °C	-30 °C	70 °C		
11b	1Mbps	1	1	2412	15.44	17.74	16.14	20	Pass
11b	1Mbps	1	7	2442	15.84	17.24	16.44	20	Pass
11b	1Mbps	1	13	2472	15.54	17.54	16.64	20	Pass
11g	6Mbps	1	1	2412	13.24	14.54	13.54	20	Pass
11g	6Mbps	1	7	2442	15.94	17.34	16.44	20	Pass
11g	6Mbps	1	13	2472	12.74	14.74	13.74	20	Pass
HT20	MCS0	1	1	2412	13.24	14.64	13.74	20	Pass
HT20	MCS0	1	7	2442	14.94	16.64	15.64	20	Pass
HT20	MCS0	1	13	2472	12.94	14.74	13.74	20	Pass
HT40	MCS0	1	3	2422	11.14	12.64	11.64	20	Pass
HT40	MCS0	1	7	2442	13.34	15.14	14.14	20	Pass
HT40	MCS0	1	11	2462	13.54	15.24	14.14	20	Pass
BT2.0	1Mbps	1	0	2402	11.74	11.84	11.34	20	Pass
BT2.0	1Mbps	1	39	2441	11.64	11.54	11.14	20	Pass
BT2.0	1Mbps	1	78	2480	11.74	11.44	10.94	20	Pass
BT4.0	1Mbps	1	0	2402	9.94	10.44	9.84	20	Pass
BT4.0	1Mbps	1	19	2440	9.94	10.34	9.84	20	Pass
BT4.0	1Mbps	1	39	2480	9.54	9.94	9.54	20	Pass



Mod.	Data Rate	N <sub>TX</sub>	Ant.	Channel	Freq. (MHz)	Conducted Power (dBm)			Gain (dBi)	Pass/Fail
						T nom	T min	T max		
						25 °C	-30 °C	70 °C		
HT20	MCS8	2	1+2	1	2412	15.80	16.80	15.50	-0.36	Pass
HT20	MCS8	2	1+2	7	2442	18.00	18.50	17.80	-0.36	Pass
HT20	MCS8	2	1+2	13	2472	16.20	16.60	15.10	-0.36	Pass

Mod.	Data Rate	N <sub>TX</sub>	Ant.	Channel	Freq. (MHz)	EIRP Power (dBm)			Power Limit (dBm)	Pass/Fail
						T nom	T min	T max		
						25 °C	-30 °C	70 °C		
HT20	MCS8	2	1+2	1	2412	15.44	16.44	15.14	20	Pass
HT20	MCS8	2	1+2	7	2442	17.64	18.14	17.44	20	Pass
HT20	MCS8	2	1+2	13	2472	15.84	16.24	14.74	20	Pass

**Note:**

EIRP = measured average power has offset cable loss + antenna gain.

For example: antenna gain = -0.36 dBi at Ch01, 2412MHz,

EIRP = 15.80 dBm (measured average power has offset cable loss) + (-0.36) dBi (antenna gain) = 15.44 dBm

### 3.2 Maximum Equivalent Isotropically Radiated Power (E.I.R.P.) Spectral Density

#### 3.2.1 Limit of Maximum Power Spectral Density

SUBCLAUSE 4.3.2.2.2	
TEST CONDITION	LIMIT
Normal and Extreme Temperature Conditions	10dBm / MHz

**Remark:** Maximum spectral power density is not applicable to FHSS system device.

#### 3.2.2 Measuring Instruments

The measuring equipment is listed in the section 7 of this test report.

#### 3.2.3 Test Procedure

1. The measurement procedure follows the clause 5.3.3.2.1 of the ETSI EN 300 328 V1.8.1 (2012-06).
2. These measurements shall only be performed at normal test conditions.
3. The measurement shall be repeated for the equipment being configured to operate at the lowest, the middle, and the highest frequency of the stated frequency range.
4. The test procedure shall be as follows:

**Step 1:**

Connect the EUT to the spectrum analyzer and use the following settings:

Start Frequency	2400MHz
Stop Frequency	2483.5MHz
Resolution BW	10kHz
Video BW	30kHz
Sweep Points	8350
Detector	RMS
Trace Mode	Max Hold
Sweep time	Auto

**Step 2:**

Add up the values for amplitude (power) for all the samples in the file.

**Step 3:**

Normalize the individual values for amplitude so that the sum is equal to the RF Output Power (e.i.r.p.) measured.

**Step 4:**

Starting from the first sample in the file (lowest frequency), add up the power of the following samples representing a 1 MHz segment and record the results for power and position (i.e. sample #1 to #100). This is the Power Spectral Density (e.i.r.p.) for the first 1 MHz segment which shall be recorded.

**Step 5:**


Shift the start point of the samples added up in step 4 by 1 sample and repeat the procedure in step 4 (i.e. sample #2 to #101).

**Step 6:**

Repeat step 5 until the end of the data set and record the radiated Power Spectral Density values for each of the 1 MHz segments.

From all the recorded results, the highest value is the maximum Power Spectral Density for the EUT. This value shall be recorded in the test report.

### 3.2.4 Test Setup







**3.2.5 Test Results**

<b>Test Item :</b>	EIRP Power Density	<b>Temperature :</b>	24~26°C
<b>Test Engineer :</b>	Alex Lee	<b>Relative Humidity :</b>	51~54%

Mod.	Data Rate	N <sub>TX</sub>	Channel	Freq. (MHz)	EIRP Power Density (dBm/MHz)	Max. Limits (dBm/MHz)	Pass/Fail
11b	1Mbps	1	1	2412	8.37	10	Pass
11b	1Mbps	1	7	2442	8.68	10	Pass
11b	1Mbps	1	13	2472	8.33	10	Pass
11g	6Mbps	1	1	2412	3.91	10	Pass
11g	6Mbps	1	7	2442	7.17	10	Pass
11g	6Mbps	1	13	2472	3.66	10	Pass
HT20	MCS0	1	1	2412	4.06	10	Pass
HT20	MCS0	1	7	2442	5.92	10	Pass
HT20	MCS0	1	13	2472	3.77	10	Pass
HT40	MCS0	1	3	2422	-0.97	10	Pass
HT40	MCS0	1	7	2442	1.42	10	Pass
HT40	MCS0	1	11	2462	1.44	10	Pass
BT4.0	1Mbps	1	0	2402	9.89	10	Pass
BT4.0	1Mbps	1	19	2440	9.89	10	Pass
BT4.0	1Mbps	1	39	2480	9.49	10	Pass

Mod.	Data Rate	N <sub>TX</sub>	Ant.	Channel	Freq. (MHz)	EIRP Power Density (dBm/MHz)	Max. Limits (dBm/MHz)	Pass/Fail
HT20	MCS8	2	1+2	1	2412	6.18	10	Pass
HT20	MCS8	2	1+2	7	2442	8.66	10	Pass
HT20	MCS8	2	1+2	13	2472	6.58	10	Pass



### 3.3 Occupied Channel Bandwidth

#### 3.3.1 Limit of Occupied Channel Bandwidth

Occupied Channel Bandwidth fall completely within 2.4 GHz – 2.4835 GHz

#### 3.3.2 Measuring Instruments

The measuring equipment is listed in the section 7 of this test report.

#### 3.3.3 Test Procedure

1. The measurement procedure follows the clause 5.3.8.2.1 of the ETSI EN 300 328 V1.8.1 (2012-06).
2. The measurement shall be performed only on the lowest and the highest frequency within the stated frequency range.
3. The test procedure shall be as follows:

**Step 1:**

Connect the EUT to the spectrum analyzer and use the following settings:

Center Frequency	Channel under test
Resolution BW	1 % of the span
Video BW	3 × RBW
Frequency Span	2 × Occupied Channel Bandwidth (e.g. 40 MHz for a 20 MHz channel)
Detector	RMS
Trace Mode	Max Hold

**Step 2:**


Wait until the trace is completed.

Find the peak value of the trace and place the analyzer marker on this peak.

**Step 3:**

Use the 99 % bandwidth function of the spectrum analyzer to measure the Occupied Channel Bandwidth of the EUT.

**3.3.4 Test Setup**



**3.3.5 Test Results**

<b>Test Item :</b>	99% Occupied BW	<b>Temperature :</b>	24~26°C
<b>Test Engineer :</b>	Alex Lee	<b>Relative Humidity :</b>	51~54%

Mod.	Data Rate	N <sub>TX</sub>	Chain Port	Channel	Freq. (MHz)	99% OBW (MHz)	FL (MHz)	FH (MHz)	Pass/Fail
11b	1Mbps	1	1	1	2412	15	2404.520	2419.520	Pass
11b	1Mbps	1	1	13	2472	15.04	2464.480	2479.520	Pass
11g	6Mbps	1	1	1	2412	17.24	2403.400	2420.640	Pass
11g	6Mbps	1	1	13	2472	17.24	2463.400	2480.640	Pass
HT20	MCS0	1	1	1	2412	18.16	2402.960	2421.120	Pass
HT20	MCS0	1	1	13	2472	18.32	2462.840	2481.160	Pass
HT40	MCS0	1	1	3	2412	36.24	2403.840	2440.080	Pass
HT40	MCS0	1	1	11	2472	36.8	2443.600	2480.400	Pass
BT2.0	1Mbps	1	1	0	2402	0.831	2401.577	2402.408	Pass
BT2.0	1Mbps	1	1	78	2480	0.822	2479.580	2480.402	Pass
BT2.0	2Mbps	1	1	0	2402	1.164	2401.412	2402.576	Pass
BT2.0	2Mbps	1	1	78	2480	1.164	2479.412	2480.576	Pass
BT2.0	3Mbps	1	1	0	2402	1.164	2401.427	2402.591	Pass
BT2.0	3Mbps	1	1	78	2480	1.161	2479.427	2480.588	Pass
BT4.0	1Mbps	1	1	0	2402	1.011	2401.502	2402.513	Pass
BT4.0	1Mbps	1	1	39	2480	1.017	2479.499	2480.516	Pass



Mod.	Data Rate	N <sub>TX</sub>	Ant.	Channel	Freq. (MHz)	99% OBW (MHz)	FL (MHz)	FH (MHz)	Pass/Fail
HT20	MCS8	2	1+2	1	2412	18.28	2402.880	2421.160	Pass
HT20	MCS8	2	1+2	13	2472	18.32	2462.840	2481.160	Pass

### 3.4 Frequency Hopping Requirements

#### 3.4.1 Dwell Time and Minimum Frequency Occupation Time

##### 3.4.1.1 Limit of Dwell Time

SUBCLAUSE 4.3.1.3.2	
TEST CONDITION	LIMIT
Non-Adaptive Frequency Hopping Systems	15 ms within 15ms * hopping frequencies (N)
Adaptive Frequency Hopping Systems	0.4s within 0.4s * hopping frequencies (N)

##### Limit of Minimum Frequency Occupation Time

SUBCLAUSE 4.3.1.3.2	
TEST CONDITION	LIMIT
Normal and Extreme Temperature Conditions	The Minimum Frequency Occupation Time shall be equal to one dwell time within a period not exceeding four times the product of the dwell time per hop and the number of hopping frequencies in use.

**Remark:** This test item is not applicable to DSSS/OFDM device.

##### 3.4.1.2 Measuring Instruments

The measuring equipment is listed in the section 7 of this test report.


**3.4.1.3 Test Procedures**

1. The measurement shall be performed on a minimum of 2 hopping frequencies chosen arbitrary from the actual hopping sequence. The results as well as the frequencies on which the test was performed shall be recorded in the test report.
2. The measurement procedure follows the clause 5.3.4.2.1 of the ETSI EN 300 328 V1.8.1 (2012-06).
3. The analyzer shall be set as follows:

Center Frequency	Channel under test
Frequency Span	0 Hz
Resolution BW	300kHz
Video BW	300kHz
Detector	RMS
Sweep time	Equal to the Dwell Time × Minimum number of hopping frequencies (N)
Number of sweep points	30000
Trace Mode	Clear / Write
Trigger	Free Run

4. For accuracy measurement, the sweep time would be zoomed in and verify the dwell time which is from the dwell time per hop across the total number of hopping channel. Then record test result in the section 3.4.1.5.
5. Make the following changes on the analyzer to get Minimum Frequency Occupation Time  
Sweep time: Equal to 4 × Dwell Time × Actual number of hopping frequencies in use

**3.4.1.4 Test Setup**






**3.4.1.5 Test Results**

<b>Test Item :</b>	Dwell Time and Occupation time	<b>Temperature :</b>	24~26°C
<b>Test Engineer :</b>	Alex Lee	<b>Relative Humidity :</b>	51~54%

<b>BT (Hopping Mode)</b>		<b>Dwell Time per hop(ms)</b>	<b>Dwell Time(ms)</b>	<b>Dwell Time Max. Limit (ms)</b>	<b>Frequency Occupation Time (ms)</b>	<b>Frequency Occupation Time min. Limit (ms)</b>	<b>Pass /Fail</b>
<b>DH1</b>	2402 MHz	0.40	337.07	400	2.78	0.40	<b>Pass</b>
	2480 MHz	0.40	336.01	400	2.84	0.40	<b>Pass</b>
<b>DH3</b>	2402 MHz	1.67	271.76	400	6.54	1.67	<b>Pass</b>
	2480 MHz	1.67	270.71	400	19.49	1.67	<b>Pass</b>
<b>DH5</b>	2402 MHz	2.92	356.03	400	11.65	2.92	<b>Pass</b>
	2480 MHz	2.92	323.37	400	34.94	2.92	<b>Pass</b>




Dwell Time - Channel 00 DH1




Date: 25.DEC.2013 23:44:29

Frequency Occupation Time - Channel 00 DH1




Date: 25.DEC.2013 23:44:38

Dwell Time - Channel 00 DH3




Date: 25.DEC.2013 23:56:00

Frequency Occupation Time - Channel 00 DH3




Date: 25.DEC.2013 23:56:09

Dwell Time - Channel 00 DH5




Date: 25.DEC.2013 23:59:51

Frequency Occupation Time - Channel 00 DH5



Date: 26.DEC.2013 00:00:00





**3.4.2 Hopping Sequence**

**3.4.2.1 Limit of Hopping Sequence**

SUBCLAUSE 4.3.1.3.2	
TEST CONDITION	LIMIT
Non-Adaptive Frequency Hopping Systems	N
Adaptive Frequency Hopping Systems	N Ch 70% of band

N= 15 or 15 divided by the minimum Hopping Frequency Separation in MHz, whichever is the greater.

**Remark:** Hopping Sequence is not applicable to DSSS/OFDM device.

**3.4.2.2 Measuring Instruments**

The section 7.0 of List of Measuring Equipment of this test report is used for test.

**3.4.2.3 Test Procedures**

The measurement procedure follows the clause 5.3.4.2.1 of the ETSI EN 300 328 V1.8.1 (2012-06).

**3.4.2.4 Test Setup**




**3.4.2.5 Test Results**

<b>Test Item:</b>	Hopping Sequence	<b>Temperature :</b>	24~26°C
<b>Test Engineer :</b>	Alex Lee	<b>Relative Humidity :</b>	51~54%


Total Number of Hopping Frequency	Limit of operating channel (at least 70% of band)	Minimum Number of Adaptive Frequency Hopping	Limit of hopping frequencies at all times
79	59	20	15



Total Number of Hopping Channel Plot on Channel 00 - 78



Date: 25.DEC.2013 16:27:30



Date: 25.DEC.2013 16:28:56

### 3.4.3 Hopping Frequency Separation

#### 3.4.4.1 Limit of Hopping Frequency Separation

SUBCLAUSE 4.3.1.4.2	
TEST CONDITION	LIMIT
Non-Adaptive Frequency Hopping Systems	MAX [ OBW, 100kHz ]
Adaptive Frequency Hopping Systems	100kHz

**Remark:** Hopping Frequency Separation is not applicable to DSSS/OFDM device.


#### 3.4.4.2 Measuring Instruments

The section 7.0 of List of Measuring Equipment of this test report is used for test.

#### 3.4.4.3 Test Procedures

1. These measurements shall only be performed at normal test conditions.
2. The measurement shall be performed on 2 adjacent hopping frequencies.
3. The frequencies on which the test was performed shall be recorded.
4. The measurement procedure follows the clause 5.3.5.2.1.2 Option 2 of the ETSI EN 300 328 V1.8.1 (2012-06).

#### 3.4.4.4 Test Setup




#### 3.4.4.5 Test Results

<b>Test Item :</b>	Frequency Separation	<b>Temperature :</b>	24~26°C
<b>Test Engineer :</b>	Alex Lee	<b>Relative Humidity :</b>	51~54%

BT	Separation(MHz)	Limit(MHz)
CH 00	0.999	>0.1
CH 78	0.999	>0.1

### 3.5 Transmitter unwanted emissions in the out-of-band domain

#### 3.5.1 Transmitter unwanted emissions in the out-of-band domain limit




#### 3.5.2 Measuring Instruments

The measuring equipment is listed in the section 7 of this test report.

#### 3.5.3 Test Procedures

1. The measurement procedure follows the clause 5.3.9.2.1 of the ETSI EN 300 328 V1.8.1 (2012-06).
2. The measurements shall be performed at both normal environmental conditions and at the extremes of the operating temperature range.
3. For conducted measurements on devices with multiple transmit chains using the results for each of the transmit chains for the corresponding 1 MHz segments shall be added and compared with the transmit mask limit.

#### 3.5.4 Test Setup






**3.5.5 Test Results**

<b>Test Item :</b>	OOB Emissions	<b>Temperature :</b>	24~26°C
<b>Test Engineer :</b>	Alex Lee	<b>Relative Humidity :</b>	51~54%


Mod.	Data Rate	N <sub>TX</sub>	Channel (Low/High)	Temp. Condition	Low channel OOB Emissions (dBm/MHz)				High channel OOB Emissions (dBm/MHz)				Pass/Fail
					Freq. (MHz)	OOB Freq. (MHz)	Worst Level	Limit	Freq. (MHz)	OOB Freq. (MHz)	Worst Level	Limit	
11b	1Mbps	1	01,13	T nom	2412	2397.5	-26.16	-10	2472	2487	-25.53	-10	Pass
11b	1Mbps	1	01,13	T min	2412	2398.5	-22.29	-10	2472	2486	-24.25	-10	Pass
11b	1Mbps	1	01,13	T max	2412	2397.5	-28.72	-10	2472	2487	-27.08	-10	Pass
11g	6Mbps	1	01,13	T nom	2412	2399.5	-10.83	-10	2472	2484	-11.41	-10	Pass
11g	6Mbps	1	01,13	T min	2412	2399.5	-10.09	-10	2472	2484	-10.32	-10	Pass
11g	6Mbps	1	01,13	T max	2412	2399.5	-11.77	-10	2472	2484	-11.84	-10	Pass
11n HT20	MCS0	1	01,13	T nom	2412	2399.5	-10.45	-10	2472	2484	-10.46	-10	Pass
11n HT20	MCS0	1	01,13	T min	2412	2399.5	-10.1	-10	2472	2484	-10.59	-10	Pass
11n HT20	MCS0	1	01,13	T max	2412	2399.5	-10.91	-10	2472	2484	-10.69	-10	Pass
11n HT40	MCS0	1	03,11	T nom	2422	2398.5	-19.34	-10	2462	2484	-12.35	-10	Pass
11n HT40	MCS0	1	03,11	T min	2422	2395.5	-19.71	-10	2462	2484	-11.54	-10	Pass
11n HT40	MCS0	1	03,11	T max	2422	2399.5	-19.62	-10	2462	2484	-13.51	-10	Pass
BT2.0	1Mbps	1	hop	T nom	hop	2399.5	-19.86	-10	hop	2484	-32.77	-10	Pass
BT2.0	1Mbps	1	hop	T min	hop	2399.5	-19.87	-10	hop	2484	-33.12	-10	Pass
BT2.0	1Mbps	1	hop	T max	hop	2399.5	-20.21	-10	hop	2484	-38.14	-10	Pass
BT2.0	2Mbps	1	hop	T nom	hop	2399.5	-20.86	-10	hop	2484	-36.61	-10	Pass
BT2.0	2Mbps	1	hop	T min	hop	2399.5	-20.09	-10	hop	2484	-36.1	-10	Pass
BT2.0	2Mbps	1	hop	T max	hop	2399.5	-21.45	-10	hop	2484	-36.98	-10	Pass
BT2.0	3Mbps	1	hop	T nom	hop	2399.5	-20.94	-10	hop	2484	-36.47	-10	Pass
BT2.0	3Mbps	1	hop	T min	hop	2399.5	-20.84	-10	hop	2484	-36.57	-10	Pass
BT2.0	3Mbps	1	hop	T max	hop	2399.5	-21.79	-10	hop	2484	-37.07	-10	Pass
BT4.0	1Mbps	1	00,39	T nom	2402	2399.5	-20.04	-10	2480	2484	-33.63	-10	Pass
BT4.0	1Mbps	1	00,39	T min	2402	2399.5	-19.51	-10	2480	2484	-33.4	-10	Pass
BT4.0	1Mbps	1	00,39	T max	2402	2399.5	-20.21	-10	2480	2484	-33.89	-10	Pass



Mod.	Data Rate	N <sub>TX</sub>	Ant.	Channel (Low/High)	Temp. Condition	Low channel OOB Emissions (dBm/MHz)				High channel OOB Emissions (dBm/MHz)				Pass/Fail
						Freq. (MHz)	OOB Freq. (MHz)	Worst Level	Limit	Freq. (MHz)	OOB Freq. (MHz)	Worst Level	Limit	
11n HT20	MCS0	2	1+2	01,13	T nom	2412	2399.5	-10.57	-10	2472	2484	-10.51	-10	Pass
11n HT20	MCS0	2	1+2	01,13	T min	2412	2399.5	-10.02	-10	2472	2484	-10.27	-10	Pass
11n HT20	MCS0	2	1+2	01,13	T max	2412	2399.5	-10.53	-10	2472	2484	-10.06	-10	Pass



**Note:** Normal and extreme condition can refer to the section 1.7 of this test report.



**Note:** Normal and extreme condition can refer to the section 1.7 of this test report.



### 3.6 Transmitter spurious emissions

#### 3.6.1 Limit of Transmitter spurious emissions

Spurious emission limits for transmitter:

SUBCLAUSE 4.3.1.9.2 and 4.3.2.8.2		
FREQUENCY RANGE	MAXIMUM POWER E.R.P. ( $\leq 1$ GHZ) E.I.R.P. ( $> 1$ GHZ)	BANDWIDTH
30 MHz to 47 MHz	-36 dBm	100 kHz
47 MHz to 74 MHz	-54 dBm	100 kHz
74 MHz to 87,5 MHz	-36 dBm	100 kHz
87,5 MHz to 118 MHz	-54 dBm	100 kHz
118 MHz to 174 MHz	-36 dBm	100 kHz
174 MHz to 230 MHz	-54 dBm	100 kHz
230 MHz to 470 MHz	-36 dBm	100 kHz
470 MHz to 862 MHz	-54 dBm	100 kHz
862 MHz to 1 GHz	-36 dBm	100 kHz
1 GHz to 12,75 GHz	-30 dBm	1 MHz

#### 3.6.2 Measuring Instruments


The measuring equipment is listed in the section 7 of this test report.

#### 3.6.3 Test Procedures


1. The measurement procedure follows the clause 5.3.10.2.2 of the ETSI EN 300 328 V1.8.1 (2012-06).
2. The EUT was placed on a turntable with 1.5m height.
3. The test distance between the receiving antenna and the EUT is 3meter below 1GHz frequency range, and 3 meter for WLAN, 1.5 meter for Bluetooth which is in far field test condition for measured frequency above 1GHz, while the receiving (test) antenna is kept at 1.5 meter height.
4. Set EUT in continuous transmitting with maximum output power.
5. The table was rotated from 0 to 360 degree to search the highest radiated emission.
6. Repeating step 3 and 4 for each polarization and channel to find the worst emission level.
7. The results obtained are compared to the limits in order to prove compliance with the requirement.

### 3.6.4 Test Setup


<Below 1GHz>



<Above 1GHz for Bluetooth>




<Above 1GHz for WLAN>





3.6.5 Test Results

Test Mode :	802.11b CH13 (2472MHz) for Ant. 1	Temperature :	21~22°C
Test Engineer :	Pony Chen	Relative Humidity :	41~42%
		Polarization :	Horizontal




Condition : EN 300328 V1.81-TX LF EIRP 131014 HORIZONTAL

	Freq	Level	Over	Limit	Read	
	MHz	dBm	Limit	Line	Level	Factor
			dB	dBm	dBm	dB
1	240.49	-67.79	-31.79	-36.00	-66.17	-1.62
2	414.12	-68.01	-32.01	-36.00	-70.58	2.57
3	1982.00	-50.95	-20.95	-30.00	-67.39	16.44
4	2978.00	-50.45	-20.45	-30.00	-67.30	16.85
5 p	4946.00	-36.75	-6.75	-30.00	-56.20	19.45
6	6662.00	-48.90	-18.90	-30.00	-71.16	22.26
7	7417.00	-48.94	-18.94	-30.00	-72.46	23.52
8	12744.50	-47.56	-17.56	-30.00	-77.40	29.84



Test Mode :	802.11b CH13 (2472MHz) for Ant. 1	Temperature :	21~22°C
Test Engineer :	Pony Chen	Relative Humidity :	41~42%
		Polarization :	Vertical




Condition : EN 300328 V1.81-TX LF EIRP 131014 VERTICAL

	Freq	Level	Over	Limit	Read	
	MHz	dBm	Limit	Line	Level	Factor
			dB	dBm	dBm	dB
1	275.41	-63.28	-27.28	-36.00	-62.63	-0.65
2	414.12	-62.86	-26.86	-36.00	-65.64	2.78
3	1994.00	-51.33	-21.33	-30.00	-67.26	15.93
4	2998.00	-49.52	-19.52	-30.00	-66.56	17.04
5 p	4944.00	-30.97	-0.97	-30.00	-50.46	19.49
6	6386.00	-45.29	-15.29	-30.00	-67.15	21.86
7	7417.00	-46.65	-16.65	-30.00	-70.22	23.57
8	9889.00	-45.46	-15.46	-30.00	-70.18	24.72
9	12747.25	-48.16	-18.16	-30.00	-78.11	29.95



Test Mode :	802.11g CH01 (2412MHz) for Ant. 1	Temperature :	21~22°C
Test Engineer :	Pony Chen	Relative Humidity :	41~42%
		Polarization :	Horizontal




Condition : EN 300328 V1.81-TX LF EIRP 131014 HORIZONTAL

	Freq	Level	Over	Limit	Read	
	MHz	dBm	Limit	Line	Level	Factor
			dB	dBm	dBm	dB
1	248.25	-65.45	-29.45	-36.00	-65.02	-0.43
2	415.09	-67.69	-31.69	-36.00	-70.40	2.71
3 p	2026.00	-43.57	-13.57	-30.00	-60.06	16.49
4	2986.00	-44.04	-14.04	-30.00	-60.98	16.94
5	4656.00	-49.98	-19.98	-30.00	-70.05	20.07
6	6768.00	-48.85	-18.85	-30.00	-71.31	22.46
7	9967.00	-51.72	-21.72	-30.00	-77.31	25.59
8	12629.00	-48.00	-18.00	-30.00	-77.33	29.33



Test Mode :	802.11g CH01 (2412MHz) for Ant. 1	Temperature :	21~22°C
Test Engineer :	Pony Chen	Relative Humidity :	41~42%
		Polarization :	Vertical




Condition : EN 300328 V1.81-TX LF EIRP 131014 VERTICAL

	Freq	Level	Over	Limit	Read	
	MHz	dBm	Limit	Line	Level	Factor
			dB	dBm	dBm	dB
1	275.41	-63.28	-27.28	-36.00	-62.63	-0.65
2	414.12	-63.38	-27.38	-36.00	-66.16	2.78
3	2016.00	-43.82	-13.82	-30.00	-59.84	16.02
4 p	2970.00	-42.87	-12.87	-30.00	-59.74	16.87
5	4782.00	-49.34	-19.34	-30.00	-69.28	19.94
6	6384.00	-48.30	-18.30	-30.00	-70.16	21.86
7	9649.00	-48.51	-18.51	-30.00	-72.96	24.45
8	12670.25	-47.81	-17.81	-30.00	-77.40	29.59



Test Mode :	802.11n HT20 CH01 (2412MHz) for SISO <Ant. 1>	Temperature :	21~22°C
Test Engineer :	Pony Chen	Relative Humidity :	41~42%
		Polarization :	Horizontal




Condition : EN 300328 V1.81-TX LF EIRP 131014 HORIZONTAL

	Freq	Level	Over	Limit	Read	
	MHz	dBm	Limit	Line	Level	Factor
			dB	dBm	dBm	dB
1	255.04	-65.08	-29.08	-36.00	-65.36	0.28
2	415.09	-63.17	-27.17	-36.00	-65.88	2.71
3	1994.00	-50.76	-20.76	-30.00	-67.20	16.44
4	2998.00	-50.17	-20.17	-30.00	-67.19	17.02
5	4758.00	-45.82	-15.82	-30.00	-68.88	23.06
6	6760.00	-43.53	-13.53	-30.00	-69.86	26.33
7	9964.00	-43.72	-13.72	-30.00	-75.84	32.12
8 p	12186.25	-41.98	-11.98	-30.00	-75.76	33.78



Test Mode :	802.11n HT20 CH01 (2412MHz) for SISO <Ant. 1>	Temperature :	21~22°C
Test Engineer :	Pony Chen	Relative Humidity :	41~42%
		Polarization :	Vertical




Condition : EN 300328 V1.81-TX LF EIRP 131014 VERTICAL

	Freq	Level	Over	Limit	Read	
	MHz	dBm	Limit	Line	Level	Factor
			dB	dBm	dBm	dB
1	247.28	-62.47	-26.47	-36.00	-61.75	-0.72
2	415.09	-63.42	-27.42	-36.00	-66.39	2.97
3	1970.00	-47.13	-17.13	-30.00	-62.82	15.69
4	2976.00	-50.81	-20.81	-30.00	-67.68	16.87
5	4490.00	-46.02	-16.02	-30.00	-68.88	22.86
6	6708.00	-43.63	-13.63	-30.00	-69.73	26.10
7	9943.00	-44.00	-14.00	-30.00	-75.62	31.62
8 p	12125.75	-41.79	-11.79	-30.00	-75.41	33.62





Test Mode :	802.11n HT40 CH03 (2422MHz) for Ant. 1	Temperature :	21~22°C
Test Engineer :	Pony Chen	Relative Humidity :	41~42%
		Polarization :	Horizontal




Condition : EN 300328 V1.81-TX LF EIRP 131014 HORIZONTAL

	Freq	Level	Over	Limit	Read	
	MHz	dBm	Limit	Line	Level	Factor
			dB	dBm	dBm	dB
1	135.73	-76.40	-40.40	-36.00	-74.84	-1.56
2	890.39	-72.82	-36.82	-36.00	-80.05	7.23
3	2038.00	-50.52	-20.52	-30.00	-66.84	16.32
4	2978.00	-50.98	-20.98	-30.00	-67.83	16.85
5	4720.00	-49.94	-19.94	-30.00	-69.91	19.97
6 p	7000.00	-48.35	-18.35	-30.00	-71.31	22.96
7	8809.00	-51.56	-21.56	-30.00	-75.50	23.94
8	12607.00	-48.46	-18.46	-30.00	-77.61	29.15



Test Mode :	802.11n HT40 CH03 (2422MHz) for Ant. 1	Temperature :	21~22°C
Test Engineer :	Pony Chen	Relative Humidity :	41~42%
		Polarization :	Vertical




Condition : EN 300328 V1.81-TX LF EIRP 131014 VERTICAL

	Freq	Level	Over Limit	Limit Line	Read Level	Factor
	MHz	dBm	dB	dBm	dBm	dB
1	186.17	-75.55	-21.55	-54.00	-70.21	-5.34
2	961.20	-72.59	-36.59	-36.00	-81.20	8.61
3	2020.00	-48.88	-18.88	-30.00	-64.90	16.02
4	2992.00	-50.74	-20.74	-30.00	-67.70	16.96
5 p	4788.00	-46.08	-16.08	-30.00	-66.02	19.94
6	6390.00	-47.42	-17.42	-30.00	-69.29	21.87
7	9688.00	-50.52	-20.52	-30.00	-74.87	24.35
8	12637.25	-48.30	-18.30	-30.00	-77.67	29.37



<b>Test Mode :</b>	Bluetooth (1Mbps) CH00 (2402MHz) for Ant. 1	<b>Temperature :</b>	23~24°C
<b>Test Engineer :</b>	Eason Huang	<b>Relative Humidity :</b>	43~44%
		<b>Polarization :</b>	Horizontal




Trace: (Discrete)  
 Site : 05CH02-HY  
 Condition : 300328\_TX HORIZONTAL  
 Power : From System

	Freq	Level	Over	Limit	Read		
	MHz	dBm	Limit	Line	Level	Factor	Pol/Phase
			dB	dBm	dBm	dB	
1	232.625	-74.21	-38.21	-36.00	-69.18	-5.03	HORIZONTAL
2	303.500	-77.80	-41.80	-36.00	-75.22	-2.58	HORIZONTAL
3	2016.000	-67.26	-37.26	-30.00	-73.72	6.46	HORIZONTAL
4	2846.000	-66.50	-36.50	-30.00	-75.06	8.57	HORIZONTAL
5	4803.000	-45.32	-15.32	-30.00	-60.13	14.81	HORIZONTAL
6	7203.000	-55.58	-25.58	-30.00	-77.12	21.54	HORIZONTAL
7	12705.000	-54.65	-24.65	-30.00	-81.34	26.69	HORIZONTAL



<b>Test Mode :</b>	Bluetooth (1Mbps) CH00 (2402MHz) for Ant. 1	<b>Temperature :</b>	23~24°C
<b>Test Engineer :</b>	Eason Huang	<b>Relative Humidity :</b>	43~44%
		<b>Polarization :</b>	Vertical




Trace: (Discrete)  
 Site : 05CH02-HY  
 Condition : 300328\_TX VERTICAL  
 Power : From System

	Freq	Level	Over	Limit	Read		
	MHz	dBm	Limit	Line	Level	Factor	Pol/Phase
			dB	dBm	dBm	dB	
1	280.200	-75.27	-39.27	-36.00	-72.67	-2.60	VERTICAL
2	431.600	-80.24	-44.24	-36.00	-81.40	1.16	VERTICAL
3	2016.000	-67.53	-37.53	-30.00	-73.99	6.46	VERTICAL
4	2880.000	-66.27	-36.27	-30.00	-74.82	8.55	VERTICAL
5 @	4803.000	-42.33	-12.33	-30.00	-57.14	14.81	VERTICAL
6	7203.000	-47.49	-17.49	-30.00	-69.04	21.54	VERTICAL
7	9603.750	-51.55	-21.55	-30.00	-74.03	22.48	VERTICAL



<b>Test Mode :</b>	Bluetooth 4.0 - LE CH00 (2402MHz) for Ant. 1	<b>Temperature :</b>	23~24°C
<b>Test Engineer :</b>	Eason Huang	<b>Relative Humidity :</b>	43~44%
		<b>Polarization :</b>	Horizontal




Trace: (Discrete)  
 Site : 05CH02-HY  
 Condition : 300328\_TX HORIZONTAL  
 Power : From System

	Freq MHz	Level dBm	Over Limit dB	Limit Line dBm	Read Level dBm	Factor dB	Pol/Phase
1	144.075	-76.71	-40.71	-36.00	-72.82	-3.89	HORIZONTAL
2	902.700	-89.50	-53.50	-36.00	-94.45	4.95	HORIZONTAL
3	2126.000	-67.05	-37.05	-30.00	-73.81	6.76	HORIZONTAL
4	2890.000	-66.81	-36.81	-30.00	-75.35	8.55	HORIZONTAL
5	4803.000	-45.42	-15.42	-30.00	-60.23	14.81	HORIZONTAL
6	7203.000	-54.76	-24.76	-30.00	-76.31	21.54	HORIZONTAL
7	12712.500	-54.59	-24.59	-30.00	-81.31	26.72	HORIZONTAL



<b>Test Mode :</b>	Bluetooth 4.0 - LE CH00 (2402MHz) for Ant. 1	<b>Temperature :</b>	23~24°C
<b>Test Engineer :</b>	Eason Huang	<b>Relative Humidity :</b>	43~44%
		<b>Polarization :</b>	Vertical



Trace: (Discrete)  
 Site : 05CH02-HY  
 Condition : 300328\_TX VERTICAL  
 Power : From System

	Freq	Level	Over	Limit	Read		
	MHz	dBm	Limit	Line	Level	Factor	Pol/Phase
			dB	dBm	dBm	dB	
1	143.525	-76.22	-40.22	-36.00	-72.33	-3.89	VERTICAL
2	398.700	-80.84	-44.84	-36.00	-80.95	0.11	VERTICAL
3	2086.000	-69.28	-39.28	-30.00	-75.94	6.66	VERTICAL
4	2902.000	-66.60	-36.60	-30.00	-75.13	8.54	VERTICAL
5 @	4803.000	-42.26	-12.26	-30.00	-57.07	14.81	VERTICAL
6	7203.000	-47.21	-17.21	-30.00	-68.75	21.54	VERTICAL
7	9603.750	-51.10	-21.10	-30.00	-73.59	22.48	VERTICAL

## 4 Receiver Parameters

### 4.1 Receiver spurious emissions

#### 4.1.1 Limit of Receiver spurious emissions

FHSS spurious emission limits for receivers:

SUBCLAUSE 4.3.1.10.2		
FREQUENCY RANGE	MAXIMUM POWER E.R.P. ( $\leq$ 1 GHZ) E.I.R.P. ( $>$ 1 GHZ)	MEASUREMENT BANDWIDTH
30 MHz to 1 GHz	-57 dBm	100kHz
1 GHz to 12,75 GHz	-47 dBm	1MHz

WLAN spurious emission limits for receivers

SUBCLAUSE 4.3.2.9		
FREQUENCY RANGE	MAXIMUM POWER, E.R.P.	MEASUREMENT BANDWIDTH
30 MHz to 1 GHz	-57 dBm	100kHz
1 GHz to 12,75 GHz	-47 dBm	1MHz

#### 4.1.2 Measuring Instruments


The measuring equipment is listed in the section 7 of this test report.

#### 4.1.3 Test Procedures


1. The measurement procedure follows the clause 5.3.11.2.2 of the ETSI EN 300 328 V1.8.1 (2012-06).
2. The EUT was placed on a turntable with 1.5m height.
3. The test distance between the receiving antenna and the EUT is 3meter below 1GHz frequency range, and 3 meter which is in far field test condition for measured frequency above 1GHz, while the receiving (test) antenna is kept at 1.5 meter height.
4. Set EUT in receiving mode.
5. The table was rotated from 0 to 360 degree to search the highest radiated emission.
6. Repeating step 3 and 4 for each polarization and channel to find the worst emission level.
7. The results obtained are compared to the limits in order to prove compliance with the requirement.

### 4.1.4 Test Setup

<Below 1GHz>



<Above 1GHz>








4.1.5 Test Results

Test Mode :	802.11n HT20 CH01 (2412MHz) for SISO <Ant. 1>	Temperature :	21~22°C
Test Engineer :	Pony Chen	Relative Humidity :	41~42%
		Polarization :	Horizontal




Condition : EN 300328 V1.81-RX LF EIRP 131014 HORIZONTAL

	Freq	Level	Over Limit	Limit	Read	Factor
	MHz	dBm	dB	dBm	dBm	dB
1	245.34	-75.06	-18.06	-57.00	-74.33	-0.73
2	942.77	-72.64	-15.64	-57.00	-80.77	8.13
3	2988.00	-54.78	-7.78	-47.00	-75.13	20.35
4 p	4790.00	-53.85	-6.85	-47.00	-76.82	22.97
5	6848.00	-54.30	-7.30	-47.00	-80.51	26.21
6	9946.00	-54.47	-7.47	-47.00	-86.32	31.85
7	12123.00	-53.91	-6.91	-47.00	-87.82	33.91



Test Mode :	802.11n HT20 CH01 (2412MHz) for SISO <Ant. 1>	Temperature :	21~22°C
Test Engineer :	Pony Chen	Relative Humidity :	41~42%
		Polarization :	Vertical



Condition : EN 300328 V1.81-RX LF EIRP 131014 VERTICAL

	Freq	Level	Over	Limit	Read	
	MHz	dBm	Limit	Line	Level	Factor
			dB	dBm	dBm	dB
1	157.07	-75.28	-18.28	-57.00	-72.34	-2.94
2	997.09	-71.88	-14.88	-57.00	-80.72	8.84
3 p	1970.00	-53.19	-6.19	-47.00	-71.75	18.56
4	4582.00	-53.86	-6.86	-47.00	-77.06	23.20
5	6986.00	-53.51	-6.51	-47.00	-79.41	25.90
6	9931.00	-54.01	-7.01	-47.00	-85.34	31.33
7	12692.25	-54.72	-7.72	-47.00	-89.65	34.93

## 5 Adaptivity Test

### 5.1 Adaptivity and Receiver Blocking

#### 5.1.1 Limit of Adaptivity and Receiver Blocking

Only for adaptive systems and RF Output Power > 10 dBm

LBT based Detect and Avoid (Load Based Equipment with spectrum sharing mechanism IEEE Std.):

LBT based spectrum sharing mechanism may implement IEEE Std. 802.11-2007 clauses 15, 17, 18 or 19, in IEEE Std. 802.11n-2009, clause 20 or in IEEE Std. 802.15.4-2006,

Short Control Signaling Transmissions shall have a maximum duty cycle of 10 % within an observation period of 50 ms.


#### 5.1.2 Measurement Instruments

The measuring equipment is listed in the section 7 of this test report.

#### 5.1.3 Test Procedures

1. The measurement procedure follows the clause 5.3.7.2.1 of the ETSI EN 300 328 V1.8.1 (2012-06).
2. For conducted measurements on devices with multiple transmit chains and receive chains. The power splitter/combiner shall be used to combine all the transmit/receive chains (antenna outputs) into a single test point. The insertion loss of the power splitter/combiner shall be taken into account.

#### 5.1.4 Test Setup





5.1.5 Support Unit used in test configuration and system

Item	Instrument	Manufacturer	Model No.	Characteristics
1.	WLAN AP	D-Link	DIR-855	Dual Band AP
2.	Notebook	Lenovo	E335	FTP / LAN

5.1.6 Test Results of Adaptivity and Receiver Blocking


	Modulation	Data Rate (single)	Nominal Bandwidth	Channel	Test Frequency	Test Result
WIFI 2.4GHz	802.11b	11Mbit/s	20MHz	01	2412 MHz	PASS
				13	2472 MHz	PASS
	802.11g	54Mbit/s	20MHz	01	2412 MHz	PASS
				13	2472 MHz	PASS
	802.11n HT20	65Mbit/s	20MHz	01	2412 MHz	PASS
				13	2472 MHz	PASS
802.11n HT40	135 Mbit/s	40MHz	03	2422 MHz	PASS	
			11	2462 MHz	PASS	

Note: The CCA time is declared by the manufacturer.

	Modulation	Data Rate (single)	Nominal Bandwidth	Channel	Test Frequency	Test Result
BT	FHSS	DH5	1MHz	00	2402 MHz	PASS
				78	2480 MHz	PASS




5.1.7 Test Plots of Adaptivity Test




Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.





**Note:** Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.



**Note:** Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.







802.11n HT20 2412MHz


Maximum Channel Occupancy Time = 3.358ms

Minimum Idle Period = 150.5  $\mu$ s




Detection Level = -68.50dBm/MHz  
Interference dwell time = 60 seconds

Transmission abort within Maximum Channel Occupancy Time after interference added and the short control signaling is less than 10% duty cycle



Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.




**Note:** Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.



802.11n HT40 2422MHz



Maximum Channel Occupancy Time = 1.639ms

Minimum Idle Period = 192.4  $\mu$ s



Detection Level = -68.50dBm/MHz  
Interference dwell time = 60 seconds

Transmission abort within Maximum Channel Occupancy Time after interference added and the short control signaling is less than 10% duty cycle





Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.



802.11n HT40 2462MHz


Maximum Channel Occupancy Time = 1.458ms

Minimum Idle Period = 156.4  $\mu$ s




Detection Level = -68.50dBm/MHz  
Interference dwell time = 60 seconds


Transmission abort within Maximum Channel Occupancy Time after interference added and the short control signaling is less than 10% duty cycle



Note: Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.



**Note:** Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.



**Note:** Detection Level = -70 + 20 – EIRP + Gain for conducted measurement.

## 6 Photographs of Radiated Emission Test Configuration

**Bluetooth Tx/Rx Mode**



**Bluetooth4.0-LE Tx/Rx Mode**



**WLAN Tx/Rx Mode**

**<LF>**



**<HF>**







## 7 List of Measuring Equipment

Instrument	Manufacturer	Model No.	Serial No.	Characteristics	Calibration Date	Test Date	Due Date	Remark
Spectrum Analyzer	R&S	FSP40	100055	9kHz~40GHz	Jun. 07, 2013	Dec. 04, 2013~ Dec. 25, 2013	Jun. 06, 2014	Conducted (TH02-HY)
Power Sensor	D.A.R.E	RPR3006	13100030SN O06	9kHz~6GHz	Apr. 24, 2013	Dec. 04, 2013~ Dec. 25, 2013	Apr. 23, 2014	Conducted (TH02-HY)
Thermal Chamber	Ten Billion	TTH-D3SP	TBN-930701	N/A	Jul. 19, 2013	Dec. 04, 2013~ Dec. 25, 2013	Jul. 18, 2014	Conducted (TH02-HY)
Signal Analyzer	Rohde & Schwarz	FSQ	200578/026	20Hz~26.5GHz	Feb. 06, 2013	Dec. 04, 2013~ Dec. 25, 2013	Feb. 05, 2014	Conducted (TH02-HY)
Signal Generator(Interferer)	Rohde & Schwarz	SMJ100A	101375	9kHz~6GHz	Feb. 19, 2013	Jan. 06, 2014	Feb. 18, 2014	Conducted (TH02-HY)
Signal Generator(Blocker)	Agilent	E4438C	MY49070755	250kHz~6GHz	Oct. 08, 2013	Jan. 06, 2014	Oct. 07, 2014	Conducted (TH02-HY)
Spectrum Analyzer	Agilent	N9030A	MY52350276	3Hz~44GHz	Mar. 13, 2013	Jan. 06, 2014	Mar. 12, 2014	Conducted (TH02-HY)
Spectrum Analyzer	Agilent	E4446A	MY50180136	3Hz~44GHz	Apr. 17, 2013	Dec. 17, 2013	Apr. 16, 2014	Radiation (05CH02-HY)
Bilog Antenna	Schaffner	CBL6112B	2892	25MHz ~ 2GHz	Oct. 10, 2013	Dec. 17, 2013	Oct. 09, 2014	Radiation (05CH02-HY)
Double Ridged Guide Horn Antenna	COM-POWER	AH118	071027	1GHz ~ 18GHz	Oct. 18, 2013	Dec. 17, 2013	Oct. 17, 2014	Radiation (05CH02-HY)
Amplifier	Langer	EM330	60364	100kHz ~ 3GHz GAIN 30dB	Nov. 10, 2013	Dec. 17, 2013	Nov. 09, 2014	Radiation (05CH02-HY)
Amplifier	Agilent	8449B	3008A02321	1GHz ~ 26.5GHz	Nov. 21, 2013	Dec. 17, 2013	Nov. 20, 2014	Radiation (05CH02-HY)
Antenna Mast	INN-CO	MM 3000	N/A	N/A	N/A	Dec. 17, 2013	N/A	Radiation (05CH02-HY)
Turn Table	INN-CO	DS2000	520604	Degree 0~360	N/A	Dec. 17, 2013	N/A	Radiation (05CH02-HY)



Instrument	Manufacturer	Model No.	Serial No.	Characteristics	Calibration Date	Test Date	Due Date	Remark
Spectrum Analyzer	R&S	FSV40	101514	9kHz ~ 40GHz	Apr. 26, 2013	Dec. 18, 2013	Apr. 25, 2014	Radiation (05CH01-HY)
Amplifier	Agilent	8447D	2944A11146	100kHz ~ 1.3GHz	Jul. 05, 2013	Dec. 18, 2013	Jul. 04, 2014	Radiation (05CH01-HY)
Amplifier	Agilent	8449B	3008A02096	1GHz ~ 26.5GHz	Mar. 27, 2013	Dec. 18, 2013	Mar. 26, 2014	Radiation (05CH01-HY)
Bilog Antenna	SCHAFFNER	CBL6111C	2737	25MHz ~ 2GHz	Oct. 18, 2013	Dec. 18, 2013	Oct. 17, 2014	Radiation (05CH01-HY)
Horn Antenna	COM-POWER	AH-118	10091	1GHz ~ 18GHz	Jan. 29, 2013	Dec. 18, 2013	Jan. 28, 2014	Radiation (05CH01-HY)
RF Cable-R03m	Jye Bao	RG142	CB031	30MHz ~ 1GHz	Dec. 01, 2013	Dec. 18, 2013	Nov. 30, 2014	Radiation (05CH01-HY)
RF Cable-10m	HUBER+SUHNER	SUCOFLEX_104	SN 345675/4	1GHz ~ 26.5GHz	Dec. 01, 2013	Dec. 18, 2013	Nov. 30, 2014	Radiation (05CH01-HY)
Horn Antenna	SCHWARZBECK	BBHA9170	BBHA9170221	15GHz ~ 40GHz	Jan. 08, 2013	Dec. 18, 2013	Jan. 07, 2014	Radiation (05CH01-HY)
Turn Table	HD	DS 420	420/655/12	0 ~ 360 degree	N/A	Dec. 18, 2013	N/A	Radiation (05CH01-HY)
Antenna Mast	HD	MA 240	240/569/12	1 ~ 4 m	N/A	Dec. 18, 2013	N/A	Radiation (05CH01-HY)



## 8 Uncertainty Evaluation

Test Item	Uncertainty
Occupied Channel Bandwidth	$\pm 0.49 \%$
RF output power, conducted	$\pm 0.61 \text{ dB}$
Power density, conducted	$\pm 0.60 \text{ dB}$
Radiated emissions	$\pm 2.86 \text{ dB}$
Temperature	$\pm 0.8 \text{ }^\circ\text{C}$
Humidity	$\pm 3 \%$
Time	$\pm 0.33 \%$