

DP83TD510E-EVM User's Guide



ABSTRACT

This User's Guide discusses how to properly operate and configure the DP83TD510E-EVM. For best layout practices, schematic files, and Bill of Materials, see the associated support documents.




Figure 1-1. DP83TD510E-EVM Consists of Two PCB's: The DP83TD510E Single-Pair-Ethernet Board and The DP83822I Media-Converter Board

Table of Contents

1 Definitions	4
2 Introduction	5
2.1 Key Features	5
2.2 Block Diagram	6
2.3 Operation – Quick Setup	7
3 Board Setup Details	10
3.1 Power Supply Selection	10
3.2 Master and Slave Mode Selection – DP83TD510E	11
3.3 Clock Selection – DP83TD510E	12
3.4 SMI Connection	12
3.5 Cable Assembly	12
3.6 LED Indication	12
3.7 Serial Management Interface	12
3.8 Configuration Options	12
4 Software	14
4.1 MSP430 Driver	14
4.2 USB-2-MDIO Software	14
5 USB to MDIO procedure	15
6 Schematics	16
6.1 Main Power Schematic	16
6.2 Main Block Schematic	17
6.3 Interface Schematic	18
6.4 Analog Front End Schematic	19
6.5 COMs Schematic	21
6.6 Header Board	22
6.7 Hardware Schematic	23
7 Layout	24
7.1 Top Overlay	24
7.2 Top Layer Mask	24
7.3 Top Layer	24
7.4 Ground Layer 1	25
7.5 Signal Layer	25
7.6 Power Layer	25
7.7 Ground Layer 2	26
7.8 Bottom Layer	26
7.9 Bottom Layer Mask	26
7.10 Bottom Overlay	27
7.11 Board Assembly	27
8 Bill of Materials	29
9 Revision History	37

List of Figures

Figure 1-1. DP83TD510E-EVM Consists of Two PCB's: The DP83TD510E Single-Pair-Ethernet Board and The DP83822I Media-Converter Board	1
Figure 2-1. DP83TD510E-EVM – Top Side	5
Figure 2-2. DP83TD510E-EVM – Bottom Side	6
Figure 2-3. DP83TD510E-EVM Block Diagram	6
Figure 2-4. Wide-Vin Supply Connection	7
Figure 2-5. DP83TD510E External Supply Connection and Jumpers	8
Figure 2-6. DP83TD510E-EVM Jumper Setup	8
Figure 2-7. DP83TD510E-EVM Resistors Modification Requirement	9
Figure 2-8. DP83TD510E-EVM 822 Board Register Settings	9
Figure 3-1. DP83TD510E USB Power Supply	11
Figure 5-1. Example of Changing Extended Register to NO	15
Figure 6-1. DP83TD510E-EVM Main Power	16
Figure 6-2. DP83TD510E-EVM Main Block	17
Figure 6-3. DP83TD510E-EVM Interface	18
Figure 6-4. DP83TD510E-EVM AFE	19
Figure 6-5. DP83822I Media Converter AFE	20
Figure 6-6. DP83TD510E-EVM COMs	21

Figure 6-7. DP83TD510E-EVM break-out connector.....	22
Figure 6-8. DP83TD510E-EVM Hardware.....	23
Figure 7-1. Top Overlay.....	24
Figure 7-2. Top Layer Mask.....	24
Figure 7-3. Top Layer.....	24
Figure 7-4. Ground Layer 1.....	25
Figure 7-5. Signal Layer.....	25
Figure 7-6. Power Layer.....	25
Figure 7-7. Ground Layer 2.....	26
Figure 7-8. Bottom Layer.....	26
Figure 7-9. Bottom Layer Mask.....	26
Figure 7-10. Bottom Overlay.....	27
Figure 7-11. Top Assembly.....	27
Figure 7-12. Bottom Assembly.....	27
Figure 7-13. Drill Drawing.....	28
Figure 7-14. Board Dimensions.....	28

List of Tables

Table 1-1. Terminology.....	4
Table 3-1. DP83822 Bootstrap Resistor Designation and Suggested Bootstrap Resistor Values.....	13
Table 3-2. DP83TD510E Bootstrap Resistor Designation and Suggested Bootstrap Resistor Values.....	13
Table 8-1. Bill of Materials.....	29

Trademarks

All trademarks are the property of their respective owners.

1 Definitions

Table 1-1. Terminology

ACRONYM	DEFINITION
PHY	Physical Layer Transceiver
MAC	Media Access Controller
SMI	Serial Management Interface
MDIO	Management Data I/O
MDC	Management Data Clock
RGMII	Reduced Gigabit Media Independent Interface
SFD	Start-of-Frame Detection
VDDA	Analog Core Supply Rail
VDDIO	Digital Supply Rail
PD	Pulldown
PU	Pullup
MC	Microcontroller
AFE	Analog Front End

2 Introduction

The DP83TD510E-EVM supports 10-Mbps speed and is IEEE 802.3cg compliant. A DP83822I media converter board is provided for 10BASE-TX Standard Ethernet support and enables bit-error rate testing, interoperability testing, and PMA compliance testing. The EVM also provides on-board tools to configure PHY register using a USB-MDIO graphical user interface tool. The EVM can be powered by a Wide-Vin 5V-36V power supply or through a microUSB cable. Both DP83TD510E and DP83822I can be set to RMI Master or Slave through an on-board 25MHz crystal oscillator or the other's RMI 50MHz clock, respectively.

2.1 Key Features

- Media Converter: 10BASE-T1L to 10BASE-TX
- DP83TD510E IEEE802.3cg Compliant
- 10Base-TX interface for standard Ethernet RJ-45 connection using DP83822H
- RMI Back-to-Back Configuration
- Onboard USB2MDIO to configure PHY
 - USB-2-MDIO Support
 - 4-Pin Dip Switch
- Status LEDs
 - DP83TD510E
 - Link
 - Link + Activity
 - DP83822
 - Link
 - SMI Command
- Variable I/O Voltage Range: 1.8-V, 2.5-V, and 3.3-V
- Bootstraps for Hardware Configuration
- 10BASE-T1L Error Free Data transfer Over 1000 meters
- 10BASE-T1 Error Free Data transfer over 200 meters




Figure 2-1. DP83TD510E-EVM – Top Side




Figure 2-2. DP83TD510E-EVM – Bottom Side

2.2 Block Diagram




Figure 2-3. DP83TD510E-EVM Block Diagram

2.3 Operation – Quick Setup

The DP83TD510E block of the DP83TD510E-EVM can operate from a single DC supply connected to the terminal block J12. The DP83822I media converter board is powered by the VDDIO and VDDA supplies of the DP83TD510E board through the Samtec connector.




Figure 2-4. Wide-Vin Supply Connection

- Place shunt at J14 header in the "On-Board" position to connect VDDIO LDO
- Place shunt at J15 header in the "On-Board" position to connect VDDA LDO
- Place shunt at J16 header in the "On-Board" position to connect DVDD LDO
- Remove Shunt at J9 header
- Connect J11 to J25 for Media Converter operation
- **Wide Vin: Connect 36-V to 5-V to pin 1 of J12 and ground to pin 2 of J12**



Figure 2-5. DP83TD510E External Supply Connection and Jumpers

- Connect USB-5V Voltage jumper [J9]
- Connect LED_0 jumper [J20] to 0 instead of 1




Figure 2-6. DP83TD510E-EVM Jumper Setup

- Change R24 to 0 ohms
- Remove R199 and R200




Figure 2-7. DP83TD510E-EVM Resistors Modification Requirement

- Write 1100 to register 0000 in PHY ID: 05




Figure 2-8. DP83TD510E-EVM 822 Board Register Settings

3 Board Setup Details

3.1 Power Supply Selection

3.1.1 Onboard Power Supply Operation

- DP83TD510E Onboard Power
 - Place shunt at J14 in the "On-Board" position to enable onboard VDDIO
 - Place shunt at J15 in the "On-Board" position to enable onboard VDDA
 - Place shunt at J16 in the "On-Board" position to enable onboard DVDD
 - Remove shunt at J9
- DP83822I Onboard Power
 - Populate R5, R6 to deliver power through J25 from DP83TD510E board

3.1.2 External Power Supply Operation

- DP83TD510E External Power
 - Place shunt at J14 in the "EXT" position
 - Place shunt at J15 in the "EXT" position
 - Place shunt at J16 in the "EXT" position
 - Connect 1.0V to DVDD-EXT on J16
 - Connect 3.3-V or 1.8V to VDDA-EXT on J15
 - Connect 1.8-V, 2.5-V, or 3.3-V to VDDIO-EXT on J14
 - Connect ground to GND on J12 pin 2
- DP83822I External Power
 - Remove R5, R6 to disconnect VDDA, VDDIO from DP83TD510E board
 - Place shunt at J26 in the "EXT" position to disable onboard VDDA
 - Place shunt at J27 in the "EXT" position to disable onboard VDDIO
 - Connect 3.3-V or 1.8-V to VDDA-EXT on J21 or J26
 - Connect 1.8-V, 2.5-V, or 3.3-V to VDDIO-EXT on J21 or J27
 - Connect ground to GND on J21

3.1.3 USB Power Supply Option

DP838TD510E block powered by USB.

- Plug in micro-USB to J4
- Place shunt at J9
- Place shunt at J14 in the "On-Board" position
- Place shunt at J15 in the "On-Board" position
- Place shunt at J16 in the "On-Board" position

Note

Only populate J9 when powering over USB.




Figure 3-1. DP83TD510E USB Power Supply

3.2 Master and Slave Mode Selection – DP83TD510E

3.2.1 DP83TD510E in RMII Master Mode, DP83822I in RMII Slave Mode (default)

- Populate R149
- Remove R143, R136, R91
- Set the correct hardware straps or perform the correct software write.

Hardware Strapping

- Populate R84, R103 with 2.49k (1%)
- Place shunt on LED_0, J20 in "Mode 0" position

Software Programming

- DP83TD510E
 - Write register 0x0017[5]=1
 - Write register 0x0017[7]=0
- DP83822I
 - Write register 0x0017[5]=1
 - Write register 0x0017[7]=1

3.2.2 DP83TD510E in Slave Mode, DP83822I in Master Mode

- Populate R136, 138, R143, R25
- Remove R135, R137, R149, R91
- Set the correct hardware straps or perform the correct software write.

Hardware Strapping

- Populate R84, R103 with 5.76k (1%), R108 with 2.49k (1%)
- Place shunt on J20 in "Mode 1" position

Software Programming

- DP83822I
 - Write register 0x0017[5]=1
 - Write register 0x0017[7]=0
- DP83TD510E
 - Write register 0x0017[5]=1
 - Write register 0x0017[7]=1

3.3 Clock Selection – DP83TD510E

3.3.1 50 MHz Reference Clock for DP83TD510E in RMII Slave Mode

- Remove R135, R137, R149
- Populate R143, R25

3.3.2 External Clock

- Remove R135
- Populate R134, J7
- Provide External Clock to SMA at J7

3.3.3 On-Board 25 MHz crystal

- Remove R134, R143, R25
- Populate R135, R137

3.4 SMI Connection

In Media Converter configurations, the MDIO/MDC lines of the DP83TD510E and DP83822I are tied together. Both PHYs can be accessed simultaneously. The DP83TD510E has been set to PHY address 00 and the DP83822I has been set to PHY address 05.

- Connect micro-USB to J4
- For direct access to MDIO, MDC lines, populate headers at J22, J23, on DP83TD510E and/or J13, J28 on DP83822I

3.5 Cable Assembly

- Plug a CAT5, CAT5E, or CAT6 cable into the RJ45 connector J2
 - Connect the far-end of the Ethernet cable to a 10BASE-TX capable PHY
- Plug a Single-Pair-Ethernet wires into the terminal block J1 as labeled
 - Connect the far-end of the cable to a 10BASE-T1L capable PHY

3.6 LED Indication

- Look for LED_0 and LED_1 to illuminate when a link is successfully established
- Look for Green LED to illuminate on the RJ45 connector J2 when a link is successfully established (in media convertor mode)
- LED_1 will blink for TX/RX activity

3.7 Serial Management Interface

The DP83TD510E-EVM supports SMI (MDIO/MDC) through J22, J23 and includes an onboard MSP430F5529 for USB-2-MDIO control.

Notes:

- DP83TD510E default PHY_ID is 0
- DP83822 default PHY_ID is 5
- PHY IDs can be changed through bootstrap options found in the data sheet

3.8 Configuration Options

3.8.1 Bootstrap Options

Some DP83TD510E and DP83822 configurations can be done through bootstrap options. Options can be selected with jumpers or resistor population. Refer to the data sheets for bootstrap options and the schematic and layout sections of this User's Guide for resistor locations.

Table 3-1. DP83822 Bootstrap Resistor Designation and Suggested Bootstrap Resistor Values

PIN NAME	PIN NUMBER	STRAP MODE	PU RESISTOR (K Ω)	PU RESISTOR DESIGNATION	PD RESISTOR (K Ω)	PD RESISTOR DESIGNATION
RX_DV	26	1	OPEN	R103	OPEN	R108
		2	10		2.49	
		3	5.76		2.49	
		4	2.49		OPEN	

Table 3-2. DP83TD510E Bootstrap Resistor Designation and Suggested Bootstrap Resistor Values

PIN NAME	PIN NUMBER	STRAP MODE	PU RESISTOR (K Ω)	PU RESISTOR DESIGNATION	PD RESISTOR (K Ω)	PD RESISTOR DESIGNATION
RX_D0	26	0	OPEN	R99	2.49	R104
		1	2.49		OPEN	
RX_D1	25	0	OPEN	R100	2.49	R105
		1	2.49		OPEN	
RX_D2	24	0	OPEN	R101	2.49	R106
		1	2.49		OPEN	
RX_D3	14	0	OPEN	R102	2.49	R107
		1	2.49		OPEN	
RX_DV	15	0	OPEN	R103	2.49	R108
		1	2.49		OPEN	
LED_0	35	0	OPEN	R185	2.49	R201
		1	2.49		OPEN	
LED_2	6	0	OPEN	R187	2.49	R203
		1	2.49		OPEN	

4 Software

The on-board MSP430 comes pre-programmed and ready to use. When using this EVM for the first time on a Windows 7 (or above) PC, MSP430 drivers and USB-2-MDIO software utility will have to be installed. USB-2-MDIO software can be used for accessing the PHY's registers. In the case where an external MSP430 or ezFET is needed, the user may simply connect the TST and RST pins of their device to the DP83TD510E-EVM

4.1 MSP430 Driver

Install the latest MSP430 driver from this website: http://software-dl.ti.com/msp430/msp430_public_sw/mcu/msp430/MSP430_FET_Drivers/latest/index_FDS.html

4.2 USB-2-MDIO Software

Download the software from <https://www.ti.com/tool/usb-2-mdio>.

The web page also contains the User's Guide for installing and using the software. Since the MSP430 is on-board the DP83TD510E-EVM, it is not necessary to purchase a separate MSP430 Launchpad kit and connect to the PHY using wires. In the case the on-board MSP430 cannot be used for some reason, MDIO and MDC pins are also broken out on J23 and J22 pins, respectively. Users can connect an MSP430 launchpad or their own MDIO-MDC utility on J23 and J22 to access the PHY.

5 USB to MDIO procedure

Please follow the procedure below when using USB to MDIO GUI for 510 EVM application:

1. Follow the general [USB to MDIO userguide](#):
2. Change the extended register to No.




Figure 5-1. Example of Changing Extended Register to NO

3. Use 000D and 000E for extended register.

2.4 Vpp with Extended Register Example:

```
//Set Output operating mode for 2.4 Vpp
begin
000D 0001
000E 08F6
000D 4001
000E 1000 //enable 2.4 Vpp operating mode

000D 0007
000E 020E
000D 4007
000E B000 //increase the transmit level

000D 001F
000E 0010
000D 401F
000E 4000 //soft reset
end
```

1V Vpp with Extended Register Example:

```
//Set Output operating mode for 1V Vpp
begin
000D 0001
000E 08F6
000D 4001
000E 0000 //enable 1 Vpp operating mode

000D 0007
000E 020E
000D 4007
000E 8000 //do not increase the transmit level

000D 001F
000E 0010
000D 401F
000E 4000 //soft reset
end
```

6 Schematics

6.1 Main Power Schematic




Figure 6-1. DP83TD510E-EVM Main Power



Figure 6-2. DP83TD510E-EVM Main Block

6.3 Interface Schematic




Figure 6-3. DP83TD510E-EVM Interface




Figure 6-4. DP83TD510E




Figure 6-5. DP83822I Media Converter AFE

Figure 6-6. DP83TD510E-EVM COMs




Figure 6-7. DP83TD510E-EVM break-out connector

6.7 Hardware Schematic




Figure 6-8. DP83TD510E-EVM Hardware

7 Layout

7.1 Top Overlay




Figure 7-1. Top Overlay

7.2 Top Layer Mask




Figure 7-2. Top Layer Mask

7.3 Top Layer




Figure 7-3. Top Layer

7.4 Ground Layer 1




Figure 7-4. Ground Layer 1

7.5 Signal Layer




Figure 7-5. Signal Layer

7.6 Power Layer




Figure 7-6. Power Layer

7.7 Ground Layer 2




Figure 7-7. Ground Layer 2

7.8 Bottom Layer




Figure 7-8. Bottom Layer

7.9 Bottom Layer Mask




Figure 7-9. Bottom Layer Mask




Figure 7-13. Drill Drawing




Figure 7-14. Board Dimensions

8 Bill of Materials

Table 8-1. Bill of Materials

Designator	Qty	Value	Description	Package Reference	Part Number	Manufacturer
C1, C3, C5, C7	4	1uF	CAP, CERM, 1 uF, 10 V, +/- 10%, X7S, AEC-Q200 Grade 1, 0402	0402	GCM155C71A105KE38D	MuRata
C2, C4, C6, C8	4	0.1uF	CAP, CERM, 0.1 uF, 16 V, +/- 10%, X7R, 0402	0402	885012205037	Wurth Elektronik
C10, C130	2	4700pF	CAP, CERM, 4700 pF, 2000 V, +/- 10%, X7R, 1812	1812	1812GC472KAT1A	AVX
C14, C15	2	10pF	CAP, CERM, 10 pF, 16 V, +/- 10%, C0G, 0402	0402	C0402C100K4GACTU	Kemet
C16, C17, C89	3	0.1uF	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402	GCM155R71H104KE02D	MuRata
C18	1	4.7uF	CAP, TA, 4.7 uF, 35 V, +/- 10%, 1.3 ohm, SMD	7343-31	293D475X9035D2TE3	Vishay-Sprague
C19, C27, C28, C29	4	0.1uF	CAP, CERM, 0.1 uF, 10 V, +/- 10%, X7R, 0402	0402	C0402C104K8RACTU	Kemet
C20, C21	2	36pF	CAP, CERM, 36 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402	CL05C360JB5NNNC	Samsung Electro-Mechanics
C22, C25	2	0.22uF	CAP, CERM, 0.22 uF, 16 V, +80/-20%, Y5V, 0603	0603	C0603C224Z4VACTU	Kemet
C23	1	0.47uF	CAP, CERM, 0.47 uF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603	GCM188R71C474KA55D	MuRata
C24	1	4.7uF	CAP, CERM, 4.7 uF, 35 V, +/- 10%, X5R, 0603	0603	C1608X5R1V475K080AC	TDK
C26	1	10uF	CAP, TA, 10 uF, 35 V, +/- 10%, 0.125 ohm, SMD	7343-31	TPSD106K035R0125	AVX
C30, C64, C72	3	1000pF	CAP, CERM, 1000 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402	GRM1555C1H102JA01D	MuRata
C57, C62, C65, C70, C101, C102	6	10uF	CAP, CERM, 10 uF, 10 V, +/- 20%, X7T, 0603	0603	GRM188D71A106MA73D	MuRata
C58, C66, C83, C113	4	1uF	CAP, CERM, 1 uF, 6.3 V, +/- 20%, X7R, 0402	0402	GRM155R70J105MA12D	MuRata
C59, C67	2	0.1uF	CAP, CERM, 0.1 uF, 50 V, +/- 20%, X7R, AEC-Q200 Grade 1, 0402	0402	CGA2B3X7R1H104M050BB	TDK
C60, C63, C68, C71, C77, C82	6	0.01uF	CAP, CERM, 0.01 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402	CGA2B3X7R1H103K050BB	TDK
C61, C69	2	100pF	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0402	0402	CGA2B2C0G1H101J050BA	TDK

Table 8-1. Bill of Materials (continued)

Designator	Qty	Value	Description	Package Reference	Part Number	Manufacturer
C78, C79, C80, C81, C97, C98, C99, C100	8	22pF	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0402	0402	GCM1555C1H220JA16D	MuRata
C84	1	100uF	CAP, AL, 100 uF, 50 V, +/- 20%, SMD	HA0	EMVE500ADA101MHA0G	Chemi-Con
C85, C87, C117	3	4.7uF	CAP, CERM, 4.7 uF, 50 V, +/- 10%, X7R, AEC- Q200 Grade 1, 1210	1210	CGA6P3X7R1H475K250AB	TDK
C86, C88	2	0.22uF	CAP, CERM, 0.22 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603	CGA3E3X7R1H224K080AB	TDK
C90	1	1uF	CAP, CERM, 1 uF, 35 V, +/- 20%, X5R, 0402	0402	GRM155R6YA105ME11D	MuRata
C91, C94	2	10uF	CAP, CERM, 10 uF, 35 V, +/- 20%, X5R, 0603	0603	GRM188R6YA106MA73D	Murata
C92, C93	2	2.2uF	CAP, CERM, 2.2 uF, 16 V, +/- 10%, X6S, 0402	0402	GRM155C81C225KE11D	MuRata
C95	1	470pF	CAP, CERM, 470 pF, 100 V, +/- 5%, X7R, 0603	0603	06031C471JAT2A	AVX
C96	1	1uF	CAP, CERM, 1 uF, 35 V, +/- 10%, X7R, AEC- Q200 Grade 1, 0603	0603	CGA3E1X7R1V105K080AC	TDK
C105, C111	2	0.01uF	CAP, CERM, 0.01 uF, 25 V, +/- 10%, X7R, 0201	0201	GRM033R71E103KE14D	MuRata
C107, C109	2	10uF	CAP, CERM, 10 uF, 6.3 V, +/- 20%, X7S, 0603	0603	C1608X7S0J106M080AC	TDK
C114	1	100uF	CAP, AL, 100 uF, 16 V, +/- 20%, 0.26 ohm, AEC-Q200 Grade 2, SMD	SMT Radial D	EEEF1C101AP	Panasonic
C115	1	10uF	CAP, CERM, 10 uF, 25 V, +/- 10%, X7S, 0805	0805	GRM21BC71E106KE11L	MuRata
C116	1	4.7uF	CAP, CERM, 4.7 uF, 10 V, +/- 10%, X7S, 0603	0603	C1608X7S1A475K080AC	TDK
C118, C128	2	0.22uF	CAP, CERM, 0.22 uF, 10 V, +/- 10%, X5R, 0402	0402	GRM155R61A224KE19D	MuRata
C122	1	27pF	CAP, CERM, 27 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402	GJM1555C1H270JB01	MuRata
C123, C124	2	100pF	CAP, CERM, 100 pF, 50 V, +/- 1%, C0G/NP0, 0402	0402	04025A101FAT2A	AVX
C131	1	0.01uF	CAP, CERM, 0.01 uF, 1500 V, +/- 10%, X7R, 1812	1812	1812SC103KAT1A	AVX
D1, D2, D5, D11, D12, D13, D14, D15, LD1, LD2, LD3, LD4	12	Green	LED, Green, SMD	2x1.25mm	QTL630C4TR	Everlight

Table 8-1. Bill of Materials (continued)

Designator	Qty	Value	Description	Package Reference	Part Number	Manufacturer
D3, D4	2	Rg	LED, Rg, SMD	1.6x0.8mm	HSMF-C165	Avago
D7	1	60V	Diode, Schottky, 60 V, 1 A, AEC-Q101, SMA	SMA	NRVBA160T3G	ON Semiconductor
H2, H3, H4, H9, H10	5		Machine Screw, Round, #4-40 x 1/4, Nylon, Phillips panhead	Screw	NY PMS 440 0025 PH	B&F Fastener Supply
H6, H7, H8, H11, H12	5		Standoff, Hex, 0.5"L #4-40 Nylon	Standoff	1902C	Keystone
J1	1		Terminal Block, 5mm, 3x1, R/A, TH	Terminal Block, 5mm, 3x1, R/A, TH	1792876	Phoenix Contact
J2	1		Connector, RJ45 with integrated magnetics, 1x1, Gold, R/A, SMT	Connector, RJ-45 with integrated magnetics, 1x1, R/A, SMT	J3011G21DNL	Pulse Engineering
J3	1		Header, 100mil, 2x2, Gold, TH	2x2 Header	TSW-102-07-G-D	Samtec
J4	1		Connector, Receptacle, Micro-USB Type AB, R/A, Bottom Mount SMT	5.6x2.5x8.2mm	475890001	Molex
J9	1		Header, 100mil, 2x1, Gold, TH	2x1 Header	TSW-102-07-G-S	Samtec
J11	1		Receptacle, 0.8mm, 30x2, Gold, Edge Mount	Receptacle, 0.8mm, 30x2, Edge Mount	ERF8-030-01-L-D-EM2-TR	Samtec
J12	1		Terminal Block, 2x1, 2.54mm, TH	Terminal Block, 2x1, 2.54mm, TH	282834-2	TE Connectivity
J14, J15, J16, J17, J18, J19, J20, J26, J27	9		Header, 100mil, 3x1, Gold, TH	3x1 Header	TSW-103-07-G-S	Samtec
J25	1		Receptacle, 0.8mm, 30x2, Tin, Edge mount	Receptacle, 0.8mm, 30x2, Edge mount	ERM8-030-01-L-D-EM2-TR	Samtec
L1	1	10uH	Inductor, Shielded, Ferrite, 10 uH, 2.75 A, 0.128 ohm, SMD	Inductor, 5.7x2.8x5.2mm	SRP5030T-100M	Bourns
L3	1	2.2mH	Coupled inductor, 2.2 mH, 0.75 A, 0.3 ohm, SMD	8.7x10mm	744272222	Würth Elektronik
R1, R2, R3, R4	4	49.9	RES, 49.9, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040249R9FKED	Vishay-Dale
R5, R6, R119, R135, R137, R149, R157, R169, R209	9	0	RES, 0, 5%, 0.063 W, 0402	0402	RC0402JR-070RL	Yageo America

Table 8-1. Bill of Materials (continued)

Designator	Qty	Value	Description	Package Reference	Part Number	Manufacturer
R7, R150	2	1.00Meg	RES, 1.00 M, 1%, 1 W, 2010	2010	HVCB2010FKC1M00	Stackpole Electronics Inc
R8, R12, R15, R26, R27, R28, R84, R86, R87, R88, R89, R92, R97, R98, R100, R103, R104, R188, R199, R200, R201, R202, R203, R204	24	2.49k	RES, 2.49 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW04022K49FKED	Vishay-Dale
R9, R13, R145, R194, R195, R196	6	470	RES, 470, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW0402470RJNED	Vishay-Dale
R14, R128	2	49.9	RES, 49.9, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	RMCF0402FT49R9	Stackpole Electronics Inc
R16, R17, R45, R46, R126, R129	6	0	RES, 0, 0%, 0.2 W, AEC-Q200 Grade 0, 0402	0402	CRCW04020000Z0EDHP	Vishay-Dale
R18, R23	2	27	RES, 27, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040227R0JNED	Vishay-Dale
R19, R124	2	2.0k	RES, 2.0 k, 5%, 1 W, AEC-Q200 Grade 0, 2512	2512	CRCW25122K00JNEG	Vishay-Dale
R21, R22	2	200k	RES, 200 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW0603200KJNEA	Vishay-Dale
R24	1	33	RES, 33, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040233R0JNED	Vishay-Dale
R29, R34, R44, R192, R205, R206, R207, R208	8	470	RES, 470, 1%, 0.1 W, AEC-Q200 Grade 0, 0402	0402	ERJ-2RKF4700X	Panasonic
R30, R31, R32, R33	4	0	RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0402	0402	ERJ-2GE0R00X	Panasonic
R35, R43	2	0	RES, 0, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW04020000Z0ED	Vishay-Dale
R36, R37, R38, R39	4	470	RES, 470, 5%, 0.05 W, 0201	0201	RC0201JR-07470RL	Yageo America
R40	1	1.40k	RES, 1.40 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW04021K40FKED	Vishay-Dale
R41	1	1.00Meg	RES, 1.00 M, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW04021M00FKED	Vishay-Dale

Table 8-1. Bill of Materials (continued)

Designator	Qty	Value	Description	Package Reference	Part Number	Manufacturer
R42	1	47k	RES, 47 k, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040247K0JNED	Vishay-Dale
R90, R111, R120, R122, R123, R125, R139, R140	8	2.20k	RES, 2.20 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW04022K20FKED	Vishay-Dale
R99	1	10.0k	RES, 10.0 k, 1%, 0.063 W, 0402	0402	RC0402FR-0710KL	Yageo America
R109, R110, R112, R113	4	0	RES, 0, 5%, 0.1 W, 0603	0603	RC0603JR-070RL	Yageo
R115, R117	2	374k	RES, 374 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW0402374KFKED	Vishay-Dale
R116, R118	2	1.00Meg	RES, 1.00 M, 1%, 0.1 W, 0402	0402	ERJ-2RKF1004X	Panasonic
R121	1	4.87k	RES, 4.87 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW04024K87FKED	Vishay-Dale
R142	1	100k	RES, 100 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW0603100KFKEA	Vishay-Dale
R144	1	100k	RES, 100 k, 0.5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW0402100KDHP	Vishay-Dale
R146	1	24.9k	RES, 24.9 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW060324K9FKEA	Vishay-Dale
R148	1	165k	RES, 165 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW0402165KFKED	Vishay-Dale
R151, R165	2	33.2k	RES, 33.2 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040233K2FKED	Vishay-Dale
R152	1	22.6k	RES, 22.6 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040222K6FKED	Vishay-Dale
R153, R166	2	13.3k	RES, 13.3 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040213K3FKED	Vishay-Dale
R163, R173	2	10.7k	RES, 10.7 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040210K7FKED	Vishay-Dale
R176	1	10.0k	RES, 10.0 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW060310K0FKEA	Vishay-Dale
R177	1	1.13k	RES, 1.13 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW06031K13FKEA	Vishay-Dale

Table 8-1. Bill of Materials (continued)

Designator	Qty	Value	Description	Package Reference	Part Number	Manufacturer
R178	1	4.53k	RES, 4.53 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	CRCW06034K53FKEA	Vishay-Dale
R181	1	1.0Meg	RES, 1.0 M, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010	CRCW20101M00JNEF	Vishay-Dale
R221, R222, R223	3	0	RES, 0, 5%, 0.05 W, 0201	0201	CRCW02010000Z0ED	Vishay-Dale
S2, S3, S4	3		Switch, Normally open, 2.3N force, 200k operations, SMD	KSR	KSR221GLFS	C&K Components
SH-J1, SH-J2, SH-J3, SH-J4, SH-J5, SH-J6, SH-J7, SH-J8, SH-J9, SH-J10	10		Single Operation 2.54mm Pitch Open Top Jumper Socket	Single Operation 2.54mm Pitch Open Top Jumper Socket	M7582-05	Harwin
U1	1		Automotive 4-Channel ESD Protection Solution for SuperSpeed (up to 5 Gbps) Interface, DQA0010A (USON-10)	DQA0010A	TPD4E05U06QDQARQ1	Texas Instruments
U2, U3	2		Dual Bidirectional Multi-Voltage Level Translator, DQE0008A (X2SON-8)	DQE0008A	LSF0102DQER	Texas Instruments
U9	1		25 MHz Mixed Signal Microcontroller with 128 KB Flash, 8192 B SRAM and 63 GPIOs, -40 to 85 degC, 80-pin QFP (PN), Green (RoHS & no Sb/Br)	PN0080A	MSP430F5529IPN	Texas Instruments
U13	1		802.3cg 10-M Single-Pair Ethernet PHY for 1000 Meter, RHB0032M (VQFN-32)	RHB0032M	DP83TD510ERHBR	Texas Instruments
U14	1		Robust, Low Power 10/100 Ethernet Physical Layer Transceiver Extended Temperature, RHB0032B (VQFN-32)	RHB0032B	DP83822HRHBR	Texas Instruments
U15	1		3.8-V to 36-V 2-A Synchronous Step-Down Voltage Regulator, RNX0012B (VQFN-HR-12)	RNX0012B	LMR33620ARNXT	Texas Instruments
U16	1		Single Output Low Noise LDO, 500 mA, Adjustable 1.3 to 6.5 V Output, 2.5 to 16 V Input, 8-pin SOIC (D), -40 to 125 degC, Green (RoHS & no Sb/Br)	D0008A	TL5209DR	Texas Instruments
U17	1		Dual 500mA Low-Noise (3.8µVRMS) LDO Voltage Regulator, RTJ0020D (WQFN-20)	RTJ0020D	TPS7A8701RTJR	Texas Instruments

Table 8-1. Bill of Materials (continued)

Designator	Qty	Value	Description	Package Reference	Part Number	Manufacturer
U19	1		Single Output LDO, 500mA, Adj. (0.8 to 3.6V), Programmable Soft-Start, DRC0010J (VSON-10)	DRC0010J	TPS74701DRCR	Texas Instruments
Y1	1		Crystal, 24 MHz, 20pF, SMD	3.2x2.5mm	ECS-240-20-33-DU-TR	ECS Inc.
Y4, Y5	2		Crystal, 25 MHz, 12pF, AEC-Q200 Grade 1, SMD	3.2x2.5mm	ABM8AIG-25.000MHZ-12-2Z-T3	Abracon Corporation
C9, C11, C12, C13	0	0.01uF	CAP, CERM, 0.01 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402	CGA2B3X7R1H103K050BB	TDK
C73	0	10uF	CAP, CERM, 10 uF, 10 V, +/- 20%, X7T, 0603	0603	GRM188D71A106MA73D	MuRata
C74	0	1uF	CAP, CERM, 1 uF, 6.3 V, +/- 20%, X7R, 0402	0402	GRM155R70J105MA12D	MuRata
C75	0	0.1uF	CAP, CERM, 0.1 uF, 50 V, +/- 20%, X7R, AEC-Q200 Grade 1, 0402	0402	CGA2B3X7R1H104M050BB	TDK
C103, C104, C108, C110	0	10uF	CAP, CERM, 10 uF, 6.3 V, +/- 20%, X7S, 0603	0603	C1608X7S0J106M080AC	TDK
C106, C112	0	0.01uF	CAP, CERM, 0.01 uF, 25 V, +/- 10%, X7R, 0201	0201	GRM033R71E103KE14D	MuRata
C127, C135	0	0.01uF	CAP, CERM, 0.01 uF, 50 V, +/- 5%, X7R, 0402	0402	C0402C103J5RACTU	Kemet
FID1, FID2, FID3, FID4, FID5, FID6	0		Fiducial mark. There is nothing to buy or mount.	N/A	N/A	N/A
J7	0		Connector, SMA, TH	SMA	142-0701-201	Cinch Connectivity
J13, J22, J23, J28	0		Header, 1x1, Tin, TH	Header, 1x1	PEC01SAAN	Sullins Connector Solutions
J21	0		Terminal Block, 2.54mm, 5 Pos, Tin, Green, R/A, TH	Terminal Block, 2.54mm, 5 Pos, R/A, TH	282834-5	TE Connectivity
R10, R79, R80, R81, R82, R85, R91, R94, R95, R105, R106, R107, R108	0	2.49k	RES, 2.49 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW04022K49FKED	Vishay-Dale
R11, R47, R48, R49, R50, R51, R52, R53, R83	0	2.20k	RES, 2.20 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW04022K20FKED	Vishay-Dale
R20, R93	0	1.00k	RES, 1.00 k, 1%, 0.1 W, 0402	0402	ERJ-2RKF1001X	Panasonic

Table 8-1. Bill of Materials (continued)

Designator	Qty	Value	Description	Package Reference	Part Number	Manufacturer
R25, R134, R136, R138, R143, R158, R159, R160, R161, R162, R170, R171, R172, R210	0	0	RES, 0, 5%, 0.063 W, 0402	0402	RC0402JR-070RL	Yageo America
R101, R102	0	5.76k	RES, 5.76 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW04025K76FKED	Vishay-Dale
R114	0	0	RES, 0, 5%, 0.1 W, 0603	0603	RC0603JR-070RL	Yageo
R127, R213	0	160k	RES, 160 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW0402160KFKED	Vishay-Dale
R141, R147, R212	0	0	RES, 0, 0%, 0.2 W, AEC-Q200 Grade 0, 0402	0402	CRCW04020000Z0EDHP	Vishay-Dale
R154, R167	0	33.2k	RES, 33.2 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040233K2FKED	Vishay-Dale
R155	0	22.6k	RES, 22.6 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040222K6FKED	Vishay-Dale
R156, R168	0	13.3k	RES, 13.3 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040213K3FKED	Vishay-Dale
R164, R174	0	10.7k	RES, 10.7 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402	CRCW040210K7FKED	Vishay-Dale
R179, R180	0	1.50k	RES, 1.50 k, 1%, 0.1 W, 0603	0603	RC0603FR-071K5L	Yageo
U18	0		Dual 500mA Low-Noise (3.8 μ VRMS) LDO Voltage Regulator, RTJ0020D (WQFN-20)	RTJ0020D	TPS7A8701RTJR	Texas Instruments

9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision A (August 2020) to Revision B (May 2022)		Page
• Updated the Operation - Quick Setup for the DP83TD510E-EVM		7
• Update the USB to MDIO procedure.....		15
Changes from Revision * (March 2020) to Revision A (August 2020)		Page
• Initial public release.....		16

DRAFT ONLY
TI Confidential – NDA Restrictions

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2022, Texas Instruments Incorporated