Hex inverting Schmitt trigger Rev. 7 — 19 November 2015

Product data sheet

#### 1. **General description**

The 74HC14; 74HCT14 is a hex inverter with Schmitt-trigger inputs. This device features reduced input threshold levels to allow interfacing to TTL logic levels. Inputs also include clamp diodes, this enables the use of current limiting resistors to interface inputs to voltages in excess of V<sub>CC</sub>. Schmitt trigger inputs transform slowly changing input signals into sharply defined jitter-free output signals.

#### **Features and benefits** 2.

- Complies with JEDEC standard no. 7A
- Low-power dissipation
- ESD protection:
  - HBM JESD22-A114F exceeds 2000 V
  - MM JESD22-A115-A exceeds 200 V
- Multiple package options
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C

#### **Applications** 3.

- Wave and pulse shapers
- Astable multivibrators
- Monostable multivibrators




### 4. Ordering information

#### Table 1. Ordering information


Type number	Package						
	Temperature range	Name	Description	Version			
74HC14D	–40 °C to +125 °C	SO14	plastic small outline package; 14 leads; body width	SOT108-1			
74HCT14D	-		3.9 mm				
74HC14DB	–40 °C to +125 °C	SSOP14	plastic shrink small outline package; 14 leads; body	SOT337-1			
74HCT14DB	-		width 5.3 mm				
74HC14PW	–40 °C to +125 °C	TSSOP14	plastic thin shrink small outline package; 14 leads;	SOT402-1			
74HCT14PW	-		body width 4.4 mm				
74HC14BQ	–40 °C to +125 °C	DHVQFN14	plastic dual in-line compatible thermal enhanced very	SOT762-1			
74HCT14BQ			thin quad flat package; no leads; 14 terminals; body $2.5 \times 3 \times 0.85$ mm				

### 5. Functional diagram



### 6. Pinning information

### 6.1 Pinning



#### 6.2 Pin description

#### Table 2. Pin description

Symbol	Pin	Description
1A to 6A	1, 3, 5, 9, 11, 13	data input 1
1Y to 6Y	2, 4, 6, 8, 10, 12	data output 1
GND	7	ground (0 V)
V <sub>CC</sub>	14	supply voltage

### 7. Functional description

#### Table 3. Function table<sup>[1]</sup>

Input	Output
nA	nY
L	Н
Н	L

[1] H = HIGH voltage level;

L = LOW voltage level.

### 8. Limiting values

#### Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V <sub>CC</sub>	supply voltage			-0.5	+7	V
I <sub>IK</sub>	input clamping current	$V_{I} < -0.5$ V or $V_{I} > V_{CC} + 0.5$ V	<u>[1]</u>	-	±20	mA
I <sub>OK</sub>	output clamping current	$V_{O}$ < -0.5 V or $V_{O}$ > $V_{CC}$ + 0.5 V	<u>[1]</u>	-	±20	mA
lo	output current	$-0.5 \text{ V} < \text{V}_{\text{O}} < \text{V}_{\text{CC}} + 0.5 \text{ V}$		-	±25	mA
I <sub>CC</sub>	supply current			-	50	mA
I <sub>GND</sub>	ground current			-50	-	mA
T <sub>stg</sub>	storage temperature			-65	+150	°C
P <sub>tot</sub>	total power dissipation	SO14, (T)SSOP14 and DHVQFN14 packages	[2]	-	500	mW

[1] The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

For SO14 package: P<sub>tot</sub> derates linearly with 8 mW/K above 70 °C.
 For (T)SSOP14 packages: P<sub>tot</sub> derates linearly with 5.5 mW/K above 60 °C.
 For DHVQFN14 packages: P<sub>tot</sub> derates linearly with 4.5 mW/K above 60 °C.

### 9. Recommended operating conditions

#### Table 5. Recommended operating conditions

Voltages are referenced to GND (ground = 0 V)

Symbol	Parameter	Conditions	74HC14		74HCT14			Unit	
			Min	Тур	Max	Min	Тур	Max	
V <sub>CC</sub>	supply voltage		2.0	5.0	6.0	4.5	5.0	5.5	V
VI	input voltage		0	-	V <sub>CC</sub>	0	-	V <sub>CC</sub>	V
Vo	output voltage		0	-	V <sub>CC</sub>	0	-	V <sub>CC</sub>	V
T <sub>amb</sub>	ambient temperature		-40	+25	+125	-40	+25	+125	°C

Hex inverting Schmitt trigger

## **10. Static characteristics**

#### Table 6. Static characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	T <sub>ar</sub>	<sub>nb</sub> = 25	°C		: –40 °C 85 °C		= –40 °C 125 °C	Unit
			Min	Тур	Max	Min	Max	Min	Max	
74HC14			1	1	1		1	•		
V <sub>ОН</sub>	HIGH-level	$V_{I} = V_{T+}$ or $V_{T-}$								
	output voltage	$I_{O} = -20 \ \mu A; V_{CC} = 2.0 \ V$	1.9	2.0	-	1.9	-	1.9	-	V
		$I_{O} = -20 \ \mu A; V_{CC} = 4.5 \ V$	4.4	4.5	-	4.4	-	4.4	-	V
		$I_{O} = -20 \ \mu A; V_{CC} = 6.0 \ V$	5.9	6.0	-	5.9	-	5.9	-	V
		$I_{O} = -4.0 \text{ mA}; V_{CC} = 4.5 \text{ V}$	3.98	4.32	-	3.84	-	3.7	-	V
		$I_{O} = -5.2 \text{ mA}; V_{CC} = 6.0 \text{ V}$	5.48	5.81	-	5.34	-	5.2	-	V
V <sub>OL</sub>	LOW-level	$V_{I} = V_{T+}$ or $V_{T-}$								
	output voltage	$I_0 = 20 \ \mu A; V_{CC} = 2.0 \ V$	-	0	0.1	-	0.1	-	0.1	V
		$I_0 = 20 \ \mu A; V_{CC} = 4.5 \ V$	-	0	0.1	-	0.1	-	0.1	V
		$I_{O} = 20 \ \mu A; V_{CC} = 6.0 \ V$	-	0	0.1	-	0.1	-	0.1	V
		$I_{O} = 4.0 \text{ mA}; V_{CC} = 4.5 \text{ V}$	-	0.15	0.26	-	0.33	-	0.4	V
		$I_{O} = 5.2 \text{ mA}; V_{CC} = 6.0 \text{ V}$	-	0.16	0.26	-	0.33	-	0.4	V
I	input leakage current	$V_{I} = V_{CC}$ or GND; $V_{CC} = 6.0$ V	-	-	±0.1	-	±1.0	-	±1.0	μA
I <sub>CC</sub>	supply current		-	-	2.0	-	20	-	40	μA
CI	input capacitance		-	3.5	-	-	-	-	-	pF
74HCT14	4			1	1		1	•	<u> </u>	
V <sub>OH</sub>	HIGH-level	$V_{I} = V_{T+}$ or $V_{T-}$ ; $V_{CC} = 4.5 V$								
	output voltage	I <sub>O</sub> = -20 μA	4.4	4.5	-	4.4	-	4.4	-	V
		I <sub>O</sub> = -4.0 mA	3.98	4.32	-	3.84	-	3.7	-	V
V <sub>OL</sub>	LOW-level	$V_{I} = V_{T+}$ or $V_{T-}$ ; $V_{CC} = 4.5 V$								
	output voltage	I <sub>O</sub> = 20 μA;	-	0	0.1	-	0.1	-	0.1	V
		l <sub>O</sub> = 4.0 mA;	-	0.15	0.26	-	0.33	-	0.4	V
I	input leakage current	$V_{I} = V_{CC}$ or GND; $V_{CC} = 5.5$ V	-	-	±0.1	-	±1.0	-	±1.0	μA
I <sub>CC</sub>	supply current	$V_I = V_{CC}$ or GND; $I_O = 0$ A; $V_{CC} = 5.5$ V	-	-	2.0	-	20	-	40	μA
Δl <sub>CC</sub>	additional supply current	per input pin; $V_I = V_{CC} - 2.1 \text{ V}$ ; other pins at $V_{CC}$ or GND; $I_O = 0 \text{ A}$ ; $V_{CC} = 4.5 \text{ V}$ to 5.5 V	-	30	108	-	135	-	147	μΑ
CI	input capacitance		-	3.5	-	-	-	-	-	pF

## **11. Dynamic characteristics**

#### Table 7. Dynamic characteristics

 $GND = 0 V; C_L = 50 pF;$  for test circuit see <u>Figure 7</u>.

Symbol	Parameter	Conditions		Ta	<sub>mb</sub> = 25	°C		-40 °C to 5 °C	Unit
				Min	Тур	Max	Max (85 °C)	Max (125 °C)	_
74HC14	1								
t <sub>pd</sub>	propagation delay	nA to nY; see Figure 6	<u>[1]</u>						
		V <sub>CC</sub> = 2.0 V		-	41	125	155	190	ns
		V <sub>CC</sub> = 4.5 V		-	15	25	31	38	ns
		V <sub>CC</sub> = 5.0 V; C <sub>L</sub> = 15 pF		-	12	-	-	-	ns
		V <sub>CC</sub> = 6.0 V		-	12	21	26	32	ns
t <sub>t</sub>	transition time	see <u>Figure 6</u>	[2]						
		V <sub>CC</sub> = 2.0 V		-	19	75	95	110	ns
		V <sub>CC</sub> = 4.5 V		-	7	15	19	22	ns
		V <sub>CC</sub> = 6.0 V		-	6	13	15	19	ns
C <sub>PD</sub>	power dissipation capacitance	per package; $V_I = GND$ to $V_{CC}$	<u>[3]</u>	-	7	-	-	-	pF
74HCT14	4	1						1	
t <sub>pd</sub>	propagation delay	nA to nY; see Figure 6	<u>[1]</u>						
		V <sub>CC</sub> = 4.5 V		-	20	34	43	51	ns
		V <sub>CC</sub> = 5.0 V; C <sub>L</sub> = 15 pF		-	17	-	-	-	ns
t <sub>t</sub>	transition time	$V_{CC} = 4.5 \text{ V}; \text{ see } \frac{\text{Figure 6}}{1000}$	[2]	-	7	15	19	22	ns
C <sub>PD</sub>	power dissipation capacitance	per package; V <sub>I</sub> = GND to V <sub>CC</sub> $-$ 1.5 V	<u>[3]</u>	-	8	-	-	-	pF

[1]  $t_{pd}$  is the same as  $t_{PHL}$  and  $t_{PLH}$ .

[2]  $t_t$  is the same as  $t_{THL}$  and  $t_{TLH}$ .

[3]  $C_{PD}$  is used to determine the dynamic power dissipation (P<sub>D</sub> in  $\mu$ W):  $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \sum (C_L \times V_{CC}^2 \times f_o)$  where:

 $f_i$  = input frequency in MHz;

 $f_o = output frequency in MHz;$ 

 $C_L$  = output load capacitance in pF;


 $V_{CC}$  = supply voltage in V;

N = number of inputs switching;

 $\sum (C_L \times V_{CC}^2 \times f_o)$  = sum of outputs.


Hex inverting Schmitt trigger

### 12. Waveforms



#### Table 8. **Measurement points**

Туре	Input	Output			
	V <sub>M</sub>	V <sub>M</sub>	V <sub>X</sub>	V <sub>Y</sub>	
74HC14	0.5V <sub>CC</sub>	0.5V <sub>CC</sub>	0.1V <sub>CC</sub>	0.9V <sub>CC</sub>	
74HCT14	1.3 V	1.3 V	0.1V <sub>CC</sub>	0.9V <sub>CC</sub>	



Tabl	e 9.	Test data	

Туре	Input Lo		Load	Test
	VI	t <sub>r</sub> , t <sub>f</sub>	CL	
74HC14	V <sub>CC</sub>	6.0 ns	15 pF, 50 pF	t <sub>PLH</sub> , t <sub>PHL</sub>
74HCT14	3.0 V	6.0 ns	15 pF, 50 pF	t <sub>PLH</sub> , t <sub>PHL</sub>


### **13. Transfer characteristics**

#### Table 10. Transfer characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); see Figure 8 and Figure 9.

Symbol	Parameter	Parameter Conditions		T <sub>amb</sub> = 25 °C		T <sub>amb</sub> = –40 °C to +85 °C		T <sub>amb</sub> = −40 °C to +125 °C		Unit
			Min	Тур	Max	Min	Max	Min	Max	
74HC14	1	1		1			1			
V <sub>T+</sub>	positive-going	V <sub>CC</sub> = 2.0 V	0.7	1.18	1.5	0.7	1.5	0.7	1.5	V
	threshold	V <sub>CC</sub> = 4.5 V	1.7	2.38	3.15	1.7	3.15	1.7	3.15	V
	voltage	V <sub>CC</sub> = 6.0 V	2.1	3.14	4.2	2.1	4.2	2.1	4.2	V
V <sub>T-</sub>	negative-going	V <sub>CC</sub> = 2.0 V	0.3	0.52	0.9	0.3	0.9	0.3	0.9	V
	threshold	V <sub>CC</sub> = 4.5 V	0.9	1.4	2.0	0.9	2.0	0.9	2.0	V
	voltage	V <sub>CC</sub> = 6.0 V	1.2	1.89	2.6	1.2	2.6	1.2	2.6	V
V <sub>H</sub>	hysteresis	V <sub>CC</sub> = 2.0 V	0.2	0.66	1.0	0.2	1.0	0.2	1.0	V
	voltage	V <sub>CC</sub> = 4.5 V	0.4	0.98	1.4	0.4	1.4	0.4	1.4	V
		V <sub>CC</sub> = 6.0 V	0.6	1.25	1.6	0.6	1.6	0.6	1.6	V
74HCT14	4	1				L			1	
V <sub>T+</sub>	positive-going	V <sub>CC</sub> = 4.5 V	1.2	1.41	1.9	1.2	1.9	1.2	1.9	V
	threshold voltage	V <sub>CC</sub> = 5.5 V	1.4	1.59	2.1	1.4	2.1	1.4	2.1	V
V <sub>T-</sub>	negative-going	V <sub>CC</sub> = 4.5 V	0.5	0.85	1.2	0.5	1.2	0.5	1.2	V
	threshold voltage	V <sub>CC</sub> = 5.5 V	0.6	0.99	1.4	0.6	1.4	0.6	1.4	V
V <sub>H</sub>	hysteresis	V <sub>CC</sub> = 4.5 V	0.4	0.56	-	0.4	-	0.4	-	V
		V <sub>CC</sub> = 5.5 V	0.4	0.6	-	0.4	-	0.4	-	V


## 14. Transfer characteristics waveforms



Product data sheet

# 74HC14; 74HCT14


Hex inverting Schmitt trigger



74HC\_HCT14
Product data sheet

# 74HC14; 74HCT14

Hex inverting Schmitt trigger



### **15. Application information**

The slow input rise and fall times cause additional power dissipation, this can be calculated using the following formula:

 $P_{add} = f_i \times (t_r \times \Delta I_{CC(AV)} + t_f \times \Delta I_{CC(AV)}) \times V_{CC}$  where:

 $P_{add}$  = additional power dissipation ( $\mu$ W);

 $f_i = input frequency (MHz);$ 

 $t_r$  = rise time (ns); 10 % to 90 %;

 $t_f = fall time (ns); 90 \% to 10 \%;$ 

 $\Delta I_{CC(AV)}$  = average additional supply current (µA).


Average  $\Delta I_{CC(AV)}$  differs with positive or negative input transitions, as shown in Figure 12 and Figure 13.


An example of a relaxation circuit using the 74HC14; 74HCT14 is shown in Figure 14.

74HC HCT14

# 74HC14; 74HCT14


Hex inverting Schmitt trigger






# 74HC14; 74HCT14


#### Hex inverting Schmitt trigger





Hex inverting Schmitt trigger

### 16. Package outline



#### Fig 16. Package outline SOT108-1 (SO14)

Hex inverting Schmitt trigger





Fig 17. Package outline SOT337-1 (SSOP14)


Hex inverting Schmitt trigger



#### Fig 18. Package outline SOT402-1 (TSSOP14)

All information provided in this document is subject to legal disclaimers.

Hex inverting Schmitt trigger



DHVQFN14: plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads;

#### Fig 19. Package outline SOT762-1 (DHVQFN14)

All information provided in this document is subject to legal disclaimers.

## **17. Abbreviations**

Table 11. Abbreviations					
Acronym	Description				
CMOS	Complementary Metal-Oxide Semiconductor				
DUT	Device Under Test				
ESD	ElectroStatic Discharge				
HBM	Human Body Model				
MM	Machine Model				
TTL	Transistor-Transistor Logic				

## **18. Revision history**

#### Table 12. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
74HC_HCT14 v.7	20151119	Product data sheet	-	74HC_HCT14 v.6
Modifications:	Type numbers 74HC14N and 74HCT14N (SOT27-1) removed.			
74HC_HCT14 v.6	20120919	Product data sheet	-	74HC_HCT14 v.5
Modifications:	<ul> <li>Figure 15 added (typical K-factor for relaxation oscillator).</li> </ul>			
74HC_HCT14 v.5	20111219	Product data sheet	-	74HC_HCT14 v.4
Modifications:	Legal pages updated.			
74HC_HCT14 v.4	20110117	Product data sheet	-	74HC_HCT14 v.3
74HC_HCT14 v.3	20031030	Product specification	-	74HC_HCT14_CNV v.2
74HC_HCT14_CNV v.2	19970826	Product specification	-	-

### **19. Legal information**

#### **19.1 Data sheet status**

Document status[1][2]	Product status <sup>[3]</sup>	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <a href="http://www.nexperia.com">http://www.nexperia.com</a>.

#### **19.2 Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any

representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and

customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

### 19.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof. Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of a Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale - Nexperia

products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Product data sheet

# 74HC14; 74HCT14

#### Hex inverting Schmitt trigger

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Non-automotive qualified products** — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of

non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the

product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond

Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### 19.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

### 20. Contact information

For more information, please visit: http://www.nexperia.com

For sales office addresses, please send an email to: salesaddresses@nexperia.com

Hex inverting Schmitt trigger

### 21. Contents

1	General description 1
2	Features and benefits 1
3	Applications 1
4	Ordering information 2
5	Functional diagram 2
6	Pinning information 3
6.1	Pinning 3
6.2	Pin description 3
7	Functional description 3
8	Limiting values 4
9	Recommended operating conditions 4
10	Static characteristics 5
11	Dynamic characteristics 6
12	Waveforms 7
13	Transfer characteristics
14	Transfer characteristics waveforms 8
15	Application information 10
16	Package outline 13
17	Abbreviations
18	Revision history 17
19	Legal information
19.1	Data sheet status 18
19.2	Definitions
19.3	Disclaimers 18
19.4	Trademarks 19
20	Contact information 19
21	Contents 20

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nexperia:

74HC14D74HC14DW74HC14DW74HC14DB74HC14DW74HC14DQ,11574HC14D,65274HC14DB,11274HC14DB,11874HC14D,65374HC14N,65274HC14PW,11274HC14PW,11874HC114BQ,11574HC114D,65274HC14DB,11274HC114DB,11274HC114DB,11874HC114D,65374HC114D,65374HC114D,65274HC114PW,112