


G3 Host Message Example

www.ti.com/smartgrid



Agenda

- **Overview**
- **System Initialization**
- **Network Configuration**
- **Data Transfer**
- **UDP Data Example**
- **IPv6 Address Mapping
(Unicast/Multicast/Broadcast)**

Message Flow Overview



System Initialization (1/3)



System Initialization (2/3)

- LOAD_SYSTEM_CONFIG (Port configuration)**

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
2	Config Type								0x0001 (port configuration)
2	Config Length								0x0001
1	Reserved				Diag Port		Host Port		0x00 (SCI-A) for both Diag/Host

- LOAD_SYSTEM_CONFIG (System Configuration)**

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
	Config Type								0X0003 (system configuration)
	Config Length								0x001A
2	Reserved								
16	Reserved								
6	Reserved								
1	Device Mode								0x0000 (G3 normal mode)
1			Auto Mode						Auto Mode: 0 (non-Auto Mode)

System Initialization (3/3)



- **LOAD_SYSTEM_CONFIG (G3 Configuration)**

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
	Config Type								0X0008 (G3 configuration)
	Config Length								0x0010 (16 bytes)
1							COH	TMR	0x00 (set flags to zero) or 0X01 (TMR on)
1	Reserved								0x00
8	G3 Long Address								Unique device long address
4	Reserved								0x00000000
2	Reserved								0x0000

- **SHUT_DOWN**

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
2	Reset Type								0x0000 (Soft Reset)

Network Configuration (1/3)



Network Configuration (2/3)

- SET_INFO (G3 TX PHY Parameters)**

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
2	INFO Type								0X0002 (G3 TX PHY Parameters)
2	INFO Length								0x0012 (18-byte)
1		Band Sel			COH			TMR	Depending on Band plan, need to set PHY parameters. Refer to Host Spec. (For Cenelec band, Band Sel=0)
1	Reserved					Modulation			
2	TX Level								
14	Tone Mask								

- SET_INFO (G3 RX PHY Parameters)**

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
2	INFO Type								0X0003 (G3 RX PHY Parameters)
2	INFO Length								0x0012 (18-byte)
1	Reserved								Depending on Band plan, need to set PHY parameters. Refer to Host Spec. NOTE that Band Sel and Tone Mask should be the same as TX parameters. Set AGC to 1.
1		Band Sel			COH	BLI		AGC	
2	Gain Value								
14	Tone Mask								

Network Configuration (3/3)



- DISCOVER**

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
1	Discover Type								0x00 (Network Discover)
1	Duration								0x05 (5 seconds: recommend)

- ATTACH**

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
2	PAN ID								PAN ID to be attached (The host needs to choose a PAN ID from a list of PAN IDs in Network Discover.confirm)
2	LBA Address								LBA Short address (based on CoordAddress from Discover.confirm)

Data Transfer (1/3)



Data Transfer (2/3)

- DATA TRANSFER.request**

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
1	NSDU Handle								Random number between 0x00-0xFF
1	Reserved				QoS	SEC	D-route		0x01 (D-route=1 for automatic route discovery)
var	L_SDU Data								IPv6 Packet

- DATA TRANSFER.confirm**



Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
1	NSDU Handle								
1	CFM	Reserved							CFM=1, meaning "confirmation"
2	Status								

Data Transfer (3/3)

- DATA TRANSFER.indication

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
1	Link Quality Indicator (0x00-0xFF)								
1	CFM	Phase	Reserved				SEC	CFM=0, meaning "indication"	
var	Data Payload								Received IPv6 Packet

G3 mini-DC: Network Configuration



G3 mini-DC: Network Configuration

- NETWORK_START**

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
2	PAN ID								Ranging from 0x0000 to 0xffff

- ATTACH.indication**

Length (octets)	Bits								Comments
	7	6	5	4	3	2	1	0	
8	Network Address 1								The IPv6 Address Prefix
8	Network Address 2								The IPv6 Address Postfix
8	Extended Address								64-bit Device long address
1	Capability Info								Capability Info as defined in Fig 56 of 802.15.4-2006
1	Reserved								

UDP Data Example

```
60 00 00 00 00 23 11 08 FE 80 00 00 00 00 00 00 74 55 00 FF FE 00 00 00 FE 80 00 00
00 00 00 00 74 55 00 FF FE 00 00 00 00 00 00 00 23 13 43 A0 AA 00 00 00 00 00 00
01 00 00 00 01 00 00 00 01 00 00 00 03 00 00 00 31 31 31
```

- IPv6 Header

- Next Header: 17 (=UDP)
- Payload Len: 35
- Hop Limit: 8
- Source Address: FE80:0000:0000:0000:7455:00FF:FE00:0000
- Destination Address: FE80:0000:0000:0000:7455:00FF:FE00:0000

- UDP Packet:


- Source Port : 0x0000
- Destination Port: 0x0000
- Length : 35
- CRC : 0x0000

- Data:

- 0xA0 AA 00 00 00 00 00 00 01 00 00 00 01 00 00 00 01 00 00 00 03 00 00 00 31
31 31

IPv6 Address Mapping

- **Unicast IPv6 Address**



- **Multicast/Broadcast**

- **0xFE80 → 0xFF02**
- **Last Two bytes**
 - **Broadcast (0x0001)**
 - **Multicast (Group_ID starting with 0b100): ADPGroupTable maintains ID's**