






SCHEMATIC, CCA, IPQ5312, AP.MI04.1, 512MB DDR4, 2X2 2G iPA, 2X2 5G iPA,2X2 6G iPA, USB2.0, QCA8386, MDIO SFP



Functional Block Diagram



Power Regs Diagram






JTAG不需要,留測試點




UART debug




刪除AUDIO_3V3這組電





GPIO #	TLMM Boot Configure Name	Description	Default board pull status
14	Boot_Config[0]	Auth enable: 0: no auth 1: auth is required	pull down
15	Boot_Config[1]	Fast boot (boot interface select): 0: SPI-NOR 1: eMMC	pull down
19	Boot_Config[2]	2: QSPI(4bit) 3: USB2.0	pull up
20	Boot_Config[3]	Routing ref clk Control ; 0: 48M 1: 96M	pull up
22	Boot_Config[4]	Hash in fuse (SW use only) 0: PK hash is stored in boot.ROM 1: PK hash is stored in OTP	pull down
38	Boot_Config[6]	Boot ROM boot speed: 0: 24MHz 1: 400MHz	pull down
42	boot_config[7]	Clock mode select: 0: Master Mode 1: Slave Mode	pull up
44	boot_config [8]	Use Serial Num: 0: Use Serial Num 1: Use OEM ID	pull down
47	boot_config [9]	txco_mode: 0: xo-mode 1: txco-mode	pull up
51	boot_config [10]	RFA refclk frequency selection: 0: 48MHz 1: 96MHz	pull up
13	forced_usb_boot	0: Not force boot from USB 1: force boot from USB	pull down





QSPI NAND Flash_128MB






Inventec Appliances Corporation

Approval:	Title10_USB Hub_TUSB4020BI		
Check:	Size	Document Number	Rev
Design:	C	LUCKY 7	PT1
Date: Thursday, July 18, 2024		Sheet	10 of 35




LED ON/OFF Control

LED ON/OFF SWITCH
P701 Connect to P702 --> LED ON
P701 Disconnect to P702 --> LED OFF









LED Board Connector


Shield Frame





Inventec Appliances Corporation			
Approval:	Title: 12_LED_Board_Connector		
Check:	Size: B	Document Number: LUCKY 7	Rev: PT1
Design:	Date: Thursday, July 18, 2024	Sheet: 12 of 35	





modif	Bit 0	Voltage
1	0	0.9
2	1	0.95




remove 3V3_SFP




保留






PoE PD 1 TPS2373




USB Adapter plug in	PoE PD 1 Disable
PoE Port 1 plug in	PoE PD 2 Disable
PoE Port 2 plug in	
USB Adapter unplugged	PoE PD 1 Enable
PoE Port 1 plug in	PoE PD 2 Disable
PoE Port 2 plug in	
USB Adapter unplugged	PoE PD 1 Disable
PoE Port 1 unplugged	PoE PD 2 Enable
PoE Port 2 plug in	

PoE PD 2 TPS2373




USB Adapter plug in PoE Port 1 plug in PoE Port 2 plug in	PoE PD 1 Disable PoE PD 2 Disable
USB Adapter unplugged PoE Port 1 plug in PoE Port 2 plug in	PoE PD 1 Enable PoE PD 2 Disable
USB Adapter unplugged PoE Port 1 unplugged PoE Port 2 plug in	PoE PD 1 Disable PoE PD 2 Enable

Boost Converter_LM5156DSSR




12V Buck Converter JWH5125




Approval:	Title 21_12V Buck Converter_JWH5125		
Check:	Size B	Document Number LUCKY 7	Rev PT1
Design:	Date: Thursday, July 18, 2024	Sheet 21 of 35	

IEEE802.3 at TYPE2


IEEE802.3 at TYPE 2 30W




1-port IN (CH3)




3-port OUT (CH1)














3-port OUT (CH0)













3-port IN (CH2)




















RF Shielding



	DATE	REV.	Revision History:
	11/25	EVT1	1. R118 change to place component. 2. R143 change to place component and R155 change to 4.7K ohm. 3. R75 change to no stuff and R74 change to place component. 4. Move D3522 to the power_54V_PD1_OUT (page.20) and move D3523 to the power_54V_PD2_OUT (page.20) 5. R387 change to 49.9K ohm and R397 change to 30K ohm. 6. Change R3786 size to 0805. Change R3683 & R3703 size to 1210.

**Inventec Appliances Corporation**

Approval:	Title 35_Change_List		
Check:	Size B	Document Number LUCKY 7	Rev PT1
Design:	Date: Monday, November 25, 2024 Sheet 35 of 35		