

ADDRESS1:
 ADDRESS2:
 ADDRESS3:

Radiated Emission Measurement


File :20240514

Data :#87

Date: 2024-09-09

Time: 上午 11:15:35

80.0 dBuV/m



Site LAB

Polarization: **Horizontal**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	X	81.4100	73.77	-21.83	51.94	40.00	11.94	peak	
2	*	165.8000	67.72	-15.22	52.50	40.00	12.50	peak	
3	X	190.0500	66.11	-17.73	48.38	40.00	8.38	peak	
4	X	295.7800	62.67	-13.33	49.34	47.00	2.34	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:


Radiated Emission Measurement

File :20240514

Data :#88

Date: 2024-09-09

Time: 上午 11:16:41



Site LAB

Polarization: **Vertical**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	X	52.3100	60.71	-18.15	42.56	40.00	2.56	peak	
2	*	79.4700	79.88	-21.66	58.22	40.00	18.22	peak	
3	X	158.0399	72.98	-14.86	58.12	40.00	18.12	peak	
4	X	196.8400	72.45	-17.36	55.09	40.00	15.09	peak	
5	X	295.7800	59.08	-11.71	47.37	47.00	0.37	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:


Radiated Emission Measurement

File :20240514

Data :#89

Date: 2024-09-09

Time: 上午 11:19:15



Site LAB

Polarization: **Vertical**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: AUX

Mode:

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	*	84.3200	78.28	-20.12	58.16	40.00	18.16	peak	
2	X	159.0100	72.72	-15.19	57.53	40.00	17.53	peak	
3	X	196.8400	69.98	-17.36	52.62	40.00	12.62	peak	
4	X	291.9000	59.28	-12.11	47.17	47.00	0.17	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
 ADDRESS2:
 ADDRESS3:

Radiated Emission Measurement


File :20240514

Data :#90

Date: 2024-09-09

Time: 上午 11:20:20

80.0 dBuV/m



Site LAB

Polarization: **Horizontal**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: AUX

Mode:

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	X	85.2900	72.00	-20.75	51.25	40.00	11.25	peak	
2	X	116.3300	60.63	-13.80	46.83	40.00	6.83	peak	
3	*	167.7400	66.66	-15.06	51.60	40.00	11.60	peak	
4	X	196.8400	66.34	-18.43	47.91	40.00	7.91	peak	
5	X	294.8100	61.45	-12.85	48.60	47.00	1.60	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
 ADDRESS2:
 ADDRESS3:

Radiated Emission Measurement


File :20240514

Data :#91

Date: 2024-09-09

Time: 上午 11:22:33

80.0 dBuV/m



Site LAB

Polarization: **Horizontal**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: USB

Mode:

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	X	79.4700	73.93	-22.16	51.77	40.00	11.77	peak	
2	*	167.7400	67.04	-15.06	51.98	40.00	11.98	peak	
3	X	196.8400	66.73	-18.43	48.30	40.00	8.30	peak	
4	X	285.1099	58.12	-10.81	47.31	47.00	0.31	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:


Radiated Emission Measurement

File :20240514

Data :#92

Date: 2024-09-09

Time: 上午 11:24:28



Site LAB

Polarization: **Vertical**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: USB

Mode:

Note:

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	X	47.4600	57.21	-15.03	42.18	40.00	2.18	peak	
2	*	79.4700	81.06	-21.66	59.40	40.00	19.40	peak	
3	X	158.0399	73.37	-14.86	58.51	40.00	18.51	peak	
4	X	195.8700	69.84	-17.41	52.43	40.00	12.43	peak	
5	X	295.7800	59.78	-11.71	48.07	47.00	1.07	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
 ADDRESS2:
 ADDRESS3:


Radiated Emission Measurement

File :20240514

Data :#93

Date: 2024-09-09

Time: 上午 11:27:16



Site LAB

Polarization: **Vertical**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 去掉灯

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	*	79.4700	80.42	-21.66	58.76	40.00	18.76	peak	
2	X	107.6000	74.25	-19.09	55.16	40.00	15.16	peak	
3	X	159.0100	72.71	-15.19	57.52	40.00	17.52	peak	
4	X	197.8100	69.41	-17.32	52.09	40.00	12.09	peak	
5	!	295.7800	58.41	-11.71	46.70	47.00	-0.30	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
 ADDRESS2:
 ADDRESS3:

Radiated Emission Measurement


File :20240514

Data :#94

Date: 2024-09-09

Time: 上午 11:29:25

80.0 dBuV/m



Site LAB

Polarization: **Vertical**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT暂停

Mode:

Note: 去掉灯

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	*	82.3800	73.44	-20.84	52.60	40.00	12.60	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:


Radiated Emission Measurement

File :20240514

Data :#95

Date: 2024-09-09

Time: 上午 11:52:24



Site LAB

Polarization: **Horizontal**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 喇叭线电池线加磁环+去掉灯

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	X	88.2000	68.44	-21.08	47.36	40.00	7.36	peak	
2	*	163.8600	65.88	-15.33	50.55	40.00	10.55	peak	
3	X	209.4500	63.66	-14.98	48.68	40.00	8.68	peak	
4	X	285.1099	67.63	-10.81	56.82	47.00	9.82	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:

Radiated Emission Measurement


File :20240514

Data :#96

Date: 2024-09-09

Time: 上午 11:53:35

80.0 dBuV/m



Site LAB

Polarization: **Vertical**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 喇叭线电池线加磁环+去掉灯

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	X	85.2900	77.38	-19.86	57.52	40.00	17.52	peak	
2	*	162.8900	75.74	-15.22	60.52	40.00	20.52	peak	
3	X	210.4200	63.44	-15.77	47.67	40.00	7.67	peak	
4	X	294.8100	63.86	-11.55	52.31	47.00	5.31	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:

Radiated Emission Measurement


File :20240514

Data :#97

Date: 2024-09-09

Time: 下午 02:54:08

80.0 dBuV/m



Site LAB

Polarization: **Horizontal**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 断开功放+去掉灯

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1		241.4600	45.54	-11.70	33.84	47.00	-13.16	peak	
2		361.7400	43.48	-10.86	32.62	47.00	-14.38	peak	
3	*	854.5000	43.02	-4.00	39.02	47.00	-7.98	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:

Radiated Emission Measurement


File :20240514

Data :#98

Date: 2024-09-09

Time: 下午 02:55:12

80.0 dBuV/m



Site LAB

Polarization: **Vertical**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 断开功放+去掉灯

No.	Mk.	Freq.	Reading Level	Correct Factor	Measurement	Limit	Over	Detector	Comment
		MHz	dBuV	dB	dBuV/m	dB/m	dB		

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:


Radiated Emission Measurement

File :20240514

Data :#99

Date: 2024-09-09

Time: 下午 03:46:15



Site LAB

Polarization: **Vertical**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 功放IC加滤波器+去掉灯

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	X	78.5000	65.83	-21.68	44.15	40.00	4.15	peak	
2	*	100.8100	71.47	-21.05	50.42	40.00	10.42	peak	
3	X	150.2800	56.80	-13.39	43.41	40.00	3.41	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:


Radiated Emission Measurement

File :20240514

Data :#100

Date: 2024-09-09

Time: 下午 03:47:22



Site LAB

Polarization: **Horizontal**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 功放IC加滤波器+去掉灯

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	*	128.9400	49.60	-13.51	36.09	40.00	-3.91	peak	
2	!	208.4800	49.98	-15.35	34.63	40.00	-5.37	peak	
3	!	278.3200	51.20	-10.19	41.01	47.00	-5.99	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
 ADDRESS2:
 ADDRESS3:


Radiated Emission Measurement

File :20240514

Data :#101

Date: 2024-09-09

Time: 下午 04:22:53



Site LAB

Polarization: **Horizontal**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 功放IC加2级滤波器+去掉灯+

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	*	81.4100	70.35	-21.83	48.52	40.00	8.52	peak	
2	!	160.9500	55.39	-15.42	39.97	40.00	-0.03	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:


Radiated Emission Measurement

File :20240514

Data :#102

Date: 2024-09-09

Time: 下午 04:23:56



Site LAB

Polarization: **Vertical**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 功放IC加2级滤波器+去掉灯+

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	*	77.5300	81.48	-21.70	59.78	40.00	19.78	peak	
2	X	163.8600	64.72	-15.14	49.58	40.00	9.58	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:

Radiated Emission Measurement


File :20240514

Data :#103

Date: 2024-09-09

Time: 下午 04:53:36

80.0 dBuV/m



Site LAB

Polarization: **Horizontal**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 功放IC加2级电容330P滤波器+去掉灯+

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	*	78.5000	74.04	-22.31	51.73	40.00	11.73	peak	
2	!	165.8000	52.06	-15.22	36.84	40.00	-3.16	peak	
3	!	211.3900	53.39	-14.62	38.77	40.00	-1.23	peak	
4	!	286.0799	56.08	-11.08	45.00	47.00	-2.00	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
 ADDRESS2:
 ADDRESS3:


Radiated Emission Measurement

File :20240514

Data :#104

Date: 2024-09-09

Time: 下午 04:54:41



Site LAB

Polarization: **Vertical**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 功放IC加2级电容330P滤波器+去掉灯+

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	*	79.4700	81.04	-21.66	59.38	40.00	19.38	peak	
2	X	162.8900	63.89	-15.22	48.67	40.00	8.67	peak	
3	!	286.0799	58.37	-12.71	45.66	47.00	-1.34	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:


Radiated Emission Measurement

File :20240514

Data :#105

Date: 2024-09-09

Time: 下午 06:07:05



Site LAB

Polarization: **Vertical**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 功放IC加1级电容330P滤波器+去掉灯+IIC电阻

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	X	54.2500	63.51	-19.11	44.40	40.00	4.40	peak	
2	*	79.4700	80.32	-21.66	58.66	40.00	18.66	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only

ADDRESS1:
ADDRESS2:
ADDRESS3:

Radiated Emission Measurement


File :20240514

Data :#106

Date: 2024-09-09

Time: 下午 06:08:13

80.0 dBuV/m



Site LAB

Polarization: **Horizontal**

Temperature: (C)

Limit: EN55032 RE-Class B 3M

Power:

Humidity: %

EUT: GP-591

M/N: BT

Mode:

Note: 功放IC加1级电容330P滤波器+去掉灯+IIC电阻

No.	Mk.	Freq. MHz	Reading Level dBuV	Correct Factor dB	Measure- ment dBuV/m	Limit dB/m	Over dB	Detector	Comment
1	*	81.4100	61.04	-21.83	39.21	40.00	-0.79	peak	

*:Maximum data x:Over limit !:over margin

<Reference Only