
- Maximum Throughput 400 KSPS
- Built-In Reference and 8× FIFO
- Differential/Integral Nonlinearity Error: ±0.5 LSB Max
- Signal-to-Noise and Distortion Ratio: 59 dB, f_i = 12 kHz
- Spurious Free Dynamic Range: 72 dB, f_i = 12 kHz
- SPI/DSP-Compatible Serial Interfaces With SCLK up to 20 MHz
- Single Supply 5 Vdc



- Analog Input Range 0 V to Supply Voltage With 500 kHz BW
- Hardware Controlled and Programmable Sampling Period
- Low Operating Current (4 mA at 5.5 V External Ref, 6 mA at 5.5 V, Internal Ref)
- Power Down: Software/Hardware Power-Down Mode (1 µA Max, Ext Ref), Auto Power-Down Mode (5 µA, Ext Ref)
- Programmable Auto-Channel Sweep
- Pin Compatible, 12-Bit Upgrades Available (TLC2554, TLC2558)

SDO [1 16] CS SDI [2 15] REFP SCLK [3 14] REFM EOC/(INT) [4 13] FS V _{CC} [5 12] PWDN	D OR PW PACKAGE (TOP VIEW)							
A0 [6 11] GND A1 [7 10] CSTART A2 [8 9] A3	SDO [SDI [SCLK [EOC/(INT) [V _{CC} [A0 [A1 [1 2 3 4 5 6 7	16 15 14 13 12 11 10] CS REFP REFM FS PWDN GND CSTART				

description

The TLC1518 and TLC1514 are a family of high-performance, 10-bit, low power, 1.4 μ s, CMOS SAR analog-to-digital converters (ADC) which operate from a single 5 V power supply. These devices have three digital inputs and a 3-state output [chip select (\overline{CS}), serial input-output clock (SCLK), serial data input (SDI), and serial data output (SDO)] that provide a direct 4-wire interface to the serial port of most popular host microprocessors (SPI interface). When interfaced with a DSP, a frame sync (FS) signal is used to indicate the start of a serial data frame.

In addition to a high-speed A/D converter and versatile control capability, these devices have an on-chip analog multiplexer that can select any analog inputs or one of three internal self-test voltages. The sample-and-hold function is automatically started after the fourth SCLK edge (normal sampling) or can be controlled by a special pin, CSTART, to extend the sampling period (extended sampling). The normal sampling period can also be programmed as short (12 SCLKs) or as long (24 SCLKs) to accommodate faster SCLK operation popular among high-performance signal processors. The TLC1518 and TLC1514 are designed to operate with very low power consumption. The power-saving feature is further enhanced with software/hardware/auto power down modes and programmable conversion speeds. The converter uses the external SCLK as the source of the conversion clock. There is a 4-V internal reference available and an optional external reference can also be used to achieve maximum flexibility.




Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.



Copyright © 1999, Texas Instruments Incorporated

functional block diagram



AVAIL	ABLE	OPTIC	ONS
/ <i>.</i>		U	

		PACKAGE	DEVICES	
TA	20-TSSOP (PW)	20-SOIC (DW)	16-SOIC (D)	16-TSSOP (PW)
-40°C to 85°C	TLC1518IPW	TLC1518IDW	TLC1514ID	TLC1514IPW



Terminal Functions

TERMINAL				
NAME	N	0.	I/O	DESCRIPTION
	TLC1514	TLC1518		
A0 A0 A1 A1 A2 A2 A3 A3 A4 A5 A6 A7	6 7 8 9	6 7 8 9 10 11 12 13	I	Analog signal inputs. The analog inputs are applied to these terminals and are internally multiplexed. The driving source impedance should be less than or equal to 1 k Ω . For a source impedance greater than 1 k Ω , use the asynchronous conversion start signal CSTART (CSTART low time controls the sampling period) or program long sampling period to increase the sampling time.
CS	16	20	I	Chip select. A high-to-low transition on the \overline{CS} input resets the internal 4-bit counter, enables SDI, and removes SDO from 3-state within a maximum setup time. SDI is disabled within a setup time after the 4-bit counter counts to 16 (clock edges) or a low-to-high transition of \overline{CS} whichever happens first. SDO is 3-stated after the rising edge of \overline{CS} . \overline{CS} can be used as the FS pin when a dedicated serial port is used.
CSTART	10	14	I	This terminal controls the start of sampling of the analog input from a selected multiplex channel. A high-to-low transition starts sampling of the analog input signal. A low-to-high transition puts the S/H in hold mode and starts the conversion. This input is independent from SCLK and works when \overline{CS} is high (inactive). The low time of \overline{CSTART} controls the duration of the sampling period of the converter (extended sampling). The this terminal to V_{CC} if not used.
EOC/(INT)	4	4	0	End of conversion or interrupt to host processor. [PROGRAMMED AS EOC]: This output goes from a high-to-low logic level at the end of the sampling period and remains low until the conversion is complete and data are ready for transfer. EOC is used in conversion mode 00 only. [PROGRAMMED AS INT]: This pin can also be programmed as an interrupt output signal to the host processor. The falling edge of \overline{INT} indicates data are ready for output. The following $\overline{CS}\downarrow$ or $\overline{FS}\uparrow$ clears INT. The falling edge of \overline{INT} puts SDO back to 3-state even if \overline{CS} is still active.
FS	13	17	I	DSP frame sync input. Indication of the start of a serial data frame in or out of the device. If FS remains low at the falling edge of \overline{CS} , SDI is not enabled until an active FS is presented. A high-to-low transition on the FS input resets the internal 4-bit counter and enables SDI within a maximum setup time. SDI is disabled within a setup time after the 4-bit counter counts to 16 (clock edges) or a low-to-high transition of \overline{CS} whichever happens first. SDO is 3-stated after the 16th bit is presented. Tie this terminal to V _{CC} if not used.
GND	11	15	I	Ground return for the internal circuitry. Unless otherwise noted, all voltage measurements are with respect to GND.
PWDN	12	16	I	Both analog and reference circuits are powered down when this pin is at logic zero. The device can be restarted by active CS or CSTART after this pin is pulled back to logic one.
SCLK	3	3	I	Input serial clock. This terminal receives the serial SCLK from the host processor. SCLK is used to clock the input SDI to the input register. It is also used as the source of the conversion clock.
SDI	2	2	I	Serial data input. The input data is presented with the MSB (D15) first. The first 4-bit MSBs, D(15–12) are decoded as one of the 16 commands (12 only for the TLC1514). All trailing blanks are filled with zeros. The configure write commands require an additional 12 bits of data. When FS is not used (FS =1), the first MSB (D15) is expected after the falling edge of CS and is shifted in on the rising edges of SCLK (after CS \downarrow). When FS is used (typical with an active FS from a DSP) the first MSB (D15) is expected after the falling edge of FS and is shifted in on the falling edges of SCLK.



SLAS252 - DECEMBER 1999

Terminal Functions (Continued)

	TERMINAL NAME NO. TLC1514 TLC1518		TERMINAL		TERMINAL			
			I/O	DESCRIPTION				
NAME								
SDO	1	1	0	The 3-state serial output for the A/D conversion result. SDO is kept in the high-impedance state when \overline{CS} is high and after the \overline{CS} falling edge and until the MSB (D15) is presented. The output format is MSB (D15) first.				
				When FS is not used (FS = 1 at the falling edge of \overline{CS}), the MSB (D15) is presented to the SDO pin after the \overline{CS} falling edge, and successive data are available at the rising edge of SCLK.				
				When FS is used (FS = 0 at the falling edge of \overline{CS}), the MSB (D15) is presented to SDO after the falling edge of \overline{CS} and FS = 0 is detected. Successive data are available at the falling edge of SCLK. (This is typically used with an active FS from a DSP.)				
				For conversion and FIFO read cycles, the first 10 bits are the result from the previous conversion (data) followed by 6 don't cares. The first four bits from SDO for CFR read cycles should be ignored. The register content is in the last 12 bits. SDO is 3 stated after the 16th bit.				
REFM	14	18	I	External reference input or internal reference decoupling.				
REFP	15	19	I	External reference input or internal reference decoupling. (Shunt capacitors of 10 μ F and 0.1 μ F between REFP and REFM.) The maximum input voltage range is determined by the difference between the voltage applied to this terminal and the REFM terminal when an external reference is used.				
V _{CC}	5	5	Ι	Positive supply voltage				

detailed description

analog inputs and internal test voltages

The 4/8 analog inputs and three internal test inputs are selected by the analog multiplexer depending on the command entered. The input multiplexer is a break-before-make type to reduce input-to-input noise injection resulting from channel switching.

pseudo-differential/single-ended input

All analog inputs can be programmed as single-ended or pseudo-differential mode. Pseudo-differential mode is enabled by setting CFR.D7 – 1. Only three analog input channels (or seven channels for the TLC1518) are available for TLC1514 since one input (A1 for TLC1514 or A2 for TLC1518) is used as the MINUS input when pseudo-differential mode is used. The minus input pin can have a maximum ± 0.2 V ripple. This is normally used for ground noise rejection.

converter

The TLC1514/18 uses a 10-bit successive approximation ADC utilizing a charge redistribution DAC. Figure 1 shows a simplified version of the DAC.

The sampling capacitor acquires the signal on Ain during the sampling period. When the conversion process starts, the SAR control logic and charge redistribution DAC are used to add and subtract fixed amounts of charge from the sampling capacitor to bring the comparator into a balanced condition. When the comparator is balanced, the conversion is complete and the ADC output code is generated.








Figure 1. Simplified Model of the Successive-Approximation System

serial interface

INPUT DATA FORMAT			
MSB LSE			
D15–D12	D11–D0		
Command	Configuration data field		

Input data is binary. All trailing blanks can be filled with zeros.

OUTPUT DATA FORMAT READ CFR					
MSB LSB					
D15–D12 D11–D0					
Don't care	Register content				
OUTPUT DATA F	FORMAT CONVERS	ION/READ FIFO			
MSB LSB					
D15	D5–D0				
Conversion result		Don't care			

The output data format is either binary (unipolar straight binary) or 2s complement.

binary

Zero scale code = 000h, Vcode = VREFM Full scale code = 3FFh, Vcode = VREFP - 1 LSB

2s complement

Minus full scale code = 200h, Vcode = VREFM Full scale code = 1FFh, Vcode = VREFP - 1 LSB



control and timing

start of the cycle:

- When FS is not used (FS = 1 at the falling edge of \overline{CS}), the falling edge of \overline{CS} is the start of the cycle. Input data is shifted in on the rising edge, and output data changes on the falling edge of SCLK. This is typically used for an SPI microcontroller, although it can also be used for a DSP.
- When FS is used (FS is an active signal from a DSP), the falling edge of FS is the start of the cycle. Input data is shifted in on the falling edge, and output data changes on the rising edge of SCLK. This is typically used for a TMS320 DSP.

first 4-MSBs: the command register (CMR)

The TLC1514/TLC1518 have a 4-bit command set (see Table 1) plus a 12-bit configuration data field. Most of the commands require only the first 4 MSBs, i.e. without the 12-bit data field.

NOTE:

The device requires a write CFR (configuration register) with 000h data (write A000h to the serial input) at power up to initialize host select mode.

The valid commands are listed in Table 1.

SDI D(15-12)	BINARY, HEX	TLC1518 COMMAND	TLC1514 COMMAND			
0000b	0000h	Select analog input channel 0 Select analog input char				
0001b	1000h	Select analog input channel 1	N/A			
0010b	2000h	Select analog input channel 2	Select analog input channel 1			
0011b	3000h	Select analog input channel 3	N/A			
0100b	4000h	Select analog input channel 4	Select analog input channel 2			
0101b	5000h	Select analog input channel 5	N/A			
0110b	6000h	Select analog input channel 6	Select analog input channel 3			
0111b	7000h	Select analog input channel 7	N/A			
1000b	8000h	SW power down (analog + reference)				
1001b	9000h	Read CFR register data shown as SDO D(11–0)				
1010b	A000h plus data	Write CFR followed by 12-bit data				
1011b	B000h	Select test, voltage = (REFP+REFM)/2	Select test, voltage = (REFP+REFM)/2			
1100b	C000h	Select test, voltage = REFM				
1101b	D000h	Select test, voltage = REFP				
1110b	E000h	FIFO read, FIFO contents shown as SDO D(15–6), D(5–0) = XXXXXX				
1111b	F000h plus data	Reserved				

Table 1. TLC1514/TLC1518 Command Set



control and timing (continued)

configuration

Configuration data is stored in one 12-bit configuration register (CFR) (see Table 2 for CFR bit definitions). Once configured after first power up, the information is retained in the H/W or S/W power-down state. When the device is being configured, a write CFR cycle is issued by the host processor. This is a 16-bit write. (If the SCLK stops after the first 8 bits are entered, then the next eight bits can be taken after the SCLK is resumed.) The status of the CFR can be read with a read CFR command when the device is programmed for one-shot conversion mode (CFR.D[6,5] = 00).

BIT	DEFIN	IITION				
D(15–12)	All zeros, nonprogrammable					
D11	Reference select 0: External 1: Internal					
D10	Output select 0: Unipolar straight binary 1: 2's complement	0: Unipolar straight binary				
D9	Sample period select 0: Short sampling 12 SCLKs (1x samplin 1: Long sampling 24 SCLKs (2x samplir					
D8	Conversion clock source select 0: Conversion clock = SCLK 1: Conversion clock = SCLK/2					
D7	Input select 0: Normal 1: Pseudo differential CH A2(1518) or CH A1 (1514) is the differential input					
D(6,5)	Conversion mode select 00: Single shot mode (single conversion from selected channel) 01: Repeat mode (repeated conversions from selected channel) 10: Sweep mode (single conversion on each channel in selected sequence) 11: Repeat sweep mode (repeated conversions on selected sequence)					
D(4,3)†	TLC1518	TLC1514				
	Sweep auto sequence select 00: 0-1-2-3-4-5-6-7 01: 0-2-4-6-0-2-4-6 10: 0-0-2-2-4-4-6-6 11: 0-2-0-2-0-2-0-2	Sweep auto sequence select 00: N/A 01: 0-1-2-3-0-1-2-3 10: 0-0-1-1-2-2-3-3 11: 0-1-0-1-0-1-0-1				
D2	EOC/INT – pin <u>fun</u> ction select 0: Pin used as INT 1: Pin used as EOC					
D(1,0)	FIFO trigger level (sweep sequence len 00: Full (INT generated after FIFO level 01: 3/4 (INT generated after FIFO level 10: 1/2 (INT generated after FIFO level 11: 1/4 (INT generated after FIFO level	7 filled) 5 filled) 3 filled)				

Table 2. TLC1514/TLC1518 Configuration Register (CFR) Bit Definitions

[†] These bits only take effect in conversion modes 10 and 11.

sampling

The sampling period starts after the first 4 input data are shifted in if they are decoded as one of the conversion commands. These are select analog input (channel 0 through 7) and select test (channel 1 through 3).



normal sampling

When the converter is using normal sampling, the sampling period is programmable. It can be 12 SCLKs (short sampling) or 24 SCLKs (long sampling). Long sampling helps the input analog signal sampled to settle to 0.5 LSB accuracy when input source resistance is high.

extended sampling

An asynchronous (to the SCLK) signal, via dedicated hardware pin CSTART, can be used in order to have total control of the sampling period and the start of a conversion. This is extended sampling. The falling edge of CSTART is the start of the sampling period. The rising edge of CSTART is the end of the sampling period and the start of the conversion. This function is useful for an application that requires:

- The use of an extended sampling period to accommodate different input source impedance.
- The use of a faster I/O clock on the serial port but not enough sampling time is available due to the fixed number of SCLKs. This could be due to a high input source impedance or due to higher MUX ON resistance at lower supply voltage (refer to application information).

Once the conversion is complete, the processor can initiate a read cycle using either the read FIFO command to read the conversion result or simply select the next channel number for conversion. Since the device has a valid conversion result in the output buffer, the conversion result is simply presented at the serial data output. $\overline{\text{CSTART}}$ is not valid when $\overline{\text{CS}}$ is active.

TLC1514/TLC1518 conversion modes

The TLC1514 and TLC1518 have four different conversion modes (mode 00, 01, 10, 11). The operation of each mode is slightly different, depending on how the converter performs the sampling and which host interface is used. The trigger for a conversion can be an active CSTART (extended sampling), CS (normal sampling, SPI interface), or FS (normal sampling, TMS320 DSP interface). When FS is used as the trigger, \overline{CS} can be held active, i.e. CS does not need to be toggled through the trigger sequence. Different types of triggers should not be mixed throughout the repeat and sweep operations. When CSTART is used as the trigger, the conversion starts on the rising edge of CSTART. The minimum low time for CSTART is 800 ns. If an active CS or FS is used as the trigger, the conversion is started after the 16th or 28th SCLK edge. Enough time (for conversion) should be allowed between consecutive triggers so that no conversion is terminated prematurely.

one shot mode (mode 00)

One shot mode (mode 00) does not use the FIFO, and the EOC is generated as the conversion is in progress (or INT is generated after the conversion is done).

repeat mode (mode 01)

Repeat mode (mode 01) uses the FIFO. Once the programmed FIFO threshold is reached, the FIFO must be read, or the data is lost and the sequence starts over again. This allows the host to set up the converter and continue monitoring a fixed input and come back to get a set of samples when preferred. The first conversion must start with a select command so an analog input channel can be selected.

sweep mode (mode 10)

Sweep mode (mode 10) also uses the FIFO. Once it is programmed in this mode, all of the channels listed in the selected sweep sequence are visited in sequence. The results are converted and stored in the FIFO. This sweep sequence may not be completed if the FIFO threshold is reached before the list is completed. This allows the system designer to change the sweep sequence length. Once the FIFO has reached its programmed threshold, an interrupt (INT) is generated. The host must issue a read FIFO command to read and clear the FIFO before the next sweep can start.



TLC1514/TLC1518 conversion modes (continued)

repeat sweep mode (mode 11)

Repeat sweep mode (mode 11) works the same way as mode 10 except the operation has an option to continue even if the FIFO threshold is reached. Once the FIFO has reached its programmed threshold, an interrupt (\overline{INT}) is generated. Then two things may happen:

- 1. The host may choose to act on it (read the FIFO) or ignore it. If the next cycle is a read FIFO cycle, all of the data stored in the FIFO is retained until it has been read in order.
- 2. If the next cycle is not a read FIFO cycle, or another CSTART is generated, all of the content stored in the FIFO is cleared before the next conversion result is stored in the FIFO, and the sweep is continued.

CONVERSION MODE	CFR D(6,5)	SAMPLING TYPE	OPERATION
One shot	00	Normal	 Single conversion from a selected channel CS or FS to start select/sampling/conversion/read One INT or EOC generated after each conversion Host must serve INT by selecting channel, and converting and reading the previous output.
		Extended	 Single conversion from a selected channel <u>CS</u> to select/read <u>CSTART</u> to start sampling and conversion One INT or EOC generated after each conversion Host must serve INT by selecting next channel and reading the previous output.
Repeat	01	Normal	 Repeated conversions from a selected channel CS or FS to start sampling/conversion One INT generated after FIFO is filled up to the threshold Host must serve INT by either 1) (FIFO read) reading out all of the FIFO contents up to the threshold, then repeat conversions from the same selected channel or 2) writing another command(s) to change the conversion mode. If the FIFO is not read when INT is served, it is cleared.
		Extended	 Same as normal sampling except CSTART starts each sampling and conversion when CS is high.
Sweep	10	Normal	 One conversion per channel from a sequence of channels CS or FS to start sampling/conversion One INT generated after FIFO is filled up to the threshold Host must serve INT by (FIFO read) reading out all of the FIFO contents up to the threshold, then write another command(s) to change the conversion mode.
		Extended	 Same as normal sampling except CSTART starts each sampling and conversion when CS is high.
Repeat sweep	11	Normal	 <u>Repeated conversions from a sequence of channels</u> <u>CS or FS to start sampling/conversion</u> One <u>INT</u> generated after FIFO is filled up to the threshold Host must serve <u>INT</u> by either 1) (FIFO read) reading out all of the FIFO contents up to the threshold, then repeat conversions from the same selected channel or <u>2</u>) writing another command(s) to change the conversion mode. If the FIFO is not read when INT is served it is cleared.
		Extended	 Same as normal sampling except CSTART starts each sampling and conversion when CS is high.

Table 3. TLC1514/TLC1518 Conversion Mode

NOTE: Programming the EOC/INT pin as the EOC signal works for mode 00 only. The other three modes automatically generate an INT signal irrespective of whether EOC/INT is programmed.



SLAS252 - DECEMBER 1999

timing diagrams

The timing diagrams can be categorized into two major groups: nonconversion and conversion. The nonconversion cycles are read and write (configuration). None of these cycles carry a conversion. The conversion cycles are the four modes shown in Figure 7 through Figure 14.

read cycle (read FIFO or read CFR)

read CFR cycle:

The read command is decoded in the first 4 clocks. SDO outputs the contents of the CFR after the 4th SCLK.





Figure 2. TLC1514/TLC1518 Read CFR Cycle (FS active)









read cycle (read FIFO or read CFR) (continued)

FIFO read cycle

The first command in the active cycle after INT is generated, if the FIFO is used, is assumed as the FIFO read command. The first FIFO content is output immediately before the command is decoded. If this command is not a FIFO read, then the output is terminated but the first data in the FIFO is retained until a valid FIFO read command is decoded. Use of more layers of the FIFO reduces the time taken to read multiple data. This is because the read cycle does not generate EOC or INT nor does it carry out any conversion.







write cycle (write CFR)

The write cycle is used to write to the configuration register CFR (with 12-bit register content). The write cycle does not generate an EOC or INT nor does it carry out any conversion.





Figure 5. TLC1514/TLC1518 Write Cycle (FS active)







conversion cycles




Figure 7. Mode 00 Single Shot/Normal Sampling (FS signal used)





Figure 8. Mode 00 Single Shot/Normal Sampling (FS = 1, FS signal not used)



conversion cycles (continued)



[†] This is one of the single shot commands. Conversion starts on next rising edge of CSTART.

Figure 9. Mode 00 Single Shot/Extended Sampling (FS signal used, FS pin connected to TMS320 DSP)

CS used as FS input

When interfacing with the TMS320 DSP using conversion mode 00, the FSR signal from the DSP may be connected to the CS input if this is the only device on the serial port. This will save one output pin from the DSP. Output data is made available on the rising edge of SCLK and input data is latched on the rising edge of SCLK in this case.

modes using the FIFO: modes 01, 10, 11 timing

Modes 01, 10, and 11 timing are very similar except for how and when the FIFO is read, how the device is configured, and how channel(s) are selected.


Mode 01 (repeat mode) requires a two-cycle configuration where the first one sets the mode and the second one selects the channel. Once the FIFO is filled up to the threshold programmed, it has the option to either read the FIFO or configure for other modes. Therefore, the sequence is either configure: select : triggered conversions : FIFO read : select : triggered conversions : FIFO read or configure : select : triggered conversions : configure : Each configure clears the FIFO and the action that follows the configure command depends on the mode setting of the device.

NOTE:

When using CSTART to sample in extended mode, the falling edge of the first CSTART trigger should occur no more than 1.5 µs after the falling edge of CS (or falling edge of FS if FS is active) of the channel select cycle (see Figure 11).



modes using the FIFO: modes 01, 10, 11 timing (continued)




[†]Command = Configure write for mode 01, FIFO threshold = 1/2

[‡]Command = Read FIFO, 1st FIFO read

§ Command = Select ch2.





[†] Command = Configure write for mode 01, FIFO threshold = 1/2

[‡]Command = Read FIFO, 1st FIFO read

§ Command = Select ch2.


Figure 11. TLC1514/TLC1518 Mode 01 μp/DSP Serial Interface (conversions triggered by CSTART)



modes using the FIFO: modes 01, 10, 11 timing (continued)

Mode 10 (sweep mode) requires reconfiguration at the start of each new sweep sequence. Once the FIFO is filled up to the programmed threshold, the host has the option to either read the FIFO or configure for other modes. Once the FIFO is read, the host must reconfigure the device before the next sweep sequence can be started. So the sequence is either configure : triggered conversions : FIFO read : configure. or configure : triggered conversions : configure : Each configure clears the FIFO and the action that follows the configure command depends on the mode setting of the device.

Mode 11 (repeat sweep mode) requires one cycle configuration. This sweep sequence can be repeated without reconfiguration. Once the FIFO is filled up to the programmed threshold, the host has the option to either read the FIFO or configure for other modes. So the sequence is either configure : triggered conversions : FIFO read : triggered conversions : FIFO read ... or configure : triggered conversions : configure : Each configure clears the FIFO and the action that follows the configure command depends on the mode setting of the device.




[†] Command = Configure write for mode 10 or 11, FIFO threshold = 1/2, sweep seq = 0-1-2-3. [‡] Command = Read FIFO

Figure 12. TLC1514/TLC1518 Mode 10/11 DSP Serial Interface (conversions triggered by FS)




SLAS252 - DECEMBER 1999

modes using the FIFO: modes 01, 10, 11 timing (continued)



[†] Command = Configure write for mode 10 or 11, FIFO threshold = 1/2, sweep seq = 0-1-2-3. ‡ Command = Read FIFO

Figure 13. TLC1514/TLC1518 Mode 10/11 DSP Serial Interface (conversions triggered by CSTART)




‡ Command = Read FIFO

Figure 14. TLC1514/TLC1518 Mode 10/11 µp Serial Interface (conversions triggered by CS)



FIFO operation



FIFO Threshold Pointer

Figure 15. TLC1514/TLC1518 FIFO

The device has an 8 layer FIFO that can be programmed for different thresholds. An interrupt is sent to the host after the preprogrammed threshold is reached. The FIFO can be used to store data from either a fixed channel or a series of channels based on a preprogrammed sweep sequence. For example, an application may require eight measurements from channel 3. In this case, the FIFO is filled with 8 data sequentially taken from channel 3. Another application may require data from channel 0, channel 2, channel 4, and channel 6 in an orderly manner. Therefore, the threshold is set for 1/2 and the sweep sequence 0-2-4-6-0-2-4-6 is chosen. An interrupt is sent to the host as soon as all four data are in the FIFO.

SCLK and conversion speed

There are multiple ways to adjust the conversion speed.

• The SCLK is used as the source of the conversion clock and 14 conversion clocks are required to complete a conversion.

The devices can operate with an SCLK up to 20 MHz for the supply voltage range specified. The clock divider provides speed options appropriate for an application where a high speed SCLK is used for faster I/O. The total conversion time is $14 \times (DIV/f_{SCLK})$ where DIV is 1 or 2. For example a 20-MHz SCLK with the divide by 2 option produces a $14 \times (2/20 \text{ M}) = 1.4 \,\mu\text{s}$ conversion time. The maximum equivalent conversion clock (f_{SCLK}/DIV) should not exceed 10 MHz.

 Auto power down can be used. This mode is always on. If the device is not accessed (by CS or CSTART), the converter is powered down to save power. The built-in reference is left on in order to quickly resume operation within one half SCLK period. This provides unlimited choices to trade speed with power savings.

reference voltage

The device has a built-in reference with a level of 4 V. If the internal reference is used, REFP is set to 4 V and REFM is set to 0 V. An external reference can also be used through two reference input pins, REFP and REFM, if the reference source is programmed as external. The voltage levels applied to these pins establish the upper and lower limits of the analog inputs to produce a full-scale and zero-scale reading respectively. The values of REFP, REFM, and the analog input should not exceed the positive supply or be lower than GND consistent with the specified absolute maximum ratings. The digital output is at full scale when the input signal is equal to or higher than REFP and at zero when the input signal is equal to or lower than REFM.



FIFO operation (continued)

power down

Writing 8000h to the device puts the device into a software power-down state. For a hardware power down, the dedicated PWDN pin provides another way to power down the device asynchronously. These two power-down modes power down the entire device including the built-in reference to save power. The internal reference requires 20 ms to resume from either a software or hardware power down.

Auto power down mode is always enabled. This mode maintains the built-in reference if an internal reference is used, so resumption is fast enough to be used between cycles.

The configuration register is not affected by any of the power down modes but the sweep operation sequence has to be started over again. All FIFO contents are cleared by the hardware and software power-down modes.

power up and initialization

Initialization requires:

- 1. Determine processor type by writing A000h to the TLC1514/18
- 2. Configure the device

The first conversion after power up or resuming from power down is not valid.

absolute maximum ratings over operating free-air temperature (unless otherwise noted)[†]

Supply voltage range, GND to V _{CC}	
Analog input voltage range	
Reference input voltage	V _{CC} + 0.3 V
Digital input voltage range	$\dots -0.3 \text{ V}$ to V _{CC} + 0.3 V
Operating virtual junction temperature range, T _J	
Operating free-air temperature range, T _A : TLC1514/18I	–40°C to 85°C
Storage temperature range, T _{stg}	
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	260°C

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

recommended operating conditions

	MIN	NOM	MAX	UNIT
Supply voltage, V _{CC}	4.5	5	5.5	V
Positive external reference voltage input, VREFP (see Note 1)	2		VCC	V
Negative external reference voltage input, VREFM (note Note 1)	0		2	V
Differential reference voltage input, V _{REFP} – V _{REFM} (see Note 1)	2	VCC	V _{CC} +0.2	V
Analog input voltage (see Note 1)	0		VCC	V
High level control input voltage, VIH	2.1			V
Low-level control input voltage, VIL			0.6	V
Rise time, for CS, CSTART SDI at 0.5 pF, t _{r(I/O)}			4.76	ns
Fall time, for CS, CSTART SDI at 0.5 pF, t _{f(I/O)}			2.91	ns
Rise time, for INT, EOC, SDO at 30 pF, tr(Output)			2.43	ns
Fall time, for INT, EOC, SDO at 30 pF, t _{f(Output)}			2.3	ns

NOTE 1: When binary output format is used, analog input voltages greater than that applied to REFP convert as all ones (111111111), while input voltages less than that applied to REFM convert as all zeros (000000000). The device is functional with reference down to 2 V (VRFFP

- V_{REFM} -1); however, the electrical specifications are no longer applicable.

SLAS252 – DECEMBER 1999

recommended operating conditions (continued)

	MIN	NOM	MAX	UNIT
Transition time, for FS, SCLK, SDI, t _{t(CLK)}	0.5			SCLK
Setup time, CS falling edge before SCLK rising edge (FS=1) or before SCLK falling edge (when FS is active), tsu(CS-SCLK)	0.5			SCLK
Hold time, CS rising edge after SCLK rising edge (FS=1) or after SCLK falling edge (when FS is active), ^t h(SCLK-CS)	5			ns
Delay time, delay from CS falling edge to FS rising edge, td(CSL-FSH)	0.5		7	SCLKs
Delay time, delay time from 16th SCLK falling edge to CS rising edge (FS is active), td(SCLK16F-CSH)	0.5			SCLKs
Setup time, FS rising edge before SCLK falling edge, t _{SU(FSH-SCLKF)}			0.5	SCLKs
Hold time, FS hold high after SCLK falling edge, th(FSH-SCLKF)	0.5			SCLKs
Pulse width, CS high time, t _{wH(CS)}	100			ns
SCLK cycle time, V _{CC} = 2.7 V to 3.6V, t _{c(SCLK)}	67			ns
SCLK cycle time, V _{CC} = 4.5 V to 5.5V, t _C (SCLK)	50			ns
Pulse width, SCLK low time, twL(SCLK)	20		30	ns
Pulse width, SCLK high time, twH(SCLK)	20		30	ns
Setup time, SDI valid before falling edge of SCLK (FS is active) or the rising edge of SCLK (FS=1), tsu(DI-SCLK)			25	ns
Hold time, SDI hold valid after falling edge of SCLK (FS is active) or the rising edge of SCLK (FS=1), ^t h(DI-SCLK)	5			ns
Delay time, delay from CS falling edge to SDO valid, td(CSL-DOV)	1		25	ns
Delay time, delay from FS falling edge to SDO valid, t _{d(FSL-DOV)}			25	ns
Delay time, delay from SCLK rising edge (FS is active) or SCLK falling edge (FS=1) SDO valid, td(CLK-DOV)			25	ns
Delay time, delay from CS rising edge to SDO 3-stated, t _{d(CSH-DOZ)}			25	ns
Delay time, delay from 16th SCLK falling edge (FS is active) or the 16th rising edge (FS=1) to EOC falling edge, td(CLK-EOCL)			25	ns
Delay time, delay from EOC rising edge to SDO 3-stated if CS is low, td(EOCH-DOZ)			50	ns
Delay time, delay from 16th SCLK rising edge to INT falling edge (FS =1) or from the 16th falling edge SCLK to INT falling edge (when FS active), t _d (SCLK-INTL)			3.5	μs
Delay time, delay from CS falling edge to INT rising edge, t _{d(CSL-INTH)}			50	ns
Delay time, delay from CS rising edge to CSTART falling edge, td(CSH-CSTARTL)				ns
Delay time, delay from CSTART rising edge to EOC falling edge, td(CSTARTH-EOCL)			50	ns
Pulse width, CSTART low time, t _{WL} (CSTART)				μs
Delay time, delay from CS rising edge to EOC rising edge, t _{d(CSH-EOCH)}			50	ns
Delay time, delay from CSTART rising edge to CSTART falling edge, td(CSTARTH-CSTARTL)				μs
Delay time, delay from CSTART rising edge to INT falling edge, td(CSTARTH-INTL)				μs
Operating free-air temperature, T _A TLC1514I/TLC1518I			85	°C

NOTE 2: This is the time required for the clock input signal to fall from VIH max or to rise from VIL max to VIH min. In the vicinity of normal room temperature, the devices function with input clock transition time as slow as 1 µs for remote data-acquisition applications where the sensor and A/D converter are placed several feet away from the controlling microprocessor.



electrical characteristics over recommended operating free-air temperature range, $V_{CC} = V_{REFP} = 4.5$ V to 5.5 V, SCLK frequency = 20 MHz at 5 V, (unless otherwise noted)

	PARAMETER	TEST C	ONDITIONS	MIN	TYP†	MAX	UNIT
V _{OH}	High-level output voltage	V_{CC} = 5.5 V, I_{OH} = -20 μ A at 30 pF load		2.4			V
V _{OL}	Low-level output voltage	V_{CC} = 5.5 V, I_{OL} = 20 μ A at 30 pF load				0.4	V
	Off-state output current	$V_{O} = V_{CC}$			1	2.5	
loz	(high-impedance-state)	$V_{O} = 0$	$\overline{CS} = V_{CC}$		-1	-2.5	μA
I _{IH}	High-level input current	$V_I = V_{CC}$			0.005	2.5	μΑ
IIL	Low-level input current	V _I = 0 V			-0.005	2.5	μA
	Operating supply current, normal sampling (short)	CS at 0 V, Ext ref	V_{CC} = 4.5 V to 5.5 V			4	mA
Icc		CS at 0 V, Int ref	V_{CC} = 4.5 V to 5.5 V			6	mA
	Operating supply current, extended sampling	CS at 0 V, Ext ref	V_{CC} = 4.5 V to 5.5 V		1.9		mA
Icc		CS at 0 V, Int ref	V_{CC} = 4.5 V to 5.5 V		2		mA
	Internal reference supply current	CS at 0 V, V _{CC} = 4.5 V to 5.5 V				2	mA
I _{CC(PD)}	Power-down supply current	For all digital inputs, $0 \le V_l \le 0.3 \text{ V}$ or $V_l \ge V_{CC} - 0.3 \text{ V}$, SCLK = 0, $V_{CC} = 4.5 \text{ V}$ to 5.5 V, Ext clock			0.1	1	μΑ
I _{CC(AUTOPWDN)}	Auto power-down current	For all digital inputs, $0 \le V_1 \le 0.3 \text{ V or } V_1 \ge V_{CC} - 0.3 \text{ V},$ SCLK = 0, $V_{CC} = 4.5 \text{ V to } 5.5 \text{ V},$ Ext clock, Ext ref				5‡	μΑ
		Selected channel at V _{CC}				1	
	Selected channel leakage current	Selected channel at 0 V				-1	μA
	Maximum static analog reference current into REFP (use external reference)	$V_{\text{REFP}} = V_{\text{CC}} = 5.5 \text{ V}, V_{\text{REFM}} = \text{GND}$				1	μA
0		Analog inputs			45	50	ъĘ
Ci	Input capacitance	Control Inputs			5	25	pF
Zi	Input MUX ON resistance	V _{CC} = 5.5 V				500	Ω

[†] All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$.

 \ddagger 800 μ A if internal reference is used.

ac specifications

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
SINAD	Signal-to-noise ratio +distortion	fl = 12 kHz at 400 KSPS	59	60		dB
THD	Total harmonic distortion	fj = 12 kHz at 400 KSPS		-80	-72	dB
ENOB	Effective number of bits	fl = 12 kHz at 400 KSPS		9.6		Bits
SFDR	Spurious free dynamic range	fl = 12 kHz at 400 KSPS		-82	-72	dB
Analog input						
	Full power bandwidth, –3 dB 1			MHz		
	Full power bandwidth, -1 dB		500		kHz	



SLAS252 – DECEMBER 1999

reference specifications (0.1 μ F and 10 μ F between REFP and REFM pins)

PARAMETER	TEST CONDITIONS		MIN	TYP	MAX	UNIT
Reference input voltage, REFP	$V_{CC} = 4.5 V$				VCC	V
Input impedance	V _{CC} = 5.5 V	CS = 1, SCLK = 0, (off)	100			MΩ
		CS = 0, SCLK = 20 MHz (on)	20	25		kΩ
Input voltage difference, REFP – REFM	$V_{CC} = 4.5 V$		2		VCC	V
Internal reference voltage, REFP – REFM	V _{CC} = 5.5 V	Reference select = internal	3.85	4	4.15	V
Internal reference start up time	V _{CC} = 5.5 V	10 μF		20		ms
Reference temperature coefficient	V _{CC} = 4.5 V			16	40	PPM/°C

operating characteristics over recommended operating free-air temperature range, V_{CC} = V_{REFP} = 4.5 V, SCLK frequency = 20 MHz (unless otherwise noted)

	PARAMETER		TEST CONDITIONS	MIN TYP [†]	MAX	UNIT
	Integral linearity error (INL) (see Note 4)				±0.5	LSB
	Differential linearity error (DNL)		See Note 3		±0.5	LSB
EO	Offset error (see Note 5)		See Note 3		±1	LSB
EG	Gain error (see Note 5)		See Note 3	±0.5	±1	LSB
ET	Total unadjusted error (see Note 6)				±1	LSB
		SDI = B000h	200h (512D)			
	Self-test output code (see Table 1 and Note 7)		SDI = C000h	000h (0D)		
			SDI = D000h	3FFh (1023D))	
t _{conv}	Conversion time	External SCLK		(14XDIV ^f SCLK		
^t sample	Sampling time		At 1 kΩ	600		ns
t _{t(I/O)}	Transition time for EOC, INT				50	ns
^t t(CLK)	Transition time for SDI, SDO				25	ns

[†]All typical values are at $T_A = 25^{\circ}C$.

NOTES: 3. Analog input voltages greater than that applied to REFP convert as all ones (1111111111), while input voltages less than that applied to REFM convert as all zeros (000000000). The device is functional with reference down to 2 V (VREFP - VREFM); however, the electrical specifications are no longer applicable.


4. Linear error is the maximum deviation from the best straight line through the A/D transfer characteristics.

5. Zero error is the difference between 0000000000 and the converted output for zero input voltage: full-scale error is the difference between 1111111111 and the converted output for full-scale input voltage.

6. Total unadjusted error comprises linearity, zero, and full-scale errors.

7. Both the input data and the output codes are expressed in positive logic.






PARAMETER MEASUREMENT INFORMATION

Figure 16. Critical Timing (normal sampling, FS is active)



SLAS252 - DECEMBER 1999



PARAMETER MEASUREMENT INFORMATION






Figure 18. Critical Timing (extended sampling, repeat/sweep/repeat sweep)




^{- t}t(I/O) ^tt(I/O) -VIH CS VIL twH(CS) tsu(CS-SCLK) td(SCLK16F-CSH) twL(SCLK) tt(CLK) twH(SCLK) Ð 16 VIH SCLK ٧_{IL} ^tc(SCLK) tsu(DI-CLK) th(DI-CLK) VIH SDI ID15 ID1 VIL td(CLK-DOV) td(CSL-DOV) -۷он Hi-Z Hi-Z SDO OD9 OD VOL td(EOCH-DOZ) td(CLK-EOCL) → VOH ECO VOL td(SCLK-INTL) td(CSL-INTH) -5 ۷он INT VOL


PARAMETER MEASUREMENT INFORMATION

Figure 19. Critical Timing (normal sampling, FS = 1)




























SLAS252 - DECEMBER 1999








PRINCIPLES OF OPERATION

NOTES: A. This curve is based on the assumption that V_{ref+} and V_{ref-} have been adjusted so that the voltage at the transition from digital 0 to 1 (V_{ZT}) is 2.44 mV, and the transition to full scale (V_{FT}) is 4.9898 V, 1 LSB = 4.88 mV.

B. The full scale value (VFS) is the step whose nominal midstep value has the highest absolute value. The zero-scale value (VZS) is the step whose nominal midstep value equals zero.

Figure 36. Ideal 10-Bit ADC Conversion Characteristics







SLAS252 - DECEMBER 1999

PRINCIPLES OF OPERATION

simplified analog input analysis

Using the equivalent circuit in Figure 39, the time required to charge the analog input capacitance from 0 to VS within 1/2 LSB can be derived as follows.

The capacitance charging voltage is given by:

$$Vc = Vs \left(1 - EXP \left(\frac{-tc}{Rt \times Ci} \right) \right)$$
(1)

Where

Rt = Rs + Zitc = Cycle time

The input impedance Zi is 0.5 k Ω at 5 V. The final voltage to 1/2 LSB is given by:

$$VC (1/2 \ LSB) = VS - \left(\frac{VS}{2048}\right)$$
(2)

Equating equation 1 to equation 2 and solving for cycle time tc gives:

$$V_{S} - \left(\frac{VS}{2048}\right) = V_{S} \left(1 - E_{X} P\left(\frac{-t_{C}}{Rt \times Ci}\right)\right)$$
(3)

and time to change to 1/2 LSB (minimum sampling time) is:

 $tch (1/2 LSB) = Rt \times Ci \times In(2048)$

Where

ln(2048) = 7.625

Therefore, with the values given, the time for the analog input signal to settle is:

$$tch (1/2 \ LSB) = (Rs + 0.5 \ k\Omega) \times Ci \times In(2048)$$
 (4)

This time must be less than the converter sample time shown in the timing diagrams. This is 12× SCLKs (if the sampling mode is short normal sampling mode).

$$tch (1/2 LSB) \leq 12 \times \frac{1}{f(SCLK)}$$
(5)


Therefore the maximum SCLK frequency is:

$$max[f(SCLK)] = \frac{12}{tch (1/2 \ LSB)} = \frac{12}{[In(2048) \times Rt \times Ci]}$$
(6)



SLAS252 - DECEMBER 1999

PRINCIPLES OF OPERATION



[†] Driving source requirements:

• Noise and distortion for the source must be equivalent to the resolution of the converter.

• R_S must be real at the input frequency.

Figure 38. Equivalent Input Circuit Including the Driving Source

maximum conversion throughput

For a supply voltage of 5 V, if the source impedance is less than 1 k Ω , and the ADC analog input capacitance Ci is less than 50 pF, this equates to a minimum sampling time tch(0.5 LSB) of 0.571 µs. Since the sampling time requires 12 SCLKs, the fastest SCLK frequency is 12/tch = 20 MHz.

The minimal total cycle time is given as:

$$tc = tcommand + tch + tconv + td(EOCH-CSL) = 4 \times \frac{1}{f(SCLK)} + 12 \times \frac{1}{f(SCLK)} + 1.4 \ \mu s + 0.1 \ \mu s$$
$$= 16 \times \frac{1}{20 \ \text{MHz}} + 1.5 \ \mu s = 2.3 \ \mu s$$

This is equivalent to a maximum throughput of 400 KSPS. The throughput can be even higher with a smaller source impedance.



PRINCIPLES OF OPERATION

power down calculations

 $i(AVERAGE) = (f_S/f_{SMAX}) \times i(ON) + (1-f_S/f_{SMAX}) \times i(OFF)$

CASE 1: If $V_{DD} = 5$ V, auto power down, and an external reference is used:

$$f_{S} = 20 \text{ kHz}$$

 $f_{SMAX} = 400 \text{ kHz}$
 $i(ON) = -4 \text{ mA}$ operating current and $i(OFF) = -5 \mu A$ auto power-down current

so

 $i(AVERAGE) = 0.05 \times 4000 \ \mu A + 0.95 \times 5 \ \mu A = 0.21 \ m A$

CASE 2: Now if software power down is used, another cycle is needed to shut it down.

$$f_{S} = 40 \text{ kHz}$$

 $f_{SMAX} = 400 \text{ kHz}$
 $i(ON) = -4 \text{ mA}$ operating current and $i(OFF) = -5 \mu A$ power-down current

so

$$i(AVERAGE) = 0.1 \times 4000 \ \mu A + 0.9 \times 5 \ \mu A = 0.41 \ m A$$

In reality this will be less since the second conversion never happened. It is only the additional cycle to shut down the ADC.

CASE 3: Now if the hardware power down is used.

$$f_S = 20 \text{ kHz}$$

 $f_{SMAX} = 400 \text{ kHz}$
 $i(ON) = -4 \text{ mA}$ operating current and $i(OFF) = -5 \mu A$ power-down current

so

 $i(AVERAGE) = 0.05 \times 4000 \ \mu A + 0.95 \times 5 \ \mu A = 0.21 \ m A$

difference between modes of conversion

The major difference between sweep mode (mode 10) and repeat sweep mode (mode 11) is that the sweep sequence ends after the FIFO is filled up to the programmed threshold. The repeat sweep can either dump the FIFO (by ignoring the FIFO content but simply reconfiguring the device) or read the FIFO and then repeat the conversions on the the same sequence of the channel as before.

FIFO reads are expected after the FIFO is filled up to the threshold in each case. Mode 10 – the device allows only FIFO read or CFR read or CFR write to be executed. Any conversion command is ignored. In the case of mode 11, in addition to the above commands, conversion commands are also executed, i.e. the FIFO is cleared and the sweep sequence is restarted.

Both single shot and repeat modes require selection of a channel after the device is configured for these modes. Single shot mode does not use the FIFO, but repeat mode does. When the device is operating in repeat mode, the FIFO can be dumped (by ignoring the FIFO content and simply reconfiguring the device) or the FIFO can be read and then the conversions repeated on the same channel as before. However, the channel has to be selected first before any conversion can be carried out. The devices can be programmed with the following sequences for operating in the different modes that use a FIFO.



PRINCIPLES OF OPERATION

difference between modes of conversion (continued)

REPEAT:

Configure FIFO Depth=4 /CONV Mode 01 Select Channel/ 1st Conv (CS or CSTART) 2nd Conv $\overline{(CS \text{ or } CSTART)}$ 3rd Conv (CS or CSTART) 4th Conv (CS or CSTART **FIFO READ 1 FIFO READ 2 FIFO READ 3 FIFO READ 4** Select Channel 1st Conv (CS or CSTART) 2nd Conv (CS or CSTART) 3rd Conv (CS or CSTART) 4th Conv (CS or CSTART SWEEP: Configure FIFO Depth=4 SEQ=1-2-3-4/CONV Mode 10 conv ch 1 (CS/CSTART) conv ch 2 (CS/CSTART) conv ch 3 (CS/CSTART) conv ch 4 (CS/CSTART FIFO READ ch 1 result FIFO READ ch 2 result FIFO READ ch 3 result FIFO READ ch 4 result Configure (not required if same sweep sequence is to be used again) **REPEAT SWEEP:** Configure FIFO Depth=4 SWEEP SEQ=1-2-3-4/CONV Mode 11 conv ch 1 (CS/CSTART) conv ch 2 (CS/CSTART) conv ch 3 (CS/CSTART)

conv ch 4 (CS/CSTART FIFO READ ch 1 result FIFO READ ch 2 result FIFO READ ch 3 result FIFO READ ch 3 result conv ch 1 (CS/CSTART) conv ch 2 (CS/CSTART) conv ch 3 (CS/CSTART) conv ch 4 (CS/CSTART)



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	dsp.ti.com	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2010, Texas Instruments Incorporated