

Test Report

Fail

Test Configuration Details	
Application	
Name	D9020DPHC MIPI D-PHY Test
Version	3.90.0.0
Device Description	
High Speed Data Rate(Mbps)	600
CTS Version	v1.2
ZID	100 ohm
Cload	50pF
Fixture Setup	Manual Load Switching
Test Session Details	
Infiniium SW Version	06.50.00906
Infiniium Model Number	MSOV134A
Infiniium Serial Number	MY57220101
Debug Mode Used	No
Compliance Limits	MIPI D-PHY Test Limit v1.2 (official)
Probe (Channel 1)	Model: 1169B Serial: US55390726 Head: N5425A/B Atten: Calibrated (14 JUN 2023 14:22:42), Using Cal Atten (3.1213E+00) Skew: Calibrated (14 JUN 2023 14:22:57), Using Cal Skew
Probe (Channel 2)	Model: 1169B Serial: US55390676 Head: N5425A/B Atten: Calibrated (14 JUN 2023 14:32:45), Using Cal Atten (3.1934E+00) Skew: Calibrated (14 JUN 2023 14:32:55), Using Cal Skew
Probe (Channel 3)	Model: 1169B Serial: US55390699 Head: N5425A/B Atten: Calibrated (14 JUN 2023 14:27:09), Using Cal Atten (3.2111E+00) Skew: Calibrated (14 JUN 2023 14:27:35), Using Cal Skew
Probe (Channel 4)	Model: 1169B Serial: US55390644 Head: N5425A/B Atten: Calibrated (14 JUN 2023 14:29:25), Using Cal Atten (3.2062E+00) Skew: Calibrated (14 JUN 2023 14:29:35), Using Cal Skew
Last Test Date	2023-06-15 22:39:49 UTC +08:00

Summary of Results

Test Statistics		Margin Thresholds	
Failed	0	Warning	< 2 %
Passed	32	Critical	< 0 %
Total	32		

Pass	# Failed	# Trials	Test Name (click to jump)	Actual Value	Margin	Pass Limits
✓	0	1	1.3.7 HS Data TX Static Common Mode Voltage(Vcmtx)	191.67 mV	41.7 %	150.00 mV <= VALUE <= 250.00 mV
✓	0	1	1.3.8 HS Data TX Vcmtx Mismatch	1.89 mV	62.2 %	VALUE < 5.00 mV
✓	0	1	1.3.10 HS Data TX Common-Level Variations Above 450MHz (VCMTX(HF))	6.83 mV	54.5 %	VALUE < 15.00 mV
✓	0	1	1.3.9 HS Data TX Common-Level Variations Between 50-450MHz (VCMTX(LF))	10.04 mV	59.8 %	VALUE < 25.00 mV
✓	0	1	1.3.4 HS Data TX Differential Voltage(VOD0 Pulse)	-200.61 mV	46.6 %	-270.00 mV <= VALUE <= -140.00 mV
✓	0	1	1.3.4 HS Data TX Differential Voltage(VOD1 Pulse)	202.28 mV	47.9 %	140.00 mV <= VALUE <= 270.00 mV
✓	0	1	1.3.5 HS Data TX Differential Voltage Mismatch (Pulse)	1.67 mV	88.1 %	VALUE < 14.00 mV
✓	0	1	1.3.6 HS Data TX Single Ended Output High Voltage(VOHHS Pulse)	297.68 mV	17.3 %	VALUE <= 360.00 mV
✓	0	1	1.4.17 HS Clock Instantaneous (UIinst)(Max)	1.292 ns	89.7 %	VALUE < 12.500 ns
✓	0	1	1.3.3 HS Entry: DATA TX THS-PREPARE+THS-ZERO	243.64 ns	54.7 %	VALUE >= TXTHSPrepereTHSZero_LimitMin s
✓	0	1	1.3.11 HS Data TX 20%-80% Rise Time (tR)[Burst Data]	188 ps	49.9 %	VALUE < DataRiseTime_LimitMax s
✓	0	1	1.3.12 HS Data TX 80%-20% Fall Time (tF)[Burst Data]	188 ps	49.9 %	VALUE < DataFallTime_LimitMax s
✓	0	1	1.4.9 HS Clock TX Common-Level Variations Between 50-450MHz (VCMTX(LF))	9.02 mV	63.9 %	VALUE < 25.00 mV
✓	0	1	1.4.7 HS Clock TX Static Common Mode Voltage(Vcmtx)	203.54 mV	46.5 %	150.00 mV <= VALUE <= 250.00 mV
✓	0	1	1.4.8 HS Clock TX Vcmtx Mismatch	2.26 mV	54.8 %	VALUE < 5.00 mV
✓	0	1	1.4.10 HS Clock TX Common-Level Variations Above 450MHz (VCMTX(HF))	5.66 mV	62.3 %	VALUE < 15.00 mV
✓	0	1	1.4.4 HS Clock TX Differential Voltage(VOD0 Pulse)	-210.95 mV	45.4 %	-270.00 mV <= VALUE <= -140.00 mV
✓	0	1	1.4.4 HS Clock TX Differential Voltage(VOD1 Pulse)	212.19 mV	44.5 %	140.00 mV <= VALUE <= 270.00 mV
✓	0	1	1.4.5 HS Clock TX Differential Voltage Mismatch (Pulse)	1.24 mV	91.1 %	VALUE < 14.00 mV
✓	0	1	1.4.6 HS Clock TX Single Ended Output High Voltage(VOHHS Pulse)	313.94 mV	12.8 %	VALUE <= 360.00 mV
✓	0	1	1.4.11 HS Clock TX 20%-80% Rise Time (tR)[Continuous Clock, Burst Data]	192 ps	48.8 %	VALUE < CLKRiseTime_LimitMax s

✓	0	1	1.4.12 HS Clock TX 80%-20% Fall Time (tF)[Continuous Clock, Burst Data]	191 ps	49.1 %	VALUE < CLKFallTime_LimitMax s
✓	0	1	1.4.17 HS Clock Instantaneous (UIinst)(Min)	1.216 ns	122E+01 %	VALUE >= UIinst_Min_Limit s
✓	0	1	1.4.18 Clock Lane HS Clock Delta UI (UI variation)	3.36 %	33.2 %	UIVariant_Limit_Min % <= VALUE <= UIVariant_Limit_Max %
✓	0	1	1.3.1 HS Entry: DATA TLPX	100.05 ns	100.1 %	VALUE >= 50.00 ns
✓	0	1	1.3.2 HS Entry: DATA TX THS-PREPARE	66.37 ns	45.0 %	THSPrepare_LimitMin s <= VALUE <= THSPrepare_LimitMax s
✓	0	1	1.3.13 HS Exit: DATA TX THS-TRAIL	93.06 ns	39.6 %	VALUE >= TXTHSTrail_LimitMin s
✓	0	1	1.3.14 HS Exit: DATA TX TREET	9.16 ns	73.8 %	VALUE <= 35.00 ns
✓	0	1	1.3.15 HS Exit: DATA TX TEOT	102.22 ns	14.8 %	VALUE <= TXTEOT_LimitMax s
✓	0	1	1.3.16 HS Exit: DATA TX THS-EXIT	14.47329 μs	144E+02 %	VALUE >= 100.00 ns
✓	0	1	1.5.4 Data-to-Clock Skew (TSKEW(TX))(Max,Min)	-109 mUIinst	13.7 %	MinMaxTSkewTest_LimitMin UIinst <= VALUE <= MinMaxTSkewTest_LimitMax UIinst
✓	0	1	1.5.4 Data-to-Clock Skew (TSKEW(TX))(Mean)	-26 mUIinst	41.3 %	MeanTSkewTest_LimitMin UIinst <= VALUE <= MeanTSkewTest_LimitMax UIinst

Report Detail

[Summary](#)

[Next](#)

✓	1.3.7 HS Data TX Static Common Mode Voltage(Vcmtx)	D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.3.7)
---	---	---

HS transmit static common-mode voltage.
 Actual Value Measurement Name: 811_Vcmtx(Worst)
 Pass Limits: 150.00 mV <= VALUE <= 250.00 mV

Actual Value	Margin	HS Data TX Common Mode Voltage	Vcmtx(Differential-1)	Number of Vcmtx(Differential-1) Measured	Vcmtx(Differential-0)
191.67 mV	41.7 %	(See image)	191.67 mV	2.423000 k	195.46 mV

Number of Vcmtx(Differential-0) Measured	ZID	DataLane	Number of HS Burst
9.117000 k	100 ohm	Lane0	1

HS Data TX Common Mode Voltage

Keysight Infiniium : Thursday, June 15, 2023 10:30:07 PM



[Summary](#)

[Previous](#)

[Next](#)

✓	1.3.8 HS Data TX Vcmtx Mismatch	D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.3.8)
---	--	---

VCMTX mismatch when output is Differential-1 or Differential-0.
 Actual Value Measurement Name: 812_Vcmtx Mismatch
 Pass Limits: VALUE < 5.00 mV

Actual Value	Margin	Vcmtx(Differential-1)	Vcmtx(Differential-0)	ZID	DataLane	Number of HS Burst
1.89 mV	62.2 %	191.67 mV	195.46 mV	100 ohm	Lane0	1


1.3.10 HS Data TX Common-Level Variations Above 450MHz (VCMTX(HF)) D-PHY Specification v1.2 Section 9.1.1 Table 20, CTS v1.2(Test 1.3.10)

Common-level variations above 450MHz.
 Actual Value Measurement Name: 818_Vcmtx(HF)
 Pass Limits: VALUE < 15.00 mV

Actual Value	Margin	Common Level Variations(>450Mhz)	ZID	DataLane	Number of HS Burst
6.83 mV	54.5 %	(See image)	100 ohm	Lane0	1

Common Level Variations(>450Mhz)

Keysight Infiniium : Thursday, June 15, 2023 10:30:20 PM




1.3.9 HS Data TX Common-Level Variations Between 50-450MHz (VCMTX(LF)) D-PHY Specification v1.2 Section 9.1.1 Table 20, CTS v1.2(Test 1.3.9)

Common-level variation between 50-450MHz.
 Actual Value Measurement Name: 819_Vcmtx(LF)
 Pass Limits: VALUE < 25.00 mV

Actual Value	Margin	Common Level Variations(50-450MHz)	ZID	DataLane	Number of HS Burst
10.04 mV	59.8 %	(See image)	100 ohm	Lane0	1

Common Level Variations(50-450MHz)

Keysight Infiniium : Thursday, June 15, 2023 10:30:32 PM




1.3.4 HS Data TX Differential Voltage(VOD0 Pulse) D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.3.4)

HS transmit differential voltage.
 This test will measure the VOD0 based on the reference data patterns(100000) of differential signal.
 Actual Value Measurement Name: 8131_Vod0(Mean)
 Pass Limits: -270.00 mV <= VALUE <= -140.00 mV

Actual Value	Margin	VOD0 (100000)	Vod(Differential-0)	Number of measurement	ZID	DataLane	Number of HS Burst
-200.61 mV	46.6 %	(See image)	-200.61 mV	441.000	100 ohm	Lane0	1

VOD0 (100000)

Keysight Infiniium : Thursday, June 15, 2023 10:30:44 PM



[Summary](#) [Previous](#) [Next](#)

1.3.4 HS Data TX Differential Voltage(VOD1 Pulse)


D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.3.4)

HS transmit differential voltage.
 This test will measure the VOD1 based on the reference data patterns(011111) of differential signal.
 Actual Value Measurement Name: 8132_Vod1(Mean)
 Pass Limits: 140.00 mV <= VALUE <= 270.00 mV

Actual Value	Margin	VOD1 (011111)	Vod(Differential-1)	Number of measurement	ZID	DataLane	Number of HS Burst
202.28 mV	47.9 %	(See image)	202.28 mV	39.000	100 ohm	Lane0	1

VOD1 (011111)

Keysight Infiniium : Thursday, June 15, 2023 10:30:57 PM



[Summary](#) [Previous](#) [Next](#)

1.3.5 HS Data TX Differential Voltage Mismatch (Pulse)

D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.3.5)

VOD mismatch when output is Differential-1 or Differential-0.
 Actual Value Measurement Name: 8141_Vod Mismatch
 Pass Limits: VALUE < 14.00 mV

Actual Value	Margin	Vod(Differential-1)	Vod(Differential-0)	ZID	DataLane	Number of HS Burst
--------------	--------	---------------------	---------------------	-----	----------	--------------------

1.67 mV	88.1 %	202.28 mV	-200.61 mV	100 ohm	Lane0	1
---------	--------	-----------	------------	---------	-------	---

Summary Previous Next



1.3.6 HS Data TX Single Ended Output High Voltage(VOHHS Pulse)


D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.3.6)

HS Single Ended output high voltage.
 This test will measure the VOHHS based on the reference pulses(100000) of single-ended Dp and Dn signals.
 Actual Value Measurement Name: 8151_Vohhs(Worst)
 Pass Limits: VALUE <= 360.00 mV

Actual Value	Margin	DpVOHHS (011111)	DnVOHHS (011111)	Vohhs(Dp)	Vohhs(Dn)	Number of measurement Vohhs(Dp)
297.68 mV	17.3 %	(See image)	(See image)	297.68 mV	297.08 mV	39.000
Number of measurement Vohhs(Dn)	ZID	DataLane	Number of HS Burst			
441.000	100 ohm	Lane0	1			


DpVOHHS (011111)

Keysight Infiniium : Thursday, June 15, 2023 10:31:12 PM



DnVOHHS (011111)

Keysight Infiniium : Thursday, June 15, 2023 10:31:27 PM



Summary Previous Next




1.4.17 HS Clock Instantaneous (UIInst)(Max)

D-PHY Specification v1.2 Section 10.1 Table 29, CTS v1.2(Test 1.4.17)

Maximum UI instantaneous of HS Clock.
 Actual Value Measurement Name: 911_UIInst(Max)
 Pass Limits: VALUE < 12.500 ns

Actual Value	Margin	UIInst	UIINST(Max)	UIINST(Mean)	Number of UI	ZID	DataLane	Number of HS Burst
1.292 ns	89.7 %	(See image)	1.291980 ns	1.249992 ns	79.999000 k	100 ohm	Lane0	1

UIInst




Summary Previous Next

1.3.3 HS Entry: DATA TX THS-PREPARE+THS-ZERO D-PHY Specification v1.2 Section 6.9 Table 14, CTS v1.2(Test 1.3.3)

THS-PREPARE+Time to drive HS-0 before Sync sequence.
 TXTHSPrepareTHSZero_LimitMin is based on 145ns+10*UI.
 Actual Value Measurement Name: 558_THS-PREPARE+THS-ZERO
 Pass Limits: VALUE >= TXTHSPrepareTHSZero_LimitMin s

Actual Value	Margin	THSPREPARE_THSZERO	UIINST(Mean)	VHS_ZERO	ZID	DataLane	PassLimit Min (TXTHSPrepareTHSZero_LimitMin)
243.64 ns	54.7 %	(See image)	1.249992 ns	-192.84 mV	100 ohm	Lane0	157.50 ns

Number of HS burst	1
--------------------	---



Summary Previous Next

1.3.11 HS Data TX 20%-80% Rise Time (tR)[Burst Data] D-PHY Specification v1.2 Section 9.1.1 Table 20, CTS v1.2(Test 1.3.11)

This test is to verify that the 20%-80% rise time of the HS Differential signal is less than the maximum conformance limit(DataRiseTime_LimitMax).
 For CTS v1.2, the maximum conformance limit(DataRiseTime_LimitMax) is 0.3*UI for Datarate = 1Gbps, 0.35*UI for Datarate > 1Gbps and = 1.5Gbps, 0.4*UI for Datarate > 1.5Gbps.
 This test will measure the rise time based on the reference data patterns(000111) of differential signal.
 This test is applicable for Burst Data signal only.
 The VHS_ZERO level measured from Data Lane will be used to calculate 20/80% reference voltage for rise time measurement in this test.

Actual Value Measurement Name: 81101_Rise Time
 Pass Limits: VALUE < DataRiseTime_LimitMax s

Actual Value	Margin	HS TX Risetime	Transition Time Measurement Lower Threshold(%)	Vod(1)	Vod(0)	UIINST(Mean)
188 ps	49.9 %	(See image)	20	192.84 mV	-192.84 mV	1.249992 ns

Number of Measurement	ZID	DataLane	PassLimit Max (DataRiseTime_LimitMax)	Number of HS Burst
-----------------------	-----	----------	---------------------------------------	--------------------

38	100 ohm	Lane0	375 ps	1
----	---------	-------	--------	---

HS TX Risetime

Keysight Infiniium : Thursday, June 15, 2023 10:33:48 PM



Summary Previous Next



1.3.12 HS Data TX 80%-20% Fall Time (tF)[Burst Data]

D-PHY Specification v1.2 Section 9.1.1 Table 20, CTS v1.2(Test 1.3.12)


This test is to verify that the 80%-20% fall time of the HS differential signal is less than the maximum conformance limit(DataFallTime_LimitMax). For CTS v1.2, the maximum conformance limit(DataFallTime_LimitMax) is 0.3*UI for Datarate = 1Gbps, 0.35*UI for Datarate > 1Gbps and = 1.5Gbps, 0.4*UI for Datarate > 1.5Gbps. This test will measure the fall time based on the reference data patterns(111000) of differential signal. This test is applicable for Burst Data signal only. The VHS_ZERO level measured from Data Lane will be used to calculate 20/80% reference voltage for fall time measurement in this test. Actual Value Measurement Name: 81111_Fall Time Pass Limits: VALUE < DataFallTime_LimitMax s

Actual Value	Margin	HS TX Falltime	Transition Time Measurement Lower Threshold(%)	Vod(1)	Vod(0)	UIINST (Mean)
188 ps	49.9 %	(See image)	20	192.84 mV	-192.84 mV	1.249992 ns

Number of Measurement	ZID	DataLane	PassLimit Max (DataFallTime_LimitMax)	Number of HS Burst
52	100 ohm	Lane0	375 ps	1

HS TX Falltime

Keysight Infiniium : Thursday, June 15, 2023 10:34:09 PM



Summary Previous Next



1.4.9 HS Clock TX Common-Level Variations Between 50-450MHz (VCMTX(LF))

D-PHY Specification v1.2 Section 9.1.1 Table 20, CTS v1.2(Test 1.4.9)


Common-level variation between 50-450MHz. This test is only available for CTS v1.2 and CTS v2.0 and v2.1. Actual Value Measurement Name: 1820_Vcmbx(LF) Pass Limits: VALUE < 25.00 mV

Actual Value	Margin	Common Level Variations(50-450MHz)	ZID	Number of HS Burst

9.02 mV	63.9 %	(See image)	100 ohm	1
---------	--------	-------------	---------	---

Common Level Variations(50-450MHz)

Keysight Infiniium : Thursday, June 15, 2023 10:34:22 PM




[Summary](#) [Previous](#) [Next](#)

1.4.7 HS Clock TX Static Common Mode Voltage(Vcmtx) D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.4.7)

HS transmit static common-mode voltage for Clock.
 Actual Value Measurement Name: 1811_Vcmtx(Worst)
 Pass Limits: 150.00 mV <= VALUE <= 250.00 mV

Actual Value	Margin	HS Clock TX Common Mode Voltage	Vcmtx(Differential-1)	Number of Vcmtx(Differential-1) Measured	Vcmtx(Differential-0)
203.54 mV	46.5 %	(See image)	203.54 mV	39.999000 k	199.01 mV
Number of Vcmtx(Differential-0) Measured		ZID	Number of HS Burst		
40.000000 k		100 ohm	1		

HS Clock TX Common Mode Voltage



1.4.8 HS Clock TX Vcmtx Mismatch Summary Previous Next
 D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.4.8)
 VCMTX mismatch when output is Differential-1 or Differential-0.
 Actual Value Measurement Name: 1812_Vcmtx Mismatch
 Pass Limits: VALUE < 5.00 mV

Actual Value	Margin	Vcmtx(Differential-1)	Vcmtx(Differential-0)	ZID	Number of HS Burst
2.26 mV	54.8 %	203.54 mV	199.01 mV	100 ohm	1

1.4.10 HS Clock TX Common-Level Variations Above 450MHz (VCMTX(HF)) Summary Previous Next
 D-PHY Specification v1.2 Section 9.1.1 Table 20, CTS v1.2(Test 1.4.10)
 Common-level variations above 450MHz.
 Actual Value Measurement Name: 1818_Vcmtx(HF)
 Pass Limits: VALUE < 15.00 mV

Actual Value	Margin	Common Level Variations(>450Mhz)	ZID	Number of HS Burst
5.66 mV	62.3 %	(See image)	100 ohm	1

Common Level Variations(>450Mhz)




1.4.4 HS Clock TX Differential Voltage(VOD0 Pulse) D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.4.4)

HS clock transmitter differential voltage.
 Actual Value Measurement Name: 18131_Vod0(Mean)
 Pass Limits: -270.00 mV <= VALUE <= -140.00 mV

Actual Value	Margin	Clock VOD0 (10)	Vod(Differential-0)	Number of measurement	ZID	Number of HS Burst
-210.95 mV	45.4 %	(See image)	-210.95 mV	40.000000 k	100 ohm	1

Clock VOD0 (10)



1.4.4 HS Clock TX Differential Voltage(VOD1 Pulse) D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.4.4)

HS clock transmitter differential voltage.
 Actual Value Measurement Name: 18132_Vod1(Mean)
 Pass Limits: 140.00 mV <= VALUE <= 270.00 mV

Actual Value	Margin	Clock VOD1 (01)	Vod(Differential-1)	Number of measurement	ZID	Number of HS Burst
212.19 mV	44.5 %	(See image)	212.19 mV	40.000000 k	100 ohm	1

Clock VOD1 (01)



[Summary](#) [Previous](#) [Next](#)

1.4.5 HS Clock TX Differential Voltage Mismatch (Pulse) D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.4.5)

VOD mismatch when output is Differential-1 or Differential-0.
 Actual Value Measurement Name: 18141_Vod Mismatch
 Pass Limits: VALUE < 14.00 mV

Actual Value	Margin	Vod(Differential-1)	Vod(Differential-0)	ZID	Number of HS Burst
1.24 mV	91.1 %	212.19 mV	-210.95 mV	100 ohm	1

[Summary](#) [Previous](#) [Next](#)

1.4.6 HS Clock TX Single Ended Output High Voltage(VOHHS Pulse) D-PHY Specification v1.2 Section 9.1.1 Table 19, CTS v1.2(Test 1.4.6)

HS Single Ended output high voltage.
 Actual Value Measurement Name: 18151_Vohhs(Worst)
 Pass Limits: VALUE <= 360.00 mV


Actual Value	Margin	ClkpVOHHS (01)	ClknVOHHS (01)	Vohhs(Clkp)	Vohhs(Clkn)	Number of measurement Vohhs(Clkp)
313.94 mV	12.8 %	(See image)	(See image)	313.94 mV	307.26 mV	40.000000 k

Number of measurement Vohhs(Clkn)	ZID	Number of HS Burst
40.000000 k	100 ohm	1

ClkpVOHHS (01)



ClknVOHHS (01)




Summary Previous Next

1.4.11 HS Clock TX 20%-80% Rise Time (tR)[Continuous Clock, Burst Data] D-PHY Specification v1.2 Section 9.1.1 Table 20, CTS v1.2(Test 1.4.11)

This test is to verify that the 20%-80% rise time of the HS differential signal is less than the maximum conformance limit(CLKRIseTime_LimitMax). For CTS v1.2, the maximum conformance limit(CLKRIseTime_LimitMax) is 0.3*UI for Datarate = 1Gbps, 0.35*UI for Datarate > 1Gbps and = 1.5Gbps, 0.4*UI for Datarate > 1.5Gbps. This test is applicable for Continuous Clock and Burst Data signal only. The VHS_ZERO level measured from Data Lane will be used to calculate 20/80% reference voltage for rise time measurement in this test. Actual Value Measurement Name: 181102_Rise Time Pass Limits: VALUE < CLKRIseTime_LimitMax s

Actual Value	Margin	HS Clock TX Risetime	Transition Time Measurement Lower Threshold(%)	Vod(1)	Vod(0)	UIINST(Mean)
192 ps	48.8 %	(See image)	20	192.84 mV	-192.84 mV	1.249992 ns
Number of Measurement	ZID	PassLimit Max (CLKRIseTime_LimitMax)	Number of HS Burst			
40.000 k	100 ohm	375 ps	1			

HS Clock TX Risetime



Summary Previous Next

1.4.12 HS Clock TX 80%-20% Fall Time (tF)[Continuous Clock, Burst Data] D-PHY Specification v1.2 Section 9.1.1 Table 20, CTS v1.2(Test 1.4.12)

This test is to verify that the 80%-20% fall time of the HS differential signal is less than the maximum conformance limit(CLKFallTime_LimitMax). For CTS v1.2, the maximum conformance limit(CLKFallTime_LimitMax) is 0.3*UI for Datarate = 1Gbps, 0.35*UI for Datarate > 1Gbps and = 1.5Gbps, 0.4*UI for Datarate > 1.5Gbps. This test is applicable for Continuous Clock and Burst Data signal only. The VHS_ZERO level measured from Data Lane will be used to calculate 20/80% reference voltage for fall time measurement in this test. Actual Value Measurement Name: 181112_Fall Time Pass Limits: VALUE < CLKFallTime_LimitMax s

Actual Value	Margin	HS Clock TX Falltime	Transition Time Measurement Lower Threshold(%)	Vod(1)	Vod(0)	UIINST(Mean)
191 ps	49.1 %	(See image)	20	192.84 mV	-192.84 mV	1.249992 ns

Number of Measurement	ZID	PassLimit Max (CLKFallTime_LimitMax)	Number of HS Burst
40.000 k	100 ohm	375 ps	1

HS Clock TX Falltime

Keysight Infiniium : Thursday, June 15, 2023 10:36:58 PM



[Summary](#) [Previous](#) [Next](#)

1.4.17 HS Clock Instantaneous (UIinst)(Min) D-PHY Specification v1.2 Section 10.1 Table 29, CTS v1.2(Test 1.4.17)

Minimum UI instantaneous (Min) of HS Clock.
 Actual Value Measurement Name: 914_UIinst(Min)
 Pass Limits: VALUE >= UIinst_Min_Limit s

Actual Value	Margin	UIINST(Min)	UIINST(Mean)	Number of UI	ZID	DataLane	PassLimit Min (UIinst_Min_Limit)	Number of HS Burst
1.216 ns	122E+01 %	1.215720 ns	1.249992 ns	79.999000 k	100 ohm	Lane0	0.000000000000 s	1

[Summary](#) [Previous](#) [Next](#)

1.4.18 Clock Lane HS Clock Delta UI (UI variation) D-PHY Specification v1.2 Section 10.1 Table 29, CTS v1.2(Test 1.4.18)

This test is to verify that the Clock lane HS Clock Delta UI is in between the minimum conformance limit(UIVariant_Limit_Min) and the maximum conformance limit(UIVariant_Limit_Max). For CTS v1.1, UIVariant_Limit_Min is -10% and UIVariant_Limit_Max is 10% for Datarate = 1Gbps, UIVariant_Limit_Min is -5% and UIVariant_Limit_Max is 5% for Datarate > 1Gbps. For CTS v1.2, UIVariant_Limit_Min is -10% and UIVariant_Limit_Max is 10% for Datarate = 1Gbps, UIVariant_Limit_Min is -5% and UIVariant_Limit_Max is 5% for Datarate > 1Gbps and = 1.5Gbps .
 Actual Value Measurement Name: 1911_UIVariant(Min)
 Pass Limits: UIVariant_Limit_Min % <= VALUE <= UIVariant_Limit_Max %

Actual Value	Margin	UIINST(Min)	UIINST(Max)	UIINST(Mean)	Number of UI	DataLane	UIVariant_min	UIVariant_max	ZID
3.36 %	33.2 %	1.215720 ns	1.291980 ns	1.249992 ns	79.999000 k	Lane0	-2.742 %	3.359 %	100 ohm

PassLimit Min (UIVariant_Limit_Min)	PassLimit Max (UIVariant_Limit_Max)	Number of HS Burst
-10.00 %	10.00 %	1


[Summary](#) [Previous](#) [Next](#)

1.3.1 HS Entry: DATA TLPX D-PHY Specification v1.2 Section 6.9 Table 14, CTS v1.2(Test 1.3.1)

Length of any Low-Power state period.
 Actual Value Measurement Name: 511_TLPX
 Pass Limits: VALUE >= 50.00 ns

Actual Value	Margin	TLPX	ZID	DataLane	Number of HS burst
100.05 ns	100.1 %	(See image)	100 ohm	Lane0	1

TLPX




Summary Previous Next

1.3.2 HS Entry: DATA TX THS-PREPARE D-PHY Specification v1.2 Section 6.9 Table 14, CTS v1.2(Test 1.3.2)

Time to drive LP-00 to prepare for HS Transmission.
 THSPrepare_LimitMin is based on $40ns+4*UI$.
 THSPrepare_LimitMax is based on $85ns+6*UI$.
 Actual Value Measurement Name: 557_THS-PREPARE
 Pass Limits: THSPrepare_LimitMin s <= VALUE <= THSPrepare_LimitMax s

Actual Value	Margin	THSPREPRE	UIINST(Mean)	ZID	DataLane	PassLimit Min (THSPrepare_LimitMin)	PassLimit Max (THSPrepare_LimitMax)
66.37 ns	45.0 %	(See image)	1.249992 ns	100 ohm	Lane0	45.00 ns	92.50 ns

Number of HS burst	1
--------------------	---




Summary Previous Next

1.3.13 HS Exit: DATA TX THS-TRAIL D-PHY Specification v1.2 Section 6.9 Table 14, CTS v1.2(Test 1.3.13)

Time to drive flipped differential state after last payload data bit of a HS transmission burst.
 TXTHSTrail_LimitMin is based on $60ns+n*4*UI$.
 The THS-SKIP parameter is useful to avoid glitch problem during THS-TRAIL measurement.
 Any transition on the Data Lane in THS-SKIP time interval will be ignored when finding last payload data bit of HS transmission burst.
 The default value of THS-SKIP is set to 0s to prevent invalid THS-TRAIL measurement.
 Actual Value Measurement Name: 546_THS-TRAIL
 Pass Limits: VALUE >= TXTHSTrail_LimitMin s

Actual Value	Margin	THSTRAIL	THS-SKIP(s)	ZID	DataLane	PassLimit Min (TXTHSTrail_LimitMin)	Number of HS burst
93.06 ns	39.6 %	(See image)	0.000000000000 s	100 ohm	Lane0	66.67 ns	1



Summary Previous Next




1.3.14 HS Exit: DATA TX TREET

D-PHY Specification v1.2 Section 9.1.2 Table 22, CTS v1.2(Test 1.3.14)

30%-85% rise time and fall time
 Actual Value Measurement Name: 549_TREET
 Pass Limits: VALUE <= 35.00 ns

Actual Value	Margin	TREET	ZID	DataLane	Number of HS burst
9.16 ns	73.8 %	(See image)	100 ohm	Lane0	1

TREET



Summary Previous Next




1.3.15 HS Exit: DATA TX TEOT

D-PHY Specification v1.2 Section 6.9 Table 14, CTS v1.2(Test 1.3.15)

Time from start of THS-TRAIL period to start of LP-11 state.
 TXTEOT_LimitMax is based on 105ns+n*12*UI.
 Actual Value Measurement Name: 547_TEOT
 Pass Limits: VALUE <= TXTEOT_LimitMax s

Actual Value	Margin	TEOT	UIINST(Mean)	ZID	DataLane	PassLimit Max (TXTEOT_LimitMax)	Number of HS burst
102.22 ns	14.8 %	(See image)	1.249992 ns	100 ohm	Lane0	120.00 ns	1

TEOT




Summary Previous Next

	1.3.16 HS Exit: DATA TX THS-EXIT	D-PHY Specification v1.2 Section 6.9 Table 14, CTS v1.2(Test 1.3.16)
Time to drive LP-11 after HS burst. Actual Value Measurement Name: 548_THS-EXIT Pass Limits: VALUE >= 100.00 ns		

Actual Value	Margin	THSEXIT	Notes:	ZID	DataLane	Number of HS burst
14.47329 μs	144E+02 %	(See image)		100 ohm	Lane0	1

THSEXIT




Summary Previous Next


	1.5.4 Data-to-Clock Skew (TSKEW(TX))(Max,Min)	D-PHY Specification v1.2 Section 10.2.1 Table 30, CTS v1.2(Test 1.5.4)
Data to Clock Skew [measured at transmitter]. Actual Value Measurement Name: 913_Tskew(Worst) Pass Limits: MinMaxTSkewTest_LimitMin UIinst <= VALUE <= MinMaxTSkewTest_LimitMax UIinst		

Actual Value	Margin	LeftCrossing	UIINST(Mean)	TSkew(Min)	TSkew(Max)	No Of Measurement	ZID	DataLane
-109 mUIinst	13.7 %	(See image)	1.2500 ns	-136.7 ps	7.8 ps	11.539000 k	100 ohm	Lane0
PassLimit Min (MinMaxTSkewTest_LimitMin)			PassLimit Max (MinMaxTSkewTest_LimitMax)			Number of HS Burst		
-150 mUIinst			150 mUIinst			1		

LeftCrossing



[Summary](#) [Previous](#)

 **1.5.4 Data-to-Clock Skew (TSKEW(TX))(Mean)** D-PHY Specification v1.2 Section 10.2.1 Table 30, CTS v1.2(Test 1.5.4)

Data to Clock Skew [measured at transmitter].
 Actual Value Measurement Name: 9131_Tskew(Mean)
 Pass Limits: MeanTSkewTest_LimitMin UIinst <= VALUE <= MeanTSkewTest_LimitMax UIinst

Actual Value	Margin	UIINST(Mean)	TSkew(Mean)	No Of Measurement	ZID	DataLane	PassLimit Min (MeanTSkewTest_LimitMin)
-26 mUIinst	41.3 %	1.2500 ns	-32.1 ps	11.539000 k	100 ohm	Lane0	-150 mUIinst
PassLimit Max (MeanTSkewTest_LimitMax)		Number of HS Burst					
150 mUIinst		1					